

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147580

Luminaire Tested: **AVS-E03-LED-E-U-5MQ**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P147580
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-5MQ
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM
Light Source: (63) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9671.3 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B3 - U0 - G2

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P147580

CATALOG NUMBER: AVS-E03-LED-E-U-5MQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 7.3 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P147580

CATALOG NUMBER: AVS-E03-LED-E-U-5MQ

Luminous Intensity Polar Plot



REPORT NUMBER: P147580

CATALOG NUMBER: AVS-E03-LED-E-U-5MQ


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4835.6	0.0	4835.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4835.6	0.0	4835.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	9671.3	0.0	9671.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	0.7
10°-20°	217.5	2.2
20°-30°	420.5	4.3
30°-40°	814.2	8.4
40°-50°	1470.1	15.2
50°-60°	2556.2	26.4
60°-70°	2902.0	30.0
70°-80°	1125.1	11.6
80°-90°	101.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9671.3	100.0
0°-180°	9671.3	100.0

Coefficient of Utilization



REPORT NUMBER: P147580


CATALOG NUMBER: AVS-E03-LED-E-U-5MQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	351.2	3.6			
FM	(30°-60°)	2420.2	25.0			
FH	(60°-80°)	2013.5	20.8			G2/5000
FVH	(80°-90°)	50.7	0.5			G1/100
BL	(0°-30°)	351.2	3.6	B1/500		
BM	(30°-60°)	2420.2	25.0	B2/2500		
BH	(60°-80°)	2013.5	20.8	B3/2500		G2/5000
BVH	(80°-90°)	50.7	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P147580

CATALOG NUMBER: AVS-E03-LED-E-U-5MQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	642.0	642.0	642.0	642.0	642.0	642.0	642.0	642.0	642.0	642.0	642.0
2.5°	646.0	648.0	647.5	646.4	646.4	646.5	646.0	644.6	643.9	645.0	646.0
5°	660.9	660.9	660.9	660.9	660.0	660.0	659.1	658.0	658.4	657.5	657.0
7.5°	683.9	682.5	682.5	682.0	682.1	681.0	679.6	677.5	678.0	677.5	677.0
10°	711.1	711.5	710.1	711.5	709.0	708.5	706.5	705.5	705.0	703.4	703.4
12.5°	743.4	742.0	742.0	740.9	740.0	739.0	736.0	735.5	733.5	732.4	731.0
15°	774.0	773.5	771.5	769.5	769.0	768.0	764.6	762.5	762.0	759.6	757.5
17.5°	804.6	803.5	801.0	800.0	797.9	796.5	793.6	790.5	789.0	788.0	785.5
20°	837.1	836.1	833.5	831.5	829.0	826.9	822.5	820.0	818.4	817.0	815.0
22.5°	877.5	875.4	871.5	868.0	862.5	860.5	854.5	851.0	848.5	846.4	845.5
25°	921.5	922.0	916.5	912.0	905.5	900.0	892.4	888.5	886.0	883.9	883.5
27.5°	976.6	977.0	972.0	965.5	955.4	949.5	939.5	934.5	933.1	931.0	930.6
30°	1063.4	1059.1	1050.5	1040.0	1031.0	1018.0	1003.5	998.5	993.6	992.0	991.9
32.5°	1223.5	1220.9	1214.0	1188.0	1176.0	1149.0	1123.5	1109.0	1092.4	1084.6	1079.5
35°	1335.5	1334.5	1328.9	1320.0	1312.5	1306.9	1292.0	1289.5	1286.4	1286.5	1290.6
37.5°	1418.0	1412.0	1411.0	1412.5	1410.5	1411.5	1423.5	1440.0	1454.0	1461.0	1460.0
40°	1540.0	1531.4	1536.6	1533.1	1528.5	1527.5	1531.5	1538.0	1544.5	1544.5	1543.0
42.5°	1699.5	1703.5	1705.5	1691.0	1681.5	1679.0	1688.5	1686.4	1693.1	1690.6	1683.9
45°	1936.5	1934.0	1930.5	1913.0	1898.0	1886.0	1888.5	1885.0	1885.5	1881.5	1876.5
47.5°	2175.5	2184.0	2169.5	2161.0	2144.0	2135.5	2142.5	2136.5	2148.0	2127.0	2117.0
50°	2407.5	2413.5	2408.5	2396.5	2396.5	2408.5	2417.0	2428.0	2443.9	2420.0	2384.0
52.5°	2597.5	2602.5	2609.9	2620.0	2644.6	2670.1	2706.0	2744.5	2775.0	2770.6	2729.5
55°	2713.5	2719.5	2732.0	2766.5	2810.6	2877.5	2959.0	3048.5	3118.5	3152.4	3122.5
57.5°	2752.5	2757.0	2791.0	2832.5	2901.0	3000.5	3137.0	3291.5	3425.9	3511.5	3498.0
60°	2743.4	2743.4	2778.0	2835.0	2931.0	3063.0	3256.0	3470.1	3676.1	3803.9	3785.1
62.5°	2649.0	2654.1	2703.5	2772.0	2888.1	3046.0	3276.1	3549.4	3796.1	3955.0	3939.5
65°	2442.1	2445.5	2499.1	2580.4	2710.1	2897.0	3148.5	3451.5	3734.0	3887.0	3858.0
67.5°	2107.6	2111.0	2154.5	2246.4	2383.4	2579.0	2850.5	3184.0	3460.5	3581.6	3494.5
70°	1676.5	1686.5	1714.5	1812.0	1916.1	2107.5	2357.5	2691.0	2951.9	3066.4	2970.6
72.5°	1142.5	1168.0	1202.0	1288.5	1388.0	1547.0	1745.9	2026.9	2236.5	2369.0	2283.5
75°	643.4	679.5	689.9	755.5	837.5	963.0	1108.5	1309.9	1521.5	1629.0	1526.0
77.5°	278.0	307.5	320.5	351.0	415.0	467.6	556.1	692.0	855.5	931.0	807.5
80°	137.0	144.0	149.4	159.0	177.0	194.0	236.1	295.5	362.5	379.5	302.0
82.5°	106.0	111.1	120.4	128.1	132.4	137.0	140.9	149.0	155.4	159.0	150.1
85°	74.4	81.0	91.5	100.0	105.1	108.5	111.9	114.5	108.5	99.1	104.0
87.5°	19.5	25.5	35.4	38.5	43.5	46.0	45.0	46.5	42.0	30.5	34.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147580

CATALOG NUMBER: AVS-E03-LED-E-U-5MQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	642.0	642.0	642.0	642.0	642.0	642.0	642.0	642.0
2.5°	645.5	645.0	645.5	645.5	645.5	645.0	645.0	645.0
5°	657.0	657.0	657.5	656.6	656.6	657.0	656.5	656.0
7.5°	676.5	676.0	676.1	675.4	676.0	675.4	675.4	675.0
10°	702.6	701.5	702.0	700.5	700.5	700.0	700.0	700.0
12.5°	730.6	729.0	729.4	728.1	725.5	726.0	726.5	726.0
15°	757.5	756.1	754.5	753.6	752.0	752.5	752.5	752.0
17.5°	785.0	782.0	781.6	780.0	779.5	779.5	779.5	780.0
20°	813.5	811.5	811.0	809.5	809.0	810.6	811.0	809.9
22.5°	843.9	843.0	844.0	843.0	844.5	845.5	845.9	845.0
25°	882.5	881.5	883.0	886.5	888.5	889.5	892.0	891.0
27.5°	932.0	931.0	934.5	939.5	942.6	947.5	950.1	951.0
30°	996.1	1000.5	1002.5	1012.5	1014.5	1022.5	1022.5	1026.0
32.5°	1089.0	1097.5	1112.5	1128.1	1149.5	1165.0	1165.0	1173.0
35°	1293.0	1296.6	1308.0	1310.5	1315.0	1320.0	1315.0	1319.0
37.5°	1449.5	1434.0	1423.0	1407.5	1398.0	1398.0	1399.0	1398.0
40°	1529.5	1523.5	1518.5	1505.5	1503.4	1503.0	1503.0	1505.0
42.5°	1672.4	1658.0	1649.9	1639.0	1635.4	1634.5	1634.0	1635.0
45°	1858.5	1835.0	1813.5	1802.5	1793.0	1784.0	1786.9	1787.0
47.5°	2075.0	2038.5	2003.5	1984.5	1968.0	1960.4	1955.4	1954.0
50°	2338.4	2287.5	2242.5	2207.0	2183.0	2182.5	2185.0	2169.0
52.5°	2661.6	2581.0	2525.0	2477.0	2454.5	2451.9	2443.9	2435.0
55°	3019.5	2923.9	2831.5	2780.0	2750.5	2734.5	2725.0	2710.1
57.5°	3388.5	3260.0	3127.0	3044.6	2992.5	2956.5	2937.4	2929.0
60°	3673.0	3497.5	3322.0	3189.5	3103.0	3049.5	3016.6	3003.0
62.5°	3785.0	3547.0	3322.1	3148.1	3023.0	2949.0	2904.5	2885.0
65°	3651.5	3369.5	3113.5	2921.5	2782.0	2699.5	2651.0	2630.1
67.5°	3278.5	3029.4	2751.0	2560.0	2416.5	2334.9	2282.5	2267.0
70°	2748.6	2494.0	2228.0	2057.5	1929.5	1863.0	1808.5	1802.0
72.5°	2065.5	1846.0	1618.0	1477.0	1374.0	1264.0	1236.1	1249.9
75°	1323.9	1118.5	915.4	788.5	694.5	589.4	549.0	559.0
77.5°	626.9	485.5	350.5	271.0	227.5	194.5	186.0	181.0
80°	232.5	188.5	166.5	157.9	152.0	146.5	142.5	138.0
82.5°	150.5	147.0	142.5	140.9	136.6	129.5	116.5	111.0
85°	112.5	112.5	106.5	106.9	103.4	94.5	82.5	76.0
87.5°	33.0	29.4	26.9	25.0	24.5	22.0	16.0	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)