

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148095

Luminaire Tested: **AVS-F02-LED-E-U-5WQ**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148095
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-5WQ
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (14) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5256.6 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G1

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148095

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.2 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P148095

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ

Luminous Intensity Polar Plot



REPORT NUMBER: P148095

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2628.3	0.0	2628.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2628.3	0.0	2628.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	5256.6	0.0	5256.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.4	0.5
10°-20°	96.8	1.8
20°-30°	196.0	3.7
30°-40°	328.6	6.3
40°-50°	579.6	11.0
50°-60°	1022.1	19.4
60°-70°	1560.5	29.7
70°-80°	1304.0	24.8
80°-90°	141.7	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5256.6	100.0
0°-180°	5256.6	100.0

Coefficient of Utilization



REPORT NUMBER: P148095


CATALOG NUMBER: AVS-F02-LED-E-U-5WQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	160.1	3.0			
FM	(30°-60°)	965.2	18.4			
FH	(60°-80°)	1432.2	27.2			G1/1800
FVH	(80°-90°)	70.8	1.3			G1/100
BL	(0°-30°)	160.1	3.0	B1/500		
BM	(30°-60°)	965.2	18.4	B1/1000		
BH	(60°-80°)	1432.2	27.2	B3/2500		G1/1800
BVH	(80°-90°)	70.8	1.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1

Type V Short





REPORT NUMBER: P148095

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0
2.5°	275.1	275.8	275.1	275.1	275.1	275.1	275.1	274.6	274.6	274.6	275.1
5°	280.7	281.2	280.7	281.2	281.2	281.2	281.2	280.7	280.7	280.7	280.7
7.5°	289.5	289.5	289.5	290.1	289.5	289.5	290.1	289.5	289.5	289.5	289.5
10°	302.2	301.6	301.6	301.6	301.6	301.6	302.2	302.2	302.2	301.6	301.6
12.5°	317.5	317.0	317.5	317.5	318.1	318.1	318.1	318.1	318.1	318.1	317.5
15°	336.3	336.3	336.3	336.8	337.9	337.9	337.4	337.9	337.9	337.9	337.9
17.5°	357.2	358.2	357.2	357.7	358.2	357.7	358.9	359.4	359.9	359.4	357.7
20°	378.7	379.2	379.2	379.2	379.2	380.3	380.8	380.8	382.5	382.0	381.3
22.5°	399.0	400.1	400.1	400.6	400.6	402.3	402.3	402.3	403.4	404.5	403.4
25°	420.5	419.9	419.9	421.0	421.6	423.7	423.7	424.9	426.5	427.0	426.0
27.5°	439.7	439.2	439.2	440.8	441.3	444.1	444.1	446.3	447.5	448.0	446.8
30°	460.1	460.1	459.6	461.2	462.8	465.1	466.1	468.4	469.9	470.6	469.4
32.5°	484.4	483.2	483.7	484.9	486.0	488.2	489.8	492.5	494.7	495.3	494.2
35°	511.8	510.2	510.7	511.8	513.5	516.8	519.5	521.1	524.5	525.6	523.4
37.5°	542.1	542.7	542.1	544.9	547.6	551.4	554.7	557.0	560.2	561.9	560.2
40°	585.0	583.4	585.0	587.8	592.2	597.1	603.7	605.4	608.7	612.0	608.2
42.5°	640.6	639.5	643.3	645.6	650.5	656.1	664.2	668.7	673.7	675.9	672.5
45°	713.3	713.3	717.6	718.2	725.9	733.1	744.7	750.2	759.5	759.5	759.5
47.5°	793.6	796.9	799.7	805.2	810.7	823.8	835.4	847.6	856.4	857.4	855.8
50°	876.7	880.0	888.3	896.0	908.1	924.6	937.2	953.2	960.9	967.6	965.3
52.5°	968.6	969.1	979.1	989.0	1006.6	1024.8	1045.1	1061.7	1075.3	1081.5	1076.5
55°	1069.3	1070.5	1079.3	1089.7	1109.5	1130.5	1155.8	1172.7	1190.4	1201.5	1193.2
57.5°	1178.3	1178.9	1187.7	1200.3	1223.9	1244.9	1269.1	1293.4	1309.8	1319.7	1314.2
60°	1298.9	1301.6	1308.2	1324.1	1346.7	1368.7	1393.0	1414.4	1433.7	1444.1	1438.7
62.5°	1427.6	1430.4	1439.7	1452.3	1472.2	1496.4	1519.5	1547.0	1563.0	1574.5	1566.3
65°	1514.0	1519.0	1533.8	1550.9	1580.1	1611.4	1638.3	1675.9	1695.1	1708.8	1701.1
67.5°	1519.5	1522.3	1540.4	1566.3	1605.4	1652.7	1707.8	1766.1	1804.0	1822.2	1809.0
69°	1482.1	1485.9	1503.5	1532.7	1576.2	1631.2	1696.7	1769.3	1827.7	1854.7	1842.1
70°	1439.7	1448.0	1467.3	1499.2	1541.6	1599.3	1667.0	1744.6	1812.8	1849.7	1840.4
72.5°	1350.6	1352.7	1365.4	1390.8	1423.2	1471.1	1534.9	1608.1	1673.1	1725.9	1733.6
75°	1198.7	1205.8	1215.1	1232.2	1248.7	1283.4	1326.3	1376.5	1414.4	1455.1	1456.8
77.5°	905.9	927.4	934.5	938.3	945.5	973.1	1010.5	1053.9	1085.3	1091.9	1090.8
80°	406.7	435.3	442.0	473.3	492.5	538.2	595.4	662.1	706.6	711.6	699.5
82.5°	79.8	85.3	99.6	124.4	169.5	196.5	233.9	280.7	323.6	348.4	333.5
85°	26.4	28.1	32.4	35.8	41.2	46.7	56.7	70.5	87.5	96.9	86.4
87.5°	10.5	10.5	12.1	13.2	14.3	14.3	14.3	13.2	12.6	10.5	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148095

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0
2.5°	274.6	274.6	274.6	274.6	274.6	274.6	274.6	274.6
5°	280.7	280.1	280.1	279.6	279.6	279.6	279.6	279.6
7.5°	288.9	288.4	287.9	288.4	287.9	287.9	287.9	287.9
10°	301.6	300.5	299.9	299.4	299.4	299.4	298.9	298.9
12.5°	316.5	316.5	315.9	315.3	314.3	314.8	314.3	313.2
15°	336.8	335.8	335.1	334.6	333.5	333.5	333.5	333.0
17.5°	357.2	356.1	356.1	354.4	353.9	353.9	353.9	354.4
20°	379.8	378.1	377.0	375.9	374.8	375.3	374.2	375.3
22.5°	402.3	400.1	399.0	397.3	395.8	395.8	395.1	394.1
25°	424.4	421.6	420.5	418.9	416.6	416.6	415.5	414.4
27.5°	445.2	442.5	441.3	438.0	435.9	435.3	434.2	433.7
30°	468.4	465.1	463.4	460.1	456.8	456.3	454.6	454.6
32.5°	492.5	489.2	488.2	483.2	480.4	480.4	479.4	478.2
35°	522.8	517.9	516.8	511.8	508.0	508.0	506.8	507.5
37.5°	558.7	554.7	550.9	547.0	542.7	542.1	541.0	539.9
40°	606.5	602.1	597.7	592.2	588.3	587.3	585.6	585.0
42.5°	670.4	665.9	657.1	652.7	648.9	645.6	645.0	644.5
45°	751.8	746.3	740.2	731.9	727.0	719.9	718.8	716.0
47.5°	849.7	839.3	828.8	821.7	814.0	805.7	804.0	799.7
50°	953.8	945.5	927.9	916.4	904.2	896.0	890.5	888.8
52.5°	1065.5	1050.1	1032.4	1017.1	999.5	988.4	978.5	975.8
55°	1182.2	1160.1	1138.1	1120.0	1102.4	1089.1	1079.8	1075.3
57.5°	1298.9	1274.6	1250.4	1230.6	1215.8	1198.7	1189.3	1187.2
60°	1420.4	1397.3	1372.5	1352.7	1334.6	1319.7	1314.2	1303.7
62.5°	1549.2	1525.0	1501.9	1482.7	1459.5	1449.1	1439.7	1433.7
65°	1675.9	1647.8	1618.5	1598.2	1575.1	1560.2	1548.7	1540.4
67.5°	1773.8	1731.4	1692.3	1658.2	1626.8	1603.7	1588.9	1581.1
69°	1801.3	1748.5	1698.3	1653.8	1616.9	1591.1	1574.5	1566.8
70°	1798.0	1739.7	1684.7	1635.6	1595.4	1568.0	1552.0	1537.7
72.5°	1696.2	1642.8	1581.7	1528.3	1492.0	1465.6	1449.6	1441.9
75°	1447.5	1411.6	1367.7	1326.3	1299.9	1284.6	1264.7	1265.3
77.5°	1053.9	1055.0	1025.3	982.9	953.2	947.7	938.9	930.1
80°	653.8	601.6	567.5	521.8	488.2	459.0	446.3	418.9
82.5°	301.6	235.5	182.7	138.1	106.2	83.1	72.6	59.5
85°	67.2	51.2	42.4	34.1	29.1	26.9	22.0	20.4
87.5°	9.3	8.3	7.7	7.2	6.0	4.4	3.3	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)