

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152605

Luminaire Tested: **AVS-F02-LED-E-U-SL4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152605
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-SL4
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (14) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4877.4 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152605

CATALOG NUMBER: AVS-F02-LED-E-U-SL4

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 10.5 fc
Type IV - Short - Full Cutoff

REPORT NUMBER: P152605

CATALOG NUMBER: AVS-F02-LED-E-U-SL4

Luminous Intensity Polar Plot



REPORT NUMBER: P152605

CATALOG NUMBER: AVS-F02-LED-E-U-SL4


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1012.5	0.0	1012.5
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	3864.9	0.0	3864.9
	% Fixture	79.2	0.0	79.2
Total	Lumens	4877.4	0.0	4877.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	2.0
10°-20°	266.2	5.5
20°-30°	394.0	8.1
30°-40°	497.9	10.2
40°-50°	563.1	11.5
50°-60°	801.3	16.4
60°-70°	1492.4	30.6
70°-80°	684.0	14.0
80°-90°	81.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4877.4	100.0
0°-180°	4877.4	100.0

Coefficient of Utilization



REPORT NUMBER: P152605


CATALOG NUMBER: AVS-F02-LED-E-U-SL4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	444.1	9.1			
FM	(30°-60°)	1428.9	29.3			
FH	(60°-80°)	1931.6	39.6			G2/5000
FVH	(80°-90°)	60.2	1.2			G1/100
BL	(0°-30°)	313.3	6.4	B1/500		
BM	(30°-60°)	433.5	8.9	B1/1000		
BH	(60°-80°)	244.8	5.0	B1/500		G1/500
BVH	(80°-90°)	21.0	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P152605

CATALOG NUMBER: AVS-F02-LED-E-U-SL4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7
2.5°	1056.7	1059.4	1056.2	1055.5	1055.5	1055.0	1051.7	1051.2	1046.7	1047.4	1048.4
5°	1064.4	1065.5	1063.3	1062.7	1061.7	1059.4	1056.7	1053.4	1050.1	1046.7	1044.0
7.5°	1072.1	1071.0	1069.3	1069.3	1067.7	1064.4	1058.9	1054.5	1047.4	1043.4	1038.5
10°	1083.1	1081.5	1079.3	1078.1	1075.3	1070.5	1062.7	1056.7	1047.9	1040.2	1031.9
12.5°	1093.6	1093.0	1089.7	1088.1	1083.6	1078.7	1069.3	1060.0	1048.4	1036.3	1025.3
15°	1112.2	1110.1	1106.7	1103.4	1096.3	1089.7	1075.3	1064.4	1047.9	1031.9	1014.8
17.5°	1144.8	1140.8	1137.6	1130.5	1121.7	1110.1	1089.1	1070.5	1047.9	1024.8	1005.5
20°	1204.1	1196.0	1191.5	1182.2	1166.7	1145.8	1113.4	1083.1	1049.5	1019.8	993.9
22.5°	1271.3	1265.8	1259.8	1253.7	1229.4	1199.2	1155.2	1110.1	1059.4	1017.6	984.6
25°	1346.7	1339.6	1336.3	1325.8	1303.2	1268.6	1208.6	1145.8	1082.0	1026.4	984.6
27.5°	1413.9	1411.6	1411.1	1399.0	1377.5	1336.8	1265.8	1190.4	1112.8	1044.6	992.8
30°	1474.9	1472.7	1471.6	1465.1	1440.3	1391.8	1314.8	1230.1	1146.4	1069.8	1008.3
32.5°	1539.9	1532.7	1529.4	1516.8	1488.7	1432.0	1343.9	1255.9	1172.7	1094.6	1025.3
35°	1592.7	1586.6	1580.1	1561.9	1522.3	1455.1	1356.6	1264.7	1183.2	1108.4	1034.1
37.5°	1631.2	1625.2	1615.9	1592.7	1543.7	1462.8	1356.1	1262.0	1179.4	1106.2	1035.8
40°	1648.3	1642.3	1632.3	1603.2	1547.6	1458.4	1345.6	1249.3	1167.9	1094.6	1029.1
42.5°	1641.7	1637.3	1624.7	1596.6	1535.4	1438.7	1324.7	1225.6	1145.8	1076.0	1014.3
45°	1616.4	1613.1	1600.9	1571.3	1508.0	1406.7	1293.9	1196.0	1119.4	1052.8	994.5
47.5°	1578.4	1577.3	1565.2	1536.1	1473.3	1374.8	1262.0	1166.7	1093.0	1030.3	977.9
50°	1536.6	1531.1	1525.0	1498.0	1440.8	1347.3	1238.9	1148.6	1078.1	1022.0	970.8
52.5°	1510.2	1508.5	1503.0	1478.8	1423.7	1331.3	1228.4	1142.0	1077.0	1020.3	966.9
55°	1744.6	1748.5	1697.8	1592.7	1500.2	1375.3	1259.8	1175.5	1104.0	1046.7	1007.7
57.5°	2580.6	2563.5	2476.6	2268.0	2032.4	1721.5	1497.5	1361.6	1273.0	1282.9	1302.7
60°	3006.5	3003.2	2987.3	2906.4	2749.5	2512.8	2250.4	1949.3	1853.6	1864.0	1871.7
62.5°	3197.0	3202.0	3214.1	3183.7	3142.5	3073.7	2942.7	2821.7	2693.4	2645.5	2517.3
65°	3285.1	3293.9	3321.3	3338.4	3354.4	3366.5	3418.2	3560.2	3653.8	3478.8	3071.5
67.5°	3102.9	3145.3	3236.1	3324.7	3403.9	3516.8	3691.7	4021.5	4250.9	4035.8	3445.2
70°	2262.0	2319.7	2423.7	2697.8	2990.6	3246.5	3585.5	4087.5	4433.6	4267.5	3537.6
72.5°	1418.2	1434.2	1480.4	1581.1	1798.5	2127.2	2719.8	3472.7	3872.2	3739.6	2990.1
75°	899.8	905.3	903.6	926.8	963.6	1035.2	1269.6	2051.2	2652.6	2445.8	1666.4
77.5°	536.1	544.2	547.6	554.7	572.3	597.7	616.9	697.8	1112.2	1079.8	604.9
80°	449.1	455.6	450.2	448.5	437.5	429.8	439.2	429.8	399.0	384.1	353.9
82.5°	237.7	237.2	235.5	251.5	283.9	309.3	328.6	324.1	293.4	249.8	211.9
85°	130.5	134.8	134.8	140.3	135.3	136.0	140.3	148.1	137.0	114.5	93.6
87.5°	11.0	17.1	13.8	17.1	23.1	16.5	16.0	16.0	13.8	9.9	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152605

CATALOG NUMBER: AVS-F02-LED-E-U-SL4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7
2.5°	1045.7	1044.6	1042.4	1040.7	1040.7	1037.9	1036.3	1035.2	1034.6	1032.4	1032.4
5°	1042.4	1038.5	1034.6	1031.9	1030.3	1027.5	1023.1	1020.9	1018.1	1016.0	1014.8
7.5°	1035.2	1028.1	1022.0	1017.6	1012.1	1007.7	1002.2	997.2	992.3	990.1	989.0
10°	1024.2	1014.8	1005.5	997.2	989.5	981.9	974.7	967.6	961.5	957.1	952.6
12.5°	1013.8	999.5	987.4	975.2	963.1	953.8	943.8	933.4	924.6	916.4	914.1
15°	999.5	982.9	967.6	952.6	937.8	922.4	910.3	898.8	884.5	875.0	867.9
17.5°	986.2	966.4	947.7	930.1	911.9	896.0	877.8	862.4	848.1	833.8	823.3
20°	971.9	950.5	930.7	910.9	891.0	870.7	849.7	829.9	812.3	795.2	778.2
22.5°	959.3	937.2	918.0	896.5	874.5	851.4	827.2	802.4	782.1	760.0	740.2
25°	951.6	927.4	907.6	886.6	862.4	837.1	809.5	780.4	755.6	730.4	706.6
27.5°	951.6	920.2	899.8	878.9	854.1	827.2	796.9	765.0	736.9	708.8	679.7
30°	959.8	921.2	893.8	871.7	846.4	817.3	783.7	750.2	719.3	686.3	658.2
32.5°	967.6	923.5	889.3	861.3	832.1	803.5	769.4	733.6	699.5	668.1	638.4
35°	972.4	923.5	881.1	845.4	812.3	784.2	750.7	714.9	680.2	649.4	621.9
37.5°	973.1	919.1	867.9	827.2	792.5	763.3	731.4	697.8	664.9	636.2	613.1
40°	967.6	910.3	854.7	807.9	771.6	741.9	712.7	682.4	652.7	629.0	609.2
42.5°	957.6	900.9	842.1	792.5	754.5	723.7	696.8	670.9	645.0	624.7	608.2
45°	942.8	888.3	830.5	783.1	745.7	713.3	686.8	665.4	643.3	626.3	609.7
47.5°	929.5	883.8	834.3	789.2	750.2	716.6	689.6	671.4	654.4	642.8	620.2
50°	926.8	881.7	836.0	794.2	754.5	720.4	696.8	687.4	682.4	675.2	640.6
52.5°	919.1	881.1	848.1	825.0	799.7	783.7	759.0	767.8	762.3	736.9	674.2
55°	1000.0	1011.0	1041.8	1085.8	1126.5	1136.0	1133.2	1122.7	1067.2	918.0	755.1
57.5°	1374.8	1437.0	1495.3	1521.1	1517.8	1488.7	1467.8	1425.4	1345.1	1163.4	914.7
60°	1895.4	1905.3	1874.5	1828.8	1751.8	1687.4	1618.5	1539.4	1422.7	1244.9	1012.6
62.5°	2374.7	2241.6	2104.6	1975.8	1858.5	1756.2	1660.4	1549.7	1397.9	1212.4	1000.0
65°	2713.3	2431.4	2215.1	2030.3	1864.6	1721.5	1602.1	1458.4	1287.3	1120.0	926.8
67.5°	2887.7	2455.6	2123.8	1866.2	1631.2	1433.2	1274.1	1134.3	1007.2	934.0	811.2
70°	2692.8	2084.1	1621.9	1330.8	1049.5	841.5	664.9	558.0	521.1	590.6	614.2
72.5°	2006.5	1356.6	964.8	746.3	571.8	455.6	349.4	274.6	223.4	234.4	304.4
75°	948.8	585.6	413.9	314.8	250.4	207.5	169.5	155.2	129.8	107.9	101.2
77.5°	369.3	269.1	222.4	162.9	115.5	93.1	79.3	76.5	78.1	76.0	74.8
80°	281.2	190.5	119.4	87.5	75.4	66.6	58.9	56.7	57.8	60.5	63.3
82.5°	156.9	97.9	72.6	63.3	56.7	48.4	44.0	40.7	41.2	44.6	50.7
85°	60.5	47.4	43.5	41.9	39.1	31.4	26.9	27.6	31.4	37.4	37.4
87.5°	6.6	6.6	8.8	6.6	6.6	6.6	6.0	7.2	7.7	9.9	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152605

CATALOG NUMBER: AVS-F02-LED-E-U-SL4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7	1040.7
2.5°	1031.4	1031.4	1031.4	1030.3	1030.8	1028.6	1028.6	1026.9	1029.7	1028.1	1027.5
5°	1015.4	1014.8	1012.6	1012.6	1012.6	1012.6	1014.3	1009.8	1013.2	1013.2	1011.5
7.5°	988.4	988.4	982.4	985.7	984.6	986.2	988.4	986.2	989.5	991.7	990.1
10°	951.0	951.0	946.0	949.9	948.3	952.1	956.0	953.8	956.0	959.3	960.3
12.5°	909.7	907.6	903.1	904.8	904.8	906.9	908.6	911.4	914.1	918.5	920.7
15°	861.9	858.5	853.1	853.1	849.7	850.9	854.1	855.2	860.7	866.8	874.0
17.5°	812.8	804.7	798.5	791.4	785.9	790.3	794.2	796.9	801.3	810.7	815.6
20°	766.6	750.2	738.5	729.2	723.1	725.9	730.9	734.2	738.0	740.2	741.9
22.5°	720.9	702.3	686.3	674.7	664.9	667.6	665.4	663.7	666.4	659.3	658.8
25°	681.3	659.3	637.8	624.1	612.0	608.2	596.6	593.8	586.1	580.1	575.6
27.5°	652.7	624.1	600.4	584.5	565.2	550.9	536.1	521.1	513.0	503.0	498.0
30°	630.2	599.9	571.8	544.9	519.5	497.5	477.7	458.4	445.2	430.9	421.6
32.5°	609.2	581.1	547.0	510.2	476.1	451.3	425.4	403.4	382.5	363.7	350.1
35°	594.9	563.5	520.1	474.9	436.5	407.3	379.8	348.4	323.0	298.9	283.9
37.5°	587.3	548.7	495.3	445.2	402.3	369.3	335.1	298.9	268.0	245.5	222.9
40°	581.1	533.9	473.3	418.9	373.7	334.1	294.4	251.5	217.4	193.7	176.1
42.5°	574.6	517.3	454.0	397.9	347.8	301.6	253.7	208.1	175.5	159.1	151.3
45°	567.5	503.0	435.9	378.1	322.5	266.3	211.3	168.9	149.7	144.1	144.1
47.5°	565.8	493.7	422.7	358.9	293.9	225.6	172.2	145.8	140.3	141.5	143.6
50°	572.3	490.9	411.1	336.3	256.0	182.7	145.8	137.0	138.1	141.5	144.8
52.5°	588.3	493.2	399.0	304.9	210.8	150.8	134.8	134.3	137.6	142.6	145.8
55°	615.3	493.2	375.9	258.1	168.4	135.3	131.0	133.2	137.6	142.0	144.8
57.5°	673.1	488.2	335.1	206.4	140.9	129.8	129.8	132.6	136.5	140.9	143.1
60°	741.9	481.6	277.9	159.6	127.2	125.5	129.3	132.6	136.0	139.8	142.0
62.5°	746.3	464.5	220.1	132.1	120.0	122.7	128.8	133.2	134.3	137.0	139.8
65°	685.7	405.1	175.0	118.3	116.7	121.0	127.2	130.5	131.0	132.1	134.8
67.5°	600.4	330.3	141.5	111.7	113.4	118.3	121.7	124.4	126.0	128.8	129.3
70°	493.2	265.3	121.0	105.1	106.7	112.2	115.0	117.8	121.0	124.4	122.7
72.5°	349.4	206.4	106.2	97.9	100.2	105.1	108.4	110.6	113.4	116.7	114.5
75°	148.6	144.1	91.9	88.6	91.9	95.2	98.5	101.9	104.6	106.2	106.2
77.5°	76.0	84.8	79.3	79.3	81.5	84.8	87.5	90.8	92.4	94.1	96.3
80°	64.4	65.5	66.6	68.8	71.0	74.3	77.1	79.8	80.3	80.9	82.0
82.5°	53.4	55.5	56.7	60.0	61.7	62.7	64.4	64.4	65.5	65.5	63.8
85°	38.5	41.2	42.9	43.5	42.9	43.5	44.0	45.1	47.9	47.9	45.7
87.5°	11.0	10.5	13.2	13.8	14.8	17.1	19.3	23.1	24.2	25.3	25.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152605

CATALOG NUMBER: AVS-F02-LED-E-U-SL4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1040.7	1040.7	1040.7	1040.7
2.5°	1026.9	1028.1	1025.8	1026.4
5°	1011.5	1013.8	1011.0	1014.3
7.5°	991.7	995.0	994.5	993.9
10°	963.1	967.6	967.6	969.1
12.5°	926.8	929.5	931.7	932.8
15°	877.8	882.8	885.5	885.5
17.5°	819.0	822.2	823.8	821.7
20°	744.0	743.0	743.5	738.0
22.5°	657.6	659.3	654.4	655.4
25°	573.0	570.2	572.3	569.0
27.5°	490.9	491.5	485.4	488.2
30°	412.7	410.1	402.3	406.1
32.5°	337.4	330.3	322.0	317.0
35°	266.3	255.3	251.5	249.8
37.5°	209.1	197.0	193.2	188.8
40°	166.2	161.8	160.1	161.2
42.5°	149.1	149.1	150.3	150.8
45°	144.8	146.4	148.1	148.6
47.5°	145.3	146.9	149.1	149.7
50°	146.4	148.1	149.7	150.3
52.5°	146.9	146.9	148.1	148.6
55°	145.8	145.3	145.8	146.4
57.5°	143.6	142.6	143.1	144.8
60°	142.6	140.9	142.0	143.1
62.5°	139.8	139.3	140.3	140.9
65°	133.8	134.3	136.0	136.0
67.5°	128.2	128.8	129.3	129.8
70°	121.7	122.2	123.3	123.8
72.5°	113.9	116.2	117.8	120.0
75°	107.9	110.1	113.4	115.5
77.5°	97.4	99.1	102.9	105.7
80°	82.6	82.0	82.6	84.2
82.5°	63.3	63.3	62.7	62.2
85°	44.6	44.0	42.4	42.4
87.5°	24.2	23.6	23.1	22.0
90°	0.0	0.0	0.0	0.0

(END OF REPORT)