

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155825

Luminaire Tested: **AVS-F02-LED-E-U-T3**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155825
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-T3
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (14) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5091.7 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P155825

CATALOG NUMBER: AVS-F02-LED-E-U-T3

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.5 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155825

CATALOG NUMBER: AVS-F02-LED-E-U-T3

Luminous Intensity Polar Plot



REPORT NUMBER: P155825

CATALOG NUMBER: AVS-F02-LED-E-U-T3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1758.3	0.0	1758.3
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	3333.4	0.0	3333.4
	% Fixture	65.5	0.0	65.5
Total	Lumens	5091.7	0.0	5091.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	1.0
10°-20°	155.1	3.0
20°-30°	266.6	5.2
30°-40°	432.8	8.5
40°-50°	722.6	14.2
50°-60°	1137.8	22.3
60°-70°	1551.6	30.5
70°-80°	671.7	13.2
80°-90°	101.0	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5091.7	100.0
0°-180°	5091.7	100.0

Coefficient of Utilization



REPORT NUMBER: P155825


CATALOG NUMBER: AVS-F02-LED-E-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	238.2	4.7			
FM	(30°-60°)	1421.9	27.9			
FH	(60°-80°)	1590.3	31.2			G1/1800
FVH	(80°-90°)	82.9	1.6			G1/100
BL	(0°-30°)	236.0	4.6	B1/500		
BM	(30°-60°)	871.3	17.1	B1/1000		
BH	(60°-80°)	632.9	12.4	B2/1000		G2/1000
BVH	(80°-90°)	18.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P155825

CATALOG NUMBER: AVS-F02-LED-E-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7
2.5°	550.9	553.1	550.9	551.4	552.0	551.4	550.9	550.9	549.2	550.4	551.4
5°	548.7	550.4	549.8	550.4	550.9	550.4	549.8	550.4	549.2	549.8	551.4
7.5°	545.9	545.4	545.9	547.0	548.2	548.2	548.2	548.7	548.2	548.2	549.8
10°	537.7	538.2	539.4	541.0	541.6	543.2	543.2	544.9	545.4	546.5	548.7
12.5°	527.3	527.8	528.9	529.9	532.7	535.4	535.4	539.4	541.0	543.7	547.6
15°	519.5	520.1	521.1	522.3	524.5	527.3	528.9	533.3	536.1	541.0	546.5
17.5°	523.9	523.4	524.5	525.1	525.1	527.3	527.3	530.6	533.9	538.2	545.4
20°	536.6	536.6	537.7	537.7	537.1	538.2	536.1	536.1	536.6	538.8	543.7
22.5°	549.2	548.7	550.9	552.0	552.5	554.2	552.0	551.4	548.7	547.0	548.7
25°	561.3	560.8	563.5	565.2	568.0	569.6	569.6	569.6	567.5	564.7	563.0
27.5°	580.1	580.1	582.8	584.5	586.6	589.9	591.6	591.6	592.2	588.3	585.6
30°	611.4	612.0	612.5	614.7	616.9	618.0	620.2	621.9	623.5	621.3	616.9
32.5°	648.9	645.6	645.6	648.9	651.6	654.9	656.1	658.2	661.6	659.9	659.3
35°	693.5	692.3	691.2	692.3	695.6	699.5	703.9	707.8	705.6	708.8	707.2
37.5°	759.5	760.6	761.1	761.1	760.6	761.7	763.8	767.8	766.6	767.8	769.9
40°	868.5	864.6	860.7	861.3	855.8	856.9	848.1	851.9	852.5	848.6	850.3
42.5°	977.4	979.6	981.2	985.7	981.9	979.6	971.4	971.4	966.9	963.1	962.0
45°	1095.2	1099.6	1100.1	1108.9	1105.7	1112.8	1118.9	1117.2	1110.1	1109.5	1101.8
47.5°	1189.3	1196.5	1204.1	1214.6	1222.9	1238.9	1257.5	1266.9	1272.4	1276.8	1268.0
50°	1259.8	1263.0	1282.9	1299.4	1317.5	1343.9	1369.8	1403.4	1430.4	1443.0	1455.1
52.5°	1297.7	1306.0	1327.5	1353.3	1385.2	1424.9	1466.6	1520.1	1566.3	1597.1	1624.7
55°	1306.0	1314.2	1338.4	1371.5	1414.9	1468.3	1528.3	1600.9	1670.4	1729.7	1787.6
57.5°	1282.9	1292.2	1318.1	1356.1	1407.3	1472.2	1547.6	1642.8	1738.5	1834.8	1920.2
60°	1240.5	1252.0	1275.8	1313.2	1369.8	1443.0	1533.3	1652.7	1786.9	1934.5	2097.9
62.5°	1170.6	1182.7	1204.8	1246.0	1304.4	1385.2	1489.8	1638.3	1828.3	2060.5	2350.6
65°	1058.3	1063.8	1090.8	1132.6	1184.4	1273.5	1388.5	1568.0	1815.0	2138.1	2537.6
66°	1007.7	1017.1	1033.6	1067.2	1116.7	1200.3	1315.9	1498.0	1765.0	2111.2	2532.7
67.5°	928.4	935.5	946.6	969.1	999.5	1061.0	1170.6	1342.9	1612.0	1974.6	2427.6
70°	750.7	754.0	768.8	776.6	787.0	807.4	846.9	946.0	1155.8	1496.4	1959.3
72.5°	511.8	521.1	537.1	559.2	587.8	615.3	634.0	646.6	691.8	892.6	1305.4
75°	375.3	385.3	405.6	434.8	484.9	542.1	601.6	629.0	610.4	584.5	727.0
77.5°	217.9	231.2	248.2	276.3	322.5	398.4	500.3	590.6	651.6	655.4	622.5
80°	91.9	93.6	104.0	118.3	146.9	200.3	279.6	409.4	544.9	636.2	657.6
82.5°	20.9	25.9	33.1	39.1	47.9	66.0	97.9	162.9	294.4	461.8	602.1
85°	7.7	7.7	10.5	15.4	17.6	19.8	25.9	41.2	70.5	129.8	270.8
87.5°	0.0	0.5	1.1	1.1	2.2	2.8	4.4	6.0	5.5	5.0	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155825

CATALOG NUMBER: AVS-F02-LED-E-U-T3

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7
2.5°	550.4	549.8	548.7	548.7	548.7	548.7	547.6	548.2	547.0	547.6	547.6
5°	549.8	549.8	549.2	548.2	548.7	548.7	549.2	548.2	548.2	548.7	548.2
7.5°	549.8	549.2	549.2	549.2	549.8	549.2	549.8	549.8	549.8	550.4	550.4
10°	549.8	549.8	550.9	551.4	551.4	552.0	553.7	553.7	554.2	554.7	555.9
12.5°	550.4	552.5	554.2	555.9	556.4	557.5	560.2	560.2	561.3	563.0	563.5
15°	550.9	554.2	557.5	558.7	559.7	561.9	564.7	565.8	567.5	569.0	570.2
17.5°	550.4	554.7	558.7	560.2	561.9	564.7	568.0	569.0	571.3	573.5	575.6
20°	549.8	555.9	561.9	564.1	566.3	570.2	574.6	577.3	579.5	582.8	585.0
22.5°	553.1	560.2	568.5	571.8	575.6	580.6	586.6	589.9	592.7	596.1	597.7
25°	563.5	569.0	579.0	584.5	589.4	597.7	605.9	609.7	613.1	615.9	616.4
27.5°	581.1	582.8	594.9	602.1	609.2	622.5	632.3	635.1	641.1	643.3	642.8
30°	609.7	607.0	616.9	628.0	638.4	656.6	668.7	675.9	681.3	681.3	676.9
32.5°	651.1	646.6	649.4	662.1	674.2	700.6	714.9	724.2	728.1	727.0	717.6
35°	705.0	702.3	700.6	710.5	729.7	760.6	779.3	784.2	790.3	789.2	777.1
37.5°	768.8	766.6	766.6	778.2	796.9	842.6	862.9	866.2	865.7	856.9	834.3
40°	844.2	843.1	838.1	844.8	860.7	920.2	947.7	952.1	946.0	931.7	905.3
42.5°	952.6	946.0	930.7	934.5	946.6	1004.4	1040.2	1052.2	1046.2	1031.9	989.0
45°	1094.1	1086.9	1061.0	1057.8	1064.4	1115.0	1161.2	1164.0	1162.9	1144.8	1094.1
47.5°	1260.3	1249.3	1221.8	1213.0	1210.8	1257.5	1302.2	1306.5	1303.7	1276.8	1209.1
50°	1440.3	1424.4	1406.1	1400.1	1391.3	1424.9	1469.9	1470.6	1459.5	1422.1	1358.9
52.5°	1632.3	1626.8	1623.5	1617.5	1613.6	1642.8	1670.4	1653.8	1637.3	1598.2	1543.2
55°	1826.0	1848.6	1871.7	1874.0	1880.5	1911.9	1911.4	1866.2	1854.1	1832.6	1778.1
57.5°	2031.9	2115.5	2188.2	2210.8	2232.7	2291.1	2285.6	2241.0	2225.6	2199.2	2154.1
60°	2312.0	2537.6	2747.4	2797.4	2832.1	2902.0	2895.4	2826.6	2858.5	2856.3	2797.9
62.5°	2704.5	3079.8	3394.0	3471.1	3495.2	3503.0	3461.1	3386.8	3418.2	3453.5	3274.0
65°	2970.3	3411.6	3734.1	3793.6	3796.9	3705.0	3611.9	3524.5	3516.8	3486.4	3230.1
66°	2976.3	3428.1	3751.7	3809.5	3789.1	3663.7	3545.9	3457.8	3419.9	3353.3	3087.5
67.5°	2869.5	3325.2	3673.6	3734.7	3690.1	3512.3	3349.9	3236.6	3162.3	3054.4	2820.0
70°	2409.9	2861.9	3291.1	3405.0	3419.3	3154.1	2928.9	2795.8	2695.6	2547.6	2345.6
72.5°	1791.9	2200.3	2579.0	2687.9	2743.5	2531.6	2341.8	2240.5	2103.4	1947.7	1804.0
75°	1123.2	1411.6	1665.4	1741.9	1689.5	1525.6	1411.6	1369.2	1234.4	1141.5	1076.0
77.5°	642.3	732.5	752.8	723.7	662.1	506.8	360.5	266.9	231.7	256.5	282.9
80°	626.8	574.6	457.9	402.9	364.9	251.0	147.5	101.2	84.2	86.4	93.6
82.5°	679.2	728.7	599.9	489.2	410.6	277.4	153.0	81.5	55.0	65.0	73.2
85°	441.3	614.2	553.1	466.1	377.5	237.2	126.0	42.4	28.1	36.9	50.7
87.5°	44.6	49.0	41.9	56.7	42.4	19.8	9.9	6.0	5.5	6.6	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155825

CATALOG NUMBER: AVS-F02-LED-E-U-T3

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7	548.7
2.5°	548.2	548.2	548.7	549.2	549.8	550.4	550.4	550.4	550.4	551.4	550.9
5°	549.2	550.4	551.4	552.0	553.1	553.1	554.7	554.2	554.2	555.9	556.4
7.5°	551.4	553.1	555.3	554.7	557.0	556.4	557.5	557.5	555.9	556.4	555.3
10°	556.4	558.7	559.7	558.0	558.7	556.4	555.9	553.1	549.8	548.2	545.9
12.5°	564.7	566.8	566.8	564.1	560.8	555.9	552.0	545.9	541.0	538.2	535.4
15°	571.8	574.0	573.5	569.0	564.1	556.4	550.9	543.7	536.6	532.2	529.4
17.5°	577.3	578.4	576.8	570.7	565.2	558.0	552.5	544.9	536.6	531.1	526.1
20°	585.6	584.5	580.6	573.0	566.8	560.2	555.9	549.2	539.9	532.7	525.6
22.5°	597.7	593.3	586.1	577.8	571.8	565.8	561.3	554.2	544.9	536.1	527.8
25°	613.7	604.9	594.9	586.1	580.6	574.0	569.0	561.3	551.4	541.6	531.6
27.5°	636.8	621.3	608.7	600.9	594.9	586.6	580.6	570.7	560.2	548.7	537.7
30°	662.6	641.7	629.6	623.5	616.9	608.2	598.8	586.1	574.0	561.3	548.2
32.5°	696.2	670.9	659.3	653.3	644.5	633.5	622.5	608.2	591.1	574.6	558.7
35°	740.2	714.4	702.3	692.8	680.8	666.4	650.5	631.3	608.2	586.1	565.8
37.5°	787.6	759.5	747.9	738.0	719.9	701.1	678.5	650.5	619.2	589.9	564.7
40°	847.6	821.7	806.8	789.7	768.3	735.9	700.6	659.9	619.7	583.9	554.2
42.5°	923.5	897.6	875.6	848.6	811.2	761.1	711.1	658.2	609.7	569.0	537.1
45°	1024.2	992.8	954.8	907.6	846.9	777.1	711.6	647.8	591.1	545.9	511.8
47.5°	1147.5	1099.6	1037.4	957.6	870.7	781.5	702.8	626.8	561.9	513.0	474.9
50°	1293.9	1218.4	1116.1	998.9	882.8	774.9	680.8	595.4	520.6	468.4	423.2
52.5°	1461.1	1337.9	1187.2	1028.6	882.2	752.8	643.3	548.2	466.7	408.4	365.4
55°	1657.6	1474.4	1260.3	1050.6	866.8	712.1	586.1	481.6	400.1	346.2	306.5
57.5°	1945.5	1695.6	1388.0	1084.8	836.0	649.4	508.5	401.8	330.3	279.1	245.5
60°	2471.6	2064.9	1618.0	1153.6	788.6	557.5	417.7	316.5	256.5	215.2	192.6
62.5°	2867.9	2350.6	1742.4	1138.1	693.5	444.1	309.8	230.6	188.8	160.7	146.4
65°	2811.2	2262.0	1609.7	980.2	543.7	313.2	205.8	156.9	129.8	116.7	108.4
66°	2683.0	2146.3	1494.7	882.2	469.9	260.3	169.5	131.5	111.7	102.4	96.9
67.5°	2439.7	1931.7	1288.9	723.1	361.0	188.8	127.7	104.0	90.8	86.9	83.1
70°	2028.1	1540.4	904.8	421.0	184.4	105.1	80.9	72.6	69.3	68.8	67.7
72.5°	1554.2	1090.3	532.7	199.3	95.8	69.8	62.7	60.0	58.9	58.9	59.5
75°	952.6	612.5	235.5	97.4	67.2	58.9	55.5	54.5	53.9	54.5	53.9
77.5°	318.1	194.8	100.7	73.8	61.1	54.5	52.3	51.2	51.2	51.2	51.2
80°	97.4	84.8	77.1	68.3	57.8	51.7	48.4	47.9	48.4	49.0	47.4
82.5°	73.2	69.3	65.0	60.5	52.3	46.2	45.1	45.1	45.1	43.5	41.2
85°	53.9	53.4	44.0	41.2	38.5	38.5	38.5	38.5	36.9	34.1	31.9
87.5°	9.9	9.3	9.9	10.5	15.4	16.5	16.5	17.6	19.3	18.1	18.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155825

CATALOG NUMBER: AVS-F02-LED-E-U-T3

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	548.7	548.7	548.7	548.7	548.7
2.5°	550.9	550.4	552.0	550.9	551.4
5°	555.9	555.3	556.4	555.3	557.0
7.5°	554.2	553.1	552.5	553.1	553.7
10°	542.7	541.6	541.0	540.4	541.0
12.5°	532.7	530.6	530.6	529.4	529.9
15°	525.6	523.9	523.4	522.3	522.8
17.5°	522.3	519.5	518.4	517.3	517.3
20°	520.1	516.8	515.1	514.0	513.5
22.5°	520.1	515.1	513.0	511.8	511.3
25°	522.3	516.3	513.0	511.3	510.7
27.5°	526.7	519.0	515.1	513.0	513.0
30°	534.4	524.5	519.0	516.3	515.6
32.5°	542.1	528.9	521.1	517.9	516.8
35°	545.9	528.9	519.5	514.0	513.0
37.5°	541.6	521.8	510.2	502.0	500.3
40°	527.8	506.8	494.2	486.5	485.4
42.5°	509.6	489.2	474.4	468.9	467.3
45°	484.9	460.6	445.8	438.0	438.7
47.5°	442.5	417.7	404.5	397.3	398.4
50°	392.4	368.2	356.6	348.9	350.6
52.5°	337.4	315.3	304.4	300.5	299.4
55°	279.6	262.5	254.8	250.4	248.8
57.5°	226.7	214.6	209.1	203.6	204.1
60°	178.9	172.8	171.2	165.1	164.6
62.5°	140.9	137.0	135.3	131.0	131.5
65°	106.7	105.7	106.7	104.0	105.1
66°	96.3	96.9	96.9	95.2	96.3
67.5°	83.1	84.2	85.8	84.2	85.3
70°	68.8	69.8	71.0	71.0	71.0
72.5°	60.0	61.1	61.7	61.7	61.7
75°	55.0	55.5	56.2	55.0	55.0
77.5°	51.7	51.7	50.7	50.1	49.5
80°	46.7	46.2	44.6	43.5	43.5
82.5°	39.1	37.9	36.9	35.2	35.2
85°	29.7	28.6	27.6	25.3	24.2
87.5°	15.4	16.0	15.4	12.6	11.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)