

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156875

Luminaire Tested: **AVS-F03-LED-E-U-T4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156875
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F03-LED-E-U-T4
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (21) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7484.3 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156875

CATALOG NUMBER: AVS-F03-LED-E-U-T4

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 10.3 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156875

CATALOG NUMBER: AVS-F03-LED-E-U-T4

Luminous Intensity Polar Plot



REPORT NUMBER: P156875

CATALOG NUMBER: AVS-F03-LED-E-U-T4


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1597.0	0.0	1597.0
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	5887.4	0.0	5887.4
	% Fixture	78.7	0.0	78.7
Total	Lumens	7484.3	0.0	7484.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.8	1.3
10°-20°	290.9	3.9
20°-30°	501.0	6.7
30°-40°	757.9	10.1
40°-50°	982.4	13.1
50°-60°	1354.4	18.1
60°-70°	2104.3	28.1
70°-80°	1223.7	16.3
80°-90°	174.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7484.3	100.0
0°-180°	7484.3	100.0

Coefficient of Utilization



REPORT NUMBER: P156875


CATALOG NUMBER: AVS-F03-LED-E-U-T4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	460.1	6.1			
FM	(30°-60°)	2402.5	32.1			
FH	(60°-80°)	2891.2	38.6			G2/5000
FVH	(80°-90°)	133.5	1.8			G2/225
BL	(0°-30°)	427.5	5.7	B1/500		
BM	(30°-60°)	692.3	9.2	B1/1000		
BH	(60°-80°)	436.8	5.8	B1/500		G1/500
BVH	(80°-90°)	40.5	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P156875

CATALOG NUMBER: AVS-F03-LED-E-U-T4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5
2.5°	968.3	971.6	969.1	969.9	969.9	970.8	970.8	971.6	970.8	973.3	974.9
5°	951.0	952.6	951.8	953.5	955.1	958.4	957.6	961.8	962.6	965.1	969.1
7.5°	944.4	942.8	943.5	946.0	947.7	949.3	951.0	954.3	956.8	962.6	965.9
10°	951.0	950.2	951.0	952.6	952.6	953.5	951.8	955.1	956.8	961.8	965.1
12.5°	978.2	978.2	976.6	976.6	974.9	973.3	969.1	966.7	965.9	966.7	968.3
15°	1022.0	1020.3	1017.1	1014.6	1011.3	1005.5	999.7	994.7	991.5	986.5	984.9
17.5°	1065.0	1062.5	1059.2	1055.9	1051.7	1045.9	1036.9	1031.1	1022.0	1016.3	1013.0
20°	1114.5	1109.5	1105.4	1101.2	1093.0	1091.3	1082.3	1072.3	1061.7	1048.4	1046.7
22.5°	1178.9	1170.6	1165.6	1163.2	1154.9	1152.4	1137.6	1123.5	1110.4	1093.0	1088.9
25°	1244.0	1235.9	1233.4	1230.1	1224.2	1220.9	1206.9	1191.2	1173.9	1149.9	1145.0
27.5°	1307.7	1308.5	1301.9	1304.4	1302.7	1296.9	1282.9	1267.2	1254.0	1225.9	1220.1
30°	1386.8	1382.0	1378.7	1383.6	1377.8	1378.7	1366.2	1358.0	1336.5	1320.0	1308.5
32.5°	1469.4	1468.6	1473.6	1476.9	1476.1	1474.4	1464.5	1456.3	1437.2	1413.3	1408.4
35°	1582.5	1587.5	1591.6	1606.4	1606.4	1617.2	1607.3	1597.4	1575.1	1546.2	1536.3
37.5°	1659.3	1660.9	1677.5	1697.3	1722.1	1745.2	1751.8	1754.2	1745.2	1723.7	1708.8
40°	1729.4	1732.7	1759.2	1789.7	1826.0	1871.5	1898.8	1911.1	1913.6	1903.6	1871.5
42.5°	1799.7	1804.6	1831.8	1876.4	1926.7	1984.6	2032.4	2063.0	2080.3	2080.3	2061.3
45°	1881.3	1888.0	1917.7	1966.4	2025.0	2097.6	2163.7	2222.3	2250.4	2252.0	2233.9
47.5°	1977.9	1983.7	2018.4	2068.0	2128.2	2201.7	2285.1	2351.9	2403.9	2407.3	2392.3
50°	2102.6	2110.9	2139.8	2184.4	2246.2	2320.5	2403.9	2497.2	2551.7	2564.9	2549.2
52.5°	2267.7	2269.3	2293.3	2334.6	2394.8	2465.8	2554.2	2655.8	2727.6	2738.2	2712.6
55°	2495.5	2493.1	2508.8	2553.4	2598.8	2654.1	2745.7	2859.6	2939.7	2956.2	2929.7
57.5°	2805.2	2802.7	2815.9	2826.6	2911.6	2965.3	3055.2	3164.2	3241.9	3289.7	3244.4
60°	3284.8	3282.3	3303.7	3366.5	3430.1	3508.5	3596.0	3726.4	3835.4	3849.4	3804.9
62.5°	3632.3	3644.7	3691.7	3765.2	3894.0	4047.6	4207.7	4379.4	4603.1	4674.1	4652.6
65°	3511.0	3535.8	3600.9	3712.4	3884.1	4096.3	4347.3	4658.4	4958.1	5125.7	5120.7
66°	3402.0	3429.2	3509.3	3616.6	3798.2	4030.3	4304.2	4643.6	4978.8	5163.6	5175.2
67.5°	3203.8	3234.4	3312.8	3440.0	3616.6	3863.4	4158.1	4527.2	4906.1	5121.6	5152.1
70°	2818.3	2853.1	2909.9	3014.8	3189.0	3409.4	3719.8	4050.1	4447.2	4693.9	4731.1
72.5°	2356.1	2386.6	2450.2	2536.1	2678.9	2817.5	3061.0	3304.6	3588.6	3870.1	3842.8
75°	1691.5	1704.7	1742.7	1836.0	1912.7	2037.4	2233.1	2432.8	2626.8	2755.6	2773.8
77.5°	879.2	913.9	967.6	1070.7	1154.1	1266.3	1393.5	1543.7	1685.7	1803.7	1771.6
80°	575.4	590.3	638.1	691.0	752.0	823.8	908.9	965.1	983.2	975.8	983.2
82.5°	331.8	359.1	422.7	463.1	508.5	533.3	600.9	665.4	701.7	656.3	639.8
85°	42.1	54.5	171.7	216.3	247.7	284.8	305.5	344.2	321.1	287.3	350.1
87.5°	9.1	8.3	11.6	24.8	25.6	21.5	40.4	42.9	26.4	13.2	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156875

CATALOG NUMBER: AVS-F03-LED-E-U-T4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5
2.5°	976.6	977.4	979.1	981.6	983.2	984.9	986.5	989.0	990.7	992.3	995.5
5°	972.4	975.8	979.1	982.4	986.5	993.1	997.2	1000.5	1003.8	1010.5	1013.0
7.5°	969.9	975.8	980.7	986.5	993.1	998.9	1006.3	1010.5	1015.4	1019.5	1024.5
10°	968.3	976.6	981.6	989.8	997.2	1003.0	1011.3	1016.3	1022.0	1026.9	1029.4
12.5°	971.6	975.8	980.7	989.0	998.0	1006.3	1015.4	1019.5	1024.5	1028.6	1029.4
15°	985.7	985.7	986.5	993.1	1002.2	1008.8	1016.3	1020.3	1022.8	1025.3	1025.3
17.5°	1011.3	1005.5	1001.3	1002.2	1008.0	1012.1	1016.3	1016.3	1014.6	1013.8	1012.1
20°	1041.0	1033.6	1025.3	1019.5	1017.8	1014.6	1012.1	1003.8	997.2	991.5	987.4
22.5°	1083.9	1072.3	1060.8	1050.1	1040.2	1027.8	1013.8	997.2	981.6	970.8	964.2
25°	1136.8	1127.7	1113.7	1097.1	1084.8	1061.7	1043.4	1019.5	999.7	985.7	974.1
27.5°	1211.9	1201.1	1188.0	1173.1	1154.9	1129.3	1107.0	1079.0	1055.0	1034.4	1019.5
30°	1305.2	1291.1	1281.2	1263.0	1250.7	1221.8	1199.5	1164.8	1118.5	1085.6	1065.0
32.5°	1400.9	1385.2	1377.0	1362.9	1348.9	1331.6	1297.7	1244.0	1184.7	1131.0	1095.4
35°	1528.9	1512.3	1497.5	1485.1	1464.5	1432.3	1402.6	1338.1	1256.5	1181.3	1121.9
37.5°	1689.8	1662.6	1625.5	1594.1	1557.7	1511.5	1466.1	1400.1	1306.8	1209.4	1130.2
40°	1861.6	1813.7	1760.8	1702.3	1639.5	1572.6	1520.6	1453.8	1348.9	1233.4	1124.4
42.5°	2040.7	1964.8	1891.3	1808.7	1721.2	1642.0	1574.3	1500.8	1380.3	1239.9	1101.2
45°	2218.1	2133.2	2021.8	1913.6	1802.9	1704.7	1628.8	1546.2	1409.2	1242.4	1070.7
47.5°	2365.1	2277.6	2150.5	2015.1	1883.8	1772.4	1683.2	1594.1	1448.0	1259.8	1063.3
50°	2520.3	2413.9	2272.6	2112.5	1963.9	1839.3	1744.4	1651.9	1502.5	1304.4	1087.3
52.5°	2689.5	2567.4	2402.3	2223.1	2060.5	1921.0	1817.8	1722.9	1571.8	1367.0	1132.6
55°	2896.0	2746.5	2567.4	2365.1	2191.0	2036.6	1922.7	1810.4	1654.3	1441.3	1189.5
57.5°	3211.3	3028.0	2826.6	2596.3	2403.1	2220.6	2084.5	1954.8	1782.3	1552.0	1267.2
60°	3781.8	3586.1	3324.4	3045.4	2818.3	2605.4	2405.6	2244.6	2032.4	1769.9	1438.9
62.5°	4599.0	4339.0	3989.7	3599.3	3302.1	2995.0	2769.6	2530.3	2266.9	1983.7	1641.1
65°	5053.1	4737.7	4270.5	3817.2	3435.0	3101.5	2815.0	2537.6	2245.4	1974.6	1688.2
66°	5109.2	4780.6	4295.2	3818.0	3416.9	3074.3	2773.0	2485.7	2186.8	1928.4	1668.4
67.5°	5086.0	4750.1	4249.8	3746.2	3338.4	2970.3	2659.1	2361.0	2063.0	1822.0	1602.4
70°	4707.2	4388.5	3897.3	3409.4	3022.3	2659.1	2361.9	2068.8	1795.5	1589.1	1427.4
72.5°	3908.9	3636.5	3209.6	2826.6	2522.8	2223.1	1971.4	1691.5	1460.3	1307.7	1211.9
75°	2821.7	2656.6	2267.7	2048.1	1781.5	1582.5	1338.1	1172.2	1006.3	932.0	915.5
77.5°	1782.3	1560.2	1313.4	1081.5	889.1	737.2	573.8	487.0	406.1	397.9	480.4
80°	902.3	812.3	625.7	498.7	419.4	339.3	268.3	203.1	142.0	170.9	204.8
82.5°	591.1	492.8	386.3	317.8	276.6	229.5	178.3	123.8	90.8	102.4	140.3
85°	319.5	272.4	219.6	173.4	140.3	125.5	84.2	59.5	58.7	62.7	80.1
87.5°	23.1	23.1	18.1	16.5	19.8	16.5	14.8	14.8	14.0	14.8	19.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156875

CATALOG NUMBER: AVS-F03-LED-E-U-T4

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5	986.5
2.5°	997.2	999.7	1000.5	1004.7	1007.2	1008.8	1010.5	1010.5	1011.3	1013.8	1014.6
5°	1016.3	1020.3	1025.3	1028.6	1030.3	1035.2	1036.9	1036.9	1038.5	1041.8	1044.2
7.5°	1027.8	1033.6	1038.5	1040.2	1043.4	1045.1	1047.6	1049.2	1049.2	1052.5	1054.2
10°	1031.9	1035.2	1040.2	1040.2	1043.4	1043.4	1045.9	1046.7	1046.7	1050.1	1052.5
12.5°	1031.9	1033.6	1037.7	1037.7	1040.2	1041.0	1044.2	1046.7	1047.6	1051.7	1055.0
15°	1026.9	1028.6	1031.9	1032.7	1038.5	1041.8	1049.2	1054.2	1054.2	1058.3	1060.0
17.5°	1013.0	1017.1	1023.6	1030.3	1041.0	1048.4	1057.5	1061.7	1058.3	1055.9	1053.4
20°	989.8	997.2	1013.0	1029.4	1048.4	1058.3	1063.3	1059.2	1047.6	1036.1	1028.6
22.5°	966.7	981.6	1008.0	1032.7	1054.2	1060.8	1058.3	1043.4	1024.5	1010.5	1000.5
25°	977.4	994.7	1020.3	1042.6	1056.7	1055.0	1045.1	1024.5	1003.8	985.7	969.1
27.5°	1022.0	1041.0	1055.0	1062.5	1060.8	1049.2	1033.6	1010.5	985.7	961.8	938.7
30°	1064.1	1074.0	1077.3	1071.5	1058.3	1039.4	1019.5	993.1	960.1	930.4	903.9
32.5°	1083.1	1073.2	1057.5	1041.8	1020.3	1003.8	976.6	947.7	906.4	870.9	844.6
35°	1083.1	1043.4	1003.8	970.8	938.7	918.0	886.6	847.8	809.8	780.1	759.5
37.5°	1059.2	983.2	918.0	864.4	823.8	801.6	754.5	719.9	687.7	677.7	664.6
40°	1015.4	903.1	809.0	738.9	687.7	654.6	607.6	583.6	571.3	566.3	563.8
42.5°	956.8	814.0	688.5	601.8	546.5	509.3	477.9	463.1	462.3	461.5	461.5
45°	894.1	718.2	571.3	468.1	419.4	386.3	371.5	365.7	370.7	369.8	370.7
47.5°	855.2	645.6	463.9	354.2	317.0	295.5	288.1	290.6	294.7	293.1	293.1
50°	850.3	608.4	392.1	275.8	247.7	236.9	235.2	235.2	237.7	236.1	235.2
52.5°	868.5	602.6	355.0	236.9	214.6	205.6	203.9	203.1	202.3	197.3	193.2
55°	899.8	615.9	344.2	227.0	203.9	194.0	191.5	189.8	186.5	180.0	172.5
57.5°	962.6	657.1	354.2	232.0	207.3	199.0	196.5	196.5	189.8	179.2	168.4
60°	1113.7	762.0	394.6	251.0	222.9	214.6	216.3	215.4	205.6	189.8	173.4
62.5°	1308.5	899.0	447.5	277.4	242.7	241.0	249.3	247.7	231.2	207.3	183.3
65°	1398.4	963.4	462.3	283.1	246.8	254.3	270.8	269.1	248.5	215.4	184.9
66°	1400.1	963.4	455.6	278.2	241.0	250.2	266.6	265.8	245.2	212.1	181.7
67.5°	1366.2	937.0	436.7	268.3	229.5	236.1	251.0	250.2	231.2	203.9	175.0
70°	1239.1	838.8	388.0	251.0	213.8	210.5	215.4	212.1	199.8	180.8	160.9
72.5°	1061.7	704.1	338.4	237.7	203.1	189.8	186.5	184.0	174.2	163.4	151.1
75°	836.3	557.2	297.2	227.9	193.2	175.9	170.1	166.7	160.1	152.7	142.8
77.5°	516.0	398.8	259.2	214.6	185.7	168.4	164.2	159.3	149.4	140.3	133.0
80°	230.4	246.8	213.0	187.4	165.9	150.3	143.6	136.2	126.3	120.5	116.4
82.5°	153.6	159.3	154.4	140.3	125.5	113.1	103.2	103.2	101.6	96.6	94.9
85°	98.2	99.1	95.8	86.6	80.9	73.5	69.3	70.2	73.5	72.6	71.8
87.5°	22.3	22.3	26.4	24.8	28.9	30.6	33.1	35.5	40.4	40.4	42.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156875

CATALOG NUMBER: AVS-F03-LED-E-U-T4

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	986.5	986.5	986.5	986.5	986.5
2.5°	1015.4	1017.1	1018.7	1016.3	1017.1
5°	1044.2	1043.4	1047.6	1045.1	1046.7
7.5°	1053.4	1054.2	1057.5	1057.5	1058.3
10°	1054.2	1055.9	1060.0	1062.5	1064.1
12.5°	1058.3	1061.7	1068.2	1069.8	1069.8
15°	1061.7	1063.3	1067.4	1069.0	1070.7
17.5°	1050.1	1046.7	1048.4	1049.2	1048.4
20°	1021.1	1017.8	1017.1	1013.8	1015.4
22.5°	989.8	980.7	974.9	968.3	968.3
25°	951.8	937.8	926.2	914.7	917.2
27.5°	916.4	898.1	886.6	879.2	877.5
30°	881.7	862.7	851.9	842.9	842.9
32.5°	823.8	810.7	796.6	790.9	790.1
35°	743.8	735.5	723.9	721.6	717.4
37.5°	653.8	651.3	641.5	640.6	636.5
40°	559.7	561.3	558.0	556.4	553.9
42.5°	465.6	473.9	472.2	471.4	469.7
45°	375.6	381.3	382.2	384.7	388.8
47.5°	295.5	297.2	298.9	298.0	298.9
50°	231.2	227.0	226.2	223.7	226.2
52.5°	186.5	180.0	176.7	173.4	171.7
55°	164.2	157.7	154.4	152.7	151.1
57.5°	158.5	151.9	146.9	143.6	142.8
60°	160.1	150.3	143.6	139.5	138.7
62.5°	164.2	151.1	142.0	137.8	137.0
65°	163.4	149.4	141.1	136.2	135.3
66°	160.9	147.8	139.5	135.3	134.6
67.5°	156.9	145.3	137.8	134.6	133.0
70°	149.4	142.0	136.2	132.1	130.5
72.5°	142.8	137.0	132.1	128.0	127.2
75°	135.3	130.5	125.5	122.2	121.3
77.5°	126.3	121.3	118.0	115.5	114.7
80°	111.4	108.2	104.9	101.6	101.6
82.5°	92.4	89.9	86.6	84.2	83.4
85°	71.0	71.0	68.5	66.0	65.2
87.5°	42.1	41.2	41.2	38.8	38.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)