

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148115

Luminaire Tested: **AVS-F04-LED-E-U-5WQ**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148115
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-5WQ
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (28) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10513.2 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148115

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 1.6 fc
Type V - Short - Semi-Cutoff

REPORT NUMBER: P148115

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ

Luminous Intensity Polar Plot



REPORT NUMBER: P148115

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5256.6	0.0	5256.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5256.6	0.0	5256.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	10513.2	0.0	10513.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.8	0.5
10°-20°	193.6	1.8
20°-30°	392.0	3.7
30°-40°	657.2	6.3
40°-50°	1159.2	11.0
50°-60°	2044.2	19.4
60°-70°	3121.0	29.7
70°-80°	2607.9	24.8
80°-90°	283.4	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10513.2	100.0
0°-180°	10513.2	100.0

Coefficient of Utilization



REPORT NUMBER: P148115


CATALOG NUMBER: AVS-F04-LED-E-U-5WQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	320.2	3.0			
FM	(30°-60°)	1930.3	18.4			
FH	(60°-80°)	2864.4	27.2			G2/5000
FVH	(80°-90°)	141.7	1.3			G2/225
BL	(0°-30°)	320.2	3.0	B1/500		
BM	(30°-60°)	1930.3	18.4	B2/2500		
BH	(60°-80°)	2864.4	27.2	B4/5000		G2/5000
BVH	(80°-90°)	141.7	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short





REPORT NUMBER: P148115

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	545.9	545.9	545.9	545.9	545.9	545.9	545.9	545.9	545.9	545.9	545.9
2.5°	550.4	551.4	550.4	550.4	550.4	550.4	550.4	549.2	549.2	549.2	550.4
5°	561.3	562.5	561.3	562.5	562.5	562.5	562.5	561.3	561.3	561.3	561.3
7.5°	579.0	579.0	579.0	580.1	579.0	579.0	580.1	579.0	579.0	579.0	579.0
10°	604.2	603.2	603.2	603.2	603.2	603.2	604.2	604.2	604.2	603.2	603.2
12.5°	635.1	634.0	635.1	635.1	636.2	636.2	636.2	636.2	636.2	636.2	635.1
15°	672.5	672.5	672.5	673.7	675.9	675.9	674.7	675.9	675.9	675.9	675.9
17.5°	714.4	716.6	714.4	715.4	716.6	715.4	717.6	718.8	719.9	718.8	715.4
20°	757.3	758.3	758.3	758.3	758.3	760.6	761.7	761.7	765.0	763.8	762.8
22.5°	798.0	800.2	800.2	801.3	801.3	804.7	804.7	804.7	806.8	809.0	806.8
25°	840.9	839.8	839.8	842.1	843.1	847.6	847.6	849.7	853.1	854.1	851.9
27.5°	879.5	878.3	878.3	881.7	882.8	888.3	888.3	892.6	894.8	896.0	893.8
30°	920.2	920.2	919.1	922.4	925.7	930.1	932.3	936.7	940.0	941.1	938.9
32.5°	968.6	966.4	967.6	969.7	971.9	976.3	979.6	985.1	989.5	990.7	988.4
35°	1023.6	1020.3	1021.5	1023.6	1026.9	1033.6	1039.1	1042.4	1049.0	1051.2	1046.7
37.5°	1084.1	1085.3	1084.1	1089.7	1095.2	1102.9	1109.5	1113.9	1120.5	1123.8	1120.5
40°	1170.1	1166.7	1170.1	1175.5	1184.4	1194.3	1207.5	1210.8	1217.4	1223.9	1216.3
42.5°	1281.2	1279.0	1286.7	1291.1	1301.0	1312.0	1328.5	1337.3	1347.3	1351.7	1345.1
45°	1426.5	1426.5	1435.3	1436.4	1451.8	1466.1	1489.2	1500.2	1519.0	1519.0	1519.0
47.5°	1587.3	1593.8	1599.3	1610.4	1621.3	1647.8	1670.9	1695.1	1712.6	1714.9	1711.6
50°	1753.4	1760.0	1776.6	1791.9	1816.2	1849.2	1874.5	1906.4	1921.9	1935.0	1930.7
52.5°	1937.2	1938.3	1958.1	1977.9	2013.2	2049.5	2090.3	2123.2	2150.8	2162.9	2153.0
55°	2138.7	2140.8	2158.4	2179.4	2219.0	2260.8	2311.5	2345.6	2380.8	2402.8	2386.3
57.5°	2356.6	2357.7	2375.3	2400.6	2448.0	2489.7	2538.2	2586.6	2619.7	2639.5	2628.5
60°	2597.6	2603.1	2616.4	2648.3	2693.4	2737.4	2785.9	2828.8	2867.4	2888.2	2877.2
62.5°	2855.2	2860.7	2879.5	2904.8	2944.4	2992.8	3039.1	3094.1	3126.0	3149.1	3132.6
65°	3028.0	3037.9	3067.7	3101.8	3160.1	3222.8	3276.8	3351.6	3390.2	3417.7	3402.3
67.5°	3039.1	3044.6	3080.8	3132.6	3210.8	3305.4	3415.4	3532.1	3608.1	3644.5	3618.0
69°	2964.1	2971.9	3007.2	3065.5	3152.4	3262.5	3393.5	3538.8	3655.4	3709.3	3684.0
70°	2879.5	2896.0	2934.5	2998.3	3083.1	3198.7	3334.0	3489.2	3625.7	3699.5	3680.7
72.5°	2701.1	2705.5	2730.9	2781.5	2846.4	2942.2	3069.8	3216.3	3346.1	3451.8	3467.3
75°	2397.3	2411.6	2430.4	2464.5	2497.5	2566.8	2652.6	2752.8	2828.8	2910.3	2913.6
77.5°	1811.7	1854.7	1869.0	1876.7	1891.0	1946.0	2020.9	2107.9	2170.6	2183.8	2181.6
80°	813.4	870.7	883.8	946.6	985.1	1076.5	1191.0	1324.1	1413.3	1423.2	1399.0
82.5°	159.6	170.6	199.3	248.8	339.1	393.0	467.8	561.3	647.3	696.8	667.0
85°	52.8	56.2	65.0	71.5	82.6	93.6	113.4	140.9	175.0	193.7	172.8
87.5°	20.9	20.9	24.2	26.4	28.6	28.6	28.6	26.4	25.3	20.9	18.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148115

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	545.9	545.9	545.9	545.9	545.9	545.9	545.9	545.9
2.5°	549.2	549.2	549.2	549.2	549.2	549.2	549.2	549.2
5°	561.3	560.2	560.2	559.2	559.2	559.2	559.2	559.2
7.5°	577.8	576.8	575.6	576.8	575.6	575.6	575.6	575.6
10°	603.2	600.9	599.9	598.8	598.8	598.8	597.7	597.7
12.5°	633.0	633.0	631.8	630.7	628.5	629.6	628.5	626.3
15°	673.7	671.4	670.4	669.2	667.0	667.0	667.0	665.9
17.5°	714.4	712.1	712.1	708.8	707.8	707.8	707.8	708.8
20°	759.5	756.2	754.0	751.8	749.5	750.7	748.5	750.7
22.5°	804.7	800.2	798.0	794.7	791.4	791.4	790.3	788.1
25°	848.6	843.1	840.9	837.6	833.3	833.3	831.0	828.8
27.5°	890.5	885.0	882.8	876.2	871.7	870.7	868.5	867.4
30°	936.7	930.1	926.8	920.2	913.6	912.4	909.2	909.2
32.5°	985.1	978.5	976.3	966.4	960.9	960.9	958.8	956.5
35°	1045.7	1035.8	1033.6	1023.6	1016.0	1016.0	1013.8	1014.8
37.5°	1117.2	1109.5	1101.8	1094.1	1085.3	1084.1	1082.0	1079.8
40°	1213.0	1204.1	1195.3	1184.4	1176.7	1174.4	1171.2	1170.1
42.5°	1340.6	1331.8	1314.2	1305.4	1297.7	1291.1	1290.1	1288.9
45°	1503.5	1492.5	1480.4	1463.9	1454.0	1439.7	1437.5	1432.0
47.5°	1699.5	1678.5	1657.6	1643.3	1628.0	1611.4	1608.1	1599.3
50°	1907.5	1891.0	1855.8	1832.6	1808.5	1791.9	1780.9	1777.6
52.5°	2131.0	2100.1	2064.9	2034.1	1998.9	1976.9	1957.0	1951.5
55°	2364.4	2320.3	2276.3	2239.9	2204.7	2178.2	2159.6	2150.8
57.5°	2597.6	2549.2	2500.8	2461.1	2431.4	2397.3	2378.7	2374.2
60°	2840.9	2794.7	2745.2	2705.5	2669.2	2639.5	2628.5	2607.6
62.5°	3098.4	3050.1	3003.8	2965.3	2919.1	2898.1	2879.5	2867.4
65°	3351.6	3295.5	3237.2	3196.5	3150.2	3120.5	3097.4	3080.8
67.5°	3547.6	3462.8	3384.7	3316.4	3253.7	3207.5	3177.7	3162.3
69°	3602.6	3496.9	3396.8	3307.6	3233.9	3182.1	3149.1	3133.7
70°	3596.0	3479.3	3369.2	3271.3	3190.9	3135.9	3103.9	3075.3
72.5°	3392.3	3285.6	3163.4	3056.7	2984.0	2931.2	2899.3	2883.8
75°	2894.8	2823.3	2735.2	2652.6	2599.9	2569.0	2529.4	2530.5
77.5°	2107.9	2110.1	2050.6	1965.8	1906.4	1895.4	1877.8	1860.2
80°	1307.7	1203.1	1134.8	1043.4	976.3	918.0	892.6	837.6
82.5°	603.2	471.1	365.4	276.3	212.4	166.2	145.3	118.9
85°	134.3	102.4	84.8	68.3	58.3	53.9	44.0	40.7
87.5°	18.8	16.5	15.4	14.3	12.1	8.8	6.6	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)