

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148105

Luminaire Tested: **AVS-F03-LED-E-U-5WQ**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148105
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F03-LED-E-U-5WQ
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (21) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7884.9 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G2

Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148105

CATALOG NUMBER: AVS-F03-LED-E-U-5WQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.8 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P148105

CATALOG NUMBER: AVS-F03-LED-E-U-5WQ

Luminous Intensity Polar Plot



REPORT NUMBER: P148105

CATALOG NUMBER: AVS-F03-LED-E-U-5WQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3942.5	0.0	3942.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3942.5	0.0	3942.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	7884.9	0.0	7884.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.1	0.5
10°-20°	145.2	1.8
20°-30°	294.0	3.7
30°-40°	492.9	6.3
40°-50°	869.4	11.0
50°-60°	1533.2	19.4
60°-70°	2340.7	29.7
70°-80°	1955.9	24.8
80°-90°	212.5	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7884.9	100.0
0°-180°	7884.9	100.0



REPORT NUMBER: P148105


CATALOG NUMBER: AVS-F03-LED-E-U-5WQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	240.1	3.0			
FM	(30°-60°)	1447.7	18.4			
FH	(60°-80°)	2148.3	27.2			G2/5000
FVH	(80°-90°)	106.3	1.3			G2/225
BL	(0°-30°)	240.1	3.0	B1/500		
BM	(30°-60°)	1447.7	18.4	B2/2500		
BH	(60°-80°)	2148.3	27.2	B3/2500		G2/5000
BVH	(80°-90°)	106.3	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P148105

CATALOG NUMBER: AVS-F03-LED-E-U-5WQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.4	409.4	409.4	409.4	409.4	409.4	409.4	409.4	409.4	409.4	409.4
2.5°	412.7	413.6	412.7	412.7	412.7	412.7	412.7	411.9	411.9	411.9	412.7
5°	421.0	421.9	421.0	421.9	421.9	421.9	421.9	421.0	421.0	421.0	421.0
7.5°	434.2	434.2	434.2	435.0	434.2	434.2	435.0	434.2	434.2	434.2	434.2
10°	453.3	452.4	452.4	452.4	452.4	452.4	453.3	453.3	453.3	452.4	452.4
12.5°	476.4	475.5	476.4	476.4	477.2	477.2	477.2	477.2	477.2	477.2	476.4
15°	504.4	504.4	504.4	505.2	506.8	506.8	506.0	506.8	506.8	506.8	506.8
17.5°	535.8	537.4	535.8	536.6	537.4	536.6	538.2	539.1	539.9	539.1	536.6
20°	568.0	568.8	568.8	568.8	568.8	570.5	571.3	571.3	573.8	573.0	572.1
22.5°	598.5	600.2	600.2	600.9	600.9	603.4	603.4	603.4	605.1	606.7	605.1
25°	630.7	629.8	629.8	631.5	632.3	635.6	635.6	637.3	639.8	640.6	639.0
27.5°	659.6	658.8	658.8	661.2	662.1	666.2	666.2	669.5	671.2	672.0	670.4
30°	690.2	690.2	689.3	691.8	694.3	697.6	699.2	702.5	705.0	705.8	704.1
32.5°	726.4	724.8	725.6	727.3	728.9	732.2	734.7	738.9	742.2	743.0	741.3
35°	767.8	765.3	766.1	767.8	770.3	775.1	779.3	781.8	786.7	788.4	785.1
37.5°	813.2	814.0	813.2	817.3	821.3	827.2	832.1	835.4	840.4	842.9	840.4
40°	877.5	875.0	877.5	881.7	888.3	895.6	905.6	908.1	913.1	918.0	912.2
42.5°	960.9	959.3	965.1	968.3	975.8	984.0	996.4	1003.0	1010.5	1013.8	1008.8
45°	1069.8	1069.8	1076.5	1077.3	1088.9	1099.6	1116.9	1125.2	1139.3	1139.3	1139.3
47.5°	1190.4	1195.3	1199.5	1207.8	1216.0	1235.9	1253.2	1271.3	1284.6	1286.2	1283.7
50°	1315.0	1320.0	1332.4	1343.9	1362.1	1386.8	1405.9	1429.8	1441.3	1451.3	1448.0
52.5°	1453.0	1453.8	1468.6	1483.4	1509.8	1537.1	1567.7	1592.4	1613.1	1622.2	1614.7
55°	1604.0	1605.6	1618.9	1634.5	1664.2	1695.6	1733.6	1759.2	1785.6	1802.1	1789.7
57.5°	1767.5	1768.3	1781.5	1800.5	1836.0	1867.4	1903.6	1940.0	1964.8	1979.6	1971.4
60°	1948.3	1952.3	1962.3	1986.2	2020.1	2053.1	2089.4	2121.6	2150.5	2166.2	2157.9
62.5°	2141.5	2145.5	2159.6	2178.5	2208.3	2244.6	2279.3	2320.5	2344.5	2361.9	2349.4
65°	2271.0	2278.4	2300.7	2326.3	2370.1	2417.1	2457.6	2513.7	2542.6	2563.2	2551.7
67.5°	2279.3	2283.4	2310.7	2349.4	2408.1	2479.1	2561.6	2649.1	2706.1	2733.3	2713.5
69°	2223.1	2228.9	2255.3	2299.1	2364.4	2446.8	2545.1	2654.1	2741.6	2782.0	2763.0
70°	2159.6	2171.9	2200.8	2248.7	2312.3	2399.0	2500.5	2616.9	2719.3	2774.6	2760.5
72.5°	2025.8	2029.1	2048.1	2086.1	2134.8	2206.6	2302.4	2412.2	2509.6	2588.8	2600.4
75°	1798.0	1808.7	1822.8	1848.4	1873.2	1925.1	1989.5	2064.7	2121.6	2182.7	2185.2
77.5°	1358.9	1391.0	1401.8	1407.6	1418.2	1459.5	1515.6	1580.8	1628.0	1637.8	1636.2
80°	610.1	653.0	662.9	709.9	738.9	807.4	893.3	993.1	1060.0	1067.4	1049.2
82.5°	119.7	128.0	149.4	186.5	254.3	294.7	350.9	421.0	485.4	522.6	500.3
85°	39.6	42.1	48.7	53.7	61.9	70.2	85.1	105.7	131.3	145.3	129.6
87.5°	15.6	15.6	18.1	19.8	21.5	21.5	21.5	19.8	19.0	15.6	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148105

CATALOG NUMBER: AVS-F03-LED-E-U-5WQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.4	409.4	409.4	409.4	409.4	409.4	409.4	409.4
2.5°	411.9	411.9	411.9	411.9	411.9	411.9	411.9	411.9
5°	421.0	420.2	420.2	419.4	419.4	419.4	419.4	419.4
7.5°	433.4	432.5	431.7	432.5	431.7	431.7	431.7	431.7
10°	452.4	450.8	449.9	449.1	449.1	449.1	448.3	448.3
12.5°	474.7	474.7	473.9	473.1	471.4	472.2	471.4	469.7
15°	505.2	503.5	502.7	502.0	500.3	500.3	500.3	499.5
17.5°	535.8	534.1	534.1	531.6	530.8	530.8	530.8	531.6
20°	569.6	567.2	565.5	563.8	562.2	563.0	561.3	563.0
22.5°	603.4	600.2	598.5	596.1	593.6	593.6	592.7	591.1
25°	636.5	632.3	630.7	628.2	625.0	625.0	623.3	621.7
27.5°	667.9	663.7	662.1	657.1	653.8	653.0	651.3	650.5
30°	702.5	697.6	695.1	690.2	685.2	684.4	681.9	681.9
32.5°	738.9	733.9	732.2	724.8	720.7	720.7	719.1	717.4
35°	784.2	776.8	775.1	767.8	762.0	762.0	760.3	761.1
37.5°	837.9	832.1	826.3	820.6	814.0	813.2	811.5	809.8
40°	909.7	903.1	896.5	888.3	882.5	880.8	878.3	877.5
42.5°	1005.5	998.9	985.7	979.1	973.3	968.3	967.6	966.7
45°	1127.7	1119.4	1110.4	1097.9	1090.6	1079.8	1078.1	1074.0
47.5°	1274.6	1259.0	1243.2	1232.5	1220.9	1208.6	1206.1	1199.5
50°	1430.7	1418.2	1391.8	1374.5	1356.4	1343.9	1335.6	1333.3
52.5°	1598.2	1575.1	1548.7	1525.6	1499.2	1482.7	1467.8	1463.6
55°	1773.3	1740.2	1707.2	1679.9	1653.6	1633.7	1619.7	1613.1
57.5°	1948.3	1911.9	1875.5	1845.9	1823.6	1798.0	1783.9	1780.6
60°	2130.7	2096.0	2058.9	2029.1	2001.9	1979.6	1971.4	1955.6
62.5°	2323.8	2287.6	2252.8	2223.9	2189.3	2173.6	2159.6	2150.5
65°	2513.7	2471.6	2427.9	2397.3	2362.7	2340.4	2323.0	2310.7
67.5°	2660.6	2597.1	2538.4	2487.4	2440.2	2405.6	2383.3	2371.7
69°	2702.0	2622.7	2547.6	2480.7	2425.4	2386.6	2361.9	2350.3
70°	2697.0	2609.5	2526.9	2453.5	2393.2	2351.9	2328.0	2306.5
72.5°	2544.2	2464.1	2372.5	2292.4	2238.0	2198.3	2174.4	2162.9
75°	2171.1	2117.5	2051.4	1989.5	1949.8	1926.7	1897.1	1897.9
77.5°	1580.8	1582.5	1537.9	1474.4	1429.8	1421.6	1408.4	1395.1
80°	980.7	902.3	851.1	782.6	732.2	688.5	669.5	628.2
82.5°	452.4	353.4	274.1	207.3	159.3	124.7	109.0	89.1
85°	100.7	76.8	63.5	51.2	43.7	40.4	33.1	30.6
87.5°	14.0	12.3	11.6	10.8	9.1	6.6	5.0	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)