

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148079

Luminaire Tested: **AVS-E01-LED-E-U-5WQ-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148079
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E01-LED-E-U-5WQ-7030
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (21) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2907.9 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G1

Input Watts (W): 24.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148079

CATALOG NUMBER: AVS-E01-LED-E-U-5WQ-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 1.8 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P148079

CATALOG NUMBER: AVS-E01-LED-E-U-5WQ-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P148079

CATALOG NUMBER: AVS-E01-LED-E-U-5WQ-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1454.0	0.0	1454.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1454.0	0.0	1454.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	2907.9	0.0	2907.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.2	0.5
10°-20°	53.5	1.8
20°-30°	108.4	3.7
30°-40°	181.8	6.3
40°-50°	320.6	11.0
50°-60°	565.4	19.4
60°-70°	863.2	29.7
70°-80°	721.3	24.8
80°-90°	78.4	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2907.9	100.0
0°-180°	2907.9	100.0

Coefficient of Utilization



REPORT NUMBER: P148079


CATALOG NUMBER: AVS-E01-LED-E-U-5WQ-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	88.6	3.0			
FM	(30°-60°)	533.9	18.4			
FH	(60°-80°)	792.3	27.2			G1/1800
FVH	(80°-90°)	39.2	1.3			G1/100
BL	(0°-30°)	88.6	3.0	B0/110		
BM	(30°-60°)	533.9	18.4	B1/1000		
BH	(60°-80°)	792.3	27.2	B2/1000		G1/1800
BVH	(80°-90°)	39.2	1.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type V Short





REPORT NUMBER: P148079

CATALOG NUMBER: AVS-E01-LED-E-U-5WQ-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	151.0	151.0	151.0	151.0	151.0	151.0	151.0	151.0	151.0	151.0	151.0
2.5°	152.2	152.5	152.2	152.2	152.2	152.2	152.2	151.9	151.9	151.9	152.2
5°	155.2	155.5	155.2	155.5	155.5	155.5	155.5	155.2	155.2	155.2	155.2
7.5°	160.1	160.1	160.1	160.4	160.1	160.1	160.4	160.1	160.1	160.1	160.1
10°	167.2	166.8	166.8	166.8	166.8	166.8	167.2	167.2	167.2	166.8	166.8
12.5°	175.6	175.3	175.6	175.6	176.0	176.0	176.0	176.0	176.0	176.0	175.6
15°	186.0	186.0	186.0	186.3	186.9	186.9	186.6	186.9	186.9	186.9	186.9
17.5°	197.6	198.2	197.6	197.9	198.2	197.9	198.5	198.8	199.1	198.8	197.9
20°	209.4	209.7	209.7	209.7	209.7	210.4	210.7	210.7	211.6	211.3	211.0
22.5°	220.7	221.3	221.3	221.7	221.7	222.6	222.6	222.6	223.2	223.7	223.2
25°	232.6	232.3	232.3	233.0	233.2	234.4	234.4	235.0	236.0	236.3	235.6
27.5°	243.2	242.9	242.9	243.8	244.1	245.7	245.7	246.9	247.6	247.8	247.3
30°	254.5	254.5	254.2	255.1	256.1	257.3	257.8	259.1	260.0	260.3	259.7
32.5°	267.9	267.4	267.6	268.2	268.8	270.1	271.0	272.4	273.7	274.0	273.4
35°	283.1	282.2	282.5	283.1	284.0	285.9	287.4	288.3	290.2	290.8	289.5
37.5°	299.9	300.2	299.9	301.5	302.9	305.1	306.8	308.1	309.9	310.9	309.9
40°	323.6	322.7	323.6	325.2	327.6	330.4	334.0	334.9	336.7	338.5	336.4
42.5°	354.4	353.8	355.9	357.1	359.9	362.9	367.5	369.9	372.6	373.9	372.0
45°	394.6	394.6	397.0	397.3	401.6	405.5	411.9	414.9	420.1	420.1	420.1
47.5°	439.1	440.8	442.4	445.4	448.5	455.8	462.2	468.8	473.7	474.3	473.5
50°	485.0	486.8	491.4	495.6	502.4	511.5	518.4	527.4	531.6	535.2	534.0
52.5°	535.9	536.2	541.7	547.0	556.8	566.8	578.1	587.3	594.9	598.2	595.5
55°	591.5	592.1	597.0	602.8	613.8	625.4	639.4	648.8	658.5	664.7	660.0
57.5°	651.8	652.1	657.0	664.0	677.1	688.7	702.1	715.4	724.6	730.1	727.0
60°	718.5	720.0	723.6	732.5	745.0	757.2	770.6	782.5	793.1	798.9	795.9
62.5°	789.7	791.3	796.5	803.4	814.4	827.8	840.6	855.9	864.7	871.0	866.4
65°	837.5	840.3	848.5	857.9	874.1	891.4	906.3	927.0	937.7	945.3	941.0
67.5°	840.6	842.1	852.1	866.4	888.1	914.3	944.7	977.0	998.0	1008.1	1000.7
69°	819.9	822.0	831.7	847.9	871.9	902.4	938.7	978.8	1011.1	1026.0	1019.0
70°	796.5	801.0	811.7	829.3	852.7	884.8	922.2	965.1	1002.9	1023.2	1018.0
72.5°	747.2	748.3	755.3	769.3	787.4	813.8	849.1	889.6	925.5	954.7	959.1
75°	663.1	667.0	672.2	681.7	690.8	709.9	733.7	761.5	782.5	805.0	805.9
77.5°	501.1	513.0	517.0	519.1	523.0	538.2	559.0	583.0	600.4	604.0	603.4
80°	225.0	240.8	244.5	261.9	272.4	297.7	329.4	366.2	390.9	393.7	386.9
82.5°	44.1	47.2	55.1	68.8	93.8	108.7	129.4	155.2	179.1	192.7	184.5
85°	14.6	15.5	17.9	19.8	22.8	25.9	31.4	39.0	48.4	53.6	47.8
87.5°	5.8	5.8	6.7	7.4	7.9	7.9	7.9	7.4	7.0	5.8	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148079

CATALOG NUMBER: AVS-E01-LED-E-U-5WQ-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	151.0	151.0	151.0	151.0	151.0	151.0	151.0	151.0
2.5°	151.9	151.9	151.9	151.9	151.9	151.9	151.9	151.9
5°	155.2	154.9	154.9	154.6	154.6	154.6	154.6	154.6
7.5°	159.8	159.5	159.3	159.5	159.3	159.3	159.3	159.3
10°	166.8	166.2	165.9	165.6	165.6	165.6	165.3	165.3
12.5°	175.0	175.0	174.7	174.4	173.9	174.2	173.9	173.3
15°	186.3	185.7	185.4	185.1	184.5	184.5	184.5	184.1
17.5°	197.6	197.0	197.0	196.1	195.8	195.8	195.8	196.1
20°	210.1	209.1	208.5	208.0	207.4	207.7	207.0	207.7
22.5°	222.6	221.3	220.7	219.8	218.9	218.9	218.5	218.0
25°	234.7	233.2	232.6	231.7	230.5	230.5	229.8	229.2
27.5°	246.3	244.8	244.1	242.4	241.1	240.8	240.2	239.9
30°	259.1	257.3	256.4	254.5	252.6	252.4	251.5	251.5
32.5°	272.4	270.7	270.1	267.4	265.8	265.8	265.2	264.6
35°	289.2	286.5	285.9	283.1	281.0	281.0	280.4	280.7
37.5°	309.0	306.8	304.8	302.6	300.2	299.9	299.3	298.7
40°	335.5	333.1	330.7	327.6	325.5	324.9	323.9	323.6
42.5°	370.8	368.4	363.5	361.0	359.0	357.1	356.8	356.5
45°	415.9	412.8	409.5	404.9	402.2	398.2	397.6	396.1
47.5°	470.1	464.2	458.5	454.5	450.3	445.7	444.8	442.4
50°	527.6	523.0	513.3	506.9	500.2	495.6	492.6	491.7
52.5°	589.4	580.9	571.2	562.6	552.8	546.8	541.3	539.8
55°	654.0	641.8	629.6	619.6	609.8	602.5	597.3	594.9
57.5°	718.5	705.1	691.7	680.7	672.5	663.1	657.9	656.7
60°	785.8	773.0	759.3	748.3	738.3	730.1	727.0	721.2
62.5°	857.0	843.6	830.9	820.2	807.4	801.7	796.5	793.1
65°	927.0	911.5	895.3	884.1	871.3	863.1	856.7	852.1
67.5°	981.2	957.8	936.2	917.3	900.0	887.2	879.0	874.7
69°	996.5	967.3	939.5	914.9	894.5	880.2	871.0	866.7
70°	994.6	962.4	931.9	904.9	882.6	867.4	858.5	850.7
72.5°	938.3	908.8	875.0	845.5	825.4	810.8	802.0	797.6
75°	800.7	780.9	756.6	733.7	719.1	710.6	699.6	699.9
77.5°	583.0	583.6	567.2	543.7	527.4	524.2	519.4	514.5
80°	361.7	332.7	313.9	288.6	270.1	253.9	246.9	231.7
82.5°	166.8	130.3	101.0	76.4	58.8	46.0	40.2	32.8
85°	37.1	28.3	23.4	18.9	16.2	14.9	12.2	11.3
87.5°	5.2	4.6	4.2	3.9	3.3	2.5	1.9	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)