

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155845

Luminaire Tested: **AVS-F04-LED-E-U-T3**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155845
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-T3
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (28) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10183.4 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P155845

CATALOG NUMBER: AVS-F04-LED-E-U-T3

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 2.7 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155845

CATALOG NUMBER: AVS-F04-LED-E-U-T3

Luminous Intensity Polar Plot



REPORT NUMBER: P155845

CATALOG NUMBER: AVS-F04-LED-E-U-T3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3516.7	0.0	3516.7
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	6666.8	0.0	6666.8
	% Fixture	65.5	0.0	65.5
Total	Lumens	10183.4	0.0	10183.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.1	1.0
10°-20°	310.2	3.0
20°-30°	533.1	5.2
30°-40°	865.6	8.5
40°-50°	1445.2	14.2
50°-60°	2275.7	22.3
60°-70°	3103.1	30.5
70°-80°	1343.3	13.2
80°-90°	202.0	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10183.4	100.0
0°-180°	10183.4	100.0

Coefficient of Utilization



REPORT NUMBER: P155845


CATALOG NUMBER: AVS-F04-LED-E-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	476.4	4.7			
FM	(30°-60°)	2843.9	27.9			
FH	(60°-80°)	3180.6	31.2			G2/5000
FVH	(80°-90°)	165.9	1.6			G2/225
BL	(0°-30°)	472.0	4.6	B1/500		
BM	(30°-60°)	1742.6	17.1	B2/2500		
BH	(60°-80°)	1265.8	12.4	B3/2500		G3/2500
BVH	(80°-90°)	36.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P155845

CATALOG NUMBER: AVS-F04-LED-E-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4
2.5°	1101.8	1106.2	1101.8	1102.9	1104.0	1102.9	1101.8	1101.8	1098.5	1100.7	1102.9
5°	1097.4	1100.7	1099.6	1100.7	1101.8	1100.7	1099.6	1100.7	1098.5	1099.6	1102.9
7.5°	1091.9	1090.8	1091.9	1094.1	1096.3	1096.3	1096.3	1097.4	1096.3	1096.3	1099.6
10°	1075.3	1076.5	1078.7	1082.0	1083.1	1086.4	1086.4	1089.7	1090.8	1093.0	1097.4
12.5°	1054.5	1055.5	1057.8	1060.0	1065.5	1071.0	1071.0	1078.7	1082.0	1087.5	1095.2
15°	1039.1	1040.2	1042.4	1044.6	1049.0	1054.5	1057.8	1066.5	1072.1	1082.0	1093.0
17.5°	1047.9	1046.7	1049.0	1050.1	1050.1	1054.5	1054.5	1061.0	1067.7	1076.5	1090.8
20°	1073.2	1073.2	1075.3	1075.3	1074.3	1076.5	1072.1	1072.1	1073.2	1077.6	1087.5
22.5°	1098.5	1097.4	1101.8	1104.0	1105.1	1108.4	1104.0	1102.9	1097.4	1094.1	1097.4
25°	1122.7	1121.7	1127.2	1130.5	1136.0	1139.3	1139.3	1139.3	1134.8	1129.3	1126.0
27.5°	1160.1	1160.1	1165.6	1168.9	1173.4	1180.0	1183.2	1183.2	1184.4	1176.7	1171.2
30°	1222.9	1223.9	1225.1	1229.4	1233.9	1236.1	1240.5	1243.8	1247.0	1242.7	1233.9
32.5°	1297.7	1291.1	1291.1	1297.7	1303.2	1309.8	1312.0	1316.5	1323.0	1319.7	1318.7
35°	1386.8	1384.7	1382.5	1384.7	1391.3	1399.0	1407.8	1415.5	1411.1	1417.7	1414.4
37.5°	1519.0	1521.1	1522.3	1522.3	1521.1	1523.4	1527.8	1535.4	1533.3	1535.4	1539.9
40°	1736.9	1729.2	1721.5	1722.6	1711.6	1713.8	1696.2	1703.8	1705.0	1697.3	1700.6
42.5°	1954.8	1959.3	1962.6	1971.4	1963.6	1959.3	1942.7	1942.7	1933.9	1926.2	1924.0
45°	2190.4	2199.2	2200.3	2217.9	2211.3	2225.6	2237.7	2234.4	2220.1	2219.0	2203.6
47.5°	2378.7	2393.0	2408.3	2429.2	2445.8	2477.7	2515.1	2533.8	2544.8	2553.6	2536.1
50°	2519.5	2526.1	2565.7	2598.8	2635.0	2687.9	2739.7	2806.7	2860.7	2886.0	2910.3
52.5°	2595.4	2611.9	2654.9	2706.6	2770.5	2849.7	2933.4	3040.1	3132.6	3194.2	3249.2
55°	2611.9	2628.5	2676.9	2742.9	2829.9	2936.7	3056.7	3202.0	3340.6	3459.5	3575.0
57.5°	2565.7	2584.5	2636.2	2712.1	2814.5	2944.4	3095.1	3285.6	3477.1	3669.7	3840.3
60°	2480.9	2504.0	2551.4	2626.3	2739.7	2886.0	3066.5	3305.4	3574.0	3868.9	4195.9
62.5°	2341.1	2365.4	2409.4	2492.0	2608.7	2770.5	2979.6	3276.8	3656.5	4121.0	4701.1
65°	2116.7	2127.7	2181.6	2265.3	2368.7	2547.0	2777.1	3135.9	3630.2	4276.3	5075.3
66°	2015.3	2034.1	2067.2	2134.3	2233.4	2400.6	2631.8	2996.1	3529.9	4222.3	5065.4
67.5°	1856.9	1871.2	1893.2	1938.3	1998.9	2122.2	2341.1	2685.7	3223.9	3949.3	4855.2
70°	1501.3	1508.0	1537.7	1553.1	1574.0	1614.7	1694.0	1892.1	2311.5	2992.8	3918.4
72.5°	1023.6	1042.4	1074.3	1118.3	1175.5	1230.6	1268.0	1293.4	1383.6	1785.3	2610.9
75°	750.7	770.5	811.2	869.5	969.7	1084.1	1203.1	1258.1	1220.7	1168.9	1454.0
77.5°	435.9	462.3	496.4	552.5	645.0	796.9	1000.5	1181.0	1303.2	1311.0	1244.9
80°	183.8	187.2	208.1	236.7	293.9	400.6	559.2	819.0	1089.7	1272.4	1315.3
82.5°	41.9	51.7	66.0	78.1	95.8	132.1	196.0	325.8	588.9	923.5	1204.1
85°	15.4	15.4	20.9	30.8	35.2	39.6	51.7	82.6	140.9	259.8	541.6
87.5°	0.0	1.1	2.2	2.2	4.4	5.5	8.8	12.1	11.0	9.9	33.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155845

CATALOG NUMBER: AVS-F04-LED-E-U-T3

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4
2.5°	1100.7	1099.6	1097.4	1097.4	1097.4	1097.4	1095.2	1096.3	1094.1	1095.2	1095.2
5°	1099.6	1099.6	1098.5	1096.3	1097.4	1097.4	1098.5	1096.3	1096.3	1097.4	1096.3
7.5°	1099.6	1098.5	1098.5	1098.5	1099.6	1098.5	1099.6	1099.6	1099.6	1100.7	1100.7
10°	1099.6	1099.6	1101.8	1102.9	1102.9	1104.0	1107.3	1107.3	1108.4	1109.5	1111.7
12.5°	1100.7	1105.1	1108.4	1111.7	1112.8	1115.0	1120.5	1120.5	1122.7	1126.0	1127.2
15°	1101.8	1108.4	1115.0	1117.2	1119.4	1123.8	1129.3	1131.5	1134.8	1138.1	1140.3
17.5°	1100.7	1109.5	1117.2	1120.5	1123.8	1129.3	1136.0	1138.1	1142.5	1146.9	1151.3
20°	1099.6	1111.7	1123.8	1128.2	1132.6	1140.3	1149.1	1154.6	1159.1	1165.6	1170.1
22.5°	1106.2	1120.5	1137.0	1143.6	1151.3	1161.2	1173.4	1180.0	1185.5	1192.0	1195.3
25°	1127.2	1138.1	1157.9	1168.9	1178.9	1195.3	1211.9	1219.6	1226.2	1231.7	1232.7
27.5°	1162.4	1165.6	1189.8	1204.1	1218.4	1244.9	1264.7	1270.3	1282.3	1286.7	1285.6
30°	1219.6	1214.1	1233.9	1255.9	1276.8	1313.2	1337.3	1351.7	1362.7	1362.7	1353.9
32.5°	1302.2	1293.4	1298.9	1324.1	1348.4	1401.1	1429.8	1448.5	1456.3	1454.0	1435.3
35°	1409.9	1404.5	1401.1	1421.0	1459.5	1521.1	1558.5	1568.5	1580.6	1578.4	1554.2
37.5°	1537.7	1533.3	1533.3	1556.4	1593.8	1685.2	1725.9	1732.5	1731.4	1713.8	1668.7
40°	1688.5	1686.3	1676.4	1689.5	1721.5	1840.4	1895.4	1904.2	1892.1	1863.5	1810.7
42.5°	1905.3	1892.1	1861.2	1869.0	1893.2	2008.8	2080.3	2104.6	2092.4	2063.8	1977.9
45°	2188.2	2173.9	2122.2	2115.5	2128.7	2230.1	2322.5	2328.0	2325.8	2289.4	2188.2
47.5°	2520.6	2498.5	2443.5	2425.9	2421.6	2515.1	2604.2	2613.1	2607.6	2553.6	2418.2
50°	2880.5	2848.6	2812.3	2800.2	2782.6	2849.7	2940.0	2941.0	2919.1	2844.2	2717.6
52.5°	3264.7	3253.7	3247.0	3234.9	3227.3	3285.6	3340.6	3307.6	3274.6	3196.5	3086.3
55°	3652.1	3697.2	3743.5	3747.9	3761.1	3823.8	3822.7	3732.4	3708.3	3665.3	3556.4
57.5°	4063.8	4231.1	4376.4	4421.6	4465.5	4582.2	4571.2	4482.1	4451.2	4398.4	4308.2
60°	4624.0	5075.3	5494.7	5594.8	5664.2	5804.0	5790.8	5653.2	5717.0	5712.6	5596.0
62.5°	5408.8	6159.5	6788.0	6942.1	6990.6	7005.9	6922.3	6773.7	6836.5	6906.9	6548.1
65°	5940.5	6823.2	7468.3	7587.2	7593.7	7409.9	7223.9	7048.9	7033.5	6973.0	6460.0
66°	5952.5	6856.3	7503.4	7619.1	7578.3	7327.4	7091.8	6915.6	6839.8	6706.5	6174.9
67.5°	5739.1	6650.5	7347.2	7469.3	7380.2	7024.7	6700.0	6473.3	6324.7	6108.9	5640.0
70°	4820.0	5723.6	6582.2	6810.1	6838.7	6308.1	5857.9	5591.6	5391.2	5095.1	4691.2
72.5°	3583.8	4400.6	5157.9	5375.9	5486.9	5063.2	4683.5	4480.9	4206.8	3895.3	3608.1
75°	2246.5	2823.3	3330.7	3483.7	3379.2	3051.2	2823.3	2738.5	2468.9	2282.9	2151.9
77.5°	1284.6	1465.1	1505.8	1447.5	1324.1	1013.8	720.9	533.9	463.4	513.0	565.8
80°	1253.7	1149.1	915.8	805.7	729.7	502.0	295.0	202.5	168.4	172.8	187.2
82.5°	1358.2	1457.3	1199.8	978.5	821.1	554.7	306.0	162.9	110.1	129.8	146.4
85°	882.8	1228.4	1106.2	932.3	755.1	474.4	252.0	84.8	56.2	73.8	101.2
87.5°	89.1	97.9	83.6	113.4	84.8	39.6	19.8	12.1	11.0	13.2	19.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155845

CATALOG NUMBER: AVS-F04-LED-E-U-T3

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4	1097.4
2.5°	1096.3	1096.3	1097.4	1098.5	1099.6	1100.7	1100.7	1100.7	1100.7	1102.9	1101.8
5°	1098.5	1100.7	1102.9	1104.0	1106.2	1106.2	1109.5	1108.4	1108.4	1111.7	1112.8
7.5°	1102.9	1106.2	1110.6	1109.5	1113.9	1112.8	1115.0	1115.0	1111.7	1112.8	1110.6
10°	1112.8	1117.2	1119.4	1116.1	1117.2	1112.8	1111.7	1106.2	1099.6	1096.3	1091.9
12.5°	1129.3	1133.7	1133.7	1128.2	1121.7	1111.7	1104.0	1091.9	1082.0	1076.5	1071.0
15°	1143.6	1148.0	1146.9	1138.1	1128.2	1112.8	1101.8	1087.5	1073.2	1064.4	1058.9
17.5°	1154.6	1156.8	1153.6	1141.5	1130.5	1116.1	1105.1	1089.7	1073.2	1062.2	1052.2
20°	1171.2	1168.9	1161.2	1145.8	1133.7	1120.5	1111.7	1098.5	1079.8	1065.5	1051.2
22.5°	1195.3	1186.5	1172.2	1155.8	1143.6	1131.5	1122.7	1108.4	1089.7	1072.1	1055.5
25°	1227.3	1209.6	1189.8	1172.2	1161.2	1148.0	1138.1	1122.7	1102.9	1083.1	1063.3
27.5°	1273.5	1242.7	1217.4	1202.0	1189.8	1173.4	1161.2	1141.5	1120.5	1097.4	1075.3
30°	1325.3	1283.4	1259.2	1247.0	1233.9	1216.3	1197.5	1172.2	1148.0	1122.7	1096.3
32.5°	1392.4	1341.8	1318.7	1306.5	1288.9	1266.9	1244.9	1216.3	1182.2	1149.1	1117.2
35°	1480.4	1428.7	1404.5	1385.8	1361.6	1333.0	1301.0	1262.5	1216.3	1172.2	1131.5
37.5°	1575.1	1519.0	1495.9	1476.1	1439.7	1402.3	1357.2	1301.0	1238.2	1180.0	1129.3
40°	1695.1	1643.3	1613.6	1579.5	1536.6	1471.6	1401.1	1319.7	1239.4	1167.9	1108.4
42.5°	1846.9	1795.2	1751.2	1697.3	1622.4	1522.3	1422.1	1316.5	1219.6	1138.1	1074.3
45°	2048.4	1985.7	1909.7	1815.0	1694.0	1554.2	1423.2	1295.5	1182.2	1091.9	1023.6
47.5°	2294.9	2199.2	2074.8	1915.2	1741.3	1563.0	1405.6	1253.7	1123.8	1025.8	949.9
50°	2587.8	2437.0	2232.2	1997.7	1765.5	1549.7	1361.6	1191.0	1041.2	936.7	846.4
52.5°	2922.4	2675.8	2374.2	2057.2	1764.5	1505.8	1286.7	1096.3	933.4	816.7	730.9
55°	3315.3	2948.8	2520.6	2101.2	1733.6	1424.4	1172.2	963.1	800.2	692.3	613.1
57.5°	3891.0	3391.3	2776.0	2169.4	1671.9	1298.9	1017.1	803.5	660.4	558.0	490.9
60°	4943.2	4129.8	3236.1	2307.0	1577.3	1115.0	835.4	633.0	513.0	430.4	385.3
62.5°	5735.8	4701.1	3484.8	2276.3	1386.8	888.3	619.7	461.2	377.5	321.5	292.7
65°	5622.4	4523.8	3219.6	1960.3	1087.5	626.3	411.7	313.7	259.8	233.4	216.8
66°	5365.9	4292.7	2989.5	1764.5	940.0	520.6	339.1	263.1	223.4	204.8	193.7
67.5°	4879.4	3863.4	2577.8	1446.3	722.1	377.5	255.3	208.1	181.7	173.9	166.2
70°	4056.1	3080.8	1809.5	842.1	368.7	210.3	161.8	145.3	138.7	137.6	135.3
72.5°	3108.4	2180.5	1065.5	398.4	191.5	139.8	125.5	120.0	117.8	117.8	118.9
75°	1905.3	1225.1	471.1	194.8	134.3	117.8	111.2	109.0	107.9	109.0	107.9
77.5°	636.2	389.6	201.5	147.5	122.2	109.0	104.6	102.4	102.4	102.4	102.4
80°	194.8	169.5	154.1	136.5	115.5	103.4	96.9	95.8	96.9	97.9	94.6
82.5°	146.4	138.7	129.8	121.0	104.6	92.4	90.3	90.3	90.3	86.9	82.6
85°	107.9	106.7	88.1	82.6	77.1	77.1	77.1	77.1	73.8	68.3	63.8
87.5°	19.8	18.8	19.8	20.9	30.8	33.1	33.1	35.2	38.5	36.4	36.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P155845

CATALOG NUMBER: AVS-F04-LED-E-U-T3

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1097.4	1097.4	1097.4	1097.4	1097.4
2.5°	1101.8	1100.7	1104.0	1101.8	1102.9
5°	1111.7	1110.6	1112.8	1110.6	1113.9
7.5°	1108.4	1106.2	1105.1	1106.2	1107.3
10°	1085.3	1083.1	1082.0	1080.9	1082.0
12.5°	1065.5	1061.0	1061.0	1058.9	1060.0
15°	1051.2	1047.9	1046.7	1044.6	1045.7
17.5°	1044.6	1039.1	1036.9	1034.6	1034.6
20°	1040.2	1033.6	1030.3	1028.1	1026.9
22.5°	1040.2	1030.3	1025.8	1023.6	1022.6
25°	1044.6	1032.4	1025.8	1022.6	1021.5
27.5°	1053.4	1037.9	1030.3	1025.8	1025.8
30°	1068.8	1049.0	1037.9	1032.4	1031.4
32.5°	1084.1	1057.8	1042.4	1035.8	1033.6
35°	1091.9	1057.8	1039.1	1028.1	1025.8
37.5°	1083.1	1043.4	1020.3	1003.8	1000.5
40°	1055.5	1013.8	988.4	973.1	970.8
42.5°	1019.3	978.5	948.8	937.8	934.5
45°	969.7	921.2	891.6	876.2	877.3
47.5°	885.0	835.4	809.0	794.7	796.9
50°	784.8	736.4	713.3	697.8	701.1
52.5°	674.7	630.7	608.7	600.9	598.8
55°	559.2	525.1	509.6	500.8	497.5
57.5°	453.5	429.2	418.2	407.3	408.4
60°	357.7	345.6	342.3	330.3	329.1
62.5°	281.8	274.1	270.8	262.0	263.1
65°	213.6	211.3	213.6	208.1	210.3
66°	192.6	193.7	193.7	190.5	192.6
67.5°	166.2	168.4	171.7	168.4	170.6
70°	137.6	139.8	142.0	142.0	142.0
72.5°	120.0	122.2	123.3	123.3	123.3
75°	110.1	111.2	112.2	110.1	110.1
77.5°	103.4	103.4	101.2	100.2	99.1
80°	93.6	92.4	89.1	86.9	86.9
82.5°	78.1	76.0	73.8	70.5	70.5
85°	59.5	57.2	55.0	50.7	48.4
87.5°	30.8	31.9	30.8	25.3	22.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)