

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P153729

Luminaire Tested: **AVS-E01-LED-E-U-SLR-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P153729
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33681)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E01-LED-E-U-SLR-7030
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - 90° SPILL LIGHT ELIMINATOR RIGHT
Light Source: (21) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2541.4 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type IV - Short - Non-Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 24.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P153729

CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4 fc
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P153729

CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P153729

CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	551.1	0.0	551.1
	% Fixture	21.7	0.0	21.7
Street Side	Lumens	1990.3	0.0	1990.3
	% Fixture	78.3	0.0	78.3
Total	Lumens	2541.4	0.0	2541.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.1	1.2
10°-20°	96.8	3.8
20°-30°	172.0	6.8
30°-40°	270.9	10.7
40°-50°	398.6	15.7
50°-60°	529.5	20.8
60°-70°	583.3	23.0
70°-80°	365.9	14.4
80°-90°	93.2	3.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2541.4	100.0
0°-180°	2541.4	100.0

Coefficient of Utilization



REPORT NUMBER: P153729


CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	162.7	6.4			
FM	(30°-60°)	923.6	36.3			
FH	(60°-80°)	822.2	32.4			G1/1800
FVH	(80°-90°)	81.8	3.2			G1/100
BL	(0°-30°)	137.2	5.4	B1/500		
BM	(30°-60°)	275.4	10.8	B1/1000		
BH	(60°-80°)	127.0	5.0	B1/500		G1/500
BVH	(80°-90°)	11.4	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P153729

CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4
2.5°	315.1	316.1	315.8	315.8	316.4	316.1	316.1	316.4	316.4	317.2	318.4
5°	312.6	312.3	311.7	312.3	312.3	312.3	311.2	312.0	312.3	313.0	313.0
7.5°	315.8	314.8	313.6	313.9	313.9	313.3	312.3	312.6	312.3	312.3	312.0
10°	319.7	317.5	316.1	316.1	316.1	315.4	313.9	314.8	314.8	314.5	314.8
12.5°	326.6	324.2	322.4	321.8	321.8	320.9	319.7	320.9	320.3	320.3	319.7
15°	338.2	335.5	333.4	331.5	331.8	331.8	330.4	329.4	328.2	326.6	323.6
17.5°	355.6	352.5	349.8	348.3	348.6	346.4	342.2	337.9	332.1	326.3	320.0
20°	380.2	379.4	375.6	374.2	370.5	365.4	353.5	343.4	332.1	321.2	310.3
22.5°	422.9	418.7	414.9	409.2	397.0	382.7	362.9	345.3	327.6	312.0	297.4
25°	480.1	472.5	454.5	436.9	411.9	386.3	359.6	336.7	314.8	294.4	276.5
27.5°	536.5	513.3	481.3	449.3	412.8	379.4	345.9	318.8	293.2	271.0	251.2
30°	604.7	565.7	516.7	466.1	414.4	369.3	329.1	297.4	267.9	244.5	223.7
32.5°	668.6	612.2	548.0	481.7	417.7	359.9	309.9	274.0	243.5	214.0	193.7
35°	712.4	639.4	561.5	483.2	409.5	341.9	285.9	243.5	213.2	185.7	161.7
37.5°	738.5	651.2	562.0	472.2	390.3	317.5	255.4	213.4	185.4	159.3	140.3
40°	755.0	654.0	554.1	456.4	365.9	286.8	225.0	187.3	161.7	140.6	126.0
42.5°	762.9	649.7	541.3	436.3	341.2	259.4	203.6	168.1	145.8	130.9	120.0
45°	764.1	642.1	527.6	418.0	319.4	239.6	189.0	160.1	141.9	129.4	118.4
47.5°	764.1	635.3	516.7	404.7	305.1	231.1	187.9	163.5	145.5	131.5	118.4
50°	764.8	633.3	512.1	397.9	300.2	235.6	198.2	173.9	153.5	135.1	118.1
52.5°	767.6	636.0	515.8	403.1	309.0	253.9	217.7	189.3	163.8	139.5	118.1
55°	773.6	645.2	531.3	421.0	332.7	281.7	241.1	206.1	172.0	141.2	116.3
57.5°	790.7	668.3	559.6	455.8	373.3	313.6	262.5	218.0	175.0	139.8	112.6
60°	824.8	714.2	608.0	504.5	416.2	340.9	274.9	219.8	172.3	134.9	106.8
62.5°	879.3	766.9	666.7	557.4	454.2	356.2	276.5	215.2	165.0	126.0	98.3
63°	898.1	780.0	679.3	567.5	459.1	357.4	275.2	213.4	163.2	123.6	97.1
65°	950.8	835.1	722.5	602.8	472.8	357.7	268.5	204.2	154.6	114.2	88.6
67.5°	1049.1	907.6	777.0	630.5	477.7	348.0	251.5	187.3	136.7	99.6	77.9
70°	1111.2	948.1	797.9	631.1	463.4	320.3	222.0	159.5	113.9	82.5	66.9
72.5°	1095.1	908.2	742.6	574.2	401.6	267.6	178.4	125.4	88.9	66.1	55.8
75°	938.0	756.0	605.9	444.8	303.5	196.7	130.6	89.5	65.8	51.7	46.6
77.5°	675.2	544.0	434.4	316.9	204.6	127.3	86.7	63.9	49.9	42.6	38.3
80°	430.2	319.1	265.8	190.6	119.7	78.9	59.7	48.4	41.1	35.6	32.8
82.5°	224.7	157.4	127.9	97.4	66.3	52.0	43.8	39.6	33.8	29.5	28.0
85°	140.0	92.8	68.8	48.1	33.2	29.8	27.4	26.8	24.0	21.3	20.4
87.5°	15.9	14.3	14.9	9.4	7.0	7.6	7.4	9.7	9.4	7.0	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153729

CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4
2.5°	317.2	317.8	317.8	318.8	318.8	319.4	320.0	320.0	320.6	320.9	321.5
5°	313.6	313.6	313.6	314.8	315.1	316.9	317.5	318.1	318.8	320.9	322.1
7.5°	312.6	311.5	312.0	312.0	313.0	314.5	316.1	316.9	317.8	320.6	322.4
10°	314.5	313.6	312.6	312.6	313.0	313.6	314.8	315.8	316.4	319.1	320.6
12.5°	319.4	317.2	315.4	313.9	312.6	312.3	311.7	312.0	312.6	314.2	316.4
15°	320.3	316.4	312.3	308.4	305.4	303.5	302.0	301.5	301.5	302.3	304.8
17.5°	314.2	307.5	301.8	296.6	293.2	289.8	288.3	287.0	286.5	287.7	288.0
20°	301.1	293.2	285.3	279.2	273.1	272.2	269.7	270.4	271.0	272.7	273.7
22.5°	283.1	273.7	263.9	257.6	252.6	248.4	245.7	246.9	247.8	249.6	250.6
25°	261.2	247.6	237.2	230.8	225.6	222.0	218.9	220.1	218.9	221.0	224.4
27.5°	235.3	219.2	208.3	200.9	197.3	194.2	191.2	191.2	194.2	194.2	197.0
30°	203.9	192.1	177.8	170.2	165.6	163.8	163.5	162.9	165.0	166.2	169.2
32.5°	174.4	159.8	146.1	138.9	134.9	132.7	133.1	133.4	134.3	136.1	140.9
35°	144.7	131.8	122.1	113.9	109.9	105.9	105.9	105.4	106.2	108.4	114.2
37.5°	125.4	114.2	106.5	100.2	96.2	93.8	91.6	90.8	90.8	91.6	93.8
40°	114.8	106.5	99.6	94.1	90.5	88.3	87.0	86.1	85.6	85.6	85.9
42.5°	109.9	101.3	94.4	89.5	86.7	85.6	85.3	85.0	84.0	83.7	83.4
45°	107.5	97.7	89.8	85.9	83.7	83.1	83.4	83.4	83.1	82.5	81.2
47.5°	105.6	94.4	86.4	82.8	81.9	81.9	81.9	81.9	81.6	81.2	80.4
50°	102.6	89.2	80.7	77.9	77.3	77.3	77.6	77.6	78.2	77.6	77.0
52.5°	99.3	84.4	75.9	73.4	73.1	72.7	72.7	72.7	73.1	73.1	72.7
55°	95.6	80.7	73.4	71.5	71.8	71.5	71.2	71.0	71.0	70.7	70.1
57.5°	91.9	77.6	71.5	70.4	70.7	70.7	70.1	69.4	69.1	68.2	67.6
60°	86.4	73.4	67.9	67.3	68.2	68.2	68.2	67.9	67.9	67.6	66.1
62.5°	79.2	67.3	63.0	63.3	63.6	64.2	64.2	64.2	64.2	63.6	62.1
63°	77.6	66.1	62.1	62.1	63.0	63.0	63.3	63.0	63.3	62.7	60.9
65°	71.5	62.1	59.1	59.4	60.0	60.0	60.0	59.7	59.7	58.8	57.8
67.5°	64.6	57.2	55.4	55.8	56.1	56.6	56.4	56.4	56.6	56.1	55.1
70°	56.6	52.0	50.9	51.2	51.5	51.5	51.2	51.2	51.5	50.9	49.9
72.5°	50.6	48.7	47.8	47.8	47.2	47.2	46.6	46.3	46.0	46.0	45.1
75°	42.6	42.3	42.6	43.2	42.6	42.0	41.7	40.8	40.2	40.2	39.9
77.5°	36.6	36.6	37.1	38.0	38.3	38.3	37.4	36.0	35.6	35.6	35.6
80°	31.7	31.1	31.1	31.9	32.8	32.5	31.1	29.5	29.5	31.1	31.4
82.5°	27.7	27.7	26.8	27.0	26.8	26.5	25.0	24.0	23.7	25.0	26.2
85°	22.0	22.2	22.0	21.7	21.3	20.4	19.2	18.2	17.9	19.2	21.0
87.5°	8.8	8.5	8.2	8.5	8.2	8.8	8.5	7.9	7.6	8.5	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153729

CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4
2.5°	321.8	322.4	323.0	323.0	323.6	323.3	323.6	323.9	323.9	324.2	324.2
5°	323.6	324.6	325.8	326.9	327.3	328.2	329.1	328.5	329.4	330.7	330.7
7.5°	324.2	326.3	327.3	329.1	329.4	330.7	332.7	331.2	333.1	334.0	334.3
10°	323.3	325.5	326.9	329.1	330.1	332.1	334.3	333.7	335.9	337.3	337.6
12.5°	317.8	320.0	323.3	326.3	328.8	332.1	336.1	334.9	337.9	339.8	340.7
15°	307.2	309.3	313.0	317.8	322.4	327.6	332.7	333.7	336.7	338.9	339.8
17.5°	290.5	293.2	297.1	302.3	308.1	316.9	323.6	326.9	331.2	332.4	334.0
20°	274.9	277.6	280.1	283.1	287.4	296.0	304.8	311.5	316.9	321.5	322.7
22.5°	254.2	256.7	259.7	262.2	265.2	271.3	278.5	286.2	294.7	297.4	300.5
25°	229.2	230.8	235.0	236.6	238.7	243.8	249.6	255.1	263.3	269.1	270.7
27.5°	202.5	203.9	208.0	208.8	211.6	216.5	220.7	222.9	230.5	236.6	241.5
30°	171.4	175.3	180.2	180.8	183.9	186.9	190.9	193.1	200.0	206.4	212.5
32.5°	144.7	148.6	152.5	154.9	156.5	159.0	162.9	165.0	171.7	177.5	183.6
35°	117.2	122.1	126.3	129.7	130.9	134.0	137.0	139.2	146.1	151.3	155.5
37.5°	96.5	100.2	104.8	108.1	111.4	113.6	117.2	120.2	124.6	127.3	131.8
40°	86.4	88.3	90.8	93.5	96.2	98.7	101.3	103.8	106.5	110.3	113.3
42.5°	83.1	83.4	83.4	84.4	85.9	87.0	89.5	91.3	93.2	95.9	97.4
45°	80.7	80.4	79.8	79.2	79.5	80.1	81.6	82.8	85.0	86.1	86.4
47.5°	79.5	78.2	77.0	76.1	75.9	76.1	77.3	78.5	79.8	80.7	80.9
50°	75.5	74.6	72.7	71.5	71.0	71.5	73.1	73.7	74.9	75.9	76.1
52.5°	71.5	70.4	69.1	67.9	67.9	68.2	69.4	70.7	71.8	72.1	72.7
55°	69.1	67.3	66.1	65.2	64.6	65.5	66.3	67.9	69.4	69.7	70.4
57.5°	66.6	64.9	63.6	62.7	62.1	63.0	63.9	66.1	67.9	67.9	67.9
60°	65.2	63.6	61.8	60.9	60.0	60.9	62.1	64.2	66.1	65.8	65.5
62.5°	60.9	59.4	58.4	58.4	57.5	59.1	60.3	62.7	63.0	62.4	61.8
63°	59.7	58.4	57.8	57.8	57.2	58.8	60.0	62.1	62.1	61.5	60.9
65°	56.6	55.8	55.1	55.8	55.8	57.2	57.5	59.1	58.8	57.8	57.5
67.5°	54.2	53.6	53.0	53.0	53.0	53.3	53.6	54.2	53.9	53.6	53.9
70°	50.3	49.9	49.3	49.3	49.0	49.0	49.0	49.3	49.3	49.6	49.9
72.5°	45.4	44.8	44.8	45.1	44.5	44.8	45.1	44.8	45.4	45.4	45.7
75°	39.9	39.6	40.2	40.8	40.5	40.5	40.8	40.8	41.1	41.1	41.5
77.5°	35.6	36.0	36.3	36.8	37.1	37.1	37.1	36.8	37.1	37.1	37.4
80°	31.7	32.2	32.8	33.5	33.8	33.8	33.8	33.5	33.5	33.5	33.5
82.5°	28.6	29.5	30.2	30.5	30.5	30.5	30.5	30.5	30.5	29.8	29.2
85°	24.0	25.9	25.9	26.2	25.3	24.7	24.0	24.4	24.7	23.4	23.1
87.5°	12.2	12.2	12.7	13.4	13.7	13.7	15.5	14.6	14.3	14.0	13.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153729

CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4
2.5°	324.6	324.2	324.9	324.2	324.6	324.9	324.2	325.2	325.8	324.9	323.9
5°	331.2	331.2	332.7	333.4	333.7	335.5	334.6	335.2	335.9	335.5	335.9
7.5°	335.5	336.7	338.2	339.8	340.1	341.6	341.2	342.2	342.8	344.4	344.4
10°	339.2	340.7	342.8	344.4	345.9	347.0	347.7	349.5	349.8	351.0	351.0
12.5°	342.5	344.4	346.4	348.9	350.5	352.8	353.2	355.9	356.8	357.1	356.2
15°	341.9	344.0	346.4	349.2	351.9	355.0	356.8	359.6	361.0	361.7	360.2
17.5°	336.1	337.9	340.9	344.7	348.0	351.9	355.3	359.3	361.7	362.3	362.0
20°	324.9	326.1	330.1	334.9	338.9	345.0	349.8	355.9	359.9	362.9	363.8
22.5°	302.6	305.7	309.6	315.1	320.9	328.5	335.5	344.4	352.8	360.2	367.5
25°	275.9	281.3	287.4	294.7	301.8	309.6	317.5	327.6	340.1	355.3	372.6
27.5°	248.7	258.1	265.8	275.2	283.4	291.4	300.2	311.2	324.9	343.1	365.4
30°	221.3	232.0	240.2	251.2	262.2	272.7	281.7	293.2	306.6	325.2	349.5
32.5°	192.1	202.8	212.5	222.6	234.7	247.6	258.1	272.4	286.8	306.0	330.7
35°	162.0	171.4	179.6	190.3	203.6	217.4	231.4	247.8	263.3	283.4	309.6
37.5°	135.8	142.5	150.4	159.8	170.2	184.8	200.6	220.1	237.8	259.7	286.5
40°	114.2	117.8	122.4	130.3	139.8	154.1	169.5	190.3	211.6	235.6	261.6
42.5°	97.4	99.3	100.5	105.6	113.3	127.3	142.2	162.3	185.7	211.9	238.0
45°	86.4	87.4	87.7	90.5	95.9	108.1	123.6	140.6	163.2	188.8	216.2
47.5°	81.2	82.2	82.8	83.4	86.7	96.2	110.3	126.3	147.0	170.5	198.5
50°	77.0	77.9	78.9	78.5	80.1	86.1	98.0	113.0	132.4	154.1	181.8
52.5°	72.7	73.4	73.4	73.4	74.3	78.2	86.7	100.5	118.4	138.9	166.2
55°	70.4	71.0	71.2	71.5	71.8	74.0	80.4	91.3	106.8	125.7	150.4
57.5°	67.9	68.2	68.8	69.1	69.7	71.0	74.9	82.8	95.9	111.7	132.4
60°	65.8	66.3	67.6	67.9	68.5	68.8	70.7	75.5	84.0	96.2	113.0
62.5°	62.4	63.3	64.6	64.9	65.5	65.8	66.1	68.8	72.7	80.1	92.5
63°	61.5	62.4	63.9	64.2	64.6	64.6	64.9	66.6	70.4	76.7	85.9
65°	58.1	59.4	60.3	60.6	60.9	60.9	60.6	61.2	61.5	64.2	69.7
67.5°	54.5	55.4	56.1	56.4	56.1	56.4	56.1	55.4	54.8	55.4	57.8
70°	50.9	51.5	51.5	51.7	52.0	52.3	51.7	51.2	50.6	50.3	51.7
72.5°	46.6	47.2	47.2	47.5	47.5	48.1	48.1	47.8	47.8	48.1	48.4
75°	42.3	42.9	42.6	43.2	43.2	44.1	44.1	44.5	45.1	44.8	44.5
77.5°	38.3	38.7	38.7	39.0	39.3	40.8	41.7	42.0	42.0	41.5	40.8
80°	34.1	34.1	33.5	33.2	33.5	35.0	36.8	37.1	38.0	37.7	38.0
82.5°	28.6	27.4	26.5	26.5	27.0	28.0	28.6	29.2	29.8	29.8	30.5
85°	22.0	20.7	19.8	20.1	21.0	21.3	21.0	21.0	22.2	23.1	22.2
87.5°	13.1	11.9	11.3	10.4	10.7	11.6	11.3	10.4	10.7	8.5	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153729

CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4
2.5°	324.6	324.2	323.6	322.7	322.4	321.8	322.1	321.2	320.6	320.0	319.1
5°	335.9	335.9	334.0	334.0	333.1	332.7	330.7	329.7	327.9	328.5	326.3
7.5°	343.7	344.7	342.5	342.2	340.9	340.7	337.9	337.0	335.5	334.9	333.1
10°	349.5	349.5	346.7	344.7	343.1	341.6	338.9	337.6	336.4	336.7	335.5
12.5°	354.1	351.9	348.0	345.0	342.8	341.2	339.2	338.2	337.9	340.1	340.4
15°	357.7	354.7	349.8	347.7	345.9	345.6	345.6	346.4	348.6	352.5	355.6
17.5°	359.9	358.0	355.6	355.0	358.0	359.9	362.3	365.1	368.1	373.6	376.9
20°	363.8	365.1	366.8	369.3	374.2	378.8	381.8	385.7	389.4	396.1	401.6
22.5°	374.2	381.1	386.9	391.8	399.2	405.5	409.5	414.9	417.7	422.3	430.8
25°	387.6	401.9	414.1	424.4	435.6	442.4	447.9	454.8	459.1	466.7	474.3
27.5°	383.6	404.0	422.3	441.5	457.0	474.3	486.5	498.0	505.4	516.7	526.7
30°	371.4	395.8	420.4	445.7	470.4	495.3	518.4	539.5	555.6	571.7	588.2
32.5°	355.0	383.0	413.2	444.1	476.5	511.2	543.1	574.8	601.6	625.1	647.9
35°	336.1	367.8	399.2	437.5	477.4	521.6	566.0	609.8	650.6	692.0	720.0
37.5°	313.6	345.9	380.8	425.0	471.9	526.4	583.0	640.2	698.1	753.8	802.2
40°	289.5	322.4	359.3	407.0	460.0	523.3	594.0	671.0	750.5	831.2	895.3
42.5°	268.2	302.0	342.2	390.6	448.2	519.4	602.8	697.5	794.6	894.5	988.8
45°	247.6	284.7	326.9	379.1	443.0	522.5	615.9	722.2	834.2	955.3	1070.5
47.5°	228.9	266.7	307.8	364.8	435.3	523.9	628.7	746.8	871.6	1002.9	1139.6
50°	212.2	248.7	289.2	346.4	423.5	523.0	640.2	769.0	903.9	1040.3	1192.8
52.5°	195.8	233.0	274.3	328.8	408.9	517.8	645.7	787.4	933.8	1078.0	1235.8
55°	179.6	216.2	257.8	312.0	389.7	504.5	645.2	799.2	957.5	1113.7	1277.2
57.5°	160.7	195.4	236.3	293.5	369.3	483.7	636.0	804.7	977.9	1149.0	1326.8
60°	137.3	169.8	209.1	266.4	342.5	457.3	616.8	801.7	989.7	1175.1	1369.1
62.5°	108.4	136.7	172.6	228.6	309.0	419.3	580.9	773.9	970.9	1171.5	1388.9
63°	102.3	129.1	164.1	219.5	294.7	408.9	570.3	762.9	961.8	1163.9	1386.1
65°	82.2	99.6	127.6	177.2	246.6	358.0	517.3	706.6	912.7	1110.4	1346.6
67.5°	63.0	71.8	86.7	121.5	174.4	281.7	419.0	598.9	792.2	977.9	1219.1
70°	53.9	57.8	64.2	80.7	110.8	177.8	294.1	446.6	614.1	775.1	991.9
72.5°	49.0	50.9	54.2	61.2	76.1	106.5	187.6	290.8	417.7	552.5	720.0
75°	45.1	46.6	49.3	53.0	58.4	71.0	106.8	177.8	271.6	362.9	485.9
77.5°	41.1	42.0	45.1	48.4	52.0	58.4	70.7	102.3	156.2	214.0	292.8
80°	37.7	37.1	39.3	44.8	48.4	52.0	55.8	66.3	88.9	117.2	158.3
82.5°	30.2	30.8	32.5	38.0	39.6	38.7	39.3	41.1	49.6	54.2	80.9
85°	20.4	18.9	18.5	19.2	19.2	18.2	18.2	17.9	19.8	22.5	38.7
87.5°	5.5	2.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153729
CATALOG NUMBER: AVS-E01-LED-E-U-SLR-7030

REPORT N
CATALOG

CANDELA DISTRIBUTION (continued):

CANDELA

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°	
0°	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	0°
2.5°	318.4	318.1	318.4	316.9	316.9	316.6	316.4	315.8	315.8	314.5	315.4	2.5°
5°	324.6	323.9	322.7	320.9	320.0	318.8	318.8	317.5	316.6	315.4	315.8	5°
7.5°	331.5	331.8	329.7	328.2	327.6	326.3	326.6	324.9	325.2	324.2	323.6	7.5°
10°	335.5	335.5	336.1	335.9	336.4	336.4	337.3	336.1	335.5	334.6	334.6	10°
12.5°	341.9	343.1	345.6	345.6	347.4	348.0	348.3	348.9	347.7	347.0	345.0	12.5°
15°	357.7	360.7	362.9	365.9	369.6	370.8	370.8	369.6	369.0	368.1	364.1	15°
17.5°	383.9	390.6	392.4	397.3	397.9	399.5	403.7	401.2	399.8	393.4	392.1	17.5°
20°	410.7	419.3	427.8	433.9	436.9	443.0	443.9	442.7	436.6	430.5	427.8	20°
22.5°	443.0	455.8	465.5	474.9	479.5	482.6	489.2	487.8	482.9	473.7	470.1	22.5°
25°	488.6	504.5	514.8	526.4	532.4	535.5	542.2	542.2	537.1	534.3	534.0	25°
27.5°	546.2	565.7	582.7	586.6	602.5	606.1	612.5	612.5	607.7	604.4	620.5	27.5°
30°	610.2	630.5	660.0	679.8	699.1	717.9	717.6	718.8	724.6	727.7	734.6	30°
32.5°	674.1	699.3	730.7	773.6	814.7	849.7	895.1	924.0	915.1	890.5	880.7	32.5°
35°	751.7	779.7	817.7	861.0	936.2	981.6	1003.4	1019.0	1020.8	1024.1	1031.2	35°
37.5°	838.1	885.1	929.2	978.2	1019.9	1075.0	1125.9	1166.6	1176.1	1195.2	1184.4	37.5°
40°	947.5	999.8	1046.1	1109.4	1165.4	1231.8	1304.6	1360.6	1383.1	1375.9	1321.0	40°
42.5°	1062.0	1126.7	1180.9	1255.5	1328.3	1416.0	1491.2	1569.4	1583.4	1527.2	1445.2	42.5°
45°	1167.3	1247.7	1314.9	1392.5	1481.5	1586.5	1686.9	1767.4	1764.6	1668.1	1558.4	45°
47.5°	1262.0	1360.6	1442.8	1543.8	1639.5	1764.6	1880.0	1939.4	1904.4	1790.2	1655.9	47.5°
50°	1340.2	1463.2	1564.6	1666.8	1788.3	1939.1	2050.2	2083.6	2016.1	1891.8	1750.6	50°
52.5°	1403.2	1557.6	1671.4	1789.2	1942.7	2101.3	2196.9	2184.5	2097.1	1969.5	1828.8	52.5°
55°	1456.5	1629.7	1765.5	1904.7	2094.9	2241.0	2304.7	2271.2	2149.1	2019.7	1882.4	55°
57.5°	1511.6	1699.8	1852.0	2013.4	2225.2	2350.7	2386.0	2317.2	2173.8	2038.9	1905.6	57.5°
60°	1566.7	1758.2	1928.4	2108.3	2323.8	2440.2	2430.5	2327.6	2166.4	2024.9	1890.1	60°
62.5°	1603.8	1793.0	1972.8	2166.7	2397.8	2485.8	2426.1	2290.7	2124.1	1969.7	1843.7	62.5°
63°	1604.8	1794.1	1975.5	2170.8	2406.1	2487.4	2417.9	2277.6	2110.8	1958.5	1830.1	63°
65°	1585.6	1771.3	1951.2	2152.7	2399.1	2452.3	2347.0	2200.3	2034.3	1880.6	1758.9	65°
67.5°	1487.6	1676.9	1835.9	2025.8	2273.7	2288.8	2157.0	2038.5	1889.4	1730.2	1602.9	67.5°
70°	1289.9	1447.4	1603.2	1761.9	1969.7	1967.0	1843.1	1782.9	1652.2	1470.8	1368.8	70°
72.5°	1026.0	1167.3	1276.9	1383.1	1520.1	1492.4	1412.6	1429.4	1344.8	1209.3	1148.7	72.5°
75°	761.8	917.0	970.6	1013.8	1071.7	1071.9	1093.9	1141.3	1140.2	1065.0	988.6	75°
77.5°	499.6	669.5	687.5	722.2	791.6	885.9	983.4	1088.1	1114.3	1054.9	942.0	77.5°
80°	278.5	455.1	434.4	464.2	539.2	667.4	811.1	926.7	994.9	961.8	842.1	80°
82.5°	142.5	262.5	250.9	292.2	352.8	464.2	559.3	648.2	728.5	723.9	678.7	82.5°
85°	74.0	143.7	163.5	185.1	215.5	255.4	291.4	317.2	350.8	409.7	429.8	85°
87.5°	0.0	0.0	0.0	0.0	0.0	0.3	0.0	22.0	15.9	43.5	62.1	87.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	90°



NUMBER: P153729

NUMBER: AVS-E01-LED-E-U-SLR-7030

DISTRIBUTION (continued):

330°	335°	340°	345°	350°	355°	360°
319.4	319.4	319.4	319.4	319.4	319.4	319.4
315.8	316.1	315.4	315.4	315.8	315.8	315.1
315.1	315.1	314.5	313.9	313.3	313.3	312.6
322.1	322.1	320.0	319.1	317.5	316.4	315.8
332.4	330.7	328.2	326.3	323.9	321.2	319.7
342.8	340.1	337.0	334.3	331.2	328.2	326.6
359.9	356.2	352.2	348.9	344.7	340.1	338.2
386.0	380.2	375.1	370.3	362.6	359.3	355.6
420.7	412.2	405.5	397.3	387.9	384.9	380.2
462.8	455.4	442.1	436.0	426.5	422.0	422.9
526.7	517.3	501.8	496.0	495.0	485.0	480.1
610.2	610.8	596.4	580.9	572.3	556.6	536.5
728.8	720.6	703.9	688.1	668.0	638.1	604.7
872.5	854.3	826.6	797.1	761.5	715.4	668.6
1013.0	980.9	936.8	887.5	836.1	778.8	712.4
1136.2	1086.6	1020.5	963.9	891.1	819.6	738.5
1248.8	1187.4	1102.1	1028.7	942.9	851.0	755.0
1357.8	1279.9	1175.4	1076.3	979.1	871.9	762.9
1461.7	1361.2	1237.3	1119.2	1005.6	885.6	764.1
1541.5	1431.8	1292.7	1150.3	1023.8	896.0	764.1
1615.4	1491.5	1335.0	1174.6	1040.9	903.0	764.8
1673.0	1533.5	1362.4	1191.9	1054.3	908.2	767.6
1714.6	1560.9	1380.7	1202.6	1064.0	915.4	773.6
1743.9	1578.9	1390.8	1212.0	1076.0	928.3	790.7
1757.9	1612.0	1407.5	1230.9	1096.4	955.3	824.8
1747.3	1663.5	1455.2	1262.9	1124.7	997.7	879.3
1742.7	1673.0	1468.4	1269.8	1131.0	1006.8	898.1
1707.0	1682.4	1522.3	1305.2	1161.5	1047.4	950.8
1596.6	1645.3	1567.6	1364.9	1226.9	1145.6	1049.1
1453.5	1590.2	1559.4	1372.4	1268.6	1226.3	1111.2
1282.1	1423.6	1395.0	1271.1	1222.7	1227.3	1095.1
1008.9	1115.2	1096.4	1052.7	1062.5	1096.1	938.0
808.3	794.0	750.5	753.5	809.8	849.1	675.2
660.3	534.6	478.0	479.5	577.8	618.7	430.2
628.4	505.7	411.9	359.9	420.4	404.9	224.7
447.6	448.5	372.0	302.3	292.8	249.0	140.0
105.9	85.0	60.6	45.1	47.5	31.4	15.9
0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)