

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155829

Luminaire Tested: **AVS-E03-LED-E-U-T3-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155829
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-T3-7030
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (63) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8450.1 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P155829

CATALOG NUMBER: AVS-E03-LED-E-U-T3-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 9.1 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155829

CATALOG NUMBER: AVS-E03-LED-E-U-T3-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P155829

CATALOG NUMBER: AVS-E03-LED-E-U-T3-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2918.1	0.0	2918.1
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	5532.0	0.0	5532.0
	% Fixture	65.5	0.0	65.5
Total	Lumens	8450.1	0.0	8450.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	1.0
10°-20°	257.4	3.0
20°-30°	442.4	5.2
30°-40°	718.3	8.5
40°-50°	1199.2	14.2
50°-60°	1888.3	22.3
60°-70°	2575.0	30.5
70°-80°	1114.7	13.2
80°-90°	167.6	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8450.1	100.0
0°-180°	8450.1	100.0

Coefficient of Utilization



REPORT NUMBER: P155829


CATALOG NUMBER: AVS-E03-LED-E-U-T3-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	395.3	4.7			
FM	(30°-60°)	2359.8	27.9			
FH	(60°-80°)	2639.3	31.2			G2/5000
FVH	(80°-90°)	137.6	1.6			G2/225
BL	(0°-30°)	391.7	4.6	B1/500		
BM	(30°-60°)	1446.0	17.1	B2/2500		
BH	(60°-80°)	1050.4	12.4	B3/2500		G3/2500
BVH	(80°-90°)	30.0	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P155829

CATALOG NUMBER: AVS-E03-LED-E-U-T3-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6
2.5°	914.3	917.9	914.3	915.1	916.1	915.1	914.3	914.3	911.5	913.4	915.1
5°	910.6	913.4	912.4	913.4	914.3	913.4	912.4	913.4	911.5	912.4	915.1
7.5°	906.0	905.2	906.0	907.9	909.7	909.7	909.7	910.6	909.7	909.7	912.4
10°	892.3	893.3	895.1	897.8	898.8	901.5	901.5	904.2	905.2	906.9	910.6
12.5°	875.0	875.9	877.7	879.6	884.1	888.7	888.7	895.1	897.8	902.4	908.8
15°	862.2	863.1	865.0	866.7	870.5	875.0	877.7	885.1	889.6	897.8	906.9
17.5°	869.5	868.6	870.5	871.3	871.3	875.0	875.0	880.5	885.9	893.3	905.2
20°	890.5	890.5	892.3	892.3	891.4	893.3	889.6	889.6	890.5	894.2	902.4
22.5°	911.5	910.6	914.3	916.1	917.0	919.8	916.1	915.1	910.6	907.9	910.6
25°	931.6	930.7	935.2	938.0	942.6	945.3	945.3	945.3	941.7	937.1	934.4
27.5°	962.7	962.7	967.3	969.9	973.7	979.1	981.9	981.9	982.8	976.4	971.8
30°	1014.7	1015.6	1016.6	1020.2	1023.8	1025.7	1029.3	1032.1	1034.8	1031.2	1023.8
32.5°	1076.9	1071.4	1071.4	1076.9	1081.5	1086.8	1088.7	1092.3	1097.8	1095.1	1094.2
35°	1150.8	1149.0	1147.2	1149.0	1154.5	1160.8	1168.2	1174.6	1170.9	1176.4	1173.7
37.5°	1260.4	1262.3	1263.2	1263.2	1262.3	1264.0	1267.8	1274.1	1272.3	1274.1	1277.8
40°	1441.2	1434.9	1428.5	1429.4	1420.3	1422.1	1407.5	1413.9	1414.8	1408.4	1411.1
42.5°	1622.1	1625.8	1628.5	1635.9	1629.4	1625.8	1612.0	1612.0	1604.8	1598.3	1596.6
45°	1817.6	1824.9	1825.8	1840.4	1834.9	1846.8	1856.9	1854.1	1842.2	1841.3	1828.5
47.5°	1973.8	1985.6	1998.4	2015.8	2029.4	2056.0	2087.0	2102.5	2111.7	2119.0	2104.4
50°	2090.7	2096.2	2129.0	2156.4	2186.5	2230.4	2273.4	2329.0	2373.8	2394.8	2414.9
52.5°	2153.7	2167.4	2203.0	2245.9	2298.9	2364.7	2434.1	2522.7	2599.4	2650.6	2696.2
55°	2167.4	2181.0	2221.2	2276.1	2348.2	2436.8	2536.4	2656.9	2772.0	2870.7	2966.5
57.5°	2129.0	2144.6	2187.5	2250.5	2335.4	2443.2	2568.3	2726.3	2885.3	3045.1	3186.6
60°	2058.7	2077.8	2117.1	2179.3	2273.4	2394.8	2544.6	2742.8	2965.7	3210.5	3481.7
62.5°	1942.7	1962.8	1999.3	2067.9	2164.7	2298.9	2472.4	2719.1	3034.2	3419.6	3900.9
65°	1756.4	1765.5	1810.3	1879.7	1965.5	2113.5	2304.4	2602.2	3012.2	3548.4	4211.5
66°	1672.3	1687.9	1715.2	1771.0	1853.2	1992.0	2183.8	2486.1	2929.1	3503.6	4203.2
67.5°	1540.8	1552.7	1571.0	1608.4	1658.7	1760.9	1942.7	2228.6	2675.2	3277.1	4028.8
70°	1245.8	1251.3	1276.0	1288.7	1306.1	1339.9	1405.6	1570.1	1918.0	2483.4	3251.5
72.5°	849.4	865.0	891.4	928.0	975.4	1021.1	1052.2	1073.2	1148.1	1481.5	2166.4
75°	622.9	639.4	673.2	721.6	804.7	899.7	998.3	1043.9	1013.0	969.9	1206.5
77.5°	361.7	383.6	411.9	458.5	535.2	661.2	830.3	980.0	1081.5	1087.8	1033.0
80°	152.5	155.2	172.6	196.4	243.8	332.4	463.9	679.5	904.2	1055.9	1091.5
82.5°	34.7	42.9	54.8	64.9	79.5	109.6	162.6	270.4	488.6	766.3	999.2
85°	12.7	12.7	17.3	25.6	29.2	32.8	42.9	68.5	116.9	215.5	449.3
87.5°	0.0	0.9	1.9	1.9	3.6	4.6	7.4	10.1	9.1	8.2	27.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155829

CATALOG NUMBER: AVS-E03-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6
2.5°	913.4	912.4	910.6	910.6	910.6	910.6	908.8	909.7	907.9	908.8	908.8
5°	912.4	912.4	911.5	909.7	910.6	910.6	911.5	909.7	909.7	910.6	909.7
7.5°	912.4	911.5	911.5	911.5	912.4	911.5	912.4	912.4	912.4	913.4	913.4
10°	912.4	912.4	914.3	915.1	915.1	916.1	918.9	918.9	919.8	920.6	922.5
12.5°	913.4	917.0	919.8	922.5	923.4	925.2	929.7	929.7	931.6	934.4	935.2
15°	914.3	919.8	925.2	927.0	928.9	932.5	937.1	939.0	941.7	944.5	946.2
17.5°	913.4	920.6	927.0	929.7	932.5	937.1	942.6	944.5	948.1	951.7	955.3
20°	912.4	922.5	932.5	936.2	939.8	946.2	953.6	958.1	961.8	967.3	970.9
22.5°	917.9	929.7	943.5	949.0	955.3	963.6	973.7	979.1	983.6	989.1	991.9
25°	935.2	944.5	960.8	969.9	978.2	991.9	1005.6	1012.0	1017.5	1022.1	1022.9
27.5°	964.5	967.3	987.4	999.2	1011.1	1033.0	1049.4	1054.0	1064.0	1067.7	1066.8
30°	1012.0	1007.5	1023.8	1042.2	1059.5	1089.6	1109.7	1121.6	1130.8	1130.8	1123.4
32.5°	1080.5	1073.2	1077.7	1098.8	1118.9	1162.7	1186.4	1202.0	1208.4	1206.5	1191.0
35°	1170.1	1165.4	1162.7	1179.2	1211.1	1262.3	1293.3	1301.6	1311.6	1309.7	1289.6
37.5°	1276.0	1272.3	1272.3	1291.5	1322.5	1398.3	1432.1	1437.6	1436.7	1422.1	1384.7
40°	1401.0	1399.3	1391.0	1402.0	1428.5	1527.2	1572.7	1580.1	1570.1	1546.3	1502.5
42.5°	1581.0	1570.1	1544.5	1550.9	1571.0	1666.8	1726.2	1746.3	1736.3	1712.5	1641.2
45°	1815.8	1803.8	1760.9	1755.4	1766.4	1850.5	1927.2	1931.7	1929.9	1899.8	1815.8
47.5°	2091.6	2073.3	2027.7	2013.1	2009.3	2087.0	2161.0	2168.3	2163.7	2119.0	2006.6
50°	2390.3	2363.7	2333.6	2323.5	2308.9	2364.7	2439.6	2440.5	2422.2	2360.1	2255.0
52.5°	2709.0	2699.9	2694.4	2684.4	2677.9	2726.3	2772.0	2744.7	2717.2	2652.3	2561.0
55°	3030.5	3068.0	3106.3	3109.9	3120.9	3173.0	3172.0	3097.2	3077.1	3041.5	2951.0
57.5°	3372.1	3510.9	3631.5	3668.9	3705.5	3802.3	3793.2	3719.2	3693.6	3649.7	3574.8
60°	3837.0	4211.5	4559.5	4642.6	4700.1	4816.1	4805.2	4691.0	4743.9	4740.3	4643.5
62.5°	4488.2	5111.1	5632.6	5760.5	5800.7	5813.5	5744.0	5620.7	5672.8	5731.3	5433.5
65°	4929.3	5661.9	6197.1	6295.8	6301.2	6148.7	5994.3	5849.1	5836.3	5786.1	5360.4
66°	4939.4	5689.2	6226.3	6322.2	6288.4	6080.2	5884.8	5738.5	5675.5	5565.1	5123.9
67.5°	4762.2	5518.4	6096.6	6198.0	6124.0	5829.0	5559.6	5371.4	5248.1	5069.1	4680.0
70°	3999.6	4749.4	5461.9	5650.9	5674.6	5234.4	4860.8	4639.8	4473.6	4227.9	3892.7
72.5°	2973.9	3651.6	4280.0	4460.8	4553.1	4201.5	3886.3	3718.2	3490.8	3232.3	2994.0
75°	1864.1	2342.7	2763.8	2890.8	2803.9	2531.8	2342.7	2272.4	2048.6	1894.3	1785.6
77.5°	1065.9	1215.6	1249.4	1201.0	1098.8	841.2	598.2	443.0	384.6	425.6	469.4
80°	1040.3	953.6	759.9	668.6	605.6	416.5	244.8	168.1	139.8	143.4	155.2
82.5°	1127.0	1209.3	995.5	811.9	681.3	460.3	253.9	135.1	91.3	107.8	121.5
85°	732.5	1019.3	917.9	773.6	626.5	393.7	209.1	70.4	46.6	61.2	84.0
87.5°	74.0	81.2	69.4	94.1	70.4	32.8	16.5	10.1	9.1	11.0	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155829

CATALOG NUMBER: AVS-E03-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6	910.6
2.5°	909.7	909.7	910.6	911.5	912.4	913.4	913.4	913.4	913.4	915.1	914.3
5°	911.5	913.4	915.1	916.1	917.9	917.9	920.6	919.8	919.8	922.5	923.4
7.5°	915.1	917.9	921.6	920.6	924.4	923.4	925.2	925.2	922.5	923.4	921.6
10°	923.4	927.0	928.9	926.1	927.0	923.4	922.5	917.9	912.4	909.7	906.0
12.5°	937.1	940.7	940.7	936.2	930.7	922.5	916.1	906.0	897.8	893.3	888.7
15°	949.0	952.6	951.7	944.5	936.2	923.4	914.3	902.4	890.5	883.2	878.7
17.5°	958.1	959.9	957.2	947.2	938.0	926.1	917.0	904.2	890.5	881.3	873.2
20°	971.8	969.9	963.6	950.8	940.7	929.7	922.5	911.5	896.0	884.1	872.2
22.5°	991.9	984.6	972.7	959.1	949.0	939.0	931.6	919.8	904.2	889.6	875.9
25°	1018.3	1003.7	987.4	972.7	963.6	952.6	944.5	931.6	915.1	898.8	882.3
27.5°	1056.8	1031.2	1010.2	997.4	987.4	973.7	963.6	947.2	929.7	910.6	892.3
30°	1099.7	1065.0	1044.9	1034.8	1023.8	1009.2	993.7	972.7	952.6	931.6	909.7
32.5°	1155.3	1113.4	1094.2	1084.1	1069.5	1051.3	1033.0	1009.2	980.9	953.6	927.0
35°	1228.5	1185.5	1165.4	1149.9	1129.8	1106.1	1079.6	1047.6	1009.2	972.7	939.0
37.5°	1307.0	1260.4	1241.2	1224.8	1194.6	1163.6	1126.1	1079.6	1027.6	979.1	937.1
40°	1406.5	1363.6	1339.0	1310.7	1275.0	1221.1	1162.7	1095.1	1028.4	969.0	919.8
42.5°	1532.6	1489.6	1453.2	1408.4	1346.3	1263.2	1180.0	1092.3	1012.0	944.5	891.4
45°	1699.8	1647.7	1584.7	1506.1	1405.6	1289.6	1180.9	1075.0	980.9	906.0	849.4
47.5°	1904.4	1824.9	1721.7	1589.2	1444.9	1297.0	1166.3	1040.3	932.5	851.2	788.2
50°	2147.3	2022.2	1852.2	1657.7	1465.0	1286.0	1129.8	988.3	864.0	777.3	702.4
52.5°	2425.0	2220.3	1970.1	1707.0	1464.1	1249.4	1067.7	909.7	774.5	677.7	606.4
55°	2751.0	2446.8	2091.6	1743.6	1438.5	1181.9	972.7	799.2	664.0	574.5	508.7
57.5°	3228.7	2814.0	2303.4	1800.2	1387.4	1077.7	843.9	666.7	548.0	463.1	407.4
60°	4101.9	3426.8	2685.3	1914.4	1308.8	925.2	693.3	525.2	425.6	357.1	319.7
62.5°	4759.5	3900.9	2891.7	1888.8	1150.8	737.1	514.2	382.7	313.3	266.7	242.9
65°	4665.4	3753.9	2671.5	1626.6	902.4	519.7	341.6	260.3	215.5	193.7	179.9
66°	4452.5	3562.1	2480.6	1464.1	780.0	432.0	281.3	218.3	185.4	169.8	160.7
67.5°	4048.9	3205.9	2139.1	1200.1	599.2	313.3	211.9	172.6	150.7	144.4	137.9
70°	3365.7	2556.5	1501.6	698.8	306.0	174.4	134.3	120.5	115.1	114.2	112.3
72.5°	2579.3	1809.3	884.1	330.7	159.0	116.0	104.1	99.6	97.7	97.7	98.7
75°	1581.0	1016.6	390.9	161.7	111.4	97.7	92.2	90.5	89.5	90.5	89.5
77.5°	527.9	323.3	167.2	122.4	101.3	90.5	86.7	85.0	85.0	85.0	85.0
80°	161.7	140.6	127.9	113.3	95.9	85.9	80.4	79.5	80.4	81.2	78.5
82.5°	121.5	115.1	107.8	100.5	86.7	76.7	74.9	74.9	74.9	72.1	68.5
85°	89.5	88.6	73.1	68.5	63.9	63.9	63.9	63.9	61.2	56.6	53.0
87.5°	16.5	15.5	16.5	17.3	25.6	27.4	27.4	29.2	31.9	30.2	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155829

CATALOG NUMBER: AVS-E03-LED-E-U-T3-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	910.6	910.6	910.6	910.6	910.6
2.5°	914.3	913.4	916.1	914.3	915.1
5°	922.5	921.6	923.4	921.6	924.4
7.5°	919.8	917.9	917.0	917.9	918.9
10°	900.5	898.8	897.8	896.9	897.8
12.5°	884.1	880.5	880.5	878.7	879.6
15°	872.2	869.5	868.6	866.7	867.7
17.5°	866.7	862.2	860.4	858.5	858.5
20°	863.1	857.6	854.9	853.1	852.1
22.5°	863.1	854.9	851.2	849.4	848.5
25°	866.7	856.7	851.2	848.5	847.6
27.5°	874.1	861.2	854.9	851.2	851.2
30°	886.8	870.5	861.2	856.7	855.9
32.5°	899.7	877.7	865.0	859.5	857.6
35°	906.0	877.7	862.2	853.1	851.2
37.5°	898.8	865.9	846.6	833.0	830.3
40°	875.9	841.2	820.2	807.4	805.6
42.5°	845.8	811.9	787.4	778.1	775.4
45°	804.7	764.5	739.8	727.0	728.0
47.5°	734.3	693.3	671.3	659.5	661.2
50°	651.2	611.0	591.8	579.1	581.8
52.5°	559.9	523.3	505.1	498.7	496.9
55°	463.9	435.6	422.9	415.5	412.8
57.5°	376.3	356.2	347.0	337.9	338.9
60°	296.8	286.8	284.0	274.0	273.1
62.5°	233.8	227.5	224.7	217.4	218.3
65°	177.2	175.3	177.2	172.6	174.4
66°	159.8	160.7	160.7	158.0	159.8
67.5°	137.9	139.8	142.5	139.8	141.6
70°	114.2	116.0	117.8	117.8	117.8
72.5°	99.6	101.3	102.3	102.3	102.3
75°	91.3	92.2	93.2	91.3	91.3
77.5°	85.9	85.9	84.0	83.1	82.2
80°	77.6	76.7	74.0	72.1	72.1
82.5°	64.9	63.0	61.2	58.4	58.4
85°	49.3	47.5	45.7	42.0	40.2
87.5°	25.6	26.5	25.6	21.0	18.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)