

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156859

Luminaire Tested: **AVS-E02-LED-E-U-T4-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156859
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-T4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (42) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5520.4 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156859

CATALOG NUMBER: AVS-E02-LED-E-U-T4-7030

Iso-Footcandle Lines of Horizontal Illumination

✘ Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 7.6 fc

Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156859

CATALOG NUMBER: AVS-E02-LED-E-U-T4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P156859

CATALOG NUMBER: AVS-E02-LED-E-U-T4-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1177.9	0.0	1177.9
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	4342.5	0.0	4342.5
	% Fixture	78.7	0.0	78.7
Total	Lumens	5520.4	0.0	5520.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.7	1.3
10°-20°	214.5	3.9
20°-30°	369.5	6.7
30°-40°	559.1	10.1
40°-50°	724.6	13.1
50°-60°	999.0	18.1
60°-70°	1552.1	28.1
70°-80°	902.6	16.3
80°-90°	128.3	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5520.4	100.0
0°-180°	5520.4	100.0

Coefficient of Utilization



REPORT NUMBER: P156859


CATALOG NUMBER: AVS-E02-LED-E-U-T4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	339.4	6.1			
FM	(30°-60°)	1772.0	32.1			
FH	(60°-80°)	2132.5	38.6			G2/5000
FVH	(80°-90°)	98.5	1.8			G1/100
BL	(0°-30°)	315.3	5.7	B1/500		
BM	(30°-60°)	510.6	9.2	B1/1000		
BH	(60°-80°)	322.2	5.8	B1/500		G1/500
BVH	(80°-90°)	29.8	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P156859

CATALOG NUMBER: AVS-E02-LED-E-U-T4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7
2.5°	714.2	716.7	714.8	715.4	715.4	716.1	716.1	716.7	716.1	717.9	719.1
5°	701.5	702.7	702.1	703.3	704.5	706.9	706.3	709.3	709.9	711.8	714.8
7.5°	696.6	695.3	696.0	697.8	699.1	700.2	701.5	703.9	705.7	709.9	712.4
10°	701.5	700.8	701.5	702.7	702.7	703.3	702.1	704.5	705.7	709.3	711.8
12.5°	721.6	721.6	720.3	720.3	719.1	717.9	714.8	713.1	712.4	713.1	714.2
15°	753.8	752.6	750.2	748.3	745.9	741.7	737.4	733.7	731.3	727.7	726.4
17.5°	785.5	783.6	781.2	778.8	775.8	771.5	764.8	760.5	753.8	749.5	747.2
20°	822.0	818.3	815.3	812.2	806.2	805.0	798.2	791.0	783.0	773.3	772.1
22.5°	869.5	863.4	859.8	857.9	851.8	850.1	839.1	828.7	819.0	806.2	803.1
25°	917.6	911.5	909.7	907.3	903.0	900.5	890.3	878.7	865.9	848.2	844.6
27.5°	964.5	965.1	960.2	962.1	960.8	956.6	946.2	934.6	924.9	904.2	900.0
30°	1022.9	1019.3	1016.9	1020.5	1016.3	1016.9	1007.8	1001.7	985.8	973.7	965.1
32.5°	1083.8	1083.2	1086.8	1089.3	1088.7	1087.5	1080.2	1074.1	1060.1	1042.5	1038.8
35°	1167.3	1170.9	1174.0	1184.9	1184.9	1192.8	1185.5	1178.2	1161.8	1140.5	1133.2
37.5°	1223.9	1225.1	1237.3	1251.9	1270.2	1287.3	1292.1	1293.9	1287.3	1271.4	1260.4
40°	1275.6	1278.0	1297.6	1320.1	1346.8	1380.4	1400.5	1409.6	1411.4	1404.1	1380.4
42.5°	1327.4	1331.1	1351.2	1384.0	1421.1	1463.8	1499.1	1521.7	1534.4	1534.4	1520.4
45°	1387.7	1392.5	1414.5	1450.4	1493.7	1547.3	1596.0	1639.2	1659.9	1661.0	1647.7
47.5°	1459.0	1463.2	1488.8	1525.3	1569.7	1623.9	1685.4	1734.7	1773.2	1775.5	1764.6
50°	1550.9	1557.0	1578.2	1611.2	1656.8	1711.6	1773.2	1842.0	1882.1	1891.8	1880.3
52.5°	1672.6	1673.9	1691.5	1722.0	1766.4	1818.8	1883.9	1958.9	2011.8	2019.7	2000.8
55°	1840.7	1838.9	1850.5	1883.3	1916.8	1957.6	2025.2	2109.2	2168.3	2180.5	2161.0
57.5°	2069.0	2067.3	2077.0	2084.9	2147.6	2187.2	2253.6	2333.9	2391.2	2426.4	2393.0
60°	2422.8	2421.0	2436.8	2483.1	2529.9	2587.9	2652.3	2748.6	2828.9	2839.3	2806.4
62.5°	2679.2	2688.3	2723.0	2777.2	2872.2	2985.4	3103.5	3230.3	3395.2	3447.6	3431.8
65°	2589.6	2607.9	2656.1	2738.2	2864.9	3021.3	3206.4	3436.1	3657.1	3780.6	3777.0
66°	2509.3	2529.3	2588.4	2667.6	2801.6	2972.6	3174.8	3425.1	3672.2	3808.7	3817.2
67.5°	2363.1	2385.7	2443.5	2537.3	2667.6	2849.6	3067.0	3339.2	3618.7	3777.6	3800.1
70°	2078.8	2104.4	2146.4	2223.7	2352.2	2514.7	2743.7	2987.3	3280.1	3462.2	3489.6
72.5°	1737.8	1760.3	1807.3	1870.6	1975.9	2078.1	2257.8	2437.4	2646.8	2854.5	2834.4
75°	1247.7	1257.4	1285.4	1354.2	1410.8	1502.8	1647.0	1794.4	1937.5	2032.5	2045.9
77.5°	648.5	674.1	713.7	789.7	851.2	934.1	1027.8	1138.7	1243.4	1330.5	1306.7
80°	424.4	435.3	470.7	509.6	554.7	607.7	670.4	711.8	725.2	719.7	725.2
82.5°	244.8	264.9	311.7	341.6	375.1	393.4	443.3	490.8	517.6	484.0	471.9
85°	31.1	40.2	126.6	159.5	182.7	210.1	225.3	253.9	236.9	211.9	258.1
87.5°	6.7	6.1	8.5	18.2	18.9	15.9	29.8	31.7	19.5	9.7	12.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156859

CATALOG NUMBER: AVS-E02-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7
2.5°	720.3	720.9	722.2	723.9	725.2	726.4	727.7	729.4	730.7	731.9	734.3
5°	717.3	719.7	722.2	724.6	727.7	732.5	735.5	738.0	740.4	745.3	747.2
7.5°	715.4	719.7	723.4	727.7	732.5	736.8	742.3	745.3	748.9	752.0	755.6
10°	714.2	720.3	723.9	730.1	735.5	739.8	745.9	749.5	753.8	757.5	759.3
12.5°	716.7	719.7	723.4	729.4	736.2	742.3	748.9	752.0	755.6	758.7	759.3
15°	727.0	727.0	727.7	732.5	739.2	744.0	749.5	752.6	754.4	756.3	756.3
17.5°	745.9	741.7	738.5	739.2	743.4	746.5	749.5	749.5	748.3	747.8	746.5
20°	767.8	762.4	756.3	752.0	750.8	748.3	746.5	740.4	735.5	731.3	728.3
22.5°	799.5	791.0	782.5	774.5	767.3	758.0	747.8	735.5	723.9	716.1	711.2
25°	838.4	831.7	821.5	809.2	800.1	783.0	769.6	752.0	737.4	727.0	718.5
27.5°	893.9	885.9	876.2	865.3	851.8	833.0	816.6	795.9	778.1	762.9	752.0
30°	962.7	952.3	945.0	931.6	922.5	901.1	884.8	859.2	825.1	800.7	785.5
32.5°	1033.3	1021.8	1015.6	1005.3	994.9	982.2	957.2	917.6	873.8	834.2	808.0
35°	1127.7	1115.5	1104.6	1095.4	1080.2	1056.5	1034.5	987.0	926.7	871.3	827.5
37.5°	1246.4	1226.3	1199.0	1175.8	1149.0	1114.9	1081.5	1032.7	963.9	892.0	833.6
40°	1373.1	1337.7	1298.8	1255.5	1209.3	1160.0	1121.6	1072.2	994.9	909.7	829.3
42.5°	1505.2	1449.2	1395.0	1334.1	1269.5	1211.1	1161.1	1106.9	1018.0	914.6	812.2
45°	1636.2	1573.4	1491.2	1411.4	1329.8	1257.4	1201.3	1140.5	1039.4	916.4	789.7
47.5°	1744.5	1680.0	1586.2	1486.3	1389.5	1307.4	1241.6	1175.8	1068.0	929.2	784.2
50°	1859.0	1780.4	1676.3	1558.1	1448.6	1356.6	1286.6	1218.4	1108.2	962.1	802.0
52.5°	1983.8	1893.7	1771.9	1639.8	1519.8	1416.9	1340.8	1270.8	1159.4	1008.3	835.4
55°	2136.1	2025.8	1893.7	1744.5	1616.1	1502.2	1418.1	1335.3	1220.2	1063.1	877.4
57.5°	2368.6	2233.5	2084.9	1915.0	1772.5	1637.9	1537.5	1441.9	1314.6	1144.8	934.6
60°	2789.3	2645.1	2452.0	2246.2	2078.8	1921.7	1774.3	1655.6	1499.1	1305.5	1061.3
62.5°	3392.2	3200.4	2942.8	2654.8	2435.6	2209.1	2042.9	1866.3	1672.0	1463.2	1210.5
65°	3727.0	3494.5	3149.8	2815.5	2533.7	2287.7	2076.4	1871.7	1656.2	1456.5	1245.2
66°	3768.5	3526.1	3168.1	2816.2	2520.2	2267.6	2045.3	1833.4	1613.0	1422.4	1230.6
67.5°	3751.4	3503.6	3134.6	2763.2	2462.4	2190.8	1961.2	1741.5	1521.7	1343.8	1181.9
70°	3471.9	3236.9	2874.6	2514.7	2229.2	1961.2	1742.1	1525.9	1324.4	1172.1	1052.7
72.5°	2883.1	2682.2	2367.4	2084.9	1860.8	1639.8	1454.1	1247.7	1077.1	964.5	893.9
75°	2081.2	1959.5	1672.6	1510.7	1314.0	1167.3	987.0	864.7	742.3	687.5	675.2
77.5°	1314.6	1150.8	968.8	797.6	655.8	543.7	423.2	359.3	299.6	293.5	354.4
80°	665.5	599.2	461.6	367.8	309.3	250.3	197.9	149.7	104.8	126.0	151.0
82.5°	436.0	363.5	285.0	234.4	203.9	169.2	131.5	91.3	66.9	75.5	103.5
85°	235.6	200.9	162.0	127.9	103.5	92.5	62.1	43.8	43.2	46.3	59.1
87.5°	17.1	17.1	13.4	12.2	14.6	12.2	11.0	11.0	10.4	11.0	14.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156859

CATALOG NUMBER: AVS-E02-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7	727.7
2.5°	735.5	737.4	738.0	741.0	742.9	744.0	745.3	745.3	745.9	747.8	748.3
5°	749.5	752.6	756.3	758.7	759.9	763.5	764.8	764.8	766.0	768.4	770.3
7.5°	758.0	762.4	766.0	767.3	769.6	770.9	772.7	773.9	773.9	776.4	777.6
10°	761.1	763.5	767.3	767.3	769.6	769.6	771.5	772.1	772.1	774.5	776.4
12.5°	761.1	762.4	765.4	765.4	767.3	767.8	770.3	772.1	772.7	775.8	778.1
15°	757.5	758.7	761.1	761.8	766.0	768.4	773.9	777.6	777.6	780.6	781.9
17.5°	747.2	750.2	755.0	759.9	767.8	773.3	780.0	783.0	780.6	778.8	777.0
20°	730.1	735.5	747.2	759.3	773.3	780.6	784.2	781.2	772.7	764.1	758.7
22.5°	713.1	723.9	743.4	761.8	777.6	782.5	780.6	769.6	755.6	745.3	738.0
25°	720.9	733.7	752.6	769.0	779.4	778.1	770.9	755.6	740.4	727.0	714.8
27.5°	753.8	767.8	778.1	783.6	782.5	773.9	762.4	745.3	727.0	709.3	692.3
30°	784.9	792.2	794.6	790.4	780.6	766.6	752.0	732.5	708.2	686.2	666.7
32.5°	798.9	791.6	780.0	768.4	752.6	740.4	720.3	699.1	668.6	642.4	622.9
35°	798.9	769.6	740.4	716.1	692.3	677.1	654.0	625.4	597.3	575.4	560.2
37.5°	781.2	725.2	677.1	637.5	607.7	591.2	556.6	531.0	507.3	499.9	490.2
40°	748.9	666.1	596.7	545.0	507.3	482.9	448.2	430.5	421.3	417.7	415.9
42.5°	705.7	600.4	507.8	443.9	403.1	375.6	352.5	341.6	340.9	340.4	340.4
45°	659.5	529.7	421.3	345.3	309.3	285.0	274.0	269.7	273.4	272.7	273.4
47.5°	630.8	476.2	342.2	261.2	233.8	218.0	212.5	214.3	217.4	216.2	216.2
50°	627.2	448.8	289.2	203.4	182.7	174.7	173.6	173.6	175.3	174.2	173.6
52.5°	640.5	444.5	261.9	174.7	158.3	151.6	150.4	149.7	149.2	145.5	142.5
55°	663.7	454.2	253.9	167.5	150.4	143.1	141.2	140.0	137.6	132.7	127.3
57.5°	709.9	484.7	261.2	171.1	152.8	146.7	144.9	144.9	140.0	132.1	124.2
60°	821.5	562.0	291.1	185.1	164.4	158.3	159.5	159.0	151.6	140.0	127.9
62.5°	965.1	663.1	330.1	204.6	179.1	177.8	183.9	182.7	170.5	152.8	135.1
65°	1031.5	710.6	340.9	208.8	182.1	187.6	199.7	198.5	183.3	159.0	136.4
66°	1032.7	710.6	336.1	205.2	177.8	184.5	196.7	196.1	180.8	156.5	134.0
67.5°	1007.8	691.1	322.1	197.9	169.2	174.2	185.1	184.5	170.5	150.4	129.1
70°	914.0	618.7	286.2	185.1	157.7	155.2	159.0	156.5	147.4	133.4	118.8
72.5°	783.0	519.4	249.6	175.3	149.7	140.0	137.6	135.8	128.5	120.5	111.4
75°	616.8	411.0	219.2	168.1	142.5	129.7	125.4	123.0	118.1	112.6	105.4
77.5°	380.5	294.1	191.2	158.3	137.0	124.2	121.1	117.5	110.3	103.5	98.0
80°	169.8	182.1	157.1	138.2	122.4	110.8	105.9	100.5	93.2	88.9	85.9
82.5°	113.3	117.5	113.9	103.5	92.5	83.4	76.1	76.1	74.9	71.2	70.1
85°	72.4	73.1	70.7	63.9	59.7	54.2	51.2	51.7	54.2	53.6	53.0
87.5°	16.5	16.5	19.5	18.2	21.3	22.5	24.4	26.2	29.8	29.8	31.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156859

CATALOG NUMBER: AVS-E02-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	727.7	727.7	727.7	727.7	727.7
2.5°	748.9	750.2	751.4	749.5	750.2
5°	770.3	769.6	772.7	770.9	772.1
7.5°	777.0	777.6	780.0	780.0	780.6
10°	777.6	778.8	781.9	783.6	784.9
12.5°	780.6	783.0	787.9	789.1	789.1
15°	783.0	784.2	787.4	788.5	789.7
17.5°	774.5	772.1	773.3	773.9	773.3
20°	753.2	750.8	750.2	747.8	748.9
22.5°	730.1	723.4	719.1	714.2	714.2
25°	702.1	691.7	683.2	674.6	676.5
27.5°	675.9	662.5	654.0	648.5	647.3
30°	650.3	636.3	628.4	621.7	621.7
32.5°	607.7	597.9	587.6	583.3	582.7
35°	548.6	542.5	534.0	532.2	529.1
37.5°	482.3	480.4	473.2	472.5	469.4
40°	412.8	414.1	411.6	410.4	408.6
42.5°	343.4	349.5	348.3	347.7	346.4
45°	277.1	281.3	282.0	283.7	286.8
47.5°	218.0	219.2	220.4	219.8	220.4
50°	170.5	167.5	166.8	165.0	166.8
52.5°	137.6	132.7	130.3	127.9	126.6
55°	121.1	116.3	113.9	112.6	111.4
57.5°	116.9	112.0	108.4	105.9	105.4
60°	118.1	110.8	105.9	102.9	102.3
62.5°	121.1	111.4	104.8	101.7	101.0
65°	120.5	110.3	104.1	100.5	99.9
66°	118.8	109.0	102.9	99.9	99.3
67.5°	115.6	107.2	101.7	99.3	98.0
70°	110.3	104.8	100.5	97.4	96.2
72.5°	105.4	101.0	97.4	94.4	93.8
75°	99.9	96.2	92.5	90.2	89.5
77.5°	93.2	89.5	87.0	85.3	84.7
80°	82.2	79.8	77.3	74.9	74.9
82.5°	68.2	66.3	63.9	62.1	61.5
85°	52.3	52.3	50.6	48.7	48.1
87.5°	31.1	30.5	30.5	28.6	28.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)