

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156869

Luminaire Tested: **AVS-E03-LED-E-U-T4-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156869
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-T4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (63) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8280.6 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156869

CATALOG NUMBER: AVS-E03-LED-E-U-T4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 11.4 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156869

CATALOG NUMBER: AVS-E03-LED-E-U-T4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P156869

CATALOG NUMBER: AVS-E03-LED-E-U-T4-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1766.9	0.0	1766.9
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	6513.7	0.0	6513.7
	% Fixture	78.7	0.0	78.7
Total	Lumens	8280.6	0.0	8280.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.0	1.3
10°-20°	321.8	3.9
20°-30°	554.3	6.7
30°-40°	838.6	10.1
40°-50°	1086.9	13.1
50°-60°	1498.5	18.1
60°-70°	2328.2	28.1
70°-80°	1353.9	16.3
80°-90°	192.5	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8280.6	100.0
0°-180°	8280.6	100.0

Coefficient of Utilization



REPORT NUMBER: P156869


CATALOG NUMBER: AVS-E03-LED-E-U-T4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	509.1	6.1			
FM	(30°-60°)	2658.1	32.1			
FH	(60°-80°)	3198.8	38.6			G2/5000
FVH	(80°-90°)	147.8	1.8			G2/225
BL	(0°-30°)	472.9	5.7	B1/500		
BM	(30°-60°)	765.9	9.2	B1/1000		
BH	(60°-80°)	483.2	5.8	B1/500		G1/500
BVH	(80°-90°)	44.8	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P156869

CATALOG NUMBER: AVS-E03-LED-E-U-T4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5
2.5°	1071.4	1075.0	1072.2	1073.2	1073.2	1074.1	1074.1	1075.0	1074.1	1076.9	1078.7
5°	1052.2	1054.0	1053.1	1054.9	1056.8	1060.4	1059.5	1064.0	1065.0	1067.7	1072.2
7.5°	1044.9	1043.0	1043.9	1046.7	1048.5	1050.4	1052.2	1055.9	1058.5	1065.0	1068.6
10°	1052.2	1051.3	1052.2	1054.0	1054.0	1054.9	1053.1	1056.8	1058.5	1064.0	1067.7
12.5°	1082.3	1082.3	1080.5	1080.5	1078.7	1076.9	1072.2	1069.5	1068.6	1069.5	1071.4
15°	1130.8	1128.9	1125.3	1122.5	1118.9	1112.4	1106.1	1100.6	1096.9	1091.5	1089.6
17.5°	1178.2	1175.4	1171.8	1168.2	1163.6	1157.2	1147.2	1140.7	1130.8	1124.4	1120.7
20°	1233.1	1227.6	1223.0	1218.4	1209.3	1207.5	1197.4	1186.4	1174.6	1160.0	1158.1
22.5°	1304.2	1295.1	1289.6	1286.9	1277.8	1275.0	1258.5	1243.1	1228.5	1209.3	1204.7
25°	1376.4	1367.3	1364.6	1360.9	1354.5	1350.9	1335.3	1317.9	1298.8	1272.3	1266.8
27.5°	1446.7	1447.7	1440.3	1443.1	1441.2	1434.9	1419.4	1402.0	1387.4	1356.4	1349.9
30°	1534.4	1528.9	1525.3	1530.8	1524.4	1525.3	1511.6	1502.5	1478.8	1460.4	1447.7
32.5°	1625.8	1624.9	1630.4	1634.0	1633.1	1631.3	1620.3	1611.2	1590.2	1563.6	1558.1
35°	1750.9	1756.4	1760.9	1777.4	1777.4	1789.2	1778.3	1767.4	1742.7	1710.7	1699.8
37.5°	1835.9	1837.6	1856.0	1877.8	1905.3	1930.8	1938.1	1940.8	1930.8	1907.0	1890.7
40°	1913.5	1917.1	1946.3	1980.1	2020.3	2070.6	2100.7	2114.4	2117.1	2106.2	2070.6
42.5°	1991.1	1996.6	2026.7	2076.1	2131.7	2195.6	2248.7	2282.5	2301.7	2301.7	2280.6
45°	2081.6	2088.8	2121.8	2175.6	2240.4	2320.8	2393.9	2458.8	2489.8	2491.6	2471.5
47.5°	2188.4	2194.8	2233.2	2288.0	2354.6	2435.9	2528.2	2602.2	2659.7	2663.3	2646.8
50°	2326.3	2335.4	2367.4	2416.7	2485.2	2567.5	2659.7	2762.9	2823.2	2837.8	2820.4
52.5°	2509.0	2510.8	2537.3	2583.0	2649.6	2728.2	2825.9	2938.2	3017.7	3029.5	3001.2
55°	2761.0	2758.3	2775.6	2825.0	2875.2	2936.4	3037.8	3163.8	3252.4	3270.7	3241.5
57.5°	3103.5	3100.8	3115.4	3127.4	3221.3	3280.7	3380.3	3500.8	3586.7	3639.7	3589.4
60°	3634.2	3631.5	3655.2	3724.7	3794.9	3881.8	3978.5	4122.9	4243.4	4259.0	4209.6
62.5°	4018.8	4032.4	4084.5	4165.8	4308.3	4478.1	4655.3	4845.3	5092.8	5171.4	5147.7
65°	3884.5	3911.9	3984.0	4107.4	4297.3	4532.0	4809.7	5154.0	5485.6	5671.0	5665.5
66°	3763.9	3794.1	3882.7	4001.3	4202.3	4459.0	4762.2	5137.6	5508.4	5713.1	5725.8
67.5°	3544.7	3578.5	3665.3	3805.9	4001.3	4274.5	4600.5	5008.8	5428.1	5666.4	5700.2
70°	3118.1	3156.6	3219.6	3335.5	3528.3	3772.1	4115.5	4480.9	4920.2	5193.3	5234.4
72.5°	2606.7	2640.5	2710.8	2805.8	2963.8	3117.3	3386.7	3656.2	3970.4	4281.8	4251.6
75°	1871.5	1886.1	1928.1	2031.3	2116.3	2254.2	2470.6	2691.6	2906.3	3048.8	3068.8
77.5°	972.7	1011.1	1070.5	1184.7	1276.9	1401.0	1541.8	1708.0	1865.1	1995.6	1960.0
80°	636.6	653.1	706.0	764.5	832.0	911.5	1005.6	1067.7	1087.8	1079.6	1087.8
82.5°	367.2	397.3	467.7	512.4	562.6	590.1	664.9	736.2	776.4	726.1	707.9
85°	46.6	60.3	189.9	239.3	274.0	315.1	337.9	380.8	355.3	317.8	387.3
87.5°	10.1	9.1	12.7	27.4	28.3	23.7	44.8	47.5	29.2	14.6	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156869

CATALOG NUMBER: AVS-E03-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5
2.5°	1080.5	1081.5	1083.2	1086.0	1087.8	1089.6	1091.5	1094.2	1096.1	1097.8	1101.5
5°	1076.0	1079.6	1083.2	1086.8	1091.5	1098.8	1103.3	1106.9	1110.7	1117.9	1120.7
7.5°	1073.2	1079.6	1085.1	1091.5	1098.8	1105.2	1113.4	1117.9	1123.4	1128.0	1133.5
10°	1071.4	1080.5	1086.0	1095.1	1103.3	1109.7	1118.9	1124.4	1130.8	1136.2	1139.0
12.5°	1075.0	1079.6	1085.1	1094.2	1104.2	1113.4	1123.4	1128.0	1133.5	1138.0	1139.0
15°	1090.6	1090.6	1091.5	1098.8	1108.8	1116.2	1124.4	1128.9	1131.6	1134.4	1134.4
17.5°	1118.9	1112.4	1107.9	1108.8	1115.2	1119.8	1124.4	1124.4	1122.5	1121.6	1119.8
20°	1151.7	1143.5	1134.4	1128.0	1126.1	1122.5	1119.8	1110.7	1103.3	1096.9	1092.3
22.5°	1199.3	1186.4	1173.7	1161.8	1150.8	1137.1	1121.6	1103.3	1086.0	1074.1	1066.8
25°	1257.7	1247.7	1232.1	1213.9	1200.1	1174.6	1154.5	1128.0	1106.1	1090.6	1077.7
27.5°	1340.8	1328.9	1314.3	1297.8	1277.8	1249.4	1224.8	1193.8	1167.3	1144.5	1128.0
30°	1444.0	1428.5	1417.5	1397.4	1383.7	1351.7	1327.0	1288.7	1237.6	1201.0	1178.2
32.5°	1549.9	1532.6	1523.4	1508.0	1492.4	1473.3	1435.8	1376.4	1310.7	1251.3	1212.0
35°	1691.5	1673.3	1656.8	1643.1	1620.3	1584.7	1551.8	1480.5	1390.2	1307.0	1241.2
37.5°	1869.6	1839.5	1798.3	1763.7	1723.5	1672.3	1622.1	1549.0	1445.8	1338.0	1250.4
40°	2059.6	2006.6	1948.2	1883.3	1813.9	1739.9	1682.4	1608.4	1492.4	1364.6	1243.9
42.5°	2257.8	2173.8	2092.4	2001.1	1904.4	1816.7	1741.8	1660.5	1527.2	1371.8	1218.4
45°	2454.2	2360.1	2236.8	2117.1	1994.7	1886.1	1802.1	1710.7	1559.1	1374.6	1184.7
47.5°	2616.8	2519.9	2379.3	2229.5	2084.2	1960.9	1862.3	1763.7	1602.0	1393.8	1176.4
50°	2788.5	2670.7	2514.4	2337.3	2172.8	2034.9	1929.9	1827.6	1662.3	1443.1	1202.9
52.5°	2975.6	2840.5	2657.8	2459.7	2279.7	2125.4	2011.2	1906.1	1739.1	1512.5	1253.2
55°	3204.0	3038.8	2840.5	2616.8	2424.0	2253.3	2127.2	2003.0	1830.4	1594.7	1316.2
57.5°	3553.0	3350.2	3127.4	2872.4	2658.8	2456.9	2306.2	2162.8	1971.9	1717.1	1402.0
60°	4184.0	3967.6	3678.0	3369.3	3118.1	2882.5	2661.6	2483.4	2248.7	1958.2	1592.0
62.5°	5088.3	4800.5	4414.2	3982.2	3653.4	3313.7	3064.2	2799.4	2508.1	2194.8	1815.8
65°	5590.6	5241.8	4724.8	4223.3	3800.4	3431.5	3114.5	2807.7	2484.4	2184.8	1867.8
66°	5652.7	5289.2	4752.1	4224.2	3780.3	3401.3	3068.0	2750.1	2419.5	2133.6	1845.9
67.5°	5627.2	5255.4	4702.0	4144.8	3693.6	3286.2	2941.9	2612.2	2282.5	2015.8	1772.8
70°	5207.9	4855.3	4311.9	3772.1	3343.7	2941.9	2613.1	2288.8	1986.5	1758.2	1579.2
72.5°	4324.7	4023.3	3551.1	3127.4	2791.2	2459.7	2181.0	1871.5	1615.8	1446.7	1340.8
75°	3121.9	2939.2	2509.0	2266.0	1971.0	1750.9	1480.5	1297.0	1113.4	1031.2	1013.0
77.5°	1971.9	1726.2	1453.2	1196.5	983.6	815.6	634.8	538.9	449.3	440.2	531.6
80°	998.3	898.8	692.3	551.7	463.9	375.3	296.8	224.7	157.1	189.0	226.5
82.5°	654.0	545.3	427.5	351.6	306.0	253.9	197.3	137.0	100.5	113.3	155.2
85°	353.5	301.5	242.9	191.8	155.2	138.9	93.2	65.8	64.9	69.4	88.6
87.5°	25.6	25.6	20.1	18.2	22.0	18.2	16.5	16.5	15.5	16.5	22.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156869

CATALOG NUMBER: AVS-E03-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5	1091.5
2.5°	1103.3	1106.1	1106.9	1111.5	1114.3	1116.2	1117.9	1117.9	1118.9	1121.6	1122.5
5°	1124.4	1128.9	1134.4	1138.0	1139.9	1145.4	1147.2	1147.2	1149.0	1152.6	1155.3
7.5°	1137.1	1143.5	1149.0	1150.8	1154.5	1156.3	1159.1	1160.8	1160.8	1164.6	1166.3
10°	1141.7	1145.4	1150.8	1150.8	1154.5	1154.5	1157.2	1158.1	1158.1	1161.8	1164.6
12.5°	1141.7	1143.5	1148.1	1148.1	1150.8	1151.7	1155.3	1158.1	1159.1	1163.6	1167.3
15°	1136.2	1138.0	1141.7	1142.6	1149.0	1152.6	1160.8	1166.3	1166.3	1170.9	1172.7
17.5°	1120.7	1125.3	1132.5	1139.9	1151.7	1160.0	1170.1	1174.6	1170.9	1168.2	1165.4
20°	1095.1	1103.3	1120.7	1139.0	1160.0	1170.9	1176.4	1171.8	1159.1	1146.2	1138.0
22.5°	1069.5	1086.0	1115.2	1142.6	1166.3	1173.7	1170.9	1154.5	1133.5	1117.9	1106.9
25°	1081.5	1100.6	1128.9	1153.6	1169.1	1167.3	1156.3	1133.5	1110.7	1090.6	1072.2
27.5°	1130.8	1151.7	1167.3	1175.4	1173.7	1160.8	1143.5	1117.9	1090.6	1064.0	1038.4
30°	1177.3	1188.3	1191.9	1185.5	1170.9	1149.9	1128.0	1098.8	1062.2	1029.3	1000.1
32.5°	1198.3	1187.4	1170.1	1152.6	1128.9	1110.7	1080.5	1048.5	1002.9	963.6	934.4
35°	1198.3	1154.5	1110.7	1074.1	1038.4	1015.6	980.9	938.0	896.0	863.1	840.3
37.5°	1171.8	1087.8	1015.6	956.3	911.5	886.8	834.8	796.5	760.8	749.8	735.2
40°	1123.4	999.2	895.1	817.4	760.8	724.2	672.2	645.7	632.0	626.5	623.8
42.5°	1058.5	900.5	761.8	665.8	604.7	563.5	528.8	512.4	511.5	510.6	510.6
45°	989.1	794.6	632.0	517.8	463.9	427.5	411.0	404.7	410.1	409.2	410.1
47.5°	946.2	714.2	513.3	391.8	350.8	326.9	318.8	321.5	326.1	324.2	324.2
50°	940.7	673.2	433.9	305.1	274.0	262.2	260.3	260.3	263.0	261.2	260.3
52.5°	960.8	666.7	392.7	262.2	237.5	227.5	225.6	224.7	223.7	218.3	213.7
55°	995.5	681.3	380.8	251.2	225.6	214.6	211.9	210.1	206.4	199.1	190.9
57.5°	1065.0	727.0	391.8	256.7	229.2	220.1	217.4	217.4	210.1	198.2	186.3
60°	1232.1	843.0	436.6	277.6	246.6	237.5	239.3	238.3	227.5	210.1	191.8
62.5°	1447.7	994.6	495.0	306.8	268.5	266.7	275.9	274.0	255.8	229.2	202.8
65°	1547.3	1065.9	511.5	313.3	273.1	281.3	299.6	297.7	274.9	238.3	204.6
66°	1549.0	1065.9	504.1	307.8	266.7	276.8	295.0	294.1	271.3	234.7	200.9
67.5°	1511.6	1036.7	483.2	296.8	253.9	261.2	277.6	276.8	255.8	225.6	193.7
70°	1371.0	928.0	429.3	277.6	236.6	233.0	238.3	234.7	221.0	200.0	178.1
72.5°	1174.6	779.1	374.5	263.0	224.7	210.1	206.4	203.6	192.7	180.8	167.2
75°	925.2	616.5	328.8	252.1	213.7	194.5	188.2	184.5	177.2	169.0	158.0
77.5°	570.9	441.1	286.8	237.5	205.5	186.3	181.8	176.3	165.3	155.2	147.0
80°	254.8	273.1	235.6	207.4	183.6	166.2	159.0	150.7	139.8	133.4	128.8
82.5°	169.8	176.3	170.8	155.2	138.9	125.1	114.2	114.2	112.3	106.8	105.1
85°	108.7	109.6	105.9	95.9	89.5	81.2	76.7	77.6	81.2	80.4	79.5
87.5°	24.7	24.7	29.2	27.4	31.9	33.8	36.6	39.3	44.8	44.8	47.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156869

CATALOG NUMBER: AVS-E03-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1091.5	1091.5	1091.5	1091.5	1091.5
2.5°	1123.4	1125.3	1127.0	1124.4	1125.3
5°	1155.3	1154.5	1159.1	1156.3	1158.1
7.5°	1165.4	1166.3	1170.1	1170.1	1170.9
10°	1166.3	1168.2	1172.7	1175.4	1177.3
12.5°	1170.9	1174.6	1181.9	1183.7	1183.7
15°	1174.6	1176.4	1180.9	1182.8	1184.7
17.5°	1161.8	1158.1	1160.0	1160.8	1160.0
20°	1129.8	1126.1	1125.3	1121.6	1123.4
22.5°	1095.1	1085.1	1078.7	1071.4	1071.4
25°	1053.1	1037.6	1024.8	1012.0	1014.7
27.5°	1013.8	993.7	980.9	972.7	970.9
30°	975.4	954.4	942.6	932.5	932.5
32.5°	911.5	896.9	881.3	875.0	874.1
35°	822.9	813.8	801.0	798.2	793.7
37.5°	723.4	720.6	709.6	708.8	704.1
40°	619.3	621.0	617.4	615.6	612.8
42.5°	515.1	524.2	522.5	521.6	519.7
45°	415.5	422.0	422.9	425.6	430.2
47.5°	326.9	328.8	330.7	329.7	330.7
50°	255.8	251.2	250.3	247.6	250.3
52.5°	206.4	199.1	195.4	191.8	189.9
55°	181.8	174.4	170.8	169.0	167.2
57.5°	175.3	168.1	162.6	159.0	158.0
60°	177.2	166.2	159.0	154.4	153.5
62.5°	181.8	167.2	157.1	152.5	151.6
65°	180.8	165.3	156.2	150.7	149.7
66°	178.1	163.5	154.4	149.7	148.9
67.5°	173.6	160.7	152.5	148.9	147.0
70°	165.3	157.1	150.7	146.1	144.4
72.5°	158.0	151.6	146.1	141.6	140.6
75°	149.7	144.4	138.9	135.1	134.3
77.5°	139.8	134.3	130.6	127.9	126.9
80°	123.3	119.7	116.0	112.3	112.3
82.5°	102.3	99.6	95.9	93.2	92.2
85°	78.5	78.5	75.9	73.1	72.1
87.5°	46.6	45.7	45.7	42.9	42.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)