

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P149759

Luminaire Tested: **AVS-E03-LED-E-U-SL2-HSS-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P149759
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33726)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-SL2-HSS-7030
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 2 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (63) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5024.1 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type II - Short - Non-Cutoff
BUG Rating: B0 - U0 - G2

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P149759

CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 10.6 fc
 Type II - Short - Non-Cutoff

REPORT NUMBER: P149759

CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P149759

CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	106.7	0.0	106.7
	% Fixture	2.1	0.0	2.1
Street Side	Lumens	4917.4	0.0	4917.4
	% Fixture	97.9	0.0	97.9
Total	Lumens	5024.1	0.0	5024.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.3	0.4
10°-20°	82.6	1.6
20°-30°	167.8	3.3
30°-40°	409.9	8.2
40°-50°	916.8	18.2
50°-60°	1289.1	25.7
60°-70°	1515.9	30.2
70°-80°	547.4	10.9
80°-90°	73.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5024.1	100.0
0°-180°	5024.1	100.0

Coefficient of Utilization



REPORT NUMBER: P149759


CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	237.4	4.7			
FM	(30°-60°)	2572.9	51.2			
FH	(60°-80°)	2034.1	40.5			G2/5000
FVH	(80°-90°)	73.0	1.5			G1/100
BL	(0°-30°)	34.3	0.7	B0/110		
BM	(30°-60°)	43.0	0.9	B0/220		
BH	(60°-80°)	29.2	0.6	B0/110		G0/110
BVH	(80°-90°)	0.2	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type II Short





REPORT NUMBER: P149759

CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	56°	57°	58°	59°
0°	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7
2.5°	252.1	254.8	253.0	248.4	242.9	235.6	229.2	229.2	228.3	225.6	226.5
5°	330.7	331.5	327.9	316.9	306.8	291.4	274.0	272.2	270.4	267.6	266.7
7.5°	407.4	411.0	407.4	395.4	375.3	351.6	324.2	321.5	316.1	316.1	312.3
10°	485.9	485.9	482.3	468.5	450.3	416.5	381.8	377.2	370.8	369.0	363.5
12.5°	541.7	541.7	539.8	532.4	517.8	487.8	445.7	441.1	433.0	430.2	423.8
15°	563.5	563.5	564.5	570.9	571.7	558.0	514.2	510.6	502.4	495.0	492.3
17.5°	577.2	576.4	576.4	585.5	601.9	611.0	582.7	579.1	569.9	566.3	557.1
20°	607.4	605.6	600.1	600.1	615.6	647.6	647.6	646.6	636.6	633.9	629.3
22.5°	652.1	650.3	633.9	620.2	627.5	667.7	705.1	703.3	699.6	696.0	693.3
25°	725.2	718.8	690.5	650.3	643.9	686.8	748.9	753.5	756.3	756.3	758.0
27.5°	835.8	827.5	777.3	702.4	674.1	717.9	797.3	806.5	814.7	816.6	824.8
30°	989.1	974.5	902.4	792.7	728.0	763.5	868.6	878.7	890.5	894.2	906.9
32.5°	1241.2	1233.1	1163.6	999.2	860.4	853.1	968.2	980.9	996.5	1002.9	1018.3
35°	1624.9	1626.6	1570.1	1422.1	1230.3	1129.8	1146.2	1157.2	1162.7	1181.9	1190.1
37.5°	1885.2	1889.7	1902.5	1844.0	1707.0	1604.8	1476.0	1487.9	1459.6	1462.3	1463.2
40°	2027.7	2042.3	2117.1	2173.8	2162.8	2103.4	2000.2	2006.6	1953.7	1941.8	1884.2
42.5°	2122.6	2141.8	2261.5	2436.8	2526.3	2580.2	2556.5	2553.7	2512.6	2497.1	2448.7
45°	2182.0	2199.4	2350.1	2608.5	2814.9	2972.0	3036.9	3044.1	3009.5	2994.0	2953.8
47.5°	2179.3	2199.4	2361.0	2672.4	2976.6	3227.8	3410.5	3419.6	3440.6	3426.8	3429.6
50°	2058.7	2077.8	2240.4	2563.7	2929.1	3344.7	3679.0	3708.2	3742.0	3764.9	3775.8
52.5°	1912.5	1926.2	2070.6	2377.4	2726.3	3296.3	3837.9	3888.1	3938.3	3981.2	4011.4
55°	1858.7	1874.2	1987.5	2242.3	2563.7	3093.5	3911.9	3985.9	4057.1	4127.5	4185.0
57.5°	1886.9	1901.6	1982.9	2178.3	2466.9	2879.8	3932.8	4048.0	4164.9	4279.1	4392.3
60°	1991.1	2006.6	2076.1	2237.7	2441.3	2756.5	3850.7	4041.6	4236.2	4435.2	4622.5
62.5°	1950.1	1956.4	2058.7	2341.9	2624.0	2651.5	3552.0	3818.8	4115.5	4422.5	4724.8
63°	1910.8	1918.0	2022.2	2313.5	2679.8	2636.0	3459.8	3741.0	4054.4	4385.0	4713.8
65°	1732.6	1733.6	1813.0	2043.2	2617.6	2663.3	3048.8	3317.3	3677.1	4073.6	4489.1
67.5°	1293.3	1286.9	1363.6	1539.0	2055.0	2664.2	2616.8	2767.5	3017.7	3369.3	3742.0
70°	458.5	448.5	572.6	815.6	1280.5	2179.3	2248.7	2258.8	2328.1	2518.1	2751.9
72.5°	148.9	151.6	182.7	298.7	590.1	1466.8	2035.9	2004.8	1986.5	1985.6	2016.7
75°	59.4	60.3	73.1	132.4	264.9	706.9	1782.9	1800.2	1806.6	1815.8	1825.8
77.5°	28.3	31.1	41.1	74.0	131.5	349.8	1276.0	1423.0	1507.0	1571.9	1611.2
80°	10.1	11.9	22.8	45.7	61.2	160.7	672.2	811.1	934.4	1093.3	1230.3
82.5°	0.0	0.0	4.6	31.9	33.8	64.9	275.9	323.3	369.9	479.5	615.6
85°	0.0	0.0	0.0	9.1	10.1	11.0	93.2	112.3	126.0	147.0	169.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.9	2.7	5.5	13.7	21.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P149759

CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

CANDELA DISTRIBUTION (continued):

	60°	61°	62°	64°	65°	66°	67°	68°	69°	70°	71°
0°	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7
2.5°	224.7	223.7	223.7	222.0	221.0	219.2	218.3	215.5	214.6	214.6	214.6
5°	265.8	262.2	260.3	255.8	253.0	252.1	247.6	245.7	242.9	243.8	239.3
7.5°	311.5	305.1	302.3	296.0	294.1	287.7	285.9	281.3	278.5	273.1	271.3
10°	361.7	353.5	348.9	338.9	336.1	331.5	326.1	320.6	316.1	310.6	307.8
12.5°	419.3	411.9	408.3	394.6	388.2	381.8	374.5	367.2	359.9	355.3	348.9
15°	486.8	474.9	471.3	458.5	447.6	439.3	429.3	420.1	414.6	405.5	399.2
17.5°	553.5	541.7	538.9	519.7	507.8	502.4	491.4	479.5	469.4	460.3	450.3
20°	620.2	611.9	604.7	586.3	573.6	564.5	549.8	537.9	529.7	517.0	504.1
22.5°	686.8	678.7	673.2	654.0	642.1	629.3	616.5	603.7	591.8	576.4	561.8
25°	755.3	749.8	747.2	729.7	718.8	706.9	694.2	679.5	664.9	647.6	632.0
27.5°	826.6	828.4	822.9	819.3	807.4	799.2	779.1	769.0	758.0	737.1	717.9
30°	917.0	922.5	920.6	923.4	916.1	910.6	895.1	882.3	869.5	849.4	827.5
32.5°	1031.2	1038.4	1042.2	1052.2	1048.5	1046.7	1042.2	1023.8	1014.7	980.0	970.9
35°	1207.5	1203.8	1219.3	1227.6	1223.9	1222.1	1216.6	1206.5	1195.5	1170.9	1148.1
37.5°	1436.7	1440.3	1445.8	1429.4	1418.4	1417.5	1401.0	1391.0	1375.5	1348.1	1320.7
40°	1856.9	1834.0	1808.4	1739.1	1708.9	1691.5	1643.1	1629.4	1602.9	1565.5	1537.2
42.5°	2403.0	2380.2	2303.4	2187.5	2125.4	2039.5	2000.2	1951.8	1914.4	1853.2	1820.3
45°	2945.6	2879.8	2870.7	2735.4	2658.8	2545.5	2475.1	2393.9	2308.9	2228.6	2170.2
47.5°	3403.1	3388.5	3343.7	3261.6	3190.4	3095.3	3005.0	2879.8	2792.1	2677.9	2573.0
50°	3769.4	3768.5	3752.0	3704.6	3645.2	3568.5	3489.0	3383.0	3283.5	3143.7	3031.4
52.5°	4043.4	4058.0	4063.5	4048.9	4026.0	3958.4	3918.2	3829.6	3745.7	3626.9	3505.4
55°	4244.4	4298.2	4325.6	4356.7	4350.3	4326.5	4324.7	4267.2	4228.8	4134.7	4048.9
57.5°	4492.7	4581.3	4666.3	4817.0	4822.5	4875.4	4902.9	4930.3	4937.6	4900.1	4871.8
60°	4808.8	4989.6	5150.4	5465.5	5547.7	5677.4	5761.5	5852.7	5930.4	5936.8	5934.9
62.5°	5031.6	5310.3	5569.6	6037.2	6197.1	6346.8	6459.2	6547.8	6601.7	6656.5	6682.1
63°	5038.0	5343.1	5619.0	6101.1	6269.2	6411.7	6518.5	6600.8	6657.4	6690.3	6706.7
65°	4883.7	5253.6	5582.4	6062.8	6220.8	6364.2	6419.9	6473.8	6501.2	6514.0	6465.6
67.5°	4139.3	4501.0	4884.6	5421.7	5556.8	5728.5	5774.2	5801.6	5814.4	5811.6	5770.6
70°	3095.3	3398.5	3825.1	4438.9	4617.9	4785.9	4890.1	4934.8	4949.4	4944.9	4883.7
72.5°	2161.0	2339.1	2690.8	3373.9	3617.8	3833.4	3962.1	4028.8	4042.5	4015.1	3958.4
75°	1814.8	1823.9	1903.4	2277.0	2505.3	2735.4	2880.7	2922.7	2895.3	2812.2	2667.9
77.5°	1620.3	1640.4	1640.4	1696.1	1740.8	1804.8	1818.4	1716.2	1597.4	1444.0	1319.8
80°	1359.1	1429.4	1478.8	1519.8	1524.4	1511.6	1477.8	1420.3	1328.9	1212.0	1082.3
82.5°	825.7	964.5	1021.1	1233.1	1337.1	1407.5	1402.0	1325.3	1255.9	1134.4	1023.8
85°	208.3	224.7	243.8	316.9	355.3	433.9	483.2	506.0	514.2	472.2	427.5
87.5°	20.1	13.7	22.8	17.3	24.7	18.2	24.7	22.8	28.3	30.2	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P149759

CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

CANDELA DISTRIBUTION (continued):

	72°	73°	74°	75°	76°	77°	78°	79°	80°	81°	82°
0°	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7
2.5°	212.8	211.9	211.0	210.1	209.1	208.3	206.4	206.4	204.6	203.6	202.8
5°	236.6	234.7	233.8	232.0	229.2	227.5	224.7	221.0	218.3	217.4	215.5
7.5°	266.7	262.2	260.3	257.6	253.9	248.4	244.8	242.1	237.5	234.7	229.2
10°	300.5	296.0	290.5	285.0	279.5	273.1	268.5	264.9	257.6	253.9	247.6
12.5°	343.4	335.2	328.8	321.5	314.2	306.8	301.5	290.5	284.0	275.9	270.4
15°	387.3	380.0	372.6	363.5	352.5	340.7	335.2	325.2	316.9	304.1	296.8
17.5°	440.2	426.5	415.5	404.7	394.6	383.6	372.6	357.1	345.3	334.3	319.7
20°	492.3	475.9	463.9	449.3	434.7	417.4	404.7	393.7	377.2	362.6	347.0
22.5°	548.0	531.6	512.4	497.8	477.7	463.9	446.6	428.4	411.9	392.7	373.6
25°	615.6	598.2	576.4	557.1	534.3	515.1	494.1	473.2	453.1	431.1	406.4
27.5°	698.8	680.4	656.7	633.9	603.7	580.0	559.9	531.6	506.0	478.5	450.3
30°	803.7	783.6	754.4	721.6	691.4	664.9	636.6	599.2	570.9	537.9	501.5
32.5°	940.7	917.0	877.7	846.6	809.2	774.5	735.2	697.8	657.6	614.7	572.6
35°	1113.4	1091.5	1045.8	1000.1	959.1	917.9	868.6	825.7	769.0	717.0	663.1
37.5°	1292.4	1253.2	1211.1	1161.8	1110.7	1061.3	1001.0	941.7	876.8	820.2	752.6
40°	1497.0	1449.5	1414.8	1361.8	1289.6	1219.3	1163.6	1089.6	1008.3	932.5	853.1
42.5°	1777.4	1724.5	1662.3	1582.0	1529.8	1447.7	1375.5	1287.9	1180.9	1096.1	1000.1
45°	2101.7	2029.4	1969.2	1891.5	1828.5	1726.2	1642.2	1525.3	1418.4	1307.0	1190.1
47.5°	2471.5	2382.0	2294.3	2217.6	2117.1	2016.7	1909.8	1785.6	1648.6	1526.2	1387.4
50°	2896.3	2769.3	2647.8	2549.1	2411.3	2295.2	2179.3	2039.5	1887.9	1747.3	1589.2
52.5°	3368.4	3221.3	3060.6	2909.0	2749.2	2600.3	2460.5	2299.8	2130.9	1959.2	1782.9
55°	3938.3	3827.9	3638.8	3446.1	3232.3	3033.3	2853.3	2654.2	2448.7	2223.1	2037.7
57.5°	4830.7	4776.8	4618.9	4426.1	4147.6	3905.5	3600.4	3356.6	3058.9	2748.3	2509.0
60°	6040.0	5973.3	5884.8	5728.5	5507.5	5178.7	4842.6	4463.5	4010.6	3580.3	3172.0
62.5°	6684.8	6661.0	6588.9	6481.1	6274.7	6015.3	5676.5	5260.0	4748.5	4226.1	3705.5
63°	6704.0	6673.9	6611.7	6502.2	6320.4	6069.2	5736.8	5332.1	4831.6	4299.2	3767.6
65°	6444.6	6432.7	6369.7	6250.1	6125.8	5934.0	5676.5	5328.5	4908.4	4405.1	3876.3
67.5°	5715.8	5680.1	5583.3	5546.7	5460.0	5326.6	5130.3	4891.0	4590.5	4195.0	3738.3
70°	4834.4	4781.3	4659.9	4595.0	4489.1	4405.1	4285.4	4114.6	3929.2	3653.4	3312.7
72.5°	3900.0	3790.4	3679.0	3510.1	3362.1	3212.2	3079.8	2959.3	2755.5	2644.1	2385.7
75°	2532.7	2333.6	2142.7	1886.9	1656.8	1453.2	1254.9	1154.5	945.3	860.4	738.9
77.5°	1202.0	1090.6	940.7	824.8	676.8	552.5	451.2	338.9	265.8	208.3	159.0
80°	969.9	875.9	785.5	680.4	569.0	453.9	348.0	260.3	184.5	127.9	90.5
82.5°	865.0	762.7	651.2	579.1	503.2	411.9	337.9	275.9	203.6	148.9	101.3
85°	336.1	283.1	218.3	178.1	138.9	114.2	103.2	71.2	55.8	43.8	33.8
87.5°	29.2	23.7	19.2	12.7	13.7	7.4	8.2	5.5	4.6	4.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P149759

CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

CANDELA DISTRIBUTION (continued):

	83°	84°	85°	86°	87°	88°	89°	90°	95°	105°	115°
0°	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7	192.7
2.5°	201.9	200.9	200.0	198.2	198.2	196.4	195.4	194.5	189.9	179.9	171.7
5°	211.9	210.1	208.3	205.5	203.6	200.9	199.1	196.4	186.3	167.2	150.7
7.5°	226.5	222.9	220.1	214.6	211.9	208.3	205.5	200.9	184.5	155.2	132.4
10°	243.8	237.5	233.0	226.5	221.0	216.5	211.9	205.5	182.7	142.5	116.0
12.5°	264.9	257.6	248.4	241.1	233.8	227.5	221.0	212.8	179.9	131.5	103.2
15°	285.9	274.9	268.5	258.4	248.4	239.3	230.2	222.9	180.8	119.7	92.2
17.5°	309.6	298.7	285.0	274.0	263.0	251.2	240.2	225.6	176.3	110.5	84.0
20°	332.4	316.9	304.1	290.5	274.9	260.3	246.6	233.8	172.6	101.3	76.7
22.5°	357.1	338.9	322.4	305.1	285.9	269.4	253.0	236.6	166.2	93.2	70.4
25°	387.3	366.2	342.5	321.5	301.5	281.3	260.3	240.2	159.8	85.9	65.8
27.5°	423.8	396.4	372.6	346.1	317.8	292.2	269.4	247.6	153.5	80.4	61.2
30°	470.4	438.4	404.7	370.8	340.7	311.5	279.5	252.1	147.0	74.9	56.6
32.5°	532.4	492.3	451.2	411.9	371.7	334.3	300.5	264.9	143.4	70.4	52.0
35°	614.7	562.6	512.4	463.1	414.6	369.0	325.2	285.0	143.4	64.9	46.6
37.5°	692.3	632.0	568.1	506.9	449.3	396.4	344.4	296.0	136.1	60.3	42.0
40°	776.4	704.1	629.3	557.1	487.8	422.0	362.6	306.8	129.7	54.8	37.4
42.5°	905.2	813.8	716.1	632.0	548.9	467.7	393.7	327.9	121.5	49.3	32.8
45°	1074.1	958.1	843.0	740.7	634.8	535.2	447.6	366.2	119.7	44.8	28.3
47.5°	1254.9	1117.9	982.8	852.1	728.0	611.9	506.9	409.2	119.7	40.2	24.7
50°	1434.9	1263.2	1118.9	967.3	827.5	690.5	565.4	453.9	120.5	36.6	20.1
52.5°	1597.4	1413.9	1252.2	1076.9	922.5	763.5	627.5	497.8	118.8	31.9	16.5
55°	1823.0	1607.5	1420.3	1226.6	1045.8	866.7	712.4	563.5	119.7	28.3	13.7
57.5°	2238.7	1985.6	1760.0	1506.1	1297.8	1066.8	879.6	698.8	130.6	23.7	10.1
60°	2835.0	2506.2	2189.3	1879.7	1614.8	1339.9	1096.9	884.1	153.5	19.2	7.4
62.5°	3236.0	2805.8	2427.7	2086.1	1778.3	1490.6	1225.7	983.6	169.0	15.5	4.6
63°	3277.1	2832.3	2452.3	2099.8	1785.6	1497.9	1231.2	991.0	169.8	14.6	4.6
65°	3354.7	2877.9	2466.0	2102.5	1778.3	1487.9	1227.6	990.1	171.7	11.9	3.6
67.5°	3266.1	2807.7	2386.6	2023.9	1714.4	1428.5	1181.9	953.6	170.8	8.2	2.7
70°	2920.9	2540.9	2171.0	1833.1	1551.8	1293.3	1076.0	869.5	157.1	5.5	1.9
72.5°	2144.6	1886.1	1599.3	1355.4	1169.1	970.9	828.4	653.1	121.5	3.6	0.9
75°	635.6	579.1	486.8	429.3	379.1	313.3	278.5	217.4	62.1	1.9	0.0
77.5°	126.9	115.1	103.2	94.1	88.6	75.9	72.1	59.4	25.6	0.9	0.0
80°	66.6	54.8	46.6	41.1	35.6	29.2	24.7	20.1	4.6	0.0	0.0
82.5°	63.9	42.9	31.1	25.6	22.0	17.3	13.7	10.1	2.7	0.0	0.0
85°	23.7	18.2	13.7	11.0	9.1	8.2	6.4	5.5	0.0	0.0	0.0
87.5°	3.6	2.7	2.7	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P149759

CATALOG NUMBER: AVS-E03-LED-E-U-SL2-HSS-7030

CANDELA DISTRIBUTION (continued):

	125°	135°	145°	155°	165°	175°	180°
0°	192.7	192.7	192.7	192.7	192.7	192.7	192.7
2.5°	163.5	156.2	152.5	148.0	148.0	147.0	148.9
5°	136.1	126.0	118.8	113.3	114.2	111.4	112.3
7.5°	115.1	105.1	98.7	95.0	94.1	93.2	93.2
10°	99.6	90.5	85.0	82.2	81.2	81.2	81.2
12.5°	88.6	79.5	74.9	73.1	73.1	72.1	72.1
15°	79.5	72.1	67.6	65.8	65.8	64.9	65.8
17.5°	72.1	64.9	61.2	59.4	59.4	58.4	58.4
20°	65.8	59.4	55.8	53.0	53.0	52.0	53.0
22.5°	60.3	53.9	49.3	47.5	46.6	45.7	46.6
25°	54.8	48.4	43.8	41.1	40.2	40.2	39.3
27.5°	50.3	43.8	38.3	35.6	34.7	34.7	33.8
30°	45.7	38.3	32.8	30.2	29.2	29.2	29.2
32.5°	41.1	32.8	28.3	25.6	24.7	24.7	24.7
35°	36.6	28.3	23.7	21.0	20.1	20.1	20.1
37.5°	31.1	23.7	18.2	16.5	15.5	14.6	14.6
40°	26.5	18.2	13.7	11.9	10.1	10.1	10.1
42.5°	22.0	14.6	10.1	7.4	6.4	5.5	6.4
45°	18.2	11.0	6.4	3.6	2.7	2.7	2.7
47.5°	14.6	7.4	2.7	0.9	0.9	0.9	0.9
50°	11.0	4.6	0.9	0.0	0.0	0.9	0.9
52.5°	8.2	2.7	0.0	0.0	0.0	0.0	0.0
55°	4.6	0.9	0.0	0.0	0.0	0.0	0.0
57.5°	2.7	0.0	0.0	0.0	0.0	0.0	0.0
60°	1.9	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.9	0.0	0.0	0.0	0.0	0.0	0.0
63°	0.9	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.9	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)