

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152619

Luminaire Tested: **AVS-E04-LED-E-U-SL4-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152619
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E04-LED-E-U-SL4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (84) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10792.6 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 97.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152619

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 5.8 fc
Type IV - Short - Full Cutoff

REPORT NUMBER: P152619

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P152619

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2240.4	0.0	2240.4
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	8552.1	0.0	8552.1
	% Fixture	79.2	0.0	79.2
Total	Lumens	10792.6	0.0	10792.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.1	2.0
10°-20°	589.0	5.5
20°-30°	871.9	8.1
30°-40°	1101.8	10.2
40°-50°	1246.1	11.5
50°-60°	1773.2	16.4
60°-70°	3302.4	30.6
70°-80°	1513.5	14.0
80°-90°	179.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10792.6	100.0
0°-180°	10792.6	100.0

Coefficient of Utilization



REPORT NUMBER: P152619


CATALOG NUMBER: AVS-E04-LED-E-U-SL4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	982.7	9.1			
FM	(30°-60°)	3161.9	29.3			
FH	(60°-80°)	4274.3	39.6			G2/5000
FVH	(80°-90°)	133.3	1.2			G2/225
BL	(0°-30°)	693.2	6.4	B2/1000		
BM	(30°-60°)	959.2	8.9	B1/1000		
BH	(60°-80°)	541.6	5.0	B2/1000		G2/1000
BVH	(80°-90°)	46.4	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P152619

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9
2.5°	2338.1	2344.2	2337.0	2335.8	2335.8	2334.5	2327.3	2326.0	2316.3	2317.5	2319.9
5°	2355.2	2357.6	2352.7	2351.6	2349.1	2344.2	2338.1	2330.9	2323.5	2316.3	2310.2
7.5°	2372.2	2369.8	2366.2	2366.2	2362.5	2355.2	2343.0	2333.3	2317.5	2308.9	2298.0
10°	2396.6	2393.0	2388.1	2385.7	2379.6	2368.6	2351.6	2338.1	2318.7	2301.7	2283.4
12.5°	2419.8	2418.5	2411.3	2407.6	2397.8	2386.8	2366.2	2345.5	2319.9	2293.2	2268.8
15°	2461.1	2456.3	2449.0	2441.7	2425.9	2411.3	2379.6	2355.2	2318.7	2283.4	2245.6
17.5°	2533.1	2524.5	2517.2	2501.3	2481.9	2456.3	2410.1	2368.6	2318.7	2267.6	2224.9
20°	2664.6	2646.3	2636.6	2615.9	2581.8	2535.4	2463.6	2396.6	2322.4	2256.6	2199.4
22.5°	2813.2	2800.9	2787.6	2774.2	2720.5	2653.6	2556.2	2456.3	2344.2	2251.7	2178.7
25°	2980.0	2964.1	2956.8	2933.7	2883.7	2807.0	2674.3	2535.4	2394.2	2271.2	2178.7
27.5°	3128.5	3123.6	3122.5	3095.6	3048.2	2958.0	2800.9	2634.1	2462.4	2311.4	2196.9
30°	3263.7	3258.9	3256.4	3241.8	3186.9	3079.8	2909.3	2721.8	2536.7	2367.4	2231.0
32.5°	3407.4	3391.6	3384.2	3356.3	3294.2	3168.7	2973.9	2779.1	2595.1	2422.2	2268.8
35°	3524.4	3510.9	3496.3	3456.2	3368.4	3219.9	3001.9	2798.5	2618.2	2452.6	2288.3
37.5°	3609.5	3596.2	3575.4	3524.4	3416.0	3236.9	3000.6	2792.4	2609.7	2447.8	2291.9
40°	3647.4	3633.9	3612.0	3547.5	3424.5	3227.2	2977.5	2764.5	2584.1	2422.2	2277.3
42.5°	3632.7	3623.0	3594.9	3532.8	3397.6	3183.3	2931.3	2712.0	2535.4	2380.8	2244.5
45°	3576.7	3569.3	3542.6	3476.8	3336.8	3112.7	2863.0	2646.3	2477.0	2329.6	2200.5
47.5°	3492.6	3490.3	3463.4	3398.9	3260.1	3042.1	2792.4	2581.8	2418.5	2279.7	2164.0
50°	3400.1	3387.9	3374.5	3314.8	3188.2	2981.1	2741.2	2541.6	2385.7	2261.5	2148.2
52.5°	3341.7	3338.0	3325.8	3272.2	3150.5	2945.9	2718.1	2526.9	2383.2	2257.8	2139.7
55°	3860.4	3868.9	3756.9	3524.4	3319.7	3043.3	2787.6	2601.2	2442.9	2316.3	2229.7
57.5°	5710.3	5672.5	5480.1	5018.5	4497.3	3809.3	3313.7	3012.8	2816.8	2838.7	2882.5
60°	6652.8	6645.5	6610.3	6431.2	6084.1	5560.5	4979.6	4313.5	4101.6	4124.7	4141.8
62.5°	7074.2	7085.2	7111.9	7045.0	6953.7	6801.5	6511.6	6243.6	5959.9	5854.0	5570.3
65°	7269.0	7288.5	7349.4	7387.2	7422.5	7449.3	7563.7	7877.9	8085.0	7697.7	6796.6
67.5°	6866.0	6959.7	7160.6	7356.7	7532.1	7781.8	8169.0	8898.4	9406.3	8930.2	7623.4
70°	5005.2	5133.1	5363.2	5969.6	6617.5	7183.8	7934.0	9044.6	9810.6	9442.8	7828.0
72.5°	3138.2	3173.6	3275.9	3498.8	3979.8	4706.8	6018.3	7684.4	8568.4	8274.9	6616.3
75°	1991.1	2003.3	1999.6	2050.8	2132.3	2290.7	2809.4	4538.8	5869.8	5411.9	3687.5
77.5°	1186.1	1204.5	1211.7	1227.6	1266.5	1322.5	1365.2	1544.1	2461.1	2389.3	1338.3
80°	993.7	1008.3	996.2	992.5	968.2	951.1	971.8	951.1	882.9	850.1	783.0
82.5°	526.1	524.9	521.2	556.6	628.4	684.4	727.0	717.3	649.1	552.8	468.8
85°	288.6	298.3	298.3	310.6	299.6	300.8	310.6	327.6	303.2	253.3	207.0
87.5°	24.4	37.7	30.5	37.7	51.2	36.6	35.3	35.3	30.5	22.0	19.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152619

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9
2.5°	2313.8	2311.4	2306.5	2302.9	2302.9	2296.8	2293.2	2290.7	2289.4	2284.6	2284.6
5°	2306.5	2298.0	2289.4	2283.4	2279.7	2273.7	2263.9	2259.1	2253.0	2248.1	2245.6
7.5°	2290.7	2274.8	2261.5	2251.7	2239.6	2229.7	2217.6	2206.6	2195.6	2190.8	2188.4
10°	2266.3	2245.6	2224.9	2206.6	2189.6	2172.5	2156.7	2140.9	2127.5	2117.7	2108.0
12.5°	2243.2	2211.5	2184.8	2157.9	2131.2	2110.5	2088.5	2065.4	2045.9	2027.7	2022.8
15°	2211.5	2175.0	2140.9	2108.0	2075.1	2041.0	2014.2	1988.7	1957.0	1936.3	1920.5
17.5°	2182.3	2138.4	2097.1	2058.0	2017.9	1982.6	1942.4	1908.3	1876.6	1845.0	1821.9
20°	2150.7	2103.1	2059.3	2015.4	1971.6	1926.5	1880.3	1836.5	1797.5	1759.7	1722.0
22.5°	2122.6	2073.9	2031.3	1983.8	1935.1	1883.9	1830.4	1775.5	1730.5	1681.8	1637.9
25°	2105.6	2052.0	2008.2	1961.9	1908.3	1852.2	1791.4	1726.8	1672.0	1616.1	1563.6
27.5°	2105.6	2036.2	1991.1	1944.9	1890.1	1830.4	1763.4	1692.7	1630.7	1568.5	1503.9
30°	2123.8	2038.5	1977.7	1929.0	1873.0	1808.4	1734.2	1659.9	1591.7	1518.5	1456.5
32.5°	2140.9	2043.4	1968.0	1905.9	1841.3	1778.0	1702.5	1623.3	1547.9	1478.4	1412.6
35°	2151.8	2043.4	1949.7	1870.6	1797.5	1735.3	1661.0	1582.0	1505.2	1437.0	1376.2
37.5°	2153.1	2033.7	1920.5	1830.4	1753.7	1689.1	1618.4	1544.1	1471.1	1407.8	1356.6
40°	2140.9	2014.2	1891.3	1787.8	1707.4	1641.6	1577.1	1510.1	1444.4	1391.9	1348.1
42.5°	2119.0	1993.6	1863.2	1753.7	1669.6	1601.5	1541.8	1484.5	1427.3	1382.2	1345.7
45°	2086.1	1965.5	1837.6	1733.0	1650.2	1578.2	1519.8	1472.3	1423.6	1385.9	1349.3
47.5°	2056.9	1955.8	1846.2	1746.3	1659.9	1585.6	1525.9	1485.7	1448.0	1422.4	1372.4
50°	2050.8	1950.9	1849.8	1757.3	1669.6	1594.1	1541.8	1521.0	1510.1	1494.2	1417.5
52.5°	2033.7	1949.7	1876.6	1825.5	1769.4	1734.2	1679.4	1698.9	1686.6	1630.7	1491.8
55°	2212.7	2237.1	2305.3	2402.7	2492.8	2513.6	2507.5	2484.4	2361.3	2031.3	1670.8
57.5°	3042.1	3179.7	3308.8	3366.0	3358.7	3294.2	3247.9	3154.1	2976.3	2574.4	2023.9
60°	4194.1	4216.1	4147.9	4046.7	3876.3	3733.8	3581.6	3406.2	3148.0	2754.7	2240.7
62.5°	5254.8	4960.1	4656.9	4371.9	4112.5	3886.0	3674.1	3429.3	3093.3	2682.8	2212.7
65°	6003.7	5380.2	4901.7	4492.4	4125.9	3809.3	3545.0	3227.2	2848.4	2478.2	2050.8
67.5°	6389.8	5433.8	4699.5	4129.5	3609.5	3171.2	2819.2	2509.8	2228.6	2066.6	1795.0
70°	5958.7	4611.8	3588.8	2944.7	2322.4	1862.0	1471.1	1234.8	1153.3	1306.7	1359.1
72.5°	4440.1	3001.9	2134.8	1651.3	1265.3	1008.3	773.3	607.7	494.4	518.8	673.5
75°	2099.5	1295.8	915.8	696.6	554.1	459.1	375.1	343.4	287.4	238.7	224.0
77.5°	817.1	595.5	492.0	360.5	255.8	205.8	175.3	169.2	173.0	168.1	165.6
80°	622.3	421.3	264.2	193.7	166.8	147.4	130.3	125.4	127.9	134.0	140.0
82.5°	347.0	216.8	160.7	140.0	125.4	107.2	97.4	90.2	91.3	98.7	112.0
85°	134.0	104.8	96.2	92.5	86.4	69.4	59.7	60.9	69.4	82.8	82.8
87.5°	14.6	14.6	19.5	14.6	14.6	14.6	13.4	15.9	17.1	22.0	25.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152619

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9	2302.9
2.5°	2282.2	2282.2	2282.2	2279.7	2280.9	2276.1	2276.1	2272.4	2278.5	2274.8	2273.7
5°	2246.8	2245.6	2240.7	2240.7	2240.7	2240.7	2244.5	2234.7	2242.0	2242.0	2238.3
7.5°	2187.2	2187.2	2173.8	2181.0	2178.7	2182.3	2187.2	2182.3	2189.6	2194.5	2190.8
10°	2104.4	2104.4	2093.4	2102.0	2098.2	2106.8	2115.3	2110.5	2115.3	2122.6	2125.1
12.5°	2013.1	2008.2	1998.4	2002.1	2002.1	2006.9	2010.6	2016.7	2022.8	2032.5	2037.4
15°	1907.0	1899.8	1887.6	1887.6	1880.3	1882.7	1890.1	1892.4	1904.7	1918.0	1933.9
17.5°	1798.7	1780.4	1767.0	1751.2	1739.1	1748.8	1757.3	1763.4	1773.2	1793.8	1804.8
20°	1696.4	1659.9	1634.3	1613.6	1600.2	1606.3	1617.2	1624.6	1633.1	1637.9	1641.6
22.5°	1595.3	1553.9	1518.5	1493.1	1471.1	1477.2	1472.3	1468.7	1474.7	1459.0	1457.7
25°	1507.7	1459.0	1411.4	1381.0	1354.2	1345.7	1320.1	1314.0	1297.0	1283.5	1273.8
27.5°	1444.4	1381.0	1328.6	1293.3	1250.7	1219.1	1186.1	1153.3	1135.0	1113.1	1102.1
30°	1394.4	1327.4	1265.3	1205.6	1149.6	1100.9	1057.1	1014.4	985.2	953.6	932.8
32.5°	1348.1	1286.0	1210.5	1128.9	1053.4	998.5	941.3	892.6	846.3	805.0	774.5
35°	1316.5	1247.0	1150.8	1051.0	965.7	901.1	840.3	770.9	714.8	661.2	628.4
37.5°	1299.4	1214.2	1096.1	985.2	890.3	817.1	741.7	661.2	593.1	543.1	493.2
40°	1286.0	1181.2	1047.4	926.7	826.8	739.2	651.5	556.6	481.0	428.7	389.7
42.5°	1271.4	1144.8	1004.7	880.5	769.6	667.4	561.5	460.3	388.5	351.9	334.9
45°	1255.5	1113.1	964.5	836.6	713.7	589.4	467.7	373.9	331.2	319.1	319.1
47.5°	1251.9	1092.3	935.2	794.0	650.3	499.3	381.1	322.7	310.6	313.0	317.8
50°	1266.5	1086.3	909.7	744.0	566.3	404.4	322.7	303.2	305.7	313.0	320.3
52.5°	1301.9	1091.2	882.9	674.6	466.4	333.7	298.3	297.1	304.5	315.4	322.7
55°	1361.5	1091.2	831.7	571.2	372.6	299.6	289.8	294.7	304.5	314.2	320.3
57.5°	1489.3	1080.2	741.7	456.7	311.7	287.4	287.4	293.5	302.0	311.7	316.6
60°	1641.6	1065.6	615.0	353.2	281.3	277.6	286.2	293.5	300.8	309.3	314.2
62.5°	1651.3	1027.8	487.2	292.2	265.5	271.6	285.0	294.7	297.1	303.2	309.3
65°	1517.4	896.3	387.3	261.9	258.1	267.9	281.3	288.6	289.8	292.2	298.3
67.5°	1328.6	730.7	313.0	247.3	250.9	261.9	269.1	275.2	278.9	285.0	286.2
70°	1091.2	586.9	267.9	232.6	236.3	248.4	254.5	260.6	267.9	275.2	271.6
72.5°	773.3	456.7	235.0	216.8	221.7	232.6	239.9	244.8	250.9	258.1	253.3
75°	328.8	319.1	203.4	196.1	203.4	210.7	218.0	225.3	231.4	235.0	235.0
77.5°	168.1	187.6	175.3	175.3	180.2	187.6	193.7	200.9	204.6	208.3	213.2
80°	142.5	144.9	147.4	152.2	157.1	164.4	170.5	176.6	177.8	179.1	181.5
82.5°	118.1	123.0	125.4	132.7	136.4	138.9	142.5	142.5	144.9	144.9	141.2
85°	85.3	91.3	95.0	96.2	95.0	96.2	97.4	99.9	105.9	105.9	101.0
87.5°	24.4	23.1	29.2	30.5	32.8	37.7	42.6	51.2	53.6	56.1	56.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152619

CATALOG NUMBER: AVS-E04-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2302.9	2302.9	2302.9	2302.9
2.5°	2272.4	2274.8	2269.9	2271.2
5°	2238.3	2243.2	2237.1	2244.5
7.5°	2194.5	2201.8	2200.5	2199.4
10°	2131.2	2140.9	2140.9	2144.6
12.5°	2050.8	2056.9	2061.8	2064.1
15°	1942.4	1953.4	1959.5	1959.5
17.5°	1812.1	1819.4	1823.0	1818.1
20°	1646.4	1644.0	1645.3	1633.1
22.5°	1455.2	1459.0	1448.0	1450.4
25°	1267.8	1261.7	1266.5	1259.2
27.5°	1086.3	1087.5	1074.1	1080.2
30°	913.4	907.3	890.3	898.8
32.5°	746.5	730.7	712.4	701.5
35°	589.4	565.1	556.6	552.8
37.5°	462.8	436.0	427.5	417.7
40°	367.8	358.0	354.4	356.8
42.5°	330.1	330.1	332.4	333.7
45°	320.3	323.9	327.6	328.8
47.5°	321.5	325.2	330.1	331.2
50°	323.9	327.6	331.2	332.4
52.5°	325.2	325.2	327.6	328.8
55°	322.7	321.5	322.7	323.9
57.5°	317.8	315.4	316.6	320.3
60°	315.4	311.7	314.2	316.6
62.5°	309.3	308.1	310.6	311.7
65°	296.0	297.1	300.8	300.8
67.5°	283.7	285.0	286.2	287.4
70°	269.1	270.4	272.7	274.0
72.5°	252.1	257.0	260.6	265.5
75°	238.7	243.5	250.9	255.8
77.5°	215.5	219.2	227.8	233.8
80°	182.7	181.5	182.7	186.3
82.5°	140.0	140.0	138.9	137.6
85°	98.7	97.4	93.8	93.8
87.5°	53.6	52.3	51.2	48.7
90°	0.0	0.0	0.0	0.0

(END OF REPORT)