

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152609

Luminaire Tested: **AVS-E03-LED-E-U-SL4-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152609
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-SL4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (63) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8094.4 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152609

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 17.4 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152609

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P152609

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1680.3	0.0	1680.3
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	6414.1	0.0	6414.1
	% Fixture	79.2	0.0	79.2
Total	Lumens	8094.4	0.0	8094.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	2.0
10°-20°	441.7	5.5
20°-30°	653.9	8.1
30°-40°	826.3	10.2
40°-50°	934.6	11.5
50°-60°	1329.9	16.4
60°-70°	2476.8	30.6
70°-80°	1135.1	14.0
80°-90°	134.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8094.4	100.0
0°-180°	8094.4	100.0

Coefficient of Utilization



REPORT NUMBER: P152609


CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	737.1	9.1			
FM	(30°-60°)	2371.4	29.3			
FH	(60°-80°)	3205.7	39.6			G2/5000
FVH	(80°-90°)	100.0	1.2			G1/100
BL	(0°-30°)	519.9	6.4	B2/1000		
BM	(30°-60°)	719.4	8.9	B1/1000		
BH	(60°-80°)	406.2	5.0	B1/500		G1/500
BVH	(80°-90°)	34.8	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P152609

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2
2.5°	1753.7	1758.2	1752.7	1751.8	1751.8	1750.9	1745.4	1744.5	1737.2	1738.1	1739.9
5°	1766.4	1768.3	1764.6	1763.7	1761.9	1758.2	1753.7	1748.2	1742.7	1737.2	1732.6
7.5°	1779.2	1777.4	1774.6	1774.6	1771.9	1766.4	1757.3	1749.9	1738.1	1731.7	1723.5
10°	1797.5	1794.7	1791.1	1789.2	1784.7	1776.5	1763.7	1753.7	1739.1	1726.2	1712.5
12.5°	1814.8	1813.9	1808.4	1805.7	1798.3	1790.2	1774.6	1759.1	1739.9	1719.8	1701.6
15°	1845.9	1842.2	1836.8	1831.3	1819.4	1808.4	1784.7	1766.4	1739.1	1712.5	1684.2
17.5°	1899.8	1893.4	1887.9	1876.1	1861.5	1842.2	1807.6	1776.5	1739.1	1700.6	1668.7
20°	1998.4	1984.7	1977.4	1961.9	1936.3	1901.6	1847.7	1797.5	1741.8	1692.4	1649.5
22.5°	2109.8	2100.7	2090.7	2080.6	2040.4	1990.2	1917.1	1842.2	1758.2	1688.8	1634.0
25°	2234.9	2223.1	2217.6	2200.3	2162.8	2105.3	2005.7	1901.6	1795.6	1703.4	1634.0
27.5°	2346.4	2342.7	2341.9	2321.8	2286.1	2218.5	2100.7	1975.5	1846.8	1733.6	1647.7
30°	2447.8	2444.1	2442.3	2431.3	2390.3	2309.8	2182.0	2041.3	1902.5	1775.5	1673.3
32.5°	2555.5	2543.7	2538.2	2517.2	2470.6	2376.6	2230.4	2084.2	1946.3	1816.7	1701.6
35°	2643.2	2633.2	2622.3	2592.1	2526.3	2414.9	2251.4	2098.9	1963.7	1839.5	1716.2
37.5°	2707.2	2697.1	2681.6	2643.2	2562.0	2427.7	2250.5	2094.3	1957.3	1835.9	1719.0
40°	2735.4	2725.4	2709.0	2660.6	2568.3	2420.4	2233.2	2073.3	1938.1	1816.7	1708.0
42.5°	2724.6	2717.2	2696.2	2649.6	2548.3	2387.5	2198.4	2034.0	1901.6	1785.6	1683.3
45°	2682.5	2677.0	2656.9	2607.6	2502.6	2334.5	2147.3	1984.7	1857.7	1747.3	1650.5
47.5°	2619.5	2617.6	2597.6	2549.1	2445.1	2281.6	2094.3	1936.3	1813.9	1709.7	1623.0
50°	2550.1	2540.9	2530.9	2486.1	2391.2	2235.9	2056.0	1906.1	1789.2	1696.1	1611.2
52.5°	2506.2	2503.5	2494.4	2454.2	2362.8	2209.4	2038.5	1895.2	1787.5	1693.4	1604.8
55°	2895.3	2901.8	2817.7	2643.2	2489.8	2282.5	2090.7	1950.9	1832.2	1737.2	1672.3
57.5°	4282.7	4254.4	4110.1	3763.9	3373.0	2857.0	2485.2	2259.6	2112.5	2129.0	2161.9
60°	4989.6	4984.1	4957.6	4823.4	4563.1	4170.4	3734.7	3235.1	3076.2	3093.5	3106.3
62.5°	5305.7	5313.9	5334.0	5283.7	5215.2	5101.0	4883.7	4682.8	4469.9	4390.5	4177.6
65°	5451.8	5466.4	5512.0	5540.4	5566.8	5586.9	5672.8	5908.5	6063.7	5773.3	5097.4
67.5°	5149.4	5219.8	5370.5	5517.5	5649.1	5836.3	6126.7	6673.9	7054.7	6697.6	5717.6
70°	3753.9	3849.7	4022.4	4477.2	4963.1	5387.9	5950.5	6783.4	7357.9	7082.1	5871.0
72.5°	2353.7	2380.2	2456.9	2624.0	2984.9	3530.1	4513.8	5763.2	6426.3	6206.2	4962.3
75°	1493.4	1502.5	1499.7	1538.0	1599.3	1718.0	2107.2	3404.0	4402.4	4059.0	2765.6
77.5°	889.6	903.3	908.8	920.6	949.8	991.9	1023.8	1158.1	1845.9	1792.0	1003.7
80°	745.3	756.3	747.2	744.4	726.1	713.4	728.8	713.4	662.2	637.5	587.3
82.5°	394.6	393.7	390.9	417.4	471.3	513.3	545.3	537.9	486.8	414.6	351.6
85°	216.5	223.7	223.7	233.0	224.7	225.6	233.0	245.7	227.5	189.9	155.2
87.5°	18.2	28.3	22.8	28.3	38.3	27.4	26.5	26.5	22.8	16.5	14.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152609

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2
2.5°	1735.3	1733.6	1729.8	1727.2	1727.2	1722.6	1719.8	1718.0	1717.1	1713.5	1713.5
5°	1729.8	1723.5	1717.1	1712.5	1709.7	1705.2	1697.9	1694.3	1689.7	1686.0	1684.2
7.5°	1718.0	1706.1	1696.1	1688.8	1679.7	1672.3	1663.2	1655.0	1646.7	1643.1	1641.2
10°	1699.8	1684.2	1668.7	1655.0	1642.2	1629.4	1617.5	1605.7	1595.6	1588.3	1581.0
12.5°	1682.4	1658.7	1638.5	1618.4	1598.3	1582.8	1566.4	1549.0	1534.4	1520.7	1517.1
15°	1658.7	1631.3	1605.7	1581.0	1556.4	1530.8	1510.7	1491.5	1467.8	1452.2	1440.3
17.5°	1636.7	1603.8	1572.7	1543.5	1513.5	1486.9	1456.8	1431.2	1407.5	1383.7	1366.3
20°	1613.0	1577.3	1544.5	1511.6	1478.8	1444.9	1410.3	1377.3	1348.1	1319.8	1291.5
22.5°	1592.0	1555.4	1523.4	1487.9	1451.3	1413.0	1372.7	1331.7	1297.8	1261.3	1228.5
25°	1579.2	1539.0	1506.1	1471.4	1431.2	1389.2	1343.5	1295.1	1254.0	1212.0	1172.7
27.5°	1579.2	1527.2	1493.4	1458.7	1417.5	1372.7	1322.5	1269.5	1223.0	1176.4	1128.0
30°	1592.8	1528.9	1483.3	1446.7	1404.8	1356.4	1300.6	1244.9	1193.8	1139.0	1092.3
32.5°	1605.7	1532.6	1476.0	1429.4	1381.0	1333.5	1276.9	1217.5	1160.8	1108.8	1059.5
35°	1613.9	1532.6	1462.3	1402.9	1348.1	1301.6	1245.8	1186.4	1128.9	1077.7	1032.1
37.5°	1614.8	1525.3	1440.3	1372.7	1315.2	1266.8	1213.9	1158.1	1103.3	1055.9	1017.5
40°	1605.7	1510.7	1418.4	1340.8	1280.5	1231.2	1182.8	1132.5	1083.2	1043.9	1011.1
42.5°	1589.2	1495.1	1397.4	1315.2	1252.2	1201.0	1156.3	1113.4	1070.5	1036.7	1009.2
45°	1564.6	1474.2	1378.2	1299.7	1237.6	1183.7	1139.9	1104.2	1067.7	1039.4	1012.0
47.5°	1542.7	1466.8	1384.7	1309.7	1244.9	1189.2	1144.5	1114.3	1086.0	1066.8	1029.3
50°	1538.0	1463.2	1387.4	1317.9	1252.2	1195.5	1156.3	1140.7	1132.5	1120.7	1063.1
52.5°	1525.3	1462.3	1407.5	1369.1	1327.0	1300.6	1259.5	1274.1	1265.0	1223.0	1118.9
55°	1659.6	1677.8	1729.0	1802.1	1869.6	1885.2	1880.6	1863.2	1771.0	1523.4	1253.2
57.5°	2281.6	2384.8	2481.6	2524.5	2519.1	2470.6	2435.9	2365.6	2232.2	1930.8	1518.0
60°	3145.6	3162.0	3110.9	3035.0	2907.2	2800.3	2686.1	2554.6	2361.0	2066.0	1680.5
62.5°	3941.1	3720.1	3492.6	3279.0	3084.4	2914.5	2755.5	2572.0	2319.9	2012.1	1659.6
65°	4502.8	4035.2	3676.3	3369.3	3094.4	2857.0	2658.8	2420.4	2136.4	1858.7	1538.0
67.5°	4792.3	4075.3	3524.7	3097.2	2707.2	2378.3	2114.4	1882.4	1671.4	1549.9	1346.3
70°	4469.0	3458.9	2691.6	2208.5	1741.8	1396.5	1103.3	926.1	865.0	980.0	1019.3
72.5°	3330.1	2251.4	1601.1	1238.5	949.0	756.3	580.0	455.8	370.8	389.1	505.1
75°	1574.6	971.8	686.8	522.5	415.5	344.4	281.3	257.6	215.5	179.1	168.1
77.5°	612.8	446.6	369.0	270.4	191.8	154.4	131.5	126.9	129.7	126.0	124.2
80°	466.7	316.1	198.2	145.2	125.1	110.5	97.7	94.1	95.9	100.5	105.1
82.5°	260.3	162.6	120.5	105.1	94.1	80.4	73.1	67.6	68.5	74.0	84.0
85°	100.5	78.5	72.1	69.4	64.9	52.0	44.8	45.7	52.0	62.1	62.1
87.5°	11.0	11.0	14.6	11.0	11.0	11.0	10.1	11.9	12.7	16.5	19.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152609

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2
2.5°	1711.6	1711.6	1711.6	1709.7	1710.7	1707.0	1707.0	1704.4	1708.9	1706.1	1705.2
5°	1685.2	1684.2	1680.5	1680.5	1680.5	1680.5	1683.3	1676.0	1681.5	1681.5	1678.8
7.5°	1640.4	1640.4	1630.4	1635.9	1634.0	1636.7	1640.4	1636.7	1642.2	1645.9	1643.1
10°	1578.2	1578.2	1570.1	1576.5	1573.7	1580.1	1586.5	1582.8	1586.5	1592.0	1593.8
12.5°	1509.7	1506.1	1498.8	1501.6	1501.6	1505.2	1508.0	1512.5	1517.1	1524.4	1528.1
15°	1430.3	1424.9	1415.6	1415.6	1410.3	1412.0	1417.5	1419.4	1428.5	1438.5	1450.4
17.5°	1349.0	1335.3	1325.3	1313.4	1304.2	1311.6	1317.9	1322.5	1329.8	1345.4	1353.6
20°	1272.3	1244.9	1225.7	1210.2	1200.1	1204.7	1213.0	1218.4	1224.8	1228.5	1231.2
22.5°	1196.5	1165.4	1139.0	1119.8	1103.3	1107.9	1104.2	1101.5	1106.1	1094.2	1093.3
25°	1130.8	1094.2	1058.5	1035.8	1015.6	1009.2	990.1	985.5	972.7	962.7	955.3
27.5°	1083.2	1035.8	996.5	969.9	938.0	914.3	889.6	865.0	851.2	834.8	826.6
30°	1045.8	995.5	949.0	904.2	862.2	825.7	792.7	760.8	738.9	715.1	699.6
32.5°	1011.1	964.5	907.9	846.6	790.1	748.9	706.0	669.5	634.8	603.7	580.9
35°	987.4	935.2	863.1	788.2	724.2	675.9	630.3	578.1	536.2	496.0	471.3
37.5°	974.5	910.6	822.0	738.9	667.7	612.8	556.3	496.0	444.8	407.4	369.9
40°	964.5	885.9	785.5	695.0	620.2	554.4	488.6	417.4	360.7	321.5	292.2
42.5°	953.6	858.5	753.5	660.3	577.2	500.5	421.0	345.3	291.4	263.9	251.2
45°	941.7	834.8	723.4	627.5	535.2	442.1	350.8	280.4	248.4	239.3	239.3
47.5°	939.0	819.3	701.5	595.5	487.8	374.5	285.9	242.1	233.0	234.7	238.3
50°	949.8	814.7	682.3	558.0	424.7	303.2	242.1	227.5	229.2	234.7	240.2
52.5°	976.4	818.3	662.2	506.0	349.8	250.3	223.7	222.9	228.3	236.6	242.1
55°	1021.1	818.3	623.8	428.4	279.5	224.7	217.4	221.0	228.3	235.6	240.2
57.5°	1117.0	810.2	556.3	342.5	233.8	215.5	215.5	220.1	226.5	233.8	237.5
60°	1231.2	799.2	461.2	264.9	211.0	208.3	214.6	220.1	225.6	232.0	235.6
62.5°	1238.5	770.9	365.4	219.2	199.1	203.6	213.7	221.0	222.9	227.5	232.0
65°	1138.0	672.2	290.5	196.4	193.7	200.9	211.0	216.5	217.4	219.2	223.7
67.5°	996.5	548.0	234.7	185.4	188.2	196.4	201.9	206.4	209.1	213.7	214.6
70°	818.3	440.2	200.9	174.4	177.2	186.3	190.9	195.4	200.9	206.4	203.6
72.5°	580.0	342.5	176.3	162.6	166.2	174.4	179.9	183.6	188.2	193.7	189.9
75°	246.6	239.3	152.5	147.0	152.5	158.0	163.5	169.0	173.6	176.3	176.3
77.5°	126.0	140.6	131.5	131.5	135.1	140.6	145.2	150.7	153.5	156.2	159.8
80°	106.8	108.7	110.5	114.2	117.8	123.3	127.9	132.4	133.4	134.3	136.1
82.5°	88.6	92.2	94.1	99.6	102.3	104.1	106.8	106.8	108.7	108.7	105.9
85°	63.9	68.5	71.2	72.1	71.2	72.1	73.1	74.9	79.5	79.5	75.9
87.5°	18.2	17.3	22.0	22.8	24.7	28.3	31.9	38.3	40.2	42.0	42.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152609

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1727.2	1727.2	1727.2	1727.2
2.5°	1704.4	1706.1	1702.5	1703.4
5°	1678.8	1682.4	1677.8	1683.3
7.5°	1645.9	1651.3	1650.5	1649.5
10°	1598.3	1605.7	1605.7	1608.4
12.5°	1538.0	1542.7	1546.3	1548.1
15°	1456.8	1465.0	1469.5	1469.5
17.5°	1359.1	1364.6	1367.3	1363.6
20°	1234.8	1233.1	1233.9	1224.8
22.5°	1091.5	1094.2	1086.0	1087.8
25°	950.8	946.2	949.8	944.5
27.5°	814.7	815.6	805.6	810.2
30°	685.0	680.4	667.7	674.1
32.5°	559.9	548.0	534.3	526.1
35°	442.1	423.8	417.4	414.6
37.5°	347.0	326.9	320.6	313.3
40°	275.9	268.5	265.8	267.6
42.5°	247.6	247.6	249.3	250.3
45°	240.2	242.9	245.7	246.6
47.5°	241.1	243.8	247.6	248.4
50°	242.9	245.7	248.4	249.3
52.5°	243.8	243.8	245.7	246.6
55°	242.1	241.1	242.1	242.9
57.5°	238.3	236.6	237.5	240.2
60°	236.6	233.8	235.6	237.5
62.5°	232.0	231.1	233.0	233.8
65°	222.0	222.9	225.6	225.6
67.5°	212.8	213.7	214.6	215.5
70°	201.9	202.8	204.6	205.5
72.5°	189.0	192.7	195.4	199.1
75°	179.1	182.7	188.2	191.8
77.5°	161.7	164.4	170.8	175.3
80°	137.0	136.1	137.0	139.8
82.5°	105.1	105.1	104.1	103.2
85°	74.0	73.1	70.4	70.4
87.5°	40.2	39.3	38.3	36.6
90°	0.0	0.0	0.0	0.0

(END OF REPORT)