

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152594

Luminaire Tested: **AVS-F01-LED-E-U-SL4-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152594
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F01-LED-E-U-SL4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (7) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2227.4 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 25.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152594

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.8 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152594

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P152594

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	462.4	0.0	462.4
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	1765.0	0.0	1765.0
	% Fixture	79.2	0.0	79.2
Total	Lumens	2227.4	0.0	2227.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	2.0
10°-20°	121.5	5.5
20°-30°	179.9	8.1
30°-40°	227.4	10.2
40°-50°	257.2	11.5
50°-60°	366.0	16.4
60°-70°	681.6	30.6
70°-80°	312.4	14.0
80°-90°	37.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2227.4	100.0
0°-180°	2227.4	100.0

Coefficient of Utilization



REPORT NUMBER: P152594


CATALOG NUMBER: AVS-F01-LED-E-U-SL4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	202.8	9.1			
FM	(30°-60°)	652.6	29.3			
FH	(60°-80°)	882.1	39.6			G1/1800
FVH	(80°-90°)	27.5	1.2			G1/100
BL	(0°-30°)	143.1	6.4	B1/500		
BM	(30°-60°)	198.0	8.9	B0/220		
BH	(60°-80°)	111.8	5.0	B1/500		G1/500
BVH	(80°-90°)	9.6	0.4			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P152594

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2
2.5°	482.6	483.8	482.3	482.1	482.1	481.8	480.3	480.0	478.0	478.2	478.8
5°	486.1	486.5	485.6	485.3	484.8	483.8	482.6	481.0	479.6	478.0	476.8
7.5°	489.6	489.1	488.3	488.3	487.6	486.1	483.5	481.6	478.2	476.5	474.3
10°	494.6	493.9	492.8	492.3	491.1	488.8	485.3	482.6	478.5	475.0	471.3
12.5°	499.4	499.2	497.6	496.9	494.9	492.6	488.3	484.0	478.8	473.3	468.2
15°	508.0	506.9	505.4	503.9	500.6	497.6	491.1	486.1	478.5	471.3	463.4
17.5°	522.8	521.0	519.5	516.3	512.2	506.9	497.4	488.8	478.5	468.0	459.2
20°	549.9	546.1	544.1	539.9	532.8	523.3	508.4	494.6	479.3	465.7	453.9
22.5°	580.6	578.0	575.3	572.5	561.5	547.7	527.6	506.9	483.8	464.7	449.6
25°	615.0	611.7	610.3	605.5	595.1	579.3	551.9	523.3	494.1	468.7	449.6
27.5°	645.7	644.7	644.5	638.9	629.1	610.5	578.0	543.6	508.2	477.0	453.4
30°	673.6	672.5	672.0	669.0	657.7	635.6	600.4	561.8	523.5	488.6	460.4
32.5°	703.2	700.0	698.4	692.6	679.9	654.0	613.8	573.6	535.5	499.9	468.2
35°	727.4	724.6	721.6	713.3	695.2	664.6	619.5	577.5	540.3	506.2	472.2
37.5°	745.0	742.2	737.9	727.4	705.0	668.1	619.3	576.3	538.7	505.2	473.1
40°	752.7	749.9	745.5	732.1	706.7	666.0	614.5	570.6	533.4	499.9	469.9
42.5°	749.7	747.7	742.0	729.1	701.2	657.0	605.0	559.7	523.3	491.4	463.2
45°	738.1	736.7	731.1	717.5	688.6	642.4	590.9	546.1	511.2	480.8	454.2
47.5°	720.8	720.3	714.8	701.5	672.8	627.9	576.3	532.8	499.2	470.5	446.6
50°	701.8	699.2	696.5	684.1	658.0	615.2	565.7	524.6	492.3	466.7	443.3
52.5°	689.6	688.9	686.4	675.3	650.2	608.0	560.9	521.6	491.8	466.0	441.6
55°	796.7	798.4	775.3	727.4	685.1	628.1	575.3	536.9	504.1	478.0	460.2
57.5°	1178.4	1170.7	1131.0	1035.8	928.2	786.1	683.8	621.8	581.3	585.8	594.9
60°	1373.1	1371.5	1364.2	1327.3	1255.6	1147.6	1027.7	890.3	846.5	851.3	854.8
62.5°	1460.0	1462.3	1467.8	1454.0	1435.1	1403.7	1343.8	1288.6	1230.1	1208.2	1149.6
65°	1500.2	1504.2	1516.8	1524.6	1531.8	1537.4	1561.0	1625.9	1668.6	1588.7	1402.7
67.5°	1417.0	1436.4	1477.8	1518.3	1554.5	1606.0	1685.9	1836.5	1941.2	1843.0	1573.4
70°	1033.0	1059.4	1106.8	1232.0	1365.7	1482.6	1637.4	1866.6	2024.8	1948.8	1615.5
72.5°	647.7	654.9	676.1	722.1	821.3	971.4	1242.1	1585.9	1768.4	1707.8	1365.5
75°	410.9	413.5	412.6	423.2	440.1	472.7	579.8	936.7	1211.4	1116.9	761.0
77.5°	244.8	248.6	250.1	253.4	261.3	273.0	281.8	318.7	508.0	493.2	276.2
80°	205.1	208.1	205.6	204.9	199.8	196.3	200.5	196.3	182.2	175.4	161.6
82.5°	108.6	108.3	107.6	114.8	129.6	141.2	150.1	148.1	134.0	114.1	96.8
85°	59.6	61.6	61.6	64.0	61.9	62.1	64.0	67.6	62.6	52.2	42.7
87.5°	5.1	7.8	6.3	7.8	10.6	7.6	7.3	7.3	6.3	4.6	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152594

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2
2.5°	477.5	477.0	476.1	475.2	475.2	474.0	473.3	472.7	472.5	471.5	471.5
5°	476.1	474.3	472.5	471.3	470.5	469.2	467.3	466.2	465.0	463.9	463.4
7.5°	472.7	469.5	466.7	464.7	462.2	460.2	457.7	455.4	453.2	452.1	451.6
10°	467.8	463.4	459.2	455.4	451.9	448.4	445.1	441.9	439.1	437.1	435.0
12.5°	462.9	456.4	450.9	445.4	439.8	435.5	431.0	426.2	422.3	418.4	417.4
15°	456.4	448.9	441.9	435.0	428.3	421.2	415.8	410.5	403.9	399.6	396.4
17.5°	450.4	441.3	432.7	424.8	416.5	409.1	400.8	393.9	387.3	380.7	376.0
20°	443.8	434.1	425.0	416.0	406.9	397.6	388.1	379.0	371.0	363.2	355.3
22.5°	438.0	428.0	419.2	409.4	399.4	388.8	377.7	366.4	357.1	347.0	338.0
25°	434.5	423.5	414.4	404.9	393.9	382.3	369.7	356.4	345.1	333.5	322.7
27.5°	434.5	420.2	410.9	401.3	390.1	377.7	363.9	349.3	336.6	323.7	310.4
30°	438.3	420.7	408.2	398.1	386.5	373.3	357.9	342.6	328.5	313.4	300.6
32.5°	441.9	421.8	406.1	393.4	380.0	366.9	351.4	335.0	319.5	305.1	291.5
35°	444.1	421.8	402.4	386.0	371.0	358.1	342.8	326.5	310.7	296.6	284.0
37.5°	444.4	419.7	396.4	377.7	361.9	348.6	334.0	318.7	303.6	290.6	280.0
40°	441.9	415.8	390.4	368.9	352.3	338.8	325.5	311.6	298.0	287.3	278.2
42.5°	437.3	411.4	384.6	361.9	344.6	330.5	318.1	306.3	294.6	285.3	277.7
45°	430.6	405.7	379.3	357.6	340.5	325.7	313.7	303.8	293.8	286.0	278.4
47.5°	424.5	403.6	381.0	360.4	342.6	327.3	314.9	306.6	298.9	293.6	283.2
50°	423.2	402.6	381.8	362.7	344.6	329.0	318.1	313.9	311.6	308.4	292.5
52.5°	419.7	402.4	387.3	376.8	365.2	357.9	346.6	350.6	348.1	336.6	307.9
55°	456.7	461.7	475.8	495.9	514.5	518.8	517.5	512.7	487.4	419.2	344.9
57.5°	627.9	656.3	682.9	694.7	693.2	679.9	670.3	651.0	614.3	531.3	417.7
60°	865.6	870.2	856.1	835.1	800.0	770.6	739.2	703.0	649.7	568.5	462.5
62.5°	1084.5	1023.6	961.1	902.3	848.7	802.0	758.2	707.8	638.3	553.7	456.7
65°	1239.1	1110.4	1011.6	927.2	851.5	786.1	731.6	666.0	587.9	511.5	423.2
67.5°	1318.8	1121.5	969.8	852.2	745.0	654.5	581.9	518.0	459.9	426.5	370.5
70°	1229.7	951.8	740.6	607.7	479.3	384.2	303.6	254.8	238.0	269.6	280.5
72.5°	916.4	619.5	440.6	340.8	261.1	208.1	159.6	125.4	102.1	107.0	139.0
75°	433.3	267.5	189.0	143.7	114.4	94.7	77.4	70.9	59.3	49.2	46.2
77.5°	168.6	122.9	101.6	74.4	52.7	42.5	36.2	34.9	35.6	34.7	34.2
80°	128.4	86.9	54.5	40.0	34.4	30.4	26.9	25.9	26.4	27.7	28.9
82.5°	71.6	44.8	33.2	28.9	25.9	22.1	20.1	18.5	18.9	20.3	23.1
85°	27.7	21.7	19.9	19.1	17.8	14.3	12.3	12.5	14.3	17.1	17.1
87.5°	3.0	3.0	4.0	3.0	3.0	3.0	2.8	3.3	3.5	4.6	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152594

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2	475.2
2.5°	471.0	471.0	471.0	470.5	470.8	469.7	469.7	469.0	470.3	469.5	469.2
5°	463.7	463.4	462.5	462.5	462.5	462.5	463.2	461.2	462.7	462.7	462.0
7.5°	451.4	451.4	448.6	450.2	449.6	450.4	451.4	450.4	451.9	452.8	452.1
10°	434.3	434.3	432.0	433.8	433.1	434.8	436.6	435.5	436.6	438.0	438.5
12.5°	415.4	414.4	412.4	413.2	413.2	414.2	414.9	416.2	417.4	419.5	420.5
15°	393.6	392.1	389.5	389.5	388.1	388.6	390.1	390.6	393.1	395.9	399.1
17.5°	371.2	367.5	364.7	361.5	358.9	360.9	362.7	363.9	365.9	370.3	372.4
20°	350.2	342.6	337.3	333.1	330.3	331.5	333.8	335.2	337.0	338.0	338.8
22.5°	329.2	320.7	313.4	308.1	303.6	304.9	303.8	303.1	304.4	301.1	300.8
25°	311.2	301.1	291.3	285.0	279.5	277.7	272.4	271.2	267.7	264.9	262.9
27.5°	298.0	285.0	274.2	266.9	258.1	251.6	244.8	238.0	234.2	229.7	227.5
30°	287.8	274.0	261.1	248.8	237.3	227.3	218.1	209.3	203.3	196.8	192.5
32.5°	278.2	265.4	249.8	233.0	217.4	206.1	194.3	184.2	174.7	166.1	159.9
35°	271.7	257.4	237.5	216.9	199.3	186.0	173.4	159.1	147.6	136.5	129.6
37.5°	268.2	250.6	226.2	203.3	183.7	168.6	153.1	136.5	122.4	112.1	101.8
40°	265.4	243.8	216.2	191.3	170.7	152.5	134.5	114.8	99.3	88.5	80.4
42.5°	262.4	236.3	207.4	181.8	158.9	137.7	115.9	95.0	80.2	72.6	69.1
45°	259.2	229.7	199.1	172.6	147.3	121.7	96.5	77.2	68.4	65.8	65.8
47.5°	258.3	225.5	193.1	163.8	134.2	103.0	78.7	66.6	64.0	64.6	65.6
50°	261.3	224.1	187.8	153.6	116.9	83.4	66.6	62.6	63.1	64.6	66.1
52.5°	268.7	225.2	182.2	139.3	96.3	68.9	61.6	61.3	62.8	65.1	66.6
55°	281.0	225.2	171.7	117.8	76.9	61.9	59.8	60.8	62.8	64.9	66.1
57.5°	307.4	222.9	153.1	94.3	64.4	59.3	59.3	60.6	62.3	64.4	65.4
60°	338.8	219.9	126.9	72.8	58.0	57.3	59.1	60.6	62.1	63.8	64.9
62.5°	340.8	212.1	100.5	60.3	54.8	56.1	58.9	60.8	61.3	62.6	63.8
65°	313.2	185.0	79.9	54.0	53.3	55.3	58.0	59.6	59.8	60.3	61.6
67.5°	274.2	150.8	64.6	51.0	51.8	54.0	55.5	56.8	57.5	58.9	59.1
70°	225.2	121.1	55.3	48.0	48.8	51.3	52.5	53.8	55.3	56.8	56.1
72.5°	159.6	94.3	48.5	44.8	45.7	48.0	49.5	50.5	51.8	53.3	52.2
75°	67.9	65.8	42.0	40.4	42.0	43.5	45.0	46.5	47.8	48.5	48.5
77.5°	34.7	38.8	36.2	36.2	37.2	38.8	40.0	41.5	42.2	43.0	43.9
80°	29.4	29.9	30.4	31.4	32.4	33.9	35.2	36.5	36.7	37.0	37.4
82.5°	24.4	25.4	25.9	27.4	28.2	28.6	29.4	29.4	29.9	29.9	29.1
85°	17.6	18.9	19.6	19.9	19.6	19.9	20.1	20.6	21.9	21.9	20.8
87.5°	5.1	4.8	6.0	6.3	6.7	7.8	8.8	10.6	11.1	11.6	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152594

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	475.2	475.2	475.2	475.2
2.5°	469.0	469.5	468.5	468.7
5°	462.0	462.9	461.7	463.2
7.5°	452.8	454.4	454.2	453.9
10°	439.8	441.9	441.9	442.6
12.5°	423.2	424.5	425.5	426.0
15°	400.8	403.1	404.4	404.4
17.5°	374.0	375.4	376.3	375.2
20°	339.8	339.3	339.6	337.0
22.5°	300.3	301.1	298.9	299.4
25°	261.7	260.4	261.3	259.9
27.5°	224.1	224.5	221.7	222.9
30°	188.5	187.3	183.7	185.5
32.5°	154.1	150.8	147.0	144.8
35°	121.7	116.6	114.8	114.1
37.5°	95.5	89.9	88.2	86.2
40°	75.9	73.9	73.2	73.7
42.5°	68.1	68.1	68.6	68.9
45°	66.1	66.8	67.6	67.9
47.5°	66.3	67.2	68.1	68.4
50°	66.8	67.6	68.4	68.6
52.5°	67.2	67.2	67.6	67.9
55°	66.6	66.3	66.6	66.8
57.5°	65.6	65.1	65.4	66.1
60°	65.1	64.4	64.9	65.4
62.5°	63.8	63.6	64.0	64.4
65°	61.0	61.3	62.1	62.1
67.5°	58.5	58.9	59.1	59.3
70°	55.5	55.8	56.3	56.6
72.5°	52.0	53.1	53.8	54.8
75°	49.2	50.3	51.8	52.7
77.5°	44.5	45.3	47.0	48.3
80°	37.7	37.4	37.7	38.4
82.5°	28.9	28.9	28.6	28.4
85°	20.3	20.1	19.4	19.4
87.5°	11.1	10.8	10.6	10.1
90°	0.0	0.0	0.0	0.0

(END OF REPORT)