

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P154774

Luminaire Tested: **AVS-F01-LED-E-U-T2-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P154774
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33671)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F01-LED-E-U-T2-7030
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 2 AREA
Light Source: (7) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2310.1 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type II - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 25.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P154774

CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.8 fc
Type II - Short - Semi-Cutoff

REPORT NUMBER: P154774

CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P154774

CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	808.9	0.0	808.9
	% Fixture	35.0	0.0	35.0
Street Side	Lumens	1501.2	0.0	1501.2
	% Fixture	65.0	0.0	65.0
Total	Lumens	2310.1	0.0	2310.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.1	1.0
10°-20°	79.4	3.4
20°-30°	156.1	6.8
30°-40°	259.3	11.2
40°-50°	381.1	16.5
50°-60°	527.6	22.8
60°-70°	629.7	27.3
70°-80°	222.7	9.6
80°-90°	31.1	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2310.1	100.0
0°-180°	2310.1	100.0

Coefficient of Utilization



REPORT NUMBER: P154774


CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	133.7	5.8			
FM	(30°-60°)	735.5	31.8			
FH	(60°-80°)	610.8	26.4			G0/660
FVH	(80°-90°)	21.3	0.9			G1/100
BL	(0°-30°)	125.0	5.4	B1/500		
BM	(30°-60°)	432.5	18.7	B1/1000		
BH	(60°-80°)	241.6	10.5	B1/500		G1/500
BVH	(80°-90°)	9.9	0.4			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type II Short





REPORT NUMBER: P154774

CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0
2.5°	241.0	241.2	240.7	240.5	239.8	238.5	237.5	236.5	236.5	236.5	235.8
5°	251.6	252.1	251.1	250.4	248.1	246.8	245.1	243.8	243.3	243.0	242.3
7.5°	264.9	264.1	262.6	262.2	260.4	257.6	254.3	251.8	251.8	251.6	251.8
10°	278.2	276.2	275.4	274.7	271.9	268.4	264.7	261.9	261.7	261.3	260.6
12.5°	291.5	290.8	290.1	287.3	284.5	279.0	274.7	271.9	271.7	271.9	271.0
15°	309.1	307.4	306.6	301.9	295.9	289.7	284.5	282.0	281.2	281.5	280.7
17.5°	322.7	322.7	320.9	315.6	307.9	299.6	294.1	292.5	292.3	292.3	292.5
20°	333.5	333.3	331.5	327.3	317.9	309.6	306.8	306.3	306.1	306.1	306.8
22.5°	339.6	339.1	338.3	333.5	326.2	320.7	320.9	322.5	323.0	323.4	324.5
25°	342.6	341.8	341.6	338.3	333.1	332.2	336.8	340.8	341.8	342.8	344.0
27.5°	347.6	346.3	346.8	345.6	344.4	346.6	355.9	360.2	360.9	362.2	362.9
30°	361.5	360.9	362.9	363.4	364.5	367.7	376.3	380.3	382.1	382.1	385.5
32.5°	387.8	388.1	388.6	393.9	395.5	397.8	402.4	405.7	405.9	406.1	409.4
35°	423.2	424.8	429.0	433.6	437.8	437.6	434.8	436.6	435.3	436.8	437.1
37.5°	468.0	466.0	472.2	482.6	489.1	487.4	475.0	466.9	469.2	468.2	467.5
40°	502.4	504.7	516.8	530.3	535.3	540.8	524.8	511.0	508.9	505.2	502.9
42.5°	549.9	550.2	560.0	570.1	584.6	596.7	586.3	566.5	560.5	556.0	546.1
45°	593.9	593.2	601.1	613.5	630.9	648.2	651.9	630.4	628.1	620.0	607.3
47.5°	623.3	622.3	627.9	643.9	672.0	700.4	716.1	709.5	705.3	702.0	681.9
50°	643.1	641.1	647.5	664.6	696.0	739.7	780.4	785.9	784.1	784.1	771.3
52.5°	658.0	658.0	662.5	676.4	708.3	762.8	835.6	863.5	865.8	868.4	867.6
55°	649.7	651.0	662.3	682.4	716.1	778.9	881.5	942.5	955.0	965.6	977.7
57.5°	621.2	625.6	640.6	673.6	718.0	791.0	932.2	1053.1	1088.5	1119.2	1166.9
60°	579.8	585.4	607.3	649.2	703.2	771.3	950.1	1146.5	1202.9	1269.7	1394.4
62.5°	508.7	514.2	535.5	577.5	623.8	696.2	876.2	1160.4	1250.4	1345.1	1533.6
65°	360.4	351.6	376.3	414.0	466.9	537.1	708.0	1067.7	1197.1	1325.5	1558.2
67.5°	200.8	200.1	215.1	243.3	294.1	369.4	487.9	818.9	937.9	1083.5	1369.2
70°	138.4	140.0	149.5	180.0	222.0	287.0	347.6	514.2	599.9	698.7	979.7
72.5°	97.3	100.5	105.8	123.9	166.8	241.8	355.1	307.4	350.2	417.4	589.1
75°	57.1	59.3	63.1	71.9	95.0	161.6	367.7	270.2	270.2	286.0	356.4
77.5°	35.2	35.2	37.4	40.9	50.5	79.2	261.9	303.6	295.0	286.0	286.7
80°	18.1	19.4	22.6	24.4	28.2	36.2	117.6	283.2	310.7	329.0	316.2
82.5°	8.3	9.3	13.8	14.8	16.4	19.1	40.4	161.1	215.9	284.2	355.1
85°	4.2	4.2	7.3	9.0	9.8	8.8	14.8	65.1	98.5	150.3	235.2
87.5°	0.7	0.7	1.2	1.6	2.3	2.0	2.5	3.7	6.3	6.7	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P154774

CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030

CANDELA DISTRIBUTION (continued):

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0
2.5°	235.5	235.8	235.5	235.2	234.7	234.7	234.7	234.5	234.5	234.5	234.2
5°	242.3	241.2	241.6	241.0	240.7	240.5	240.7	240.3	239.8	240.0	239.8
7.5°	250.8	250.4	249.3	249.3	249.1	248.6	248.6	247.8	247.6	247.0	246.8
10°	260.4	259.2	259.6	259.2	259.4	258.3	257.8	257.4	256.9	256.9	257.1
12.5°	270.2	269.9	269.2	268.7	268.7	267.9	268.2	267.9	267.2	266.9	266.1
15°	280.2	280.2	279.5	279.7	279.5	279.0	278.4	278.4	277.9	277.5	277.7
17.5°	292.0	292.0	292.0	292.0	292.3	291.5	291.8	291.3	290.8	291.8	291.8
20°	307.4	308.4	308.4	308.1	309.4	308.6	308.4	309.6	308.4	310.2	309.8
22.5°	325.0	326.0	326.0	326.9	327.3	328.0	328.5	328.0	329.0	329.9	329.9
25°	344.6	345.6	346.3	347.9	348.6	348.1	348.4	349.6	350.2	351.1	352.1
27.5°	365.2	365.4	366.4	368.2	369.4	369.9	370.3	372.2	372.4	373.0	374.0
30°	385.3	387.8	387.3	389.5	390.4	391.1	392.5	393.4	395.1	396.1	396.1
32.5°	408.9	408.4	410.5	412.2	413.5	414.7	416.0	417.0	417.9	418.4	420.9
35°	438.3	439.4	439.4	439.6	442.6	442.8	443.8	446.1	446.8	448.4	449.4
37.5°	467.5	465.7	465.5	465.5	464.5	465.2	465.5	465.7	466.7	466.9	468.0
40°	500.1	497.9	495.9	494.6	492.6	489.8	489.3	488.1	488.8	488.6	488.8
42.5°	544.9	538.7	533.8	530.3	526.3	523.3	521.0	517.7	515.4	512.7	512.2
45°	602.0	590.2	582.1	576.3	570.6	562.2	557.4	552.4	547.9	543.4	539.6
47.5°	676.8	664.2	651.4	640.9	631.8	618.5	605.0	597.4	588.6	580.8	575.3
50°	765.1	749.9	743.9	729.1	717.8	697.7	680.8	668.5	651.0	639.2	628.8
52.5°	855.2	851.5	848.3	835.6	822.4	810.8	796.0	774.3	756.5	742.9	721.9
55°	978.1	979.9	978.7	971.9	967.2	956.1	950.1	931.2	923.1	903.5	881.5
57.5°	1185.1	1199.1	1217.0	1223.9	1233.6	1224.5	1235.0	1247.9	1216.0	1227.0	1207.2
60°	1449.2	1513.8	1552.2	1599.5	1630.4	1673.6	1681.5	1692.7	1689.4	1695.8	1708.5
62.5°	1610.6	1687.2	1760.8	1814.4	1871.7	1903.3	1941.6	1968.2	1995.9	2014.4	2009.1
65°	1658.0	1737.0	1803.8	1862.4	1913.7	1952.3	1987.8	2021.2	2046.6	2064.5	2075.0
67.5°	1483.6	1586.6	1657.0	1725.6	1791.7	1832.4	1862.1	1894.5	1931.7	1962.7	1968.7
70°	1116.4	1271.0	1370.8	1453.0	1530.6	1585.4	1626.8	1657.0	1685.9	1708.1	1732.1
72.5°	698.2	833.4	947.6	1054.1	1136.5	1211.9	1246.8	1313.7	1304.9	1321.8	1339.9
75°	418.4	484.4	547.2	622.3	665.5	728.4	739.7	750.8	745.0	726.1	740.2
77.5°	290.8	301.6	301.1	296.8	292.3	281.2	266.9	259.2	253.9	246.3	249.3
80°	292.5	269.2	233.5	196.3	162.1	139.5	130.5	130.5	139.7	153.1	166.4
82.5°	349.6	324.8	289.5	242.3	192.0	156.4	132.4	122.9	124.7	138.2	155.3
85°	235.8	241.2	211.6	193.6	153.3	119.4	100.0	81.1	71.9	74.1	83.9
87.5°	8.5	10.3	3.7	5.1	3.5	3.0	3.0	3.3	2.3	2.8	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P154774

CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030

CANDELA DISTRIBUTION (continued):

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0
2.5°	234.0	233.8	233.8	233.3	233.3	233.0	233.0	232.7	232.4	232.4	232.2
5°	239.5	239.3	238.8	238.5	238.0	238.0	237.7	237.3	237.3	236.8	236.5
7.5°	247.4	246.8	246.3	246.0	245.8	245.1	245.1	244.6	244.6	244.0	243.8
10°	256.6	256.1	255.6	255.9	255.1	254.8	254.3	254.3	253.6	253.4	253.4
12.5°	266.6	266.4	266.4	265.7	265.4	265.2	264.1	264.1	264.1	263.6	263.9
15°	277.5	277.7	277.0	277.7	277.5	276.7	276.7	276.7	275.8	277.0	276.0
17.5°	292.0	292.8	292.3	292.5	292.0	292.0	292.3	292.0	292.5	292.5	294.1
20°	310.2	310.4	311.6	311.2	311.2	310.9	311.4	311.6	312.6	312.1	313.2
22.5°	329.9	331.3	331.5	332.5	332.5	332.2	332.7	333.8	334.3	335.0	334.8
25°	352.6	353.4	354.4	353.2	355.1	355.1	355.6	356.9	357.1	357.1	358.9
27.5°	373.7	375.8	376.0	377.2	376.5	377.0	378.8	379.5	380.5	380.5	381.0
30°	397.6	398.3	398.9	400.4	400.1	400.4	400.6	401.9	401.9	403.1	404.4
32.5°	422.3	422.7	423.2	424.8	425.3	426.2	425.8	426.7	428.0	428.3	429.0
35°	451.6	452.1	452.6	454.9	455.1	456.9	457.4	456.9	459.0	457.7	459.0
37.5°	468.7	471.0	471.5	473.1	472.5	473.8	474.5	475.5	476.1	477.0	479.1
40°	489.6	490.4	491.8	492.6	493.6	493.9	494.9	495.6	496.4	498.7	500.9
42.5°	511.0	511.9	512.7	513.7	515.0	516.0	516.8	519.0	519.5	521.0	525.3
45°	536.9	536.4	536.6	536.9	537.3	538.7	540.8	543.1	544.7	548.2	551.7
47.5°	569.0	565.7	564.5	562.5	563.0	565.7	566.2	570.1	573.1	576.3	580.6
50°	617.7	609.0	603.7	598.4	597.9	599.4	601.5	605.5	609.0	613.3	619.3
52.5°	699.7	682.9	672.3	657.7	653.7	653.0	651.4	653.7	654.7	660.5	671.8
55°	865.6	834.4	814.3	791.7	770.6	764.2	752.2	754.7	752.2	755.8	772.6
57.5°	1211.9	1187.0	1167.5	1138.5	1102.4	1063.8	1054.3	1014.9	1022.7	1045.3	1030.7
60°	1714.8	1705.8	1691.7	1677.9	1628.4	1600.5	1555.0	1549.9	1518.0	1518.3	1497.4
62.5°	1996.4	2007.9	1999.4	1995.3	1992.5	1983.7	1961.1	1934.0	1893.3	1863.8	1820.6
65°	2076.8	2066.9	2057.6	2056.4	2055.6	2069.9	2073.3	2054.1	2017.2	1971.4	1921.7
67.5°	1983.0	1977.5	1977.9	1967.5	1974.0	1998.9	2016.2	2010.9	1977.0	1921.7	1858.3
70°	1759.8	1749.0	1760.1	1773.9	1783.7	1798.0	1815.3	1819.7	1788.7	1731.9	1667.4
72.5°	1317.7	1319.5	1330.1	1333.8	1373.3	1369.2	1384.9	1334.1	1311.7	1257.6	1224.5
75°	693.5	682.1	711.5	649.2	623.5	641.3	591.4	543.4	553.5	561.8	501.9
77.5°	245.1	229.2	202.3	191.5	159.4	134.9	110.4	99.5	93.8	90.8	86.9
80°	176.0	180.9	175.4	162.4	138.0	110.6	87.3	68.9	59.1	53.8	50.3
82.5°	177.9	197.8	206.6	202.8	180.7	136.7	90.3	57.5	42.7	35.6	33.2
85°	95.5	104.6	100.5	84.7	76.2	45.5	31.2	20.8	17.6	16.1	14.8
87.5°	3.7	3.0	2.5	2.5	2.8	3.0	2.5	2.8	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P154774

CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030

CANDELA DISTRIBUTION (continued):

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0	231.0
2.5°	231.7	231.7	231.7	231.5	231.0	229.7	228.5	227.5	226.7	225.9	225.0
5°	236.3	235.8	235.8	235.8	233.8	231.7	229.9	228.2	226.7	225.5	224.5
7.5°	243.8	243.5	242.5	242.3	240.7	237.5	235.5	232.4	230.7	228.9	228.5
10°	252.8	252.5	252.3	252.1	250.1	246.8	244.2	241.6	239.1	236.5	234.0
12.5°	263.4	263.1	262.9	262.2	261.3	259.6	256.9	253.9	250.8	245.6	242.8
15°	276.5	277.0	276.5	276.2	275.8	276.0	274.2	269.9	265.2	258.3	252.5
17.5°	293.8	293.3	293.1	294.1	293.8	295.0	294.6	289.0	281.8	271.0	260.9
20°	313.0	313.0	313.9	314.7	316.9	320.2	318.7	311.9	298.5	283.5	270.5
22.5°	335.8	336.3	337.3	336.8	340.3	345.6	346.1	336.6	319.2	298.3	280.0
25°	359.7	360.2	359.2	360.6	366.4	374.0	375.4	361.9	339.1	311.9	288.0
27.5°	382.3	382.8	382.8	384.8	390.4	403.1	404.7	389.5	359.2	323.7	293.8
30°	404.4	406.4	406.9	407.4	415.8	433.6	436.8	414.9	376.8	332.5	297.8
32.5°	432.3	433.1	434.1	435.3	444.9	466.7	466.7	436.8	388.1	338.0	298.5
35°	462.2	462.5	464.7	465.0	478.5	500.4	496.2	454.9	396.1	336.8	293.1
37.5°	480.3	481.3	483.5	486.5	500.9	531.8	522.0	470.5	397.6	328.5	280.5
40°	502.7	504.7	506.9	509.9	531.3	563.7	543.8	480.3	391.3	312.1	261.7
42.5°	526.8	529.5	533.1	538.7	563.9	591.9	560.5	481.8	377.0	293.8	239.3
45°	553.9	559.0	563.0	569.5	598.1	616.3	570.6	473.1	358.9	269.6	215.4
47.5°	585.4	589.3	596.4	603.4	632.1	632.8	571.5	456.0	334.3	245.6	190.1
50°	624.0	626.5	637.1	641.3	668.3	650.2	564.2	432.7	308.4	218.4	161.9
52.5°	675.5	679.1	692.6	699.2	718.3	673.8	553.9	407.7	278.8	188.0	133.0
55°	777.4	792.7	802.3	813.6	825.9	727.4	549.4	380.7	245.3	152.8	105.3
57.5°	1063.1	1058.1	1079.2	1104.9	1104.6	849.7	576.6	357.6	205.8	116.9	80.9
60°	1488.9	1493.7	1482.9	1498.1	1449.4	1001.6	613.8	333.3	161.3	86.9	61.9
62.5°	1805.3	1777.6	1762.4	1744.2	1636.9	1018.1	586.6	283.2	117.4	61.0	47.5
65°	1880.2	1847.8	1814.8	1780.4	1618.5	917.8	481.3	207.9	75.9	42.0	37.7
67.5°	1806.3	1754.3	1712.3	1676.9	1483.1	760.8	351.8	127.7	43.5	33.9	32.1
70°	1614.8	1557.2	1489.4	1449.6	1248.9	560.7	225.5	68.9	33.5	30.2	29.4
72.5°	1182.0	1134.7	1060.6	1015.1	896.8	340.8	125.9	38.8	31.2	28.9	27.9
75°	460.4	435.9	404.9	407.4	363.6	150.8	57.1	33.5	30.4	28.4	27.4
77.5°	79.2	77.2	71.4	71.4	81.1	55.0	37.9	33.7	30.2	27.9	26.1
80°	47.5	46.5	44.2	43.7	42.2	38.8	36.5	34.2	29.6	26.4	24.1
82.5°	31.2	29.9	29.1	28.9	31.4	33.9	34.2	33.9	28.2	22.9	19.6
85°	13.4	13.4	13.4	13.6	18.1	27.4	28.2	30.2	23.1	17.8	14.1
87.5°	2.3	2.8	2.8	3.0	3.3	6.0	7.6	9.8	7.8	7.6	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P154774

CATALOG NUMBER: AVS-F01-LED-E-U-T2-7030

CANDELA DISTRIBUTION (continued):

	165°	175°	180°
0°	231.0	231.0	231.0
2.5°	224.7	224.1	224.1
5°	223.9	223.4	223.7
7.5°	226.9	225.9	226.2
10°	232.4	231.5	231.0
12.5°	239.5	238.2	238.2
15°	246.8	243.8	243.5
17.5°	252.8	249.1	248.6
20°	259.6	254.6	253.9
22.5°	265.9	259.2	258.1
25°	270.5	262.2	260.9
27.5°	272.4	262.6	261.7
30°	274.0	262.9	261.3
32.5°	272.4	260.6	259.4
35°	264.1	251.3	250.6
37.5°	249.8	235.5	234.5
40°	231.0	215.9	213.4
42.5°	206.8	192.7	190.1
45°	183.5	167.4	166.1
47.5°	158.3	143.0	143.7
50°	131.9	118.1	117.8
52.5°	106.8	94.7	94.0
55°	84.1	75.6	74.9
57.5°	66.6	62.1	61.3
60°	54.3	52.0	51.3
62.5°	43.7	43.0	42.7
65°	36.5	36.5	36.5
67.5°	31.7	31.9	31.9
70°	29.1	29.4	29.1
72.5°	28.2	28.9	28.9
75°	27.4	27.9	26.9
77.5°	26.9	27.2	25.4
80°	26.6	26.4	23.1
82.5°	23.1	22.4	19.6
85°	21.1	16.1	13.6
87.5°	10.8	7.6	5.8
90°	0.0	0.0	0.0

(END OF REPORT)