

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156854

Luminaire Tested: **AVS-F01-LED-E-U-T4-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156854
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F01-LED-E-U-T4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (7) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2278.6 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 25.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156854

CATALOG NUMBER: AVS-F01-LED-E-U-T4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.1 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156854

CATALOG NUMBER: AVS-F01-LED-E-U-T4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P156854

CATALOG NUMBER: AVS-F01-LED-E-U-T4-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	486.2	0.0	486.2
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	1792.4	0.0	1792.4
	% Fixture	78.7	0.0	78.7
Total	Lumens	2278.6	0.0	2278.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.2	1.3
10°-20°	88.5	3.9
20°-30°	152.5	6.7
30°-40°	230.8	10.1
40°-50°	299.1	13.1
50°-60°	412.4	18.1
60°-70°	640.7	28.1
70°-80°	372.5	16.3
80°-90°	53.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2278.6	100.0
0°-180°	2278.6	100.0

Coefficient of Utilization



REPORT NUMBER: P156854


CATALOG NUMBER: AVS-F01-LED-E-U-T4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	140.1	6.1			
FM	(30°-60°)	731.4	32.1			
FH	(60°-80°)	880.2	38.6			G1/1800
FVH	(80°-90°)	40.7	1.8			G1/100
BL	(0°-30°)	130.1	5.7	B1/500		
BM	(30°-60°)	210.8	9.2	B0/220		
BH	(60°-80°)	133.0	5.8	B1/500		G1/500
BVH	(80°-90°)	12.3	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P156854

CATALOG NUMBER: AVS-F01-LED-E-U-T4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3
2.5°	294.8	295.9	295.0	295.3	295.3	295.5	295.5	295.9	295.5	296.3	296.8
5°	289.5	290.1	289.7	290.3	290.8	291.8	291.5	292.8	293.1	293.8	295.0
7.5°	287.6	287.0	287.3	288.0	288.5	289.0	289.5	290.6	291.3	293.1	294.1
10°	289.5	289.3	289.5	290.1	290.1	290.3	289.7	290.8	291.3	292.8	293.8
12.5°	297.8	297.8	297.3	297.3	296.8	296.3	295.0	294.3	294.1	294.3	294.8
15°	311.2	310.7	309.6	308.9	307.9	306.1	304.4	302.9	301.9	300.3	299.8
17.5°	324.2	323.4	322.5	321.5	320.2	318.4	315.6	313.9	311.2	309.4	308.4
20°	339.3	337.8	336.6	335.2	332.7	332.2	329.5	326.5	323.2	319.2	318.7
22.5°	358.9	356.4	354.9	354.1	351.6	350.9	346.3	342.1	338.0	332.7	331.5
25°	378.8	376.3	375.4	374.5	372.7	371.7	367.5	362.7	357.4	350.2	348.6
27.5°	398.1	398.3	396.4	397.1	396.6	394.8	390.6	385.8	381.8	373.3	371.5
30°	422.3	420.7	419.7	421.2	419.5	419.7	416.0	413.5	406.9	401.9	398.3
32.5°	447.4	447.2	448.6	449.6	449.4	448.9	445.9	443.3	437.6	430.3	428.8
35°	481.8	483.3	484.6	489.1	489.1	492.3	489.3	486.3	479.6	470.8	467.8
37.5°	505.2	505.7	510.7	516.8	524.2	531.3	533.4	534.1	531.3	524.8	520.2
40°	526.5	527.6	535.5	544.9	556.0	569.7	578.0	581.9	582.6	579.6	569.7
42.5°	547.9	549.4	557.7	571.3	586.6	604.2	618.8	628.1	633.4	633.4	627.6
45°	572.7	574.8	583.8	598.7	616.5	638.7	658.8	676.6	685.1	685.6	680.1
47.5°	602.2	603.9	614.5	629.5	648.0	670.3	695.6	716.1	731.9	732.8	728.4
50°	640.1	642.7	651.4	665.0	683.8	706.5	731.9	760.3	776.9	780.9	776.1
52.5°	690.4	690.9	698.2	710.8	729.1	750.8	777.6	808.5	830.4	833.7	825.9
55°	759.8	759.1	763.8	777.4	791.2	808.0	836.0	870.6	895.0	900.0	892.0
57.5°	854.0	853.3	857.3	860.5	886.4	902.8	930.2	963.3	986.9	1001.6	987.8
60°	1000.0	999.3	1005.8	1025.0	1044.2	1068.2	1094.8	1134.5	1167.7	1171.9	1158.3
62.5°	1105.9	1109.6	1123.9	1146.3	1185.5	1232.2	1281.0	1333.3	1401.5	1423.0	1416.5
65°	1068.9	1076.5	1096.3	1130.3	1182.5	1247.2	1323.5	1418.2	1509.5	1560.5	1559.0
66°	1035.8	1044.0	1068.4	1101.0	1156.4	1227.0	1310.5	1413.8	1515.8	1572.1	1575.5
67.5°	975.4	984.8	1008.6	1047.3	1101.0	1176.3	1265.9	1378.3	1493.7	1559.3	1568.6
70°	858.0	868.6	885.9	917.8	970.9	1038.0	1132.5	1233.1	1353.9	1429.1	1440.4
72.5°	717.3	726.6	745.9	772.1	815.5	857.8	931.9	1006.1	1092.5	1178.2	1169.9
75°	515.0	519.0	530.6	559.0	582.4	620.3	679.9	740.6	799.7	839.0	844.5
77.5°	267.7	278.2	294.6	326.0	351.4	385.5	424.2	469.9	513.3	549.1	539.4
80°	175.1	179.7	194.3	210.4	228.9	250.8	276.7	293.8	299.4	297.1	299.4
82.5°	101.0	109.3	128.7	141.0	154.8	162.4	183.0	202.6	213.7	199.8	194.8
85°	12.8	16.6	52.2	65.8	75.4	86.7	93.0	104.8	97.7	87.5	106.5
87.5°	2.8	2.5	3.5	7.6	7.8	6.5	12.3	13.1	8.1	4.0	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156854

CATALOG NUMBER: AVS-F01-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3
2.5°	297.3	297.6	298.0	298.9	299.4	299.8	300.3	301.1	301.6	302.1	303.1
5°	296.1	297.1	298.0	299.1	300.3	302.4	303.6	304.7	305.6	307.7	308.4
7.5°	295.3	297.1	298.5	300.3	302.4	304.1	306.3	307.7	309.1	310.4	311.9
10°	294.8	297.3	298.9	301.3	303.6	305.4	307.9	309.4	311.2	312.6	313.4
12.5°	295.9	297.1	298.5	301.1	303.8	306.3	309.1	310.4	311.9	313.2	313.4
15°	300.1	300.1	300.3	302.4	305.1	307.2	309.4	310.7	311.4	312.1	312.1
17.5°	307.9	306.1	304.9	305.1	306.8	308.1	309.4	309.4	308.9	308.6	308.1
20°	316.9	314.7	312.1	310.4	309.8	308.9	308.1	305.6	303.6	301.9	300.6
22.5°	329.9	326.5	323.0	319.7	316.7	313.0	308.6	303.6	298.9	295.5	293.6
25°	346.1	343.3	339.1	334.0	330.3	323.2	317.7	310.4	304.4	300.1	296.6
27.5°	368.9	365.7	361.7	357.1	351.6	343.8	337.0	328.5	321.2	314.9	310.4
30°	397.3	393.1	390.1	384.6	380.7	372.0	365.2	354.6	340.5	330.5	324.2
32.5°	426.5	421.8	419.2	414.9	410.7	405.4	395.1	378.8	360.6	344.4	333.5
35°	465.5	460.4	456.0	452.1	445.9	436.1	427.0	407.4	382.5	359.7	341.6
37.5°	514.5	506.2	494.9	485.3	474.3	460.2	446.3	426.2	397.8	368.2	344.0
40°	566.7	552.1	536.1	518.2	499.2	478.8	462.9	442.6	410.7	375.4	342.3
42.5°	621.2	598.1	575.8	550.7	524.0	499.9	479.3	456.9	420.2	377.5	335.2
45°	675.3	649.4	615.5	582.6	548.9	519.0	495.9	470.8	429.0	378.2	326.0
47.5°	720.1	693.5	654.7	613.5	573.6	539.6	512.4	485.3	440.8	383.5	323.7
50°	767.4	734.9	691.9	643.1	597.9	560.0	531.1	502.9	457.4	397.1	331.0
52.5°	818.9	781.7	731.4	676.8	627.4	584.9	553.5	524.6	478.5	416.2	344.9
55°	881.7	836.2	781.7	720.1	667.0	620.0	585.4	551.2	503.6	438.9	362.2
57.5°	977.7	921.9	860.5	790.5	731.6	676.1	634.6	595.1	542.6	472.5	385.8
60°	1151.4	1091.8	1012.1	927.2	858.0	793.2	732.3	683.4	618.8	538.9	438.0
62.5°	1400.2	1321.0	1214.7	1095.9	1005.3	911.8	843.2	770.4	690.2	603.9	499.7
65°	1538.4	1442.4	1300.1	1162.2	1045.8	944.2	857.0	772.6	683.6	601.1	514.0
66°	1555.4	1455.4	1307.7	1162.4	1040.3	936.0	844.2	756.8	665.8	587.2	508.0
67.5°	1548.5	1446.1	1293.9	1140.5	1016.4	904.2	809.5	718.8	628.1	554.7	487.9
70°	1433.1	1336.1	1186.5	1038.0	920.1	809.5	719.1	629.8	546.6	483.8	434.5
72.5°	1190.1	1107.2	977.2	860.5	768.1	676.8	600.2	515.0	444.6	398.1	368.9
75°	859.1	808.8	690.4	623.5	542.4	481.8	407.4	356.9	306.3	283.7	278.8
77.5°	542.6	475.0	399.9	329.2	270.7	224.5	174.7	148.3	123.6	121.1	146.3
80°	274.7	247.4	190.5	151.8	127.7	103.3	81.7	61.9	43.2	52.0	62.3
82.5°	180.0	150.1	117.6	96.8	84.1	69.8	54.3	37.7	27.7	31.2	42.7
85°	97.3	82.9	66.8	52.7	42.7	38.2	25.6	18.1	17.8	19.1	24.4
87.5°	7.0	7.0	5.5	5.1	6.0	5.1	4.6	4.6	4.2	4.6	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156854

CATALOG NUMBER: AVS-F01-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3	300.3
2.5°	303.6	304.4	304.7	305.9	306.6	307.2	307.7	307.7	307.9	308.6	308.9
5°	309.4	310.7	312.1	313.2	313.7	315.1	315.6	315.6	316.2	317.2	317.9
7.5°	313.0	314.7	316.2	316.7	317.7	318.1	319.0	319.5	319.5	320.4	320.9
10°	314.2	315.1	316.7	316.7	317.7	317.7	318.4	318.7	318.7	319.7	320.4
12.5°	314.2	314.7	316.0	316.0	316.7	316.9	317.9	318.7	319.0	320.2	321.2
15°	312.6	313.2	314.2	314.4	316.2	317.2	319.5	320.9	320.9	322.2	322.7
17.5°	308.4	309.6	311.6	313.7	316.9	319.2	322.0	323.2	322.2	321.5	320.7
20°	301.3	303.6	308.4	313.4	319.2	322.2	323.7	322.5	319.0	315.4	313.2
22.5°	294.3	298.9	306.8	314.4	320.9	323.0	322.2	317.7	311.9	307.7	304.7
25°	297.6	302.9	310.7	317.4	321.7	321.2	318.1	311.9	305.6	300.1	295.0
27.5°	311.2	316.9	321.2	323.4	323.0	319.5	314.7	307.7	300.1	292.8	285.8
30°	323.9	326.9	328.0	326.2	322.2	316.5	310.4	302.4	292.3	283.2	275.2
32.5°	329.7	326.7	322.0	317.2	310.7	305.6	297.3	288.5	276.0	265.2	257.1
35°	329.7	317.7	305.6	295.5	285.8	279.5	269.9	258.1	246.5	237.5	231.2
37.5°	322.5	299.4	279.5	263.1	250.8	244.0	229.7	219.2	209.3	206.3	202.3
40°	309.1	274.9	246.3	225.0	209.3	199.3	185.0	177.7	173.9	172.4	171.7
42.5°	291.3	247.8	209.6	183.2	166.4	155.0	145.5	141.0	140.7	140.5	140.5
45°	272.2	218.7	173.9	142.5	127.7	117.6	113.1	111.3	112.8	112.6	112.8
47.5°	260.4	196.6	141.2	107.8	96.5	89.9	87.7	88.5	89.7	89.2	89.2
50°	258.9	185.2	119.4	83.9	75.4	72.1	71.6	71.6	72.3	71.9	71.6
52.5°	264.4	183.5	108.1	72.1	65.4	62.6	62.1	61.9	61.6	60.1	58.9
55°	274.0	187.5	104.8	69.1	62.1	59.1	58.3	57.8	56.8	54.8	52.5
57.5°	293.1	200.1	107.8	70.7	63.1	60.6	59.8	59.8	57.8	54.5	51.3
60°	339.1	232.0	120.1	76.4	67.9	65.4	65.8	65.6	62.6	57.8	52.7
62.5°	398.3	273.7	136.3	84.5	73.9	73.4	75.9	75.4	70.4	63.1	55.8
65°	425.8	293.3	140.7	86.2	75.1	77.4	82.5	82.0	75.6	65.6	56.3
66°	426.2	293.3	138.8	84.7	73.4	76.2	81.1	80.9	74.6	64.6	55.3
67.5°	416.0	285.3	133.0	81.7	69.8	71.9	76.4	76.2	70.4	62.1	53.3
70°	377.2	255.3	118.1	76.4	65.1	64.0	65.6	64.6	60.8	55.0	49.0
72.5°	323.2	214.4	103.0	72.3	61.9	57.8	56.8	56.1	53.1	49.7	46.0
75°	254.6	169.6	90.5	69.3	58.9	53.6	51.8	50.8	48.8	46.5	43.5
77.5°	157.1	121.3	79.0	65.4	56.6	51.3	50.1	48.5	45.5	42.7	40.4
80°	70.2	75.1	64.9	57.1	50.5	45.7	43.7	41.5	38.4	36.7	35.4
82.5°	46.7	48.5	47.0	42.7	38.2	34.4	31.4	31.4	30.9	29.4	28.9
85°	29.9	30.2	29.1	26.4	24.7	22.4	21.1	21.3	22.4	22.1	21.9
87.5°	6.7	6.7	8.1	7.6	8.8	9.3	10.1	10.8	12.3	12.3	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156854

CATALOG NUMBER: AVS-F01-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	300.3	300.3	300.3	300.3	300.3
2.5°	309.1	309.6	310.2	309.4	309.6
5°	317.9	317.7	319.0	318.1	318.7
7.5°	320.7	320.9	322.0	322.0	322.2
10°	320.9	321.5	322.7	323.4	323.9
12.5°	322.2	323.2	325.2	325.7	325.7
15°	323.2	323.7	325.0	325.5	326.0
17.5°	319.7	318.7	319.2	319.5	319.2
20°	310.9	309.8	309.6	308.6	309.1
22.5°	301.3	298.5	296.8	294.8	294.8
25°	289.7	285.5	282.0	278.4	279.3
27.5°	279.0	273.5	269.9	267.7	267.2
30°	268.4	262.6	259.4	256.6	256.6
32.5°	250.8	246.8	242.5	240.7	240.5
35°	226.4	223.9	220.4	219.7	218.4
37.5°	199.1	198.3	195.2	195.0	193.8
40°	170.4	170.9	169.9	169.4	168.6
42.5°	141.8	144.2	143.7	143.5	143.0
45°	114.4	116.2	116.4	117.1	118.3
47.5°	89.9	90.5	91.0	90.8	91.0
50°	70.4	69.1	68.9	68.1	68.9
52.5°	56.8	54.8	53.8	52.7	52.2
55°	50.1	48.0	47.0	46.5	46.0
57.5°	48.3	46.2	44.8	43.7	43.5
60°	48.8	45.7	43.7	42.5	42.2
62.5°	50.1	46.0	43.2	42.0	41.8
65°	49.7	45.5	43.0	41.5	41.2
66°	49.0	45.0	42.5	41.2	40.9
67.5°	47.8	44.2	42.0	40.9	40.4
70°	45.5	43.2	41.5	40.2	39.7
72.5°	43.5	41.8	40.2	39.0	38.8
75°	41.2	39.7	38.2	37.2	37.0
77.5°	38.4	37.0	36.0	35.2	34.9
80°	33.9	33.0	31.9	30.9	30.9
82.5°	28.2	27.4	26.4	25.6	25.4
85°	21.7	21.7	20.8	20.1	19.9
87.5°	12.8	12.5	12.5	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)