

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P150894

Luminaire Tested: **AVS-F02-LED-E-U-SL3-HSS-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P150894
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33727)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-SL3-HSS-7030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (14) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2614.6 lumens
Efficiency: N/A
Efficacy: 47.5 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type III - Short - Non-Cutoff
BUG Rating: B0 - U0 - G1

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P150894

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.3 fc
 Type III - Short - Non-Cutoff

REPORT NUMBER: P150894

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P150894

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	56.7	0.0	56.7
	% Fixture	2.2	0.0	2.2
Street Side	Lumens	2557.9	0.0	2557.9
	% Fixture	97.8	0.0	97.8
Total	Lumens	2614.6	0.0	2614.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.8	0.3
10°-20°	37.5	1.4
20°-30°	80.8	3.1
30°-40°	172.5	6.6
40°-50°	381.6	14.6
50°-60°	646.6	24.7
60°-70°	862.9	33.0
70°-80°	380.1	14.5
80°-90°	43.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2614.6	100.0
0°-180°	2614.6	100.0

Coefficient of Utilization



REPORT NUMBER: P150894


CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	109.2	4.2			
FM	(30°-60°)	1175.9	45.0			
FH	(60°-80°)	1230.8	47.1			G1/1800
FVH	(80°-90°)	42.0	1.6			G1/100
BL	(0°-30°)	17.9	0.7	B0/110		
BM	(30°-60°)	24.9	1.0	B0/220		
BH	(60°-80°)	12.2	0.5	B0/110		G0/110
BVH	(80°-90°)	1.7	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type III Short





REPORT NUMBER: P150894

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	67°	68°
0°	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0
2.5°	99.5	99.1	97.0	97.0	94.0	92.0	89.4	86.9	86.9	86.4	85.9
5°	131.7	128.7	128.2	122.7	118.1	111.6	105.6	97.5	96.5	95.5	95.0
7.5°	167.4	166.8	162.4	155.9	146.7	134.7	122.7	109.5	107.6	106.5	104.6
10°	213.7	211.1	205.1	194.0	180.4	164.4	144.8	124.1	121.7	119.6	118.7
12.5°	257.8	253.4	249.8	235.8	218.7	195.0	171.4	141.8	139.7	137.2	133.2
15°	299.1	295.0	289.0	277.0	257.8	228.2	200.5	164.4	159.4	155.9	152.8
17.5°	331.3	328.7	321.7	308.1	287.6	261.3	228.2	187.5	183.5	179.0	173.4
20°	361.9	358.4	347.4	328.7	306.6	286.5	260.9	217.6	212.1	206.6	200.5
22.5°	391.1	387.6	369.4	338.8	315.1	306.6	297.6	251.8	243.3	238.8	232.7
25°	431.8	424.2	396.1	347.4	315.6	322.2	337.8	296.1	288.0	281.5	271.9
27.5°	486.5	476.5	432.3	359.9	317.7	339.3	384.0	349.8	341.3	333.8	323.2
30°	548.4	541.9	489.1	390.1	332.2	364.5	435.9	418.2	408.2	399.1	386.5
32.5°	610.8	601.7	549.4	447.4	371.5	413.2	500.6	497.6	484.6	476.1	462.5
35°	665.5	661.0	622.3	541.3	460.9	498.7	587.2	590.7	579.1	570.1	554.9
37.5°	702.7	702.7	695.2	642.4	603.2	631.3	714.3	714.8	703.2	682.6	675.0
40°	721.9	727.4	754.5	764.6	762.5	798.8	881.1	872.1	862.6	852.0	826.8
42.5°	761.0	766.0	823.8	893.3	938.4	986.2	1043.0	1040.0	1028.5	1009.3	986.2
45°	827.4	833.9	902.8	1012.8	1105.9	1173.7	1209.9	1195.9	1184.2	1166.2	1154.1
47.5°	911.8	924.4	1002.3	1138.5	1250.7	1362.7	1400.4	1363.2	1353.2	1339.1	1319.5
50°	1001.8	1013.9	1096.8	1252.6	1379.3	1513.1	1575.9	1513.1	1498.4	1493.9	1471.8
52.5°	1079.7	1089.7	1169.7	1340.6	1477.8	1634.6	1726.1	1643.2	1632.6	1617.6	1601.5
55°	1126.0	1134.0	1208.9	1382.8	1544.7	1744.2	1871.4	1798.5	1782.9	1776.9	1753.8
57.5°	1141.6	1149.6	1217.0	1388.4	1580.8	1844.2	2047.9	2050.4	2031.7	2010.2	2003.1
60°	1141.6	1150.6	1207.4	1374.8	1616.1	1950.9	2283.1	2492.7	2452.5	2448.5	2422.8
62.5°	1094.3	1102.8	1160.1	1333.1	1663.3	2094.6	2610.8	2980.8	2969.2	2943.1	2900.8
65°	991.7	996.8	1053.1	1226.5	1645.2	2226.8	2894.8	3305.5	3286.9	3235.6	3181.3
66°	945.5	949.5	1002.3	1165.7	1585.9	2244.9	2945.1	3346.2	3315.5	3272.3	3211.0
67.5°	878.7	885.7	922.9	1052.5	1443.6	2182.1	2913.5	3317.6	3290.9	3238.7	3177.3
70°	586.6	581.6	712.7	807.8	1099.8	1777.9	2613.9	2978.8	2979.3	2954.6	2930.1
72.5°	278.4	281.5	319.7	497.1	719.8	1187.8	2080.5	2377.6	2411.8	2367.6	2336.9
75°	200.1	204.6	227.7	304.1	429.2	712.7	1348.6	1662.8	1663.8	1585.4	1515.5
77.5°	58.3	60.8	85.5	187.5	321.7	481.0	774.6	924.4	902.8	846.5	793.7
80°	24.1	24.1	25.2	59.8	129.2	326.7	541.9	711.8	709.2	687.7	656.5
82.5°	9.0	9.5	12.0	24.7	30.7	80.4	361.5	617.7	616.3	585.6	563.5
85°	1.0	1.0	3.0	10.6	11.6	15.1	72.3	272.4	271.0	272.4	238.8
87.5°	0.0	0.0	0.5	1.0	1.6	2.0	3.0	10.6	11.6	11.1	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150894

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7030

CANDELA DISTRIBUTION (continued):

	69°	70°	71°	72°	73°	74°	75°	76°	77°	78°	79°
0°	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0
2.5°	85.9	85.0	85.0	84.5	84.5	84.5	83.9	83.4	83.4	82.9	82.5
5°	94.0	93.0	92.5	91.5	91.0	90.5	89.4	89.0	88.0	87.5	86.9
7.5°	103.5	101.6	101.0	99.5	98.0	97.0	96.0	94.5	93.5	91.5	91.0
10°	115.6	113.1	111.1	109.1	107.6	105.1	103.5	101.6	99.5	98.0	96.5
12.5°	131.2	127.7	124.7	122.7	119.2	116.2	113.1	111.6	107.6	105.6	103.0
15°	148.3	144.2	140.7	136.7	134.2	129.2	125.2	120.6	118.7	115.1	111.1
17.5°	170.4	163.8	158.3	154.3	149.3	144.2	139.7	135.2	129.2	125.2	120.1
20°	194.0	188.5	180.9	173.9	167.9	161.9	155.3	149.3	143.7	137.2	131.2
22.5°	224.1	216.2	207.0	200.1	192.0	185.5	176.5	168.4	159.4	150.8	143.7
25°	262.4	251.8	243.3	233.3	223.7	213.7	202.6	192.5	180.9	173.0	160.8
27.5°	309.6	299.6	288.0	274.9	265.4	250.4	235.8	223.2	209.6	197.0	183.5
30°	369.9	355.3	343.3	330.8	311.6	297.1	280.0	262.9	244.2	231.7	211.1
32.5°	442.4	426.7	408.7	390.6	373.0	352.3	331.3	310.2	289.5	266.4	245.3
35°	530.8	512.2	491.6	472.0	444.9	422.7	396.1	366.9	343.8	317.2	290.6
37.5°	648.0	617.3	599.2	578.5	541.9	511.7	482.1	452.8	412.2	384.0	346.3
40°	794.7	776.6	746.9	713.8	680.6	640.9	600.7	562.0	514.7	475.5	431.8
42.5°	967.2	940.5	910.4	862.6	828.9	782.2	736.4	685.1	627.4	577.1	525.8
45°	1129.0	1097.3	1074.2	1026.4	991.3	936.0	880.6	826.4	759.5	694.7	635.3
47.5°	1303.9	1277.7	1239.6	1200.8	1165.2	1102.8	1043.0	977.2	906.8	829.8	753.0
50°	1457.7	1437.1	1411.0	1364.2	1324.6	1272.2	1201.9	1129.9	1041.0	964.6	877.1
52.5°	1588.4	1572.3	1535.6	1502.5	1466.7	1417.5	1354.7	1285.8	1189.8	1105.9	1006.3
55°	1742.7	1731.2	1699.0	1678.3	1646.7	1599.5	1540.6	1476.8	1375.2	1283.8	1171.2
57.5°	1995.5	1986.5	1958.3	1949.8	1918.7	1877.4	1805.1	1736.7	1618.0	1504.5	1375.8
60°	2414.3	2396.2	2354.9	2333.9	2268.0	2212.7	2118.8	2024.8	1881.5	1736.7	1581.9
62.5°	2862.7	2811.9	2733.5	2666.1	2572.6	2476.6	2351.0	2207.2	2039.3	1867.4	1689.4
65°	3104.5	3018.0	2919.0	2811.9	2690.8	2549.5	2391.2	2218.8	2038.3	1856.8	1668.8
66°	3132.1	3034.6	2929.5	2810.4	2675.6	2525.4	2364.6	2183.5	1996.1	1819.2	1631.1
67.5°	3097.4	2995.3	2884.2	2752.1	2606.3	2450.5	2281.6	2093.6	1913.2	1733.7	1550.7
70°	2854.6	2753.1	2654.1	2514.8	2359.5	2202.7	2042.8	1832.7	1661.8	1496.9	1334.1
72.5°	2279.6	2210.7	2112.6	1993.6	1842.3	1658.2	1525.1	1337.1	1188.8	1028.9	902.8
75°	1424.6	1327.6	1206.4	1054.6	939.0	789.6	711.8	569.0	484.6	410.7	339.3
77.5°	728.4	655.4	570.6	485.1	403.1	321.7	248.8	176.0	118.7	82.5	61.3
80°	601.7	537.3	466.9	389.0	316.7	245.8	176.9	120.6	76.9	50.3	39.2
82.5°	497.1	442.8	380.0	307.7	244.8	193.1	134.2	87.5	54.3	35.2	27.7
85°	211.6	192.0	148.3	117.6	88.5	65.4	45.7	30.7	21.7	17.6	16.1
87.5°	9.0	10.1	9.5	7.6	5.5	5.5	5.1	4.0	4.0	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150894

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7030

CANDELA DISTRIBUTION (continued):

	80°	81°	82°	83°	84°	85°	95°	105°	115°	125°	135°
0°	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0
2.5°	82.5	82.0	81.5	81.5	80.9	80.4	77.4	74.9	71.9	69.8	67.9
5°	85.9	85.5	84.5	83.9	82.9	82.5	75.9	70.4	65.8	62.3	59.8
7.5°	89.4	89.0	87.5	85.9	85.5	84.5	73.9	66.8	60.8	56.8	54.3
10°	94.0	92.5	91.0	89.0	87.5	85.9	71.9	62.8	56.3	52.7	50.3
12.5°	100.5	98.0	95.5	93.0	91.0	88.5	70.9	59.3	52.7	48.8	46.2
15°	108.1	104.6	101.6	98.5	95.0	92.5	68.9	56.3	49.7	45.7	42.7
17.5°	115.1	111.1	106.5	102.1	98.5	95.0	66.8	53.3	46.7	42.7	39.7
20°	125.2	119.2	113.6	108.1	103.0	98.5	63.8	50.3	44.2	39.7	36.7
22.5°	136.3	129.2	122.2	114.6	108.1	102.1	61.3	47.8	41.8	37.2	33.7
25°	150.3	141.8	132.2	122.7	115.1	107.0	58.9	45.3	39.2	34.7	31.2
27.5°	169.9	157.8	147.3	135.2	123.6	114.6	56.8	43.2	36.7	32.1	28.6
30°	196.6	179.0	162.4	149.3	135.8	122.7	54.8	40.7	34.7	29.6	25.6
32.5°	226.2	205.6	186.5	166.8	149.8	134.7	52.7	38.8	32.1	27.2	23.6
35°	262.9	236.8	211.1	188.5	167.9	147.8	50.8	36.7	30.2	24.7	21.1
37.5°	315.6	283.0	249.3	220.2	193.6	166.8	49.2	34.7	27.7	22.1	18.5
40°	388.1	345.8	304.7	264.9	230.3	197.0	47.3	32.6	25.6	20.1	16.6
42.5°	466.4	415.2	360.9	316.2	268.4	226.7	45.3	30.7	23.6	18.1	14.6
45°	563.9	500.1	434.3	373.5	315.1	261.3	43.2	28.6	21.1	16.1	12.5
47.5°	670.6	589.1	514.7	438.3	368.9	304.7	40.7	27.2	19.1	14.1	11.1
50°	780.1	694.2	600.2	513.3	430.8	347.9	38.2	24.7	17.1	12.5	9.0
52.5°	898.2	796.7	700.7	592.6	496.6	404.7	35.6	22.6	15.5	11.1	7.6
55°	1048.6	934.9	822.4	701.2	585.6	470.5	33.2	20.1	13.6	9.5	6.0
57.5°	1237.5	1102.8	964.6	827.9	687.7	557.0	31.2	17.6	11.6	8.1	5.1
60°	1416.0	1258.7	1091.3	934.0	775.6	623.3	28.2	15.5	10.1	6.5	5.1
62.5°	1508.5	1329.0	1148.6	975.1	806.3	646.9	25.2	13.1	8.5	5.5	4.6
65°	1485.9	1302.9	1128.0	953.1	787.7	631.8	22.1	11.6	7.6	5.1	4.6
66°	1453.2	1272.2	1096.3	929.9	772.1	615.8	20.6	11.1	7.0	5.1	4.0
67.5°	1381.9	1206.9	1039.0	884.1	729.3	585.1	18.5	10.1	6.5	4.6	4.0
70°	1180.2	1021.5	887.2	749.4	623.3	493.2	15.1	8.5	5.5	4.0	4.0
72.5°	781.1	673.1	583.6	502.2	419.7	325.7	12.5	7.0	4.6	4.0	3.5
75°	294.6	266.4	228.7	205.6	179.5	157.3	10.1	4.6	3.5	3.5	3.5
77.5°	52.2	48.3	42.7	39.2	36.2	33.2	8.1	3.0	3.0	3.5	3.5
80°	35.2	32.6	29.6	27.2	25.2	22.6	5.5	2.5	3.0	3.0	3.5
82.5°	25.2	23.6	22.1	20.1	18.5	16.6	3.5	2.5	3.0	3.0	3.0
85°	15.1	14.1	13.1	12.0	10.6	10.1	2.5	2.5	2.5	3.0	3.0
87.5°	4.0	3.5	4.0	4.0	3.0	3.5	2.0	2.0	2.0	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150894

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7030

CANDELA DISTRIBUTION (continued):

	145°	155°	165°	175°	180°
0°	79.0	79.0	79.0	79.0	79.0
2.5°	66.8	66.8	65.8	67.4	67.4
5°	57.8	57.8	57.3	57.8	57.8
7.5°	52.7	52.2	52.2	52.2	52.7
10°	48.3	47.8	47.8	47.8	47.8
12.5°	44.2	43.7	43.2	43.7	43.7
15°	40.7	39.7	39.7	39.7	39.7
17.5°	37.7	36.7	36.2	36.2	36.2
20°	34.7	33.2	33.2	33.2	33.2
22.5°	31.7	30.2	30.2	30.2	30.2
25°	28.6	27.2	27.2	27.2	27.2
27.5°	26.1	24.7	24.7	24.7	24.7
30°	23.1	22.1	22.1	22.6	22.1
32.5°	21.1	19.6	19.6	20.1	20.1
35°	18.5	17.6	17.6	17.6	17.6
37.5°	16.1	15.1	15.1	15.1	15.1
40°	14.1	13.1	12.5	13.1	13.1
42.5°	12.0	11.1	10.6	10.6	10.6
45°	10.6	9.0	8.5	9.0	9.0
47.5°	8.5	7.6	7.6	8.1	8.1
50°	6.5	6.5	7.0	8.1	8.1
52.5°	6.0	6.0	7.0	8.1	8.1
55°	5.5	6.0	7.0	7.6	8.1
57.5°	5.1	6.0	7.0	7.6	7.6
60°	5.1	5.5	6.5	7.6	7.6
62.5°	4.6	5.1	6.0	7.0	7.0
65°	4.6	5.1	6.0	7.0	7.0
66°	4.6	5.1	6.0	7.0	7.0
67.5°	4.6	5.1	6.0	7.0	7.0
70°	4.6	5.1	6.0	6.5	6.5
72.5°	4.0	4.6	5.5	6.5	6.5
75°	4.0	4.6	5.5	6.5	6.5
77.5°	4.0	4.6	5.5	6.5	6.5
80°	4.0	4.6	5.5	6.0	6.5
82.5°	3.5	4.6	5.1	6.0	6.0
85°	3.5	4.0	5.1	5.5	6.0
87.5°	3.0	3.5	4.0	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)