

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156864

Luminaire Tested: **AVS-F02-LED-E-U-T4-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156864
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-T4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (14) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4557.2 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156864

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 6.3 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156864

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P156864

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	972.4	0.0	972.4
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	3584.8	0.0	3584.8
	% Fixture	78.7	0.0	78.7
Total	Lumens	4557.2	0.0	4557.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.3	1.3
10°-20°	177.1	3.9
20°-30°	305.0	6.7
30°-40°	461.5	10.1
40°-50°	598.2	13.1
50°-60°	824.7	18.1
60°-70°	1281.3	28.1
70°-80°	745.1	16.3
80°-90°	106.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4557.2	100.0
0°-180°	4557.2	100.0

Coefficient of Utilization



REPORT NUMBER: P156864


CATALOG NUMBER: AVS-F02-LED-E-U-T4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	280.2	6.1			
FM	(30°-60°)	1462.9	32.1			
FH	(60°-80°)	1760.4	38.6			G1/1800
FVH	(80°-90°)	81.3	1.8			G1/100
BL	(0°-30°)	260.3	5.7	B1/500		
BM	(30°-60°)	421.5	9.2	B1/1000		
BH	(60°-80°)	265.9	5.8	B1/500		G1/500
BVH	(80°-90°)	24.6	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P156864

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7
2.5°	589.6	591.6	590.2	590.7	590.7	591.1	591.1	591.6	591.1	592.6	593.7
5°	579.1	580.1	579.6	580.6	581.6	583.6	583.1	585.6	586.1	587.6	590.2
7.5°	575.0	574.0	574.5	576.1	577.1	578.0	579.1	581.0	582.6	586.1	588.1
10°	579.1	578.5	579.1	580.1	580.1	580.6	579.6	581.6	582.6	585.6	587.6
12.5°	595.6	595.6	594.6	594.6	593.7	592.6	590.2	588.6	588.1	588.6	589.6
15°	622.3	621.2	619.3	617.7	615.8	612.2	608.7	605.7	603.7	600.7	599.7
17.5°	648.4	646.9	644.9	642.9	640.4	636.9	631.3	627.9	622.3	618.8	616.8
20°	678.5	675.5	673.1	670.6	665.5	664.6	659.0	653.0	646.4	638.3	637.4
22.5°	717.8	712.7	709.7	708.3	703.2	701.8	692.6	684.1	676.1	665.5	663.0
25°	757.5	752.4	751.0	749.0	745.5	743.4	734.9	725.4	714.8	700.2	697.2
27.5°	796.2	796.7	792.7	794.2	793.2	789.6	781.1	771.6	763.5	746.4	742.9
30°	844.5	841.5	839.5	842.5	839.0	839.5	831.9	826.8	813.8	803.7	796.7
32.5°	894.7	894.2	897.2	899.3	898.8	897.7	891.7	886.7	875.1	860.5	857.5
35°	963.6	966.6	969.1	978.1	978.1	984.8	978.7	972.6	959.1	941.5	935.4
37.5°	1010.4	1011.4	1021.5	1033.5	1048.6	1062.6	1066.6	1068.2	1062.6	1049.5	1040.5
40°	1053.1	1055.1	1071.2	1089.7	1111.9	1139.6	1156.2	1163.6	1165.2	1159.2	1139.6
42.5°	1095.9	1098.9	1115.4	1142.6	1173.3	1208.4	1237.5	1256.2	1266.7	1266.7	1255.1
45°	1145.6	1149.6	1167.7	1197.3	1233.1	1277.3	1317.5	1353.2	1370.3	1371.3	1360.2
47.5°	1204.4	1207.9	1229.0	1259.2	1295.9	1340.6	1391.4	1432.1	1463.7	1465.8	1456.7
50°	1280.3	1285.3	1302.9	1330.1	1367.8	1413.0	1463.7	1520.5	1553.7	1561.8	1552.2
52.5°	1380.8	1381.9	1396.4	1421.6	1458.2	1501.5	1555.2	1617.1	1660.8	1667.4	1651.7
55°	1519.6	1518.0	1527.6	1554.7	1582.4	1616.1	1671.8	1741.2	1789.9	1800.0	1783.9
57.5°	1708.1	1706.5	1714.6	1721.1	1772.8	1805.6	1860.3	1926.7	1974.0	2003.1	1975.4
60°	2000.1	1998.5	2011.6	2049.8	2088.6	2136.3	2189.6	2269.0	2335.3	2343.9	2316.8
62.5°	2211.7	2219.3	2247.9	2292.6	2371.1	2464.6	2562.1	2666.6	2802.8	2846.1	2833.0
65°	2137.8	2153.0	2192.6	2260.5	2365.1	2494.2	2647.0	2836.5	3019.0	3121.0	3118.0
66°	2071.5	2088.1	2136.8	2202.2	2312.7	2454.0	2620.9	2827.5	3031.6	3144.1	3151.2
67.5°	1950.9	1969.4	2017.2	2094.6	2202.2	2352.4	2531.9	2756.6	2987.4	3118.5	3137.1
70°	1716.1	1737.2	1771.9	1835.8	1941.8	2076.0	2265.0	2466.0	2707.9	2858.1	2880.7
72.5°	1434.6	1453.2	1491.9	1544.1	1631.1	1715.5	1863.8	2012.1	2185.1	2356.5	2339.9
75°	1029.9	1038.0	1061.1	1117.9	1164.7	1240.6	1359.7	1481.3	1599.5	1677.9	1688.9
77.5°	535.3	556.5	589.1	651.9	702.7	771.1	848.5	940.0	1026.4	1098.3	1078.8
80°	350.4	359.4	388.6	420.7	457.9	501.7	553.5	587.6	598.7	594.2	598.7
82.5°	202.1	218.7	257.4	282.0	309.6	324.8	365.9	405.2	427.3	399.6	389.5
85°	25.6	33.2	104.6	131.7	150.8	173.4	186.0	209.6	195.5	174.9	213.2
87.5°	5.5	5.1	7.0	15.1	15.5	13.1	24.7	26.1	16.1	8.1	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156864

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7
2.5°	594.6	595.1	596.2	597.6	598.7	599.7	600.7	602.2	603.2	604.2	606.2
5°	592.1	594.2	596.2	598.1	600.7	604.7	607.3	609.2	611.2	615.2	616.8
7.5°	590.7	594.2	597.2	600.7	604.7	608.2	612.7	615.2	618.2	620.8	623.8
10°	589.6	594.6	597.6	602.7	607.3	610.8	615.8	618.8	622.3	625.3	626.8
12.5°	591.6	594.2	597.2	602.2	607.7	612.7	618.2	620.8	623.8	626.3	626.8
15°	600.2	600.2	600.7	604.7	610.3	614.3	618.8	621.2	622.8	624.4	624.4
17.5°	615.8	612.2	609.7	610.3	613.8	616.3	618.8	618.8	617.7	617.3	616.3
20°	633.9	629.3	624.4	620.8	619.8	617.7	616.3	611.2	607.3	603.7	601.1
22.5°	660.0	653.0	645.9	639.4	633.4	625.8	617.3	607.3	597.6	591.1	587.2
25°	692.1	686.6	678.1	668.1	660.5	646.4	635.3	620.8	608.7	600.2	593.2
27.5°	737.9	731.4	723.3	714.3	703.2	687.7	674.1	657.0	642.4	629.8	620.8
30°	794.7	786.1	780.1	769.1	761.6	743.9	730.4	709.2	681.1	661.0	648.4
32.5°	853.1	843.4	838.4	829.8	821.3	810.8	790.2	757.5	721.3	688.6	667.0
35°	930.9	920.8	911.8	904.2	891.7	872.1	854.0	814.8	765.1	719.3	683.1
37.5°	1028.9	1012.3	989.7	970.7	948.5	920.4	892.7	852.5	795.8	736.4	688.2
40°	1133.5	1104.4	1072.2	1036.5	998.2	957.6	925.9	885.2	821.3	751.0	684.7
42.5°	1242.6	1196.4	1151.6	1101.3	1048.1	999.8	958.5	913.9	840.4	755.0	670.6
45°	1350.7	1298.9	1231.0	1165.2	1097.8	1038.0	991.7	941.5	858.0	756.5	651.9
47.5°	1440.1	1386.8	1309.4	1227.0	1147.0	1079.2	1025.0	970.7	881.7	767.0	647.5
50°	1534.6	1469.7	1383.8	1286.3	1195.9	1119.9	1062.2	1005.8	914.8	794.2	662.0
52.5°	1637.7	1563.3	1462.8	1353.7	1254.6	1169.7	1106.8	1049.0	957.1	832.4	689.6
55°	1763.3	1672.3	1563.3	1440.1	1334.1	1240.1	1170.7	1102.4	1007.4	877.6	724.4
57.5°	1955.3	1843.7	1721.1	1580.8	1463.2	1352.1	1269.2	1190.3	1085.3	945.0	771.6
60°	2302.7	2183.5	2024.2	1854.3	1716.1	1586.4	1464.8	1366.7	1237.5	1077.7	876.2
62.5°	2800.3	2642.0	2429.3	2191.6	2010.7	1823.6	1686.4	1540.6	1380.3	1207.9	999.3
65°	3076.8	2884.8	2600.3	2324.4	2091.6	1888.5	1714.1	1545.2	1367.3	1202.4	1028.0
66°	3111.0	2910.9	2615.3	2324.8	2080.5	1871.9	1688.4	1513.5	1331.5	1174.2	1015.9
67.5°	3096.9	2892.3	2587.7	2281.0	2032.7	1808.6	1619.1	1437.6	1256.2	1109.3	975.6
70°	2866.2	2672.1	2373.1	2076.0	1840.2	1619.1	1438.1	1259.7	1093.3	967.7	869.1
72.5°	2380.1	2214.2	1954.3	1721.1	1536.2	1353.7	1200.3	1029.9	889.2	796.2	737.9
75°	1718.1	1617.6	1380.8	1247.2	1084.8	963.6	814.8	713.8	612.7	567.5	557.4
77.5°	1085.3	950.1	799.7	658.4	541.3	448.9	349.3	296.6	247.4	242.3	292.5
80°	549.4	494.6	381.0	303.6	255.3	206.6	163.3	123.6	86.4	104.0	124.7
82.5°	359.9	300.1	235.2	193.6	168.4	139.7	108.6	75.4	55.3	62.3	85.5
85°	194.5	165.9	133.7	105.6	85.5	76.4	51.3	36.2	35.6	38.2	48.8
87.5°	14.1	14.1	11.1	10.1	12.0	10.1	9.0	9.0	8.5	9.0	12.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156864

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7	600.7
2.5°	607.3	608.7	609.2	611.7	613.3	614.3	615.2	615.2	615.8	617.3	617.7
5°	618.8	621.2	624.4	626.3	627.4	630.4	631.3	631.3	632.3	634.4	635.9
7.5°	625.8	629.3	632.3	633.4	635.3	636.4	637.9	638.9	638.9	640.9	641.9
10°	628.3	630.4	633.4	633.4	635.3	635.3	636.9	637.4	637.4	639.4	640.9
12.5°	628.3	629.3	631.8	631.8	633.4	633.9	635.9	637.4	637.9	640.4	642.4
15°	625.3	626.3	628.3	628.8	632.3	634.4	638.9	641.9	641.9	644.5	645.4
17.5°	616.8	619.3	623.3	627.4	633.9	638.3	643.9	646.4	644.5	642.9	641.3
20°	602.7	607.3	616.8	626.8	638.3	644.5	647.5	644.9	637.9	630.9	626.3
22.5°	588.6	597.6	613.8	628.8	641.9	645.9	644.5	635.3	623.8	615.2	609.2
25°	595.1	605.7	621.2	634.8	643.4	642.4	636.4	623.8	611.2	600.2	590.2
27.5°	622.3	633.9	642.4	646.9	645.9	638.9	629.3	615.2	600.2	585.6	571.5
30°	648.0	654.0	656.0	652.4	644.5	632.8	620.8	604.7	584.6	566.5	550.5
32.5°	659.5	653.5	643.9	634.4	621.2	611.2	594.6	577.1	551.9	530.3	514.2
35°	659.5	635.3	611.2	591.1	571.5	559.0	539.9	516.3	493.2	475.0	462.5
37.5°	644.9	598.7	559.0	526.3	501.7	488.1	459.5	438.3	418.8	412.6	404.7
40°	618.2	549.9	492.6	449.8	418.8	398.7	369.9	355.3	347.9	344.9	343.3
42.5°	582.6	495.6	419.2	366.4	332.7	310.2	291.1	282.0	281.5	281.0	281.0
45°	544.4	437.3	347.9	285.0	255.3	235.2	226.2	222.7	225.7	225.2	225.7
47.5°	520.7	393.1	282.5	215.6	193.1	180.0	175.4	176.9	179.5	178.4	178.4
50°	517.7	370.5	238.8	167.9	150.8	144.2	143.2	143.2	144.8	143.7	143.2
52.5°	528.8	366.9	216.2	144.2	130.7	125.2	124.1	123.6	123.1	120.1	117.6
55°	547.9	375.0	209.6	138.2	124.1	118.1	116.6	115.6	113.6	109.5	105.1
57.5°	586.1	400.1	215.6	141.2	126.2	121.1	119.6	119.6	115.6	109.1	102.6
60°	678.1	463.9	240.3	152.8	135.8	130.7	131.7	131.2	125.2	115.6	105.6
62.5°	796.7	547.4	272.4	168.9	147.8	146.7	151.8	150.8	140.7	126.2	111.6
65°	851.5	586.6	281.5	172.4	150.3	154.8	164.9	163.8	151.3	131.2	112.6
66°	852.5	586.6	277.5	169.4	146.7	152.3	162.4	161.9	149.3	129.2	110.6
67.5°	831.9	570.6	265.9	163.3	139.7	143.7	152.8	152.3	140.7	124.1	106.5
70°	754.5	510.7	236.3	152.8	130.2	128.2	131.2	129.2	121.7	110.1	98.0
72.5°	646.4	428.8	206.1	144.8	123.6	115.6	113.6	112.1	106.0	99.5	92.0
75°	509.2	339.3	180.9	138.8	117.6	107.0	103.5	101.6	97.5	93.0	86.9
77.5°	314.2	242.8	157.8	130.7	113.1	102.6	100.0	97.0	91.0	85.5	80.9
80°	140.2	150.3	129.6	114.1	101.0	91.5	87.5	82.9	76.9	73.4	70.9
82.5°	93.5	97.0	94.0	85.5	76.4	68.9	62.8	62.8	61.9	58.9	57.8
85°	59.8	60.3	58.3	52.7	49.2	44.8	42.2	42.7	44.8	44.2	43.7
87.5°	13.6	13.6	16.1	15.1	17.6	18.5	20.1	21.7	24.7	24.7	26.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156864

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	600.7	600.7	600.7	600.7	600.7
2.5°	618.2	619.3	620.3	618.8	619.3
5°	635.9	635.3	637.9	636.4	637.4
7.5°	641.3	641.9	643.9	643.9	644.5
10°	641.9	642.9	645.4	646.9	648.0
12.5°	644.5	646.4	650.5	651.4	651.4
15°	646.4	647.5	649.9	651.0	651.9
17.5°	639.4	637.4	638.3	638.9	638.3
20°	621.8	619.8	619.3	617.3	618.2
22.5°	602.7	597.2	593.7	589.6	589.6
25°	579.6	571.0	563.9	557.0	558.4
27.5°	557.9	546.9	539.9	535.3	534.3
30°	536.9	525.3	518.8	513.3	513.3
32.5°	501.7	493.6	485.1	481.6	481.0
35°	452.8	447.9	440.8	439.4	436.8
37.5°	398.1	396.6	390.6	390.1	387.6
40°	340.8	341.8	339.8	338.8	337.3
42.5°	283.5	288.5	287.6	287.0	286.0
45°	228.7	232.2	232.7	234.2	236.8
47.5°	180.0	180.9	182.0	181.5	182.0
50°	140.7	138.2	137.7	136.3	137.7
52.5°	113.6	109.5	107.6	105.6	104.6
55°	100.0	96.0	94.0	93.0	92.0
57.5°	96.5	92.5	89.4	87.5	86.9
60°	97.5	91.5	87.5	85.0	84.5
62.5°	100.0	92.0	86.4	83.9	83.4
65°	99.5	91.0	85.9	82.9	82.5
66°	98.0	89.9	85.0	82.5	82.0
67.5°	95.5	88.5	83.9	82.0	80.9
70°	91.0	86.4	82.9	80.4	79.4
72.5°	86.9	83.4	80.4	77.9	77.4
75°	82.5	79.4	76.4	74.4	73.9
77.5°	76.9	73.9	71.9	70.4	69.8
80°	67.9	65.8	63.8	61.9	61.9
82.5°	56.3	54.8	52.7	51.3	50.8
85°	43.2	43.2	41.8	40.2	39.7
87.5°	25.6	25.2	25.2	23.6	23.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)