

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P153171

Luminaire Tested: **AVS-E02-LED-E-U-SLL-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P153171
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33681)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-SLL-7050
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - 90° SPILL LIGHT ELIMINATOR LEFT
Light Source: (42) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5710.2 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Non-Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P153171

CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 14.2 fc
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P153171

CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P153171

CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1238.2	0.0	1238.2
	% Fixture	21.7	0.0	21.7
Street Side	Lumens	4471.9	0.0	4471.9
	% Fixture	78.3	0.0	78.3
Total	Lumens	5710.2	0.0	5710.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.9	1.2
10°-20°	217.6	3.8
20°-30°	386.5	6.8
30°-40°	608.6	10.7
40°-50°	895.7	15.7
50°-60°	1189.8	20.8
60°-70°	1310.5	23.0
70°-80°	822.2	14.4
80°-90°	209.4	3.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5710.2	100.0
0°-180°	5710.2	100.0

Coefficient of Utilization



REPORT NUMBER: P153171


CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	365.6	6.4			
FM	(30°-60°)	2075.2	36.3			
FH	(60°-80°)	1847.3	32.4			G2/5000
FVH	(80°-90°)	183.8	3.2			G2/225
BL	(0°-30°)	308.3	5.4	B1/500		
BM	(30°-60°)	618.9	10.8	B1/1000		
BH	(60°-80°)	285.4	5.0	B1/500		G1/500
BVH	(80°-90°)	25.6	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P153171

CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6
2.5°	708.0	709.4	709.4	708.7	708.7	710.1	709.4	708.7	706.6	709.4	709.4
5°	702.6	703.9	703.9	705.3	706.6	708.0	708.0	709.4	708.7	711.4	713.5
7.5°	709.4	710.8	713.5	716.9	719.0	723.7	723.7	727.2	728.5	730.6	729.9
10°	718.2	721.7	727.9	733.4	737.4	742.9	747.0	751.8	751.8	753.9	755.2
12.5°	734.0	737.4	744.2	751.1	757.3	764.1	770.3	775.0	779.8	781.2	783.9
15°	760.0	764.1	774.4	783.9	791.5	800.3	808.6	818.1	827.0	829.1	830.5
17.5°	799.0	807.3	814.7	831.8	842.8	854.4	867.4	881.0	883.8	898.1	901.6
20°	854.4	864.7	871.5	892.7	911.2	926.2	945.4	961.1	967.3	980.9	994.6
22.5°	950.2	948.1	958.3	979.6	993.3	1023.4	1039.8	1056.2	1064.5	1085.0	1095.9
25°	1078.8	1089.7	1112.3	1114.3	1127.4	1162.3	1183.4	1199.9	1200.5	1206.7	1218.3
27.5°	1205.3	1250.5	1286.0	1305.2	1340.1	1372.2	1370.9	1394.1	1357.9	1365.4	1376.4
30°	1358.5	1433.8	1500.8	1546.0	1581.6	1619.2	1637.6	1650.7	1634.9	1628.1	1615.1
32.5°	1502.2	1607.6	1710.9	1790.9	1857.2	1919.5	1960.5	1979.0	2000.9	2056.3	2076.2
35°	1600.7	1749.8	1878.4	1994.1	2104.9	2204.0	2275.9	2317.0	2301.2	2293.7	2289.5
37.5°	1659.6	1841.6	2002.3	2165.8	2293.0	2441.5	2553.0	2661.0	2685.7	2642.6	2621.3
40°	1696.5	1912.0	2118.5	2311.5	2476.4	2667.9	2806.0	2968.2	3091.3	3107.8	3057.1
42.5°	1714.3	1959.2	2200.0	2418.2	2641.2	2875.9	3051.0	3247.3	3431.3	3557.8	3526.4
45°	1717.0	1989.9	2259.5	2514.6	2780.1	3058.4	3284.2	3501.8	3748.0	3964.9	3971.0
47.5°	1717.0	2013.3	2300.5	2584.5	2904.6	3217.2	3463.4	3720.6	4022.4	4278.9	4357.5
50°	1718.3	2028.9	2338.9	2639.2	2999.7	3351.3	3629.6	3933.4	4250.8	4529.9	4681.8
52.5°	1724.6	2040.6	2368.9	2678.1	3061.2	3445.7	3759.0	4109.2	4425.3	4711.9	4908.2
55°	1738.2	2057.0	2390.8	2702.1	3102.3	3507.3	3852.6	4229.6	4538.1	4828.8	5103.2
57.5°	1776.6	2085.7	2417.5	2723.3	3124.9	3547.6	3918.3	4281.6	4581.2	4884.2	5206.4
60°	1853.2	2146.6	2463.3	2765.7	3162.5	3622.2	3949.8	4246.7	4549.7	4867.9	5229.7
62.5°	1975.5	2241.7	2526.9	2837.5	3269.8	3737.7	3925.9	4142.7	4425.9	4772.7	5146.9
63°	2018.0	2262.2	2541.3	2853.3	3299.3	3759.0	3915.6	4111.9	4400.6	4742.7	5117.5
65°	2136.4	2353.2	2609.7	2932.6	3420.3	3780.2	3835.5	3951.9	4225.5	4571.0	4943.7
67.5°	2357.3	2574.2	2756.8	3066.7	3522.3	3696.7	3587.3	3601.7	3887.6	4245.4	4580.5
70°	2496.9	2755.4	2850.6	3083.8	3503.8	3572.8	3265.8	3075.5	3304.8	3712.4	4005.9
72.5°	2460.6	2757.5	2747.3	2856.0	3134.4	3198.8	2880.6	2581.0	2717.1	3021.6	3211.7
75°	2107.7	2462.7	2387.4	2365.5	2463.3	2505.7	2267.0	2221.1	2392.8	2561.9	2564.6
77.5°	1517.3	1907.9	1819.6	1693.1	1686.2	1784.0	1816.2	2116.5	2370.3	2503.7	2444.9
80°	966.6	1390.1	1298.3	1077.4	1074.0	1201.2	1483.7	1892.1	2160.9	2235.5	2082.3
82.5°	504.9	909.8	944.7	808.6	925.6	1136.3	1411.9	1524.8	1626.7	1637.0	1456.4
85°	314.7	559.6	658.0	679.3	836.0	1007.7	1005.6	965.9	920.7	788.1	712.8
87.5°	35.5	70.5	106.7	101.2	136.2	190.9	238.0	139.6	97.8	35.5	49.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153171

CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6
2.5°	710.8	711.4	712.1	712.1	715.5	714.8	715.5	716.9	719.0	720.3	721.7
5°	716.3	716.3	719.0	721.0	725.1	727.9	729.2	733.4	738.1	736.8	740.8
7.5°	734.0	733.4	736.1	737.4	740.8	745.6	745.0	748.4	752.4	753.9	757.3
10°	757.9	755.9	755.9	754.5	755.2	753.9	753.9	753.9	756.6	755.9	758.7
12.5°	782.6	781.9	780.5	776.4	776.4	771.0	768.2	764.8	764.1	759.3	760.0
15°	833.2	833.2	830.5	822.3	815.4	810.7	803.8	799.0	792.1	783.2	778.4
17.5°	907.0	897.5	894.1	892.7	881.8	877.6	862.6	846.8	839.4	827.0	820.2
20°	997.4	995.3	981.7	974.8	961.1	942.0	922.8	902.3	889.9	874.9	866.7
22.5°	1099.3	1084.2	1077.4	1067.2	1045.9	1024.0	995.3	968.0	948.8	938.5	932.4
25°	1218.3	1203.3	1196.5	1182.8	1156.8	1133.5	1097.9	1065.8	1048.7	1031.6	1022.0
27.5°	1376.4	1362.0	1353.8	1318.2	1309.3	1271.0	1227.3	1183.4	1160.8	1135.5	1119.2
30°	1612.3	1613.1	1570.7	1527.6	1483.1	1416.7	1370.9	1321.7	1284.7	1248.4	1212.1
32.5°	2011.2	1909.2	1830.6	1738.2	1641.8	1571.3	1514.5	1455.8	1404.4	1351.7	1291.5
35°	2254.7	2205.5	2103.5	1934.5	1837.4	1751.9	1689.0	1617.8	1554.9	1461.9	1370.2
37.5°	2529.7	2415.4	2291.6	2197.9	2087.8	1988.6	1883.2	1802.5	1693.8	1568.6	1438.5
40°	2931.2	2767.8	2618.7	2492.7	2350.5	2246.5	2128.8	2011.8	1867.5	1686.2	1507.7
42.5°	3350.6	3181.7	2984.6	2821.1	2653.5	2531.7	2386.0	2221.9	2009.8	1785.4	1567.3
45°	3790.5	3564.7	3328.7	3128.9	2954.5	2803.3	2622.7	2405.2	2146.6	1874.4	1622.6
47.5°	4224.1	3964.9	3683.7	3468.9	3241.8	3057.1	2835.4	2560.5	2253.4	1958.4	1678.0
50°	4606.5	4356.9	4018.2	3745.3	3515.4	3287.7	3011.3	2680.2	2337.5	2031.0	1728.0
52.5°	4936.3	4721.5	4365.1	4020.3	3755.5	3499.7	3152.8	2776.7	2422.3	2098.0	1769.0
55°	5178.4	5035.4	4707.0	4279.6	3966.9	3661.9	3272.6	2869.6	2502.3	2151.4	1795.6
57.5°	5361.0	5281.7	4999.9	4523.7	4161.2	3819.2	3396.4	2981.1	2581.7	2197.2	1808.0
60°	5460.9	5482.8	5221.6	4737.2	4332.8	3950.5	3520.2	3076.3	2640.5	2223.9	1801.1
62.5°	5451.4	5585.4	5387.8	4868.5	4432.7	4028.5	3603.7	3120.7	2632.3	2181.5	1738.9
63°	5432.8	5588.8	5406.2	4877.4	4439.0	4031.2	3605.7	3114.6	2615.2	2160.9	1714.3
65°	5273.5	5510.2	5390.5	4837.1	4384.2	3979.9	3562.6	3025.6	2494.8	2050.9	1587.8
67.5°	4846.6	5142.8	5108.6	4551.8	4125.0	3767.9	3342.4	2739.1	2197.2	1780.0	1345.6
70°	4141.3	4419.8	4425.9	3958.8	3602.3	3252.0	2898.4	2228.7	1741.7	1379.8	1003.5
72.5°	3174.1	3353.3	3415.5	3107.8	2869.0	2622.7	2305.3	1617.8	1241.6	938.5	653.3
75°	2457.8	2408.6	2407.9	2277.9	2180.8	2060.4	1711.5	1091.8	815.4	610.2	399.5
77.5°	2209.5	1990.7	1778.5	1622.6	1544.7	1504.2	1122.6	658.0	480.9	350.9	229.8
80°	1822.4	1499.5	1211.5	1043.2	976.2	1022.7	625.9	355.8	263.3	199.8	149.1
82.5°	1256.7	1043.2	792.8	656.7	563.6	589.6	320.1	182.0	121.8	111.5	92.3
85°	654.6	573.9	484.4	416.0	367.4	322.9	166.2	86.8	50.6	44.5	40.3
87.5°	0.0	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153171

CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6
2.5°	723.7	723.1	724.5	725.1	727.2	728.5	729.2	727.9	729.9	731.9	730.6
5°	742.9	747.7	748.4	750.5	750.5	754.5	754.5	754.5	753.9	754.5	753.2
7.5°	759.3	765.5	766.1	768.9	769.5	774.4	772.3	773.7	773.7	770.3	768.9
10°	761.3	767.6	771.0	774.4	779.2	785.3	785.3	788.7	788.7	786.0	785.3
12.5°	762.1	766.8	770.3	775.0	781.9	790.8	795.5	800.3	802.4	801.8	799.7
15°	776.4	776.4	777.1	781.2	786.0	796.9	803.8	809.2	812.6	811.3	807.9
17.5°	814.1	808.6	804.5	797.6	799.0	804.5	808.6	813.4	814.1	812.6	807.3
20°	857.8	851.0	840.7	829.7	824.4	820.2	817.5	817.5	815.4	808.6	799.7
22.5°	920.1	911.2	896.8	880.4	869.4	856.5	840.7	825.7	809.2	792.8	773.7
25°	1006.2	994.0	978.9	953.6	930.4	903.0	870.8	837.3	798.3	764.1	736.1
27.5°	1093.2	1065.8	1026.8	991.9	948.8	907.8	862.0	820.9	771.0	729.9	699.2
30°	1165.0	1113.0	1056.9	1001.5	944.7	889.3	834.6	785.3	730.6	688.8	658.8
32.5°	1220.4	1148.6	1070.6	998.0	928.3	860.5	797.6	742.9	687.5	644.4	612.2
35°	1271.7	1171.8	1072.6	983.0	896.8	826.3	755.2	695.8	636.9	591.7	556.8
37.5°	1309.9	1182.8	1060.3	954.9	855.8	777.1	704.6	643.7	583.5	534.3	494.6
40°	1334.6	1176.0	1033.7	914.6	807.3	724.5	650.6	587.6	529.4	475.4	427.6
42.5°	1354.5	1167.0	1006.9	877.6	768.9	678.5	602.7	534.9	476.1	417.3	364.6
45°	1383.8	1173.9	995.3	851.7	734.7	639.6	556.2	485.7	424.1	366.6	316.1
47.5°	1412.6	1177.3	978.2	819.5	691.6	599.3	514.4	446.0	383.1	330.4	283.9
50°	1438.5	1175.2	951.5	778.4	649.8	558.9	476.8	408.4	346.1	297.6	253.8
52.5°	1450.9	1163.6	918.8	738.8	616.4	523.3	439.9	373.5	311.9	266.1	225.7
55°	1449.5	1133.5	875.6	701.1	579.4	485.7	403.6	337.9	282.5	240.1	205.2
57.5°	1429.0	1086.9	829.7	659.5	530.9	439.2	361.1	297.6	251.1	215.4	186.1
60°	1385.9	1027.5	769.5	598.5	469.9	381.8	308.5	253.8	216.2	188.8	169.6
62.5°	1305.2	942.0	694.3	513.8	387.9	307.2	243.5	208.0	179.9	163.5	154.6
63°	1281.2	918.8	662.2	493.3	368.7	290.1	229.8	193.0	172.4	158.0	149.8
65°	1162.3	804.5	554.1	398.1	286.6	223.7	184.7	156.7	144.4	138.1	137.5
67.5°	941.2	632.7	392.0	273.0	194.9	161.5	141.6	129.9	124.5	123.1	124.5
70°	660.8	399.5	249.0	181.2	144.4	129.9	121.0	116.3	112.8	113.6	114.9
72.5°	421.3	239.4	171.0	137.5	121.8	114.2	110.2	108.8	108.1	107.4	107.4
75°	240.1	159.4	131.3	119.1	110.8	104.7	101.2	99.9	100.5	101.2	99.9
77.5°	158.7	131.3	117.0	108.8	101.2	94.4	92.3	91.7	93.1	94.4	94.4
80°	125.2	117.0	108.8	100.5	88.3	83.4	84.9	85.5	84.9	85.5	83.4
82.5°	88.3	86.8	88.9	85.5	73.2	69.1	67.8	68.4	67.0	67.0	65.7
85°	41.0	41.0	43.1	43.1	41.8	42.4	45.8	49.9	52.0	49.9	47.2
87.5°	0.0	0.0	0.0	0.0	0.0	6.1	12.3	17.8	19.2	23.9	23.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153171

CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6
2.5°	728.5	729.9	729.2	728.5	729.9	728.5	729.2	728.5	728.5	727.9	727.9
5°	751.8	753.9	749.7	749.0	747.7	744.2	744.2	742.9	742.9	740.2	738.1
7.5°	766.8	767.6	764.1	763.4	760.0	756.6	753.9	751.1	750.5	748.4	744.2
10°	781.2	779.8	777.1	773.7	770.3	765.5	762.1	758.7	757.9	754.5	749.7
12.5°	793.5	792.8	787.4	783.9	778.4	773.7	769.5	765.5	763.4	759.3	752.4
15°	801.8	797.6	790.8	784.7	778.4	773.0	768.2	763.4	761.3	756.6	749.7
17.5°	798.3	790.8	781.9	774.4	766.1	759.3	755.2	750.5	747.0	744.2	734.7
20°	786.0	775.0	761.3	752.4	741.6	732.6	729.9	725.1	722.4	712.1	699.8
22.5°	753.9	738.1	721.0	708.0	695.8	686.8	680.0	675.1	668.3	662.2	643.0
25°	713.5	695.8	677.9	662.2	645.8	632.1	619.8	608.2	604.8	591.7	573.3
27.5°	674.5	654.6	636.9	618.4	597.2	580.1	558.9	542.5	531.5	517.8	500.7
30°	632.7	613.0	589.0	564.4	539.7	521.2	497.3	477.5	463.8	449.4	433.7
32.5°	580.1	556.2	527.5	500.1	477.5	455.5	431.6	412.5	398.9	385.8	370.8
35°	519.9	488.4	457.6	427.6	403.6	385.2	363.9	349.5	340.0	328.4	312.6
37.5°	450.8	415.2	382.4	359.2	337.9	320.1	305.1	296.2	285.9	279.8	270.3
40°	381.0	346.1	314.0	292.7	275.0	264.8	256.5	254.5	247.7	239.4	233.3
42.5°	319.5	285.9	254.5	237.4	225.7	223.0	218.9	218.9	215.4	209.3	205.2
45°	277.7	242.8	215.4	203.2	197.0	196.4	194.3	194.3	193.6	190.9	186.1
47.5°	247.7	216.2	194.9	187.5	186.1	184.7	182.7	182.0	181.2	179.3	176.5
50°	220.3	193.6	179.9	176.5	177.2	175.1	173.1	171.0	170.4	168.3	165.6
52.5°	194.9	175.9	166.9	164.9	164.9	164.9	163.5	163.5	162.2	161.5	158.7
55°	180.6	166.2	161.5	160.7	160.1	159.4	158.0	158.0	156.7	156.0	152.5
57.5°	168.3	159.4	156.7	155.2	154.6	153.3	152.5	152.5	152.5	152.5	148.4
60°	158.7	154.6	153.9	152.5	151.8	149.1	147.8	147.0	147.8	148.4	144.4
62.5°	148.4	147.8	147.0	145.7	145.0	142.3	140.2	138.9	140.2	141.6	140.9
63°	145.7	145.0	145.0	144.4	143.6	140.2	138.1	136.8	138.1	139.6	139.6
65°	136.2	136.8	136.8	136.2	135.4	133.4	130.7	129.3	129.9	132.0	132.7
67.5°	125.9	126.5	125.9	126.5	125.9	124.5	122.5	121.0	120.4	121.0	121.8
70°	116.3	117.6	117.0	116.3	115.6	115.6	114.2	112.2	111.5	110.8	110.8
72.5°	108.1	108.1	106.7	106.7	106.0	106.0	104.7	102.6	102.0	102.0	100.5
75°	99.2	99.2	97.1	97.1	95.8	96.5	95.1	93.1	92.3	92.3	91.7
77.5°	93.7	91.7	88.3	87.6	86.8	86.8	86.2	84.1	83.4	83.4	82.8
80°	82.8	78.7	75.2	74.6	75.2	76.6	76.6	75.2	75.2	75.2	75.2
82.5°	64.4	62.9	60.9	59.5	59.5	61.6	64.4	65.7	67.0	68.4	68.4
85°	47.2	47.9	47.2	45.2	44.5	46.5	49.2	52.0	52.6	55.4	54.7
87.5°	25.3	26.0	23.9	23.2	25.3	26.6	29.4	30.1	31.5	32.1	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153171

CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6
2.5°	727.2	726.5	727.2	725.8	725.8	724.5	723.1	722.4	721.0	720.3	719.0
5°	739.5	737.4	735.3	734.7	731.9	729.2	727.2	723.7	721.0	716.3	714.8
7.5°	747.7	742.9	740.2	739.5	735.3	733.4	728.5	724.5	720.3	714.2	712.1
10°	751.1	746.3	741.6	739.5	734.7	731.3	726.5	720.3	716.9	710.8	709.4
12.5°	755.2	746.3	738.8	733.4	726.5	719.0	714.2	710.8	706.0	702.6	701.1
15°	747.7	736.1	724.5	714.2	703.2	695.0	690.3	684.8	679.3	677.2	677.2
17.5°	727.2	712.1	692.2	679.3	667.7	658.8	652.6	647.2	646.4	643.7	645.1
20°	684.8	664.9	645.8	636.2	629.3	623.8	617.7	615.0	613.0	608.8	607.5
22.5°	625.9	609.5	595.9	589.0	583.5	576.7	571.2	563.0	560.9	556.8	554.8
25°	560.9	548.0	536.3	531.5	528.1	518.5	515.1	504.1	496.7	491.8	494.6
27.5°	496.0	486.4	475.4	469.2	467.3	458.3	454.9	442.6	436.5	436.5	429.6
30°	428.9	420.0	413.2	406.3	405.0	394.0	385.2	380.3	373.5	370.8	366.0
32.5°	366.0	357.1	351.6	348.2	342.7	333.8	325.0	316.7	305.8	301.7	299.6
35°	307.9	301.0	294.2	291.4	283.9	274.3	263.3	256.5	243.5	238.8	236.7
37.5°	263.3	255.1	250.4	242.8	235.3	225.1	216.9	210.7	205.9	203.8	203.8
40°	227.8	221.7	216.2	210.1	203.8	198.3	194.3	193.0	192.2	192.2	193.6
42.5°	201.1	195.6	193.0	189.5	187.5	187.5	186.7	187.5	188.1	188.8	190.9
45°	183.3	179.9	178.5	177.8	179.3	180.6	181.2	182.7	185.4	186.7	187.5
47.5°	173.8	171.0	170.4	171.0	173.1	175.9	178.5	180.6	182.7	183.3	184.0
50°	164.1	160.7	159.4	160.7	163.5	167.6	169.6	173.1	174.4	175.9	174.4
52.5°	156.0	153.3	152.5	152.5	155.2	158.0	160.7	163.5	164.1	164.1	163.5
55°	149.1	147.0	145.0	146.4	148.4	151.2	155.2	157.3	158.7	159.4	159.4
57.5°	143.6	141.6	139.6	140.9	143.0	145.7	149.8	151.8	153.3	155.2	156.0
60°	139.6	136.8	134.7	136.8	138.9	143.0	146.4	148.4	151.8	152.5	152.5
62.5°	135.4	132.7	129.3	131.3	131.3	133.4	136.8	139.6	143.0	144.4	144.4
63°	134.7	132.0	128.6	129.9	129.9	131.3	134.1	136.8	140.9	142.3	141.6
65°	129.3	128.6	125.2	125.2	123.8	125.2	127.3	129.9	132.0	134.1	134.1
67.5°	120.4	119.7	119.1	119.1	119.1	120.4	121.8	123.8	125.9	127.3	126.5
70°	110.2	110.2	110.2	110.8	110.8	112.2	112.8	112.2	114.2	115.6	114.9
72.5°	101.2	100.5	99.9	101.2	100.5	100.5	102.0	101.2	103.3	103.3	103.9
75°	91.7	91.0	91.0	91.7	90.3	88.9	89.6	89.6	90.3	90.3	91.7
77.5°	83.4	83.4	83.4	82.8	81.5	80.7	80.0	80.0	80.0	80.0	80.7
80°	76.0	76.0	76.0	75.2	73.9	72.5	71.2	70.5	69.7	66.3	66.3
82.5°	68.4	68.4	68.4	68.4	67.8	66.3	64.4	58.9	56.1	53.4	54.1
85°	54.1	55.4	56.8	58.9	58.1	58.1	54.1	47.2	43.1	40.3	41.0
87.5°	34.9	30.8	30.8	30.1	28.7	27.4	27.4	23.2	19.2	17.1	17.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153171
CATALOG NUMBER: AVS-E02-LED-E-U-SLL-7050

REPORT N
CATALOG

CANDELA DISTRIBUTION (continued):

CANDELA

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°	
0°	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	0°
2.5°	719.0	717.6	716.3	716.3	714.2	714.2	712.8	715.5	712.8	710.8	710.8	2.5°
5°	713.5	712.1	708.0	707.4	704.6	704.6	704.6	703.2	703.2	701.9	701.1	5°
7.5°	710.1	706.6	703.2	701.1	701.1	699.8	702.6	701.1	701.9	701.9	702.6	7.5°
10°	707.4	704.6	703.2	702.6	702.6	704.6	706.6	707.4	706.6	707.4	707.4	10°
12.5°	700.5	701.9	702.6	705.3	708.7	712.8	717.6	718.2	719.7	719.7	721.0	12.5°
15°	678.5	682.0	686.1	693.0	701.9	710.8	719.7	727.2	734.0	737.4	740.2	15°
17.5°	647.8	651.2	658.8	666.3	677.9	690.9	706.0	719.0	733.4	746.3	759.3	17.5°
20°	606.1	611.6	613.6	627.3	640.9	658.8	676.6	697.1	721.7	746.3	771.6	20°
22.5°	552.0	558.2	567.8	578.8	593.1	615.0	636.2	668.3	701.1	736.1	775.8	22.5°
25°	491.8	498.7	506.9	518.5	532.8	556.2	586.9	621.1	661.5	707.4	756.6	25°
27.5°	429.6	436.5	443.3	451.5	467.9	492.5	528.8	564.4	608.8	658.8	716.3	27.5°
30°	367.4	368.0	372.1	382.4	399.5	431.6	458.3	502.8	549.3	602.0	668.3	30°
32.5°	299.0	298.2	303.0	311.9	328.4	359.2	392.0	435.0	480.9	547.3	615.6	32.5°
35°	238.0	238.0	246.9	255.9	274.3	296.2	325.0	363.2	417.3	478.9	547.3	35°
37.5°	205.9	210.7	216.2	225.1	239.4	256.5	281.9	315.3	357.7	416.6	479.5	37.5°
40°	195.6	198.3	203.2	211.4	223.7	239.4	257.9	283.2	316.1	363.2	420.7	40°
42.5°	191.5	192.2	194.9	201.1	212.0	227.8	246.9	269.5	294.2	327.7	377.6	42.5°
45°	187.5	186.7	188.1	193.0	201.8	219.6	241.5	266.1	290.8	318.8	359.8	45°
47.5°	184.0	184.0	184.0	186.1	194.3	212.0	237.4	266.1	295.5	326.9	367.4	47.5°
50°	174.4	173.8	173.8	175.1	181.2	200.4	230.6	265.4	303.7	344.8	390.6	50°
52.5°	163.5	163.5	164.1	164.9	170.4	189.5	223.0	265.4	313.3	368.0	425.5	52.5°
55°	160.1	160.7	161.5	160.7	164.9	181.2	214.8	261.3	317.4	386.5	463.1	55°
57.5°	157.3	158.7	158.7	158.0	160.7	174.4	206.6	253.1	314.0	393.4	489.8	57.5°
60°	153.3	153.3	153.3	151.2	152.5	164.9	194.3	240.1	303.0	387.2	493.9	60°
62.5°	144.4	144.4	143.0	142.3	141.6	151.2	177.8	220.9	283.2	370.8	483.6	62.5°
63°	142.3	141.6	141.6	139.6	139.6	148.4	174.4	218.2	277.7	366.6	479.5	63°
65°	134.7	134.7	134.7	133.4	132.7	139.6	160.7	199.1	256.5	347.5	459.0	65°
67.5°	126.5	127.3	125.9	125.2	124.5	128.6	145.0	175.1	223.7	307.2	420.7	67.5°
70°	114.9	115.6	115.6	114.9	114.2	117.0	127.3	150.5	185.4	255.9	358.4	70°
72.5°	104.7	106.0	106.0	107.4	107.4	109.4	113.6	125.2	148.4	199.8	281.9	72.5°
75°	93.7	94.4	95.8	97.1	95.8	95.1	95.8	104.7	116.3	147.8	201.1	75°
77.5°	84.1	86.2	86.2	85.5	83.4	82.1	82.1	86.2	95.8	112.2	143.6	77.5°
80°	69.7	73.2	73.9	71.8	69.7	69.7	71.2	73.9	80.0	92.3	108.8	80°
82.5°	56.1	59.5	60.2	60.9	60.2	62.3	62.3	62.9	66.3	76.0	88.9	82.5°
85°	43.1	45.8	47.9	48.6	49.2	49.9	49.2	45.8	47.9	54.1	60.2	85°
87.5°	19.2	19.8	18.4	19.2	18.4	19.2	19.8	16.4	15.8	21.2	21.9	87.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	90°



NUMBER: P153171

NUMBER: AVS-E02-LED-E-U-SLL-7050

DISTRIBUTION (continued):

330°	335°	340°	345°	350°	355°	360°
717.6	717.6	717.6	717.6	717.6	717.6	717.6
710.1	710.1	710.8	709.4	709.4	710.1	708.0
699.2	701.9	701.9	701.9	700.5	701.9	702.6
701.9	703.9	705.3	705.3	704.6	707.4	709.4
705.3	708.7	710.1	710.1	710.1	713.5	718.2
718.2	721.0	723.1	723.1	724.5	728.5	734.0
742.2	745.6	745.6	745.0	749.0	753.9	760.0
768.9	778.4	783.2	782.6	786.0	792.1	799.0
794.2	820.9	832.5	840.7	844.1	852.3	854.4
815.4	859.9	892.0	919.4	932.4	940.6	950.2
807.9	868.1	925.6	981.7	1021.3	1061.7	1078.8
777.1	852.3	927.6	1009.6	1081.6	1153.4	1205.3
739.5	829.7	931.0	1047.4	1160.8	1271.0	1358.5
696.4	808.6	938.5	1082.2	1231.3	1375.6	1502.2
642.4	768.2	920.1	1085.6	1261.5	1436.6	1600.7
573.9	713.5	877.0	1061.0	1262.8	1463.2	1659.6
505.5	644.4	822.3	1025.4	1245.0	1469.4	1696.5
457.6	582.8	766.8	980.3	1216.3	1459.8	1714.3
424.8	538.3	717.6	939.3	1185.5	1442.7	1717.0
422.1	519.2	685.4	909.1	1160.8	1427.7	1717.0
445.3	529.4	674.5	894.1	1150.6	1422.9	1718.3
489.1	570.5	694.3	905.7	1158.9	1429.0	1724.6
541.8	632.7	747.7	946.1	1193.7	1449.5	1738.2
589.6	704.6	838.7	1024.0	1257.3	1501.6	1776.6
617.7	766.1	935.1	1133.5	1366.1	1604.9	1853.2
621.1	800.3	1020.6	1252.5	1498.1	1723.2	1975.5
618.4	803.1	1031.6	1275.1	1526.1	1752.5	2018.0
603.3	803.8	1062.4	1354.5	1623.3	1876.4	2136.4
565.1	781.9	1073.3	1416.7	1745.7	2039.2	2357.3
498.7	719.7	1041.1	1418.0	1793.0	2130.2	2496.9
400.8	601.3	902.3	1290.2	1668.5	2040.6	2460.6
293.5	441.9	682.0	999.4	1361.3	1698.5	2107.7
194.9	285.9	459.7	712.1	976.2	1222.4	1517.3
134.1	177.2	268.8	428.2	597.2	716.9	966.6
98.5	117.0	149.1	218.9	287.4	353.7	504.9
61.6	67.0	74.6	108.1	154.6	208.6	314.7
16.4	17.1	15.8	21.2	33.5	32.1	35.5
0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)