

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152044

Luminaire Tested: **AVS-F03-LED-E-U-SL4-HSS-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152044
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F03-LED-E-U-SL4-HSS-7030
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (21) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4602.7 lumens
Efficiency: N/A
Efficacy: 58.8 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G2

Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152044

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 10.3 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P152044

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P152044

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	137.1	0.0	137.1
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	4465.6	0.0	4465.6
	% Fixture	97.0	0.0	97.0
Total	Lumens	4602.7	0.0	4602.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	0.8
10°-20°	123.2	2.7
20°-30°	235.8	5.1
30°-40°	392.1	8.5
40°-50°	530.5	11.5
50°-60°	829.7	18.0
60°-70°	1705.8	37.1
70°-80°	686.4	14.9
80°-90°	63.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4602.7	100.0
0°-180°	4602.7	100.0

Coefficient of Utilization



REPORT NUMBER: P152044


CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	342.5	7.4			
FM	(30°-60°)	1689.7	36.7			
FH	(60°-80°)	2372.2	51.5			G2/5000
FVH	(80°-90°)	61.1	1.3			G1/100
BL	(0°-30°)	52.1	1.1	B0/110		
BM	(30°-60°)	62.6	1.4	B0/220		
BH	(60°-80°)	20.0	0.4	B0/110		G0/110
BVH	(80°-90°)	2.4	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type IV Short





REPORT NUMBER: P152044

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6
2.5°	463.7	458.4	452.4	452.4	444.9	444.9	440.3	428.3	426.7	420.0	413.2
5°	591.9	587.4	579.8	573.1	567.0	556.5	548.9	534.6	518.8	503.6	490.1
7.5°	717.1	714.8	701.2	699.0	689.1	671.8	656.7	635.6	608.5	587.4	562.5
10°	833.2	827.9	824.9	812.0	797.7	778.9	755.5	729.8	698.2	665.0	629.5
12.5°	925.2	922.2	908.6	903.3	888.2	869.3	840.0	806.7	775.1	732.1	690.7
15°	993.8	988.5	979.5	971.2	953.1	936.5	909.3	873.2	834.7	787.9	738.1
17.5°	1051.1	1041.2	1039.0	1026.2	1007.4	987.8	957.6	924.4	879.2	832.4	778.1
20°	1128.0	1114.4	1109.8	1091.0	1069.1	1042.0	1007.4	965.9	918.3	867.0	811.3
22.5°	1218.4	1208.6	1198.9	1182.3	1154.4	1116.0	1065.4	1020.1	959.8	903.3	843.0
25°	1346.6	1338.3	1322.5	1299.9	1265.2	1219.2	1158.1	1091.8	1020.9	948.5	877.6
27.5°	1471.1	1463.5	1452.2	1434.8	1395.6	1345.1	1269.7	1185.3	1095.5	1008.1	929.6
30°	1587.9	1581.1	1569.8	1552.4	1517.8	1468.0	1382.8	1292.3	1180.7	1079.0	984.8
32.5°	1713.8	1711.6	1698.8	1673.9	1643.7	1576.6	1483.8	1386.6	1273.5	1155.9	1045.8
35°	1856.4	1839.0	1826.9	1802.1	1750.8	1679.2	1570.6	1464.2	1345.1	1224.5	1101.6
37.5°	1977.0	1960.4	1945.3	1913.7	1851.1	1759.8	1636.9	1520.0	1397.1	1274.3	1149.1
40°	2065.2	2056.9	2038.8	1997.3	1927.3	1818.7	1685.9	1558.5	1434.8	1311.2	1187.6
42.5°	2130.8	2117.9	2097.6	2054.6	1971.7	1848.1	1705.5	1574.3	1452.2	1333.8	1212.4
45°	2154.9	2144.4	2125.5	2078.8	1989.0	1856.4	1704.8	1569.8	1453.0	1340.6	1229.0
47.5°	2140.6	2130.1	2113.5	2069.7	1981.5	1846.5	1691.2	1557.0	1445.4	1342.9	1244.0
50°	2093.1	2087.0	2074.2	2037.3	1958.1	1827.7	1679.2	1550.3	1443.9	1354.2	1265.2
52.5°	2088.6	2084.8	2068.9	2032.0	1951.3	1821.7	1677.6	1554.0	1456.7	1368.5	1280.3
55°	2552.2	2498.8	2378.9	2277.1	2109.6	1910.6	1753.8	1615.0	1511.0	1425.1	1363.2
57.5°	3627.5	3547.6	3389.9	3196.2	2811.6	2433.9	2131.5	1912.8	1805.1	1765.8	1789.2
60°	4131.1	4116.8	4091.9	3999.9	3803.1	3478.1	3116.3	2725.0	2568.1	2554.5	2602.1
62.5°	4370.2	4361.1	4368.6	4357.3	4296.3	4201.2	4097.2	3928.3	3773.0	3672.7	3460.1
65°	4480.2	4486.2	4529.2	4563.2	4570.7	4595.5	4671.7	4882.1	5036.0	4777.3	4186.9
67.5°	4200.5	4236.0	4334.7	4458.3	4603.1	4743.4	4969.5	5413.0	5728.8	5425.0	4586.5
69°	3477.4	3494.7	3736.1	3969.0	4322.7	4569.9	4897.9	5479.3	5834.4	5491.3	4554.9
70°	2737.7	2753.6	3012.2	3328.9	3926.8	4245.0	4674.0	5366.9	5735.6	5403.1	4392.0
72.5°	1235.0	1212.4	1303.6	1473.3	2123.2	2628.4	3378.7	4348.3	4732.0	4328.7	3285.9
75°	862.6	852.7	862.6	863.3	964.4	1244.0	1569.8	2357.0	2914.9	2515.3	1569.8
77.5°	668.1	661.2	654.5	646.9	659.0	738.1	769.8	836.2	1085.7	1026.9	598.7
80°	528.6	522.5	539.1	533.8	533.8	542.9	536.9	511.9	465.2	431.3	386.0
82.5°	245.8	247.4	247.4	268.4	323.4	377.7	395.1	370.3	328.7	279.7	225.5
85°	23.4	26.4	44.5	68.6	136.5	153.8	154.6	128.2	128.2	101.0	81.5
87.5°	0.0	0.7	0.7	0.7	6.7	18.9	15.9	4.6	2.3	2.3	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152044

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6
2.5°	401.1	398.9	389.8	380.7	372.4	363.4	355.1	346.8	337.8	331.0	322.7
5°	469.0	452.4	433.6	415.4	397.3	378.5	358.9	341.6	323.4	306.8	291.1
7.5°	537.6	505.2	479.6	447.2	417.7	388.3	361.1	333.3	307.7	283.5	260.9
10°	595.6	556.5	516.5	475.0	432.7	393.6	355.9	322.7	288.8	259.4	231.5
12.5°	643.1	593.4	544.4	492.3	444.9	395.1	348.4	308.4	268.4	235.2	206.6
15°	686.1	628.8	570.1	509.7	449.4	392.8	340.8	291.1	250.4	212.6	180.2
17.5°	720.8	655.2	588.9	521.0	456.2	389.8	331.0	279.0	231.5	192.2	160.6
20°	751.0	682.4	610.8	534.6	460.7	389.0	322.7	263.9	214.9	173.4	142.5
22.5°	778.9	710.3	633.4	551.9	467.5	388.3	315.1	252.5	200.5	159.1	128.2
25°	810.6	738.1	657.5	570.1	479.6	391.3	310.7	243.5	187.8	145.5	116.9
27.5°	846.0	769.8	686.1	592.6	495.3	397.3	309.1	233.8	176.5	132.7	107.8
30°	895.8	807.6	714.8	615.2	509.7	404.1	307.7	227.7	165.1	122.9	98.8
32.5°	939.5	844.5	746.4	638.7	525.5	410.9	306.8	219.4	154.6	113.1	92.0
35°	985.5	878.4	773.6	661.2	539.1	418.4	306.1	213.4	144.8	103.3	85.2
37.5°	1025.4	907.0	794.7	680.8	554.2	425.3	306.8	208.1	135.8	95.0	79.2
40°	1059.4	936.5	818.1	699.0	570.1	435.9	307.7	202.8	126.6	87.5	73.9
42.5°	1089.5	964.4	843.0	719.3	588.1	447.9	312.1	198.3	119.2	80.7	68.6
45°	1112.8	989.9	870.2	748.0	617.5	467.5	320.4	195.2	111.6	74.6	64.0
47.5°	1137.0	1027.7	916.1	793.2	660.5	498.3	334.8	194.5	105.6	70.2	60.3
50°	1170.2	1065.4	956.8	839.2	699.7	530.1	352.1	195.2	98.0	65.6	56.6
52.5°	1194.3	1103.8	1009.6	919.1	793.2	626.5	419.2	208.8	94.3	61.9	52.0
55°	1336.8	1321.0	1323.2	1338.3	1241.0	1066.1	701.2	301.6	110.9	70.2	51.3
57.5°	1885.0	1940.8	1973.2	1972.4	1811.8	1502.7	941.8	387.6	123.6	81.5	61.0
60°	2605.8	2563.6	2504.0	2357.0	2143.6	1715.3	1053.4	417.0	107.0	64.9	55.8
62.5°	3242.9	2995.6	2776.2	2537.9	2258.2	1789.2	1076.0	414.7	93.5	49.0	39.2
65°	3640.3	3195.4	2841.0	2542.5	2213.0	1727.4	1017.9	380.7	79.2	40.0	32.4
67.5°	3735.2	3087.6	2586.2	2205.4	1848.8	1344.4	747.3	286.5	61.9	33.2	28.6
69°	3528.0	2744.6	2142.8	1710.8	1345.1	892.0	462.2	180.9	47.5	30.2	26.4
70°	3245.2	2387.2	1745.5	1373.1	996.1	626.5	323.4	127.5	38.4	27.9	24.1
72.5°	2087.8	1253.9	858.0	597.2	410.9	249.5	126.6	57.3	29.4	23.4	19.6
75°	809.7	463.7	336.3	255.6	199.8	138.8	76.9	37.0	24.9	19.6	15.1
77.5°	398.9	305.4	249.5	171.2	99.5	61.9	41.5	28.6	20.3	14.3	9.8
80°	315.1	209.6	125.2	77.6	58.9	44.5	31.7	23.4	15.1	9.0	6.7
82.5°	161.3	88.2	64.9	52.7	43.7	34.7	25.6	16.6	9.8	6.0	5.3
85°	50.5	37.0	33.2	32.4	30.2	24.9	18.1	10.6	6.0	3.7	3.7
87.5°	3.7	5.3	6.7	5.3	6.0	5.3	6.7	4.6	3.0	3.0	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152044

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6
2.5°	316.7	307.7	299.4	294.1	284.2	280.5	276.7	275.2	268.4	269.9	263.9
5°	276.7	260.9	248.8	236.8	225.5	217.1	210.4	202.1	195.2	192.2	186.2
7.5°	240.5	220.2	204.4	191.5	177.9	167.4	158.3	152.3	146.3	140.2	137.2
10°	208.8	186.9	168.9	156.1	143.2	134.2	127.5	122.9	119.2	116.9	116.2
12.5°	179.5	158.3	141.8	130.5	120.6	116.2	113.1	110.9	110.1	109.3	109.3
15°	156.8	135.8	122.9	114.6	110.1	107.8	107.0	105.6	104.0	103.3	103.3
17.5°	135.8	119.9	110.9	106.3	104.0	102.6	101.0	99.5	98.0	97.3	97.3
20°	121.3	108.6	104.0	101.0	98.8	97.3	95.0	93.5	92.7	92.0	91.2
22.5°	110.1	101.8	98.8	96.5	93.5	91.2	89.7	88.2	86.7	85.9	85.2
25°	101.8	96.5	94.3	91.2	88.2	85.9	83.7	81.5	79.9	79.2	77.6
27.5°	95.8	92.0	89.0	85.2	82.2	79.9	77.6	75.4	73.9	72.3	71.6
30°	90.5	86.7	82.9	79.9	76.2	73.9	70.9	68.6	67.9	66.3	64.9
32.5°	85.2	81.5	77.6	73.9	70.2	67.2	65.6	62.6	61.0	60.3	58.9
35°	79.2	75.4	70.9	67.9	64.0	61.0	58.9	56.6	55.0	53.6	52.7
37.5°	73.9	69.3	64.9	61.0	58.0	55.0	52.7	50.5	49.0	47.5	46.7
40°	67.9	63.3	58.9	55.0	52.0	49.7	47.5	45.3	43.7	43.0	43.0
42.5°	62.6	57.3	52.7	49.7	47.5	44.5	42.2	40.0	39.2	38.4	39.2
45°	57.3	52.0	48.3	45.3	43.0	40.0	37.7	36.2	35.4	36.2	37.0
47.5°	52.7	47.5	43.7	41.5	39.2	37.0	34.7	33.2	33.2	34.7	36.2
50°	48.3	43.0	40.0	38.4	36.2	33.9	30.9	30.2	30.9	32.4	33.9
52.5°	43.7	37.7	35.4	34.7	32.4	30.2	27.9	27.2	27.9	29.4	28.6
55°	39.2	33.2	32.4	31.7	29.4	26.4	24.1	24.1	24.1	23.4	21.9
57.5°	37.7	29.4	28.6	27.9	25.6	22.6	21.1	19.6	18.9	16.6	15.9
60°	39.2	26.4	26.4	24.9	22.6	19.6	17.3	15.1	13.6	12.0	12.0
62.5°	31.7	24.1	23.4	21.9	18.9	15.9	13.6	11.3	10.6	9.8	9.8
65°	25.6	21.9	20.3	18.1	15.9	12.8	10.6	9.0	8.3	8.3	9.0
67.5°	23.4	19.6	17.3	15.1	12.8	9.8	8.3	7.6	7.6	8.3	8.3
69°	21.9	18.1	15.9	13.6	11.3	9.0	7.6	7.6	7.6	7.6	8.3
70°	20.3	17.3	15.1	12.8	9.8	7.6	6.7	6.7	7.6	7.6	8.3
72.5°	15.9	13.6	12.8	10.6	7.6	6.7	6.0	6.7	6.7	7.6	7.6
75°	12.0	9.8	9.8	8.3	6.0	5.3	5.3	6.0	6.0	6.7	6.7
77.5°	8.3	6.7	6.7	6.0	5.3	4.6	4.6	5.3	6.0	6.0	6.7
80°	6.0	5.3	4.6	5.3	4.6	3.7	4.6	5.3	5.3	6.0	6.0
82.5°	4.6	4.6	4.6	4.6	3.7	3.7	4.6	4.6	5.3	6.0	6.0
85°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	4.6	4.6	5.3	5.3
87.5°	2.3	2.3	2.3	3.0	3.0	3.7	3.7	3.7	3.7	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152044

CATALOG NUMBER: AVS-F03-LED-E-U-SL4-HSS-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	347.6	347.6	347.6	347.6
2.5°	262.4	261.7	258.7	259.4
5°	183.9	179.5	182.5	181.8
7.5°	134.9	134.2	133.5	134.9
10°	115.3	115.3	114.6	115.3
12.5°	108.6	108.6	108.6	108.6
15°	103.3	103.3	102.6	102.6
17.5°	97.3	97.3	97.3	96.5
20°	91.2	90.5	90.5	90.5
22.5°	84.5	83.7	83.7	83.7
25°	77.6	76.9	76.9	76.9
27.5°	70.9	70.2	69.3	69.3
30°	64.0	63.3	62.6	62.6
32.5°	57.3	56.6	55.8	55.8
35°	51.3	51.3	50.5	49.7
37.5°	46.0	46.0	46.0	46.0
40°	42.2	43.0	43.0	43.0
42.5°	40.0	40.7	41.5	42.2
45°	38.4	40.0	40.7	40.7
47.5°	37.7	38.4	39.2	39.2
50°	34.7	33.9	33.9	33.9
52.5°	27.9	26.4	25.6	24.9
55°	20.3	19.6	18.1	18.1
57.5°	14.3	14.3	13.6	13.6
60°	11.3	11.3	10.6	11.3
62.5°	9.8	9.8	9.8	9.8
65°	9.0	9.0	9.0	9.0
67.5°	9.0	9.0	9.0	9.0
69°	8.3	8.3	8.3	8.3
70°	8.3	8.3	8.3	8.3
72.5°	7.6	7.6	7.6	7.6
75°	6.7	7.6	7.6	7.6
77.5°	6.7	6.7	6.7	6.7
80°	6.0	6.0	6.7	6.7
82.5°	6.0	6.0	6.0	6.0
85°	5.3	5.3	6.0	6.0
87.5°	4.6	4.6	5.3	5.3
90°	0.0	0.0	0.0	0.0

(END OF REPORT)