

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152611

Luminaire Tested: **AVS-E03-LED-E-U-SL4-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152611
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-SL4-7050
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (63) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9093.7 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152611

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 19.5 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152611

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P152611

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1887.7	0.0	1887.7
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	7205.9	0.0	7205.9
	% Fixture	79.2	0.0	79.2
Total	Lumens	9093.7	0.0	9093.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.3	2.0
10°-20°	496.2	5.5
20°-30°	734.6	8.1
30°-40°	928.4	10.2
40°-50°	1049.9	11.5
50°-60°	1494.1	16.4
60°-70°	2782.6	30.6
70°-80°	1275.3	14.0
80°-90°	151.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9093.7	100.0
0°-180°	9093.7	100.0

Coefficient of Utilization



REPORT NUMBER: P152611


CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	828.0	9.1			
FM	(30°-60°)	2664.1	29.3			
FH	(60°-80°)	3601.5	39.6			G2/5000
FVH	(80°-90°)	112.3	1.2			G2/225
BL	(0°-30°)	584.1	6.4	B2/1000		
BM	(30°-60°)	808.2	8.9	B1/1000		
BH	(60°-80°)	456.4	5.0	B1/500		G1/500
BVH	(80°-90°)	39.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P152611

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4
2.5°	1970.2	1975.2	1969.1	1968.1	1968.1	1967.0	1960.9	1959.9	1951.6	1952.6	1954.7
5°	1984.5	1986.5	1982.5	1981.5	1979.4	1975.2	1970.2	1963.9	1957.8	1951.6	1946.5
7.5°	1998.9	1996.8	1993.7	1993.7	1990.7	1984.5	1974.2	1966.0	1952.6	1945.5	1936.3
10°	2019.4	2016.3	2012.2	2010.2	2005.0	1995.8	1981.5	1970.2	1953.7	1939.4	1923.9
12.5°	2038.9	2037.8	2031.7	2028.6	2020.4	2011.2	1993.7	1976.3	1954.7	1932.1	1911.6
15°	2073.8	2069.6	2063.5	2057.3	2044.0	2031.7	2005.0	1984.5	1953.7	1923.9	1892.1
17.5°	2134.3	2127.2	2120.9	2107.7	2091.2	2069.6	2030.7	1995.8	1953.7	1910.6	1874.7
20°	2245.1	2229.7	2221.6	2204.0	2175.3	2136.4	2075.9	2019.4	1956.8	1901.3	1853.2
22.5°	2370.3	2360.0	2348.7	2337.5	2292.3	2235.9	2153.8	2069.6	1975.2	1897.3	1835.8
25°	2510.9	2497.5	2491.4	2471.9	2429.8	2365.2	2253.4	2136.4	2017.3	1913.7	1835.8
27.5°	2636.1	2631.9	2631.0	2608.4	2568.3	2492.4	2360.0	2219.5	2074.8	1947.6	1851.1
30°	2749.9	2745.9	2743.8	2731.5	2685.3	2595.0	2451.4	2293.4	2137.4	1994.7	1879.8
32.5°	2871.1	2857.7	2851.5	2828.0	2775.6	2669.9	2505.7	2341.6	2186.6	2040.9	1911.6
35°	2969.5	2958.2	2945.9	2912.1	2838.2	2713.1	2529.3	2358.0	2206.1	2066.5	1928.1
37.5°	3041.3	3030.1	3012.6	2969.5	2878.2	2727.4	2528.3	2352.8	2199.0	2062.5	1931.1
40°	3073.2	3061.9	3043.4	2989.0	2885.4	2719.2	2508.8	2329.2	2177.4	2040.9	1918.9
42.5°	3060.8	3052.6	3029.0	2976.7	2862.8	2682.3	2469.8	2285.2	2136.4	2006.0	1891.1
45°	3013.7	3007.6	2985.0	2929.5	2811.5	2622.7	2412.3	2229.7	2087.2	1962.9	1854.2
47.5°	2942.9	2940.8	2918.2	2863.8	2746.8	2563.2	2352.8	2175.3	2037.8	1920.8	1823.4
50°	2864.9	2854.6	2843.3	2793.1	2686.3	2511.9	2309.7	2141.5	2010.2	1905.5	1810.1
52.5°	2815.6	2812.5	2802.3	2757.1	2654.5	2482.2	2290.3	2129.1	2008.1	1902.4	1802.9
55°	3252.7	3259.9	3165.5	2969.5	2797.2	2564.2	2348.7	2191.7	2058.3	1951.6	1878.8
57.5°	4811.4	4779.6	4617.5	4228.6	3789.4	3209.6	2792.0	2538.5	2373.4	2391.8	2428.8
60°	5605.6	5599.5	5569.7	5418.9	5126.4	4685.2	4195.8	3634.5	3456.0	3475.4	3489.7
62.5°	5960.6	5969.8	5992.4	5936.1	5859.1	5730.8	5486.6	5260.8	5021.8	4932.5	4693.4
65°	6124.9	6141.2	6192.5	6224.4	6254.1	6276.7	6373.2	6637.9	6812.3	6486.0	5726.7
67.5°	5785.2	5864.1	6033.5	6198.7	6346.4	6556.8	6883.1	7497.7	7925.6	7524.5	6423.4
70°	4217.3	4325.1	4519.0	5029.9	5575.9	6053.0	6685.1	7620.9	8266.3	7956.4	6595.9
72.5°	2644.2	2674.0	2760.2	2948.0	3353.3	3965.9	5071.0	6474.7	7219.7	6972.4	5574.8
75°	1677.7	1688.0	1684.9	1728.0	1796.7	1930.2	2367.3	3824.2	4945.8	4560.0	3107.0
77.5°	999.4	1014.8	1020.9	1034.3	1067.2	1114.3	1150.3	1301.1	2073.8	2013.3	1127.7
80°	837.3	849.6	839.4	836.3	815.8	801.3	818.9	801.3	743.9	716.3	659.8
82.5°	443.3	442.3	439.2	468.9	529.4	576.7	612.5	604.4	546.9	465.8	395.0
85°	243.2	251.4	251.4	261.7	252.4	253.5	261.7	276.1	255.5	213.5	174.4
87.5°	20.5	31.8	25.7	31.8	43.1	30.8	29.7	29.7	25.7	18.4	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152611

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4
2.5°	1949.6	1947.6	1943.4	1940.4	1940.4	1935.2	1932.1	1930.2	1929.1	1925.0	1925.0
5°	1943.4	1936.3	1929.1	1923.9	1920.8	1915.8	1907.6	1903.4	1898.3	1894.2	1892.1
7.5°	1930.2	1916.8	1905.5	1897.3	1887.0	1878.8	1868.5	1859.3	1850.1	1846.0	1843.9
10°	1909.5	1892.1	1874.7	1859.3	1845.0	1830.6	1817.2	1803.9	1792.6	1784.4	1776.2
12.5°	1890.1	1863.4	1840.8	1818.2	1795.6	1778.2	1759.8	1740.3	1723.8	1708.5	1704.4
15°	1863.4	1832.6	1803.9	1776.2	1748.5	1719.8	1697.2	1675.6	1648.9	1631.5	1618.1
17.5°	1838.8	1801.9	1766.9	1734.1	1700.2	1670.5	1636.7	1607.9	1581.2	1554.5	1535.0
20°	1812.1	1772.1	1735.1	1698.2	1661.2	1623.3	1584.4	1547.4	1514.5	1482.7	1450.9
22.5°	1788.5	1747.5	1711.5	1671.5	1630.5	1587.4	1542.3	1496.1	1458.1	1417.1	1380.1
25°	1774.1	1729.0	1692.0	1653.1	1607.9	1560.7	1509.4	1455.0	1408.8	1361.7	1317.5
27.5°	1774.1	1715.6	1677.7	1638.7	1592.5	1542.3	1485.8	1426.3	1374.0	1321.7	1267.3
30°	1789.5	1717.7	1666.4	1625.4	1578.1	1523.7	1461.1	1398.5	1341.1	1279.6	1227.3
32.5°	1803.9	1721.8	1658.1	1605.9	1551.5	1498.1	1434.5	1367.8	1304.1	1245.7	1190.3
35°	1813.2	1721.8	1642.8	1576.1	1514.5	1462.2	1399.6	1333.0	1268.3	1210.8	1159.5
37.5°	1814.2	1713.6	1618.1	1542.3	1477.6	1423.2	1363.7	1301.1	1239.6	1186.2	1143.1
40°	1803.9	1697.2	1593.6	1506.3	1438.5	1383.2	1328.8	1272.3	1217.0	1172.8	1135.9
42.5°	1785.4	1679.7	1569.9	1477.6	1406.8	1349.3	1299.1	1250.8	1202.6	1164.7	1133.9
45°	1757.7	1656.2	1548.4	1460.1	1390.4	1329.8	1280.6	1240.5	1199.5	1167.7	1136.9
47.5°	1733.1	1647.9	1555.5	1471.4	1398.5	1336.0	1285.7	1251.8	1220.0	1198.4	1156.4
50°	1728.0	1643.8	1558.7	1480.6	1406.8	1343.2	1299.1	1281.6	1272.3	1259.1	1194.4
52.5°	1713.6	1642.8	1581.2	1538.1	1490.9	1461.1	1415.0	1431.4	1421.1	1374.0	1257.0
55°	1864.5	1885.0	1942.4	2024.5	2100.4	2117.9	2112.7	2093.3	1989.6	1711.5	1407.8
57.5°	2563.2	2679.2	2788.0	2836.2	2829.9	2775.6	2736.6	2657.6	2507.8	2169.2	1705.4
60°	3533.9	3552.3	3494.9	3409.7	3266.1	3146.0	3017.8	2870.1	2652.4	2321.0	1888.1
62.5°	4427.7	4179.4	3923.8	3683.7	3465.2	3274.3	3095.8	2889.5	2606.3	2260.5	1864.5
65°	5058.7	4533.4	4130.1	3785.3	3476.5	3209.6	2986.9	2719.2	2400.1	2088.1	1728.0
67.5°	5383.9	4578.4	3959.7	3479.5	3041.3	2672.0	2375.4	2114.8	1877.8	1741.3	1512.4
70°	5020.7	3885.9	3023.9	2481.1	1956.8	1568.9	1239.6	1040.5	971.7	1101.0	1145.2
72.5°	3741.1	2529.3	1798.8	1391.4	1066.1	849.6	651.6	512.0	416.6	437.1	567.5
75°	1769.0	1091.8	771.6	586.9	466.8	386.8	316.1	289.3	242.2	201.1	188.8
77.5°	688.5	501.8	414.5	303.7	215.4	173.4	147.8	142.6	145.7	141.6	139.6
80°	524.4	355.0	222.7	163.1	140.6	124.1	109.8	105.7	107.8	112.8	118.0
82.5°	292.4	182.7	135.4	118.0	105.7	90.3	82.1	76.0	77.0	83.1	94.4
85°	112.8	88.3	81.0	78.0	72.8	58.4	50.3	51.3	58.4	69.7	69.7
87.5°	12.3	12.3	16.4	12.3	12.3	12.3	11.3	13.4	14.4	18.4	21.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152611

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7050

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4	1940.4
2.5°	1922.9	1922.9	1922.9	1920.8	1921.9	1917.8	1917.8	1914.7	1919.8	1916.8	1915.8
5°	1893.2	1892.1	1888.1	1888.1	1888.1	1888.1	1891.1	1882.9	1889.0	1889.0	1886.0
7.5°	1842.9	1842.9	1831.6	1837.7	1835.8	1838.8	1842.9	1838.8	1845.0	1849.0	1846.0
10°	1773.2	1773.2	1763.8	1771.1	1768.0	1775.1	1782.4	1778.2	1782.4	1788.5	1790.6
12.5°	1696.2	1692.0	1683.8	1686.9	1686.9	1691.0	1694.1	1699.3	1704.4	1712.5	1716.7
15°	1606.8	1600.7	1590.5	1590.5	1584.4	1586.3	1592.5	1594.6	1604.9	1616.2	1629.4
17.5°	1515.5	1500.2	1488.9	1475.5	1465.3	1473.5	1480.6	1485.8	1494.0	1511.5	1520.7
20°	1429.3	1398.5	1377.0	1359.6	1348.3	1353.5	1362.7	1368.8	1376.0	1380.1	1383.2
22.5°	1344.2	1309.3	1279.6	1258.0	1239.6	1244.7	1240.5	1237.5	1242.6	1229.2	1228.3
25°	1270.4	1229.2	1189.2	1163.6	1141.0	1133.9	1112.3	1107.2	1092.8	1081.6	1073.3
27.5°	1217.0	1163.6	1119.5	1089.7	1053.8	1027.2	999.4	971.7	956.4	937.8	928.6
30°	1174.9	1118.4	1066.1	1015.9	968.6	927.6	890.7	854.7	830.2	803.4	786.0
32.5°	1135.9	1083.5	1020.0	951.2	887.6	841.5	793.2	752.1	713.2	678.2	652.6
35°	1109.2	1050.8	969.6	885.5	813.7	759.3	708.0	649.5	602.3	557.2	529.4
37.5°	1094.8	1023.0	923.5	830.2	750.1	688.5	624.9	557.2	499.7	457.6	415.5
40°	1083.5	995.3	882.5	780.8	696.7	622.8	549.0	468.9	405.3	361.1	328.4
42.5°	1071.3	964.6	846.5	741.9	648.5	562.3	473.1	387.9	327.4	296.6	282.2
45°	1057.9	937.8	812.6	705.0	601.3	496.7	394.0	315.0	279.1	268.8	268.8
47.5°	1054.8	920.4	788.1	669.0	548.0	420.7	321.1	271.9	261.7	263.7	267.8
50°	1067.2	915.3	766.5	626.9	477.1	340.6	271.9	255.5	257.5	263.7	269.8
52.5°	1096.9	919.4	743.9	568.5	393.0	281.1	251.4	250.4	256.5	265.8	271.9
55°	1147.2	919.4	700.8	481.2	314.0	252.4	244.2	248.3	256.5	264.8	269.8
57.5°	1254.9	910.2	624.9	384.8	262.7	242.2	242.2	247.3	254.5	262.7	266.7
60°	1383.2	897.8	518.1	297.6	237.0	234.0	241.1	247.3	253.5	260.6	264.8
62.5°	1391.4	866.0	410.5	246.2	223.7	228.8	240.1	248.3	250.4	255.5	260.6
65°	1278.5	755.2	326.3	220.6	217.5	225.7	237.0	243.2	244.2	246.2	251.4
67.5°	1119.5	615.6	263.7	208.3	211.4	220.6	226.7	231.9	235.0	240.1	241.1
70°	919.4	494.6	225.7	196.0	199.1	209.3	214.5	219.6	225.7	231.9	228.8
72.5°	651.6	384.8	198.0	182.7	186.7	196.0	202.2	206.2	211.4	217.5	213.5
75°	277.1	268.8	171.4	165.2	171.4	177.5	183.6	189.8	194.9	198.0	198.0
77.5°	141.6	158.0	147.8	147.8	151.8	158.0	163.1	169.3	172.4	175.4	179.6
80°	120.1	122.1	124.1	128.3	132.3	138.5	143.6	148.8	149.8	150.9	152.8
82.5°	99.5	103.6	105.7	111.8	114.9	117.0	120.1	120.1	122.1	122.1	119.1
85°	71.8	77.0	80.0	81.0	80.0	81.0	82.1	84.1	89.2	89.2	85.2
87.5°	20.5	19.5	24.7	25.7	27.7	31.8	36.0	43.1	45.2	47.2	47.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152611

CATALOG NUMBER: AVS-E03-LED-E-U-SL4-7050

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1940.4	1940.4	1940.4	1940.4
2.5°	1914.7	1916.8	1912.6	1913.7
5°	1886.0	1890.1	1885.0	1891.1
7.5°	1849.0	1855.2	1854.2	1853.2
10°	1795.6	1803.9	1803.9	1806.9
12.5°	1728.0	1733.1	1737.2	1739.3
15°	1636.7	1645.9	1651.0	1651.0
17.5°	1526.8	1533.0	1536.1	1532.0
20°	1387.3	1385.3	1386.2	1376.0
22.5°	1226.2	1229.2	1220.0	1222.1
25°	1068.2	1063.0	1067.2	1061.0
27.5°	915.3	916.3	905.0	910.2
30°	769.5	764.5	750.1	757.3
32.5°	629.0	615.6	600.3	591.1
35°	496.7	476.1	468.9	465.8
37.5°	389.9	367.4	360.2	351.9
40°	309.8	301.7	298.5	300.6
42.5°	278.0	278.0	280.1	281.1
45°	269.8	273.0	276.1	277.1
47.5°	270.9	274.0	278.0	279.1
50°	273.0	276.1	279.1	280.1
52.5°	274.0	274.0	276.1	277.1
55°	271.9	270.9	271.9	273.0
57.5°	267.8	265.8	266.7	269.8
60°	265.8	262.7	264.8	266.7
62.5°	260.6	259.6	261.7	262.7
65°	249.3	250.4	253.5	253.5
67.5°	239.1	240.1	241.1	242.2
70°	226.7	227.8	229.8	230.9
72.5°	212.4	216.5	219.6	223.7
75°	201.1	205.2	211.4	215.4
77.5°	181.7	184.7	191.9	197.0
80°	153.9	152.8	153.9	157.0
82.5°	118.0	118.0	117.0	116.0
85°	83.1	82.1	79.0	79.0
87.5°	45.2	44.1	43.1	41.0
90°	0.0	0.0	0.0	0.0

(END OF REPORT)