

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147594

Luminaire Tested: **AVS-F04-LED-E-U-5MQ-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P147594
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-5MQ-7030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM
Light Source: (28) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9722.8 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B3 - U0 - G2

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P147594

CATALOG NUMBER: AVS-F04-LED-E-U-5MQ-7030

Iso-Footcandle Lines of Horizontal Illumination

✗ Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 7.3 fc
Type V - Short - Full Cutoff

REPORT NUMBER: P147594

CATALOG NUMBER: AVS-F04-LED-E-U-5MQ-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P147594

CATALOG NUMBER: AVS-F04-LED-E-U-5MQ-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4861.4	0.0	4861.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4861.4	0.0	4861.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	9722.8	0.0	9722.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	0.7
10°-20°	218.6	2.2
20°-30°	422.8	4.3
30°-40°	818.5	8.4
40°-50°	1477.9	15.2
50°-60°	2569.8	26.4
60°-70°	2917.4	30.0
70°-80°	1131.1	11.6
80°-90°	102.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9722.8	100.0
0°-180°	9722.8	100.0

Coefficient of Utilization



REPORT NUMBER: P147594


CATALOG NUMBER: AVS-F04-LED-E-U-5MQ-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	353.0	3.6			
FM	(30°-60°)	2433.1	25.0			
FH	(60°-80°)	2024.2	20.8			G2/5000
FVH	(80°-90°)	51.0	0.5			G1/100
BL	(0°-30°)	353.0	3.6	B1/500		
BM	(30°-60°)	2433.1	25.0	B2/2500		
BH	(60°-80°)	2024.2	20.8	B3/2500		G2/5000
BVH	(80°-90°)	51.0	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P147594

CATALOG NUMBER: AVS-F04-LED-E-U-5MQ-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	645.4	645.4	645.4	645.4	645.4	645.4	645.4	645.4	645.4	645.4	645.4
2.5°	649.5	651.4	651.0	649.9	649.9	649.9	649.4	647.9	647.5	648.5	649.4
5°	664.5	664.5	664.5	664.5	663.5	663.4	662.5	661.5	662.0	661.0	660.5
7.5°	687.7	686.1	686.1	685.7	685.6	684.7	683.1	681.1	681.7	681.0	680.6
10°	714.8	715.3	713.8	715.2	712.7	712.2	710.3	709.2	708.8	707.2	707.3
12.5°	747.5	745.9	745.9	745.0	743.9	743.0	739.9	739.5	737.4	736.4	734.9
15°	778.1	777.6	775.6	773.6	773.1	772.0	768.5	766.6	766.0	763.5	761.6
17.5°	808.8	807.9	805.3	804.2	802.3	800.7	797.7	794.7	793.2	792.1	789.6
20°	841.5	840.4	837.9	836.0	833.4	831.4	826.9	824.4	822.8	821.3	819.4
22.5°	882.1	880.2	876.2	872.6	867.2	865.1	859.1	855.5	853.1	851.0	849.9
25°	926.4	926.8	921.5	916.9	910.3	904.8	897.2	893.3	890.8	888.7	888.2
27.5°	981.8	982.2	977.2	970.7	960.6	954.6	944.5	939.5	938.0	936.0	935.4
30°	1069.2	1064.7	1056.1	1045.6	1036.5	1023.4	1008.9	1003.7	998.8	997.3	997.3
32.5°	1230.1	1227.5	1220.5	1194.3	1182.3	1155.1	1129.5	1114.9	1098.2	1090.3	1085.2
35°	1342.6	1341.6	1336.2	1327.0	1319.5	1314.0	1298.9	1296.4	1293.4	1293.4	1297.3
37.5°	1425.5	1419.5	1418.5	1420.0	1418.0	1419.1	1431.1	1447.7	1461.8	1468.8	1467.8
40°	1548.2	1539.7	1544.7	1541.1	1536.6	1535.6	1539.7	1546.2	1552.7	1552.7	1551.2
42.5°	1708.6	1712.5	1714.6	1700.0	1690.5	1688.0	1697.5	1695.4	1702.0	1699.5	1693.0
45°	1946.8	1944.2	1940.7	1923.1	1908.1	1896.1	1898.5	1895.0	1895.5	1891.6	1886.5
47.5°	2187.2	2195.6	2181.0	2172.4	2155.4	2146.9	2154.0	2147.9	2159.4	2138.2	2128.3
50°	2420.3	2426.3	2421.3	2409.3	2409.2	2421.3	2429.8	2440.9	2457.0	2433.0	2396.7
52.5°	2611.3	2616.4	2623.8	2634.0	2658.5	2684.1	2720.4	2759.2	2789.7	2785.3	2744.0
55°	2727.9	2734.0	2746.5	2781.2	2825.5	2892.8	2974.7	3064.7	3135.1	3169.3	3139.1
57.5°	2767.2	2771.6	2805.8	2847.6	2916.5	3016.5	3153.8	3309.0	3444.2	3530.2	3516.7
60°	2758.1	2758.1	2792.7	2850.2	2946.6	3079.3	3273.4	3488.5	3695.5	3824.2	3805.2
62.5°	2663.1	2668.2	2717.9	2786.7	2903.4	3062.2	3293.5	3568.4	3816.2	3976.1	3960.5
65°	2455.0	2458.5	2512.3	2594.2	2724.4	2912.4	3165.3	3469.8	3753.9	3907.7	3878.5
67.5°	2118.8	2122.3	2166.0	2258.4	2396.2	2592.7	2865.7	3200.9	3479.0	3600.6	3513.2
70°	1685.4	1695.4	1723.6	1821.7	1926.2	2118.7	2370.1	2705.3	2967.8	3082.8	2986.3
72.5°	1148.6	1174.2	1208.4	1295.3	1395.4	1555.2	1755.3	2037.7	2248.4	2381.6	2295.6
75°	646.8	683.1	693.7	759.6	842.0	968.1	1114.4	1317.0	1529.6	1637.7	1534.1
77.5°	279.5	309.1	322.3	352.8	417.2	470.1	559.0	695.6	860.1	936.0	811.8
80°	137.7	144.8	150.3	159.8	177.9	195.0	237.3	297.1	364.5	381.6	303.6
82.5°	106.5	111.6	121.1	128.7	133.3	137.7	141.8	149.8	156.4	159.8	150.8
85°	74.8	81.5	92.0	100.5	105.5	109.0	112.5	115.1	109.1	99.5	104.6
87.5°	19.6	25.7	35.6	38.8	43.7	46.2	45.3	46.7	42.3	30.7	34.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147594

CATALOG NUMBER: AVS-F04-LED-E-U-5MQ-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	645.4	645.4	645.4	645.4	645.4	645.4	645.4	645.4
2.5°	648.9	648.5	648.9	648.9	648.9	648.5	648.5	648.4
5°	660.5	660.5	661.0	660.0	660.0	660.5	660.0	659.5
7.5°	680.0	679.6	679.6	679.1	679.6	679.1	679.2	678.5
10°	706.3	705.3	705.7	704.2	704.2	703.7	703.7	703.7
12.5°	734.4	732.8	733.4	731.8	729.3	729.8	730.4	729.8
15°	761.6	760.0	758.5	757.5	756.1	756.5	756.6	756.0
17.5°	789.2	786.1	785.7	784.1	783.6	783.6	783.6	784.1
20°	817.8	815.9	815.3	813.8	813.3	814.8	815.3	814.3
22.5°	848.5	847.5	848.5	847.5	848.9	849.9	850.6	849.5
25°	887.2	886.2	887.7	891.2	893.3	894.3	896.8	895.8
27.5°	937.0	936.0	939.5	944.5	947.6	952.5	955.0	956.1
30°	1001.2	1005.8	1007.9	1017.8	1019.9	1028.0	1028.0	1031.5
32.5°	1094.8	1103.4	1118.4	1134.1	1155.6	1171.2	1171.2	1179.3
35°	1299.9	1303.4	1315.0	1317.5	1322.1	1327.0	1322.0	1326.0
37.5°	1457.2	1441.7	1430.6	1415.0	1405.4	1405.4	1406.4	1405.5
40°	1537.6	1531.6	1526.6	1513.6	1511.5	1511.0	1511.0	1513.1
42.5°	1681.5	1666.8	1658.9	1647.8	1644.1	1643.2	1642.7	1643.7
45°	1868.4	1844.8	1823.2	1812.0	1802.5	1793.5	1796.5	1796.5
47.5°	2086.0	2049.3	2014.1	1995.0	1978.4	1971.0	1965.9	1964.5
50°	2351.0	2299.7	2254.5	2218.8	2194.6	2194.2	2196.7	2180.5
52.5°	2675.6	2594.8	2538.4	2490.2	2467.6	2465.1	2457.0	2448.0
55°	3035.5	2939.6	2846.6	2794.8	2765.2	2749.1	2739.5	2724.5
57.5°	3406.5	3277.3	3143.6	3060.7	3008.5	2972.2	2953.2	2944.6
60°	3692.6	3516.1	3339.7	3206.5	3119.5	3065.7	3032.5	3019.0
62.5°	3805.2	3565.8	3339.7	3164.8	3039.2	2964.8	2920.0	2900.3
65°	3670.9	3387.5	3130.1	2937.0	2796.8	2713.9	2665.1	2644.0
67.5°	3296.0	3045.6	2765.7	2573.7	2429.4	2347.4	2294.6	2279.1
70°	2763.1	2507.3	2239.9	2068.4	1939.8	1873.0	1818.1	1811.6
72.5°	2076.5	1855.9	1626.6	1484.9	1381.3	1270.7	1242.6	1256.7
75°	1331.0	1124.5	920.4	792.7	698.2	592.6	551.9	562.0
77.5°	630.3	488.1	352.3	272.5	228.8	195.5	187.0	182.0
80°	233.8	189.4	167.5	158.9	152.7	147.3	143.2	138.8
82.5°	151.3	147.8	143.2	141.8	137.2	130.2	117.1	111.6
85°	113.1	113.1	107.0	107.6	104.0	95.0	82.9	76.4
87.5°	33.2	29.6	27.2	25.1	24.7	22.2	16.1	14.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)