

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148634

Luminaire Tested: **AVS-F04-LED-E-U-5XQ-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148634
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-5XQ-7030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (28) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9591.9 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148634

CATALOG NUMBER: AVS-F04-LED-E-U-5XQ-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 9.1 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148634

CATALOG NUMBER: AVS-F04-LED-E-U-5XQ-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P148634

CATALOG NUMBER: AVS-F04-LED-E-U-5XQ-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4796.0	0.0	4796.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4796.0	0.0	4796.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	9591.9	0.0	9591.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.6	0.9
10°-20°	256.2	2.7
20°-30°	429.0	4.5
30°-40°	654.1	6.8
40°-50°	1044.4	10.9
50°-60°	1605.9	16.7
60°-70°	2338.1	24.4
70°-80°	2633.9	27.5
80°-90°	543.7	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9591.9	100.0
0°-180°	9591.9	100.0

Coefficient of Utilization



REPORT NUMBER: P148634


CATALOG NUMBER: AVS-F04-LED-E-U-5XQ-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	385.9	4.0			
FM	(30°-60°)	1652.2	17.2			
FH	(60°-80°)	2486.0	25.9			G2/5000
FVH	(80°-90°)	271.9	2.8			G3/500
BL	(0°-30°)	385.9	4.0	B1/500		
BM	(30°-60°)	1652.2	17.2	B2/2500		
BH	(60°-80°)	2486.0	25.9	B3/2500		G2/5000
BVH	(80°-90°)	271.9	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type V Short





REPORT NUMBER: P148634

CATALOG NUMBER: AVS-F04-LED-E-U-5XQ-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	908.8	908.8	908.8	908.8	908.8	908.8	908.8	908.8	908.8	908.8	908.8
2.5°	910.3	910.9	910.6	910.1	910.4	910.1	909.6	909.3	907.6	908.6	910.1
5°	910.3	909.8	909.5	909.3	909.3	910.1	909.3	908.6	908.3	908.8	908.1
7.5°	909.8	908.8	908.4	908.1	908.4	908.6	907.8	906.7	907.6	906.8	905.8
10°	908.3	907.6	907.8	906.8	907.0	906.7	905.8	905.1	905.6	904.8	903.5
12.5°	908.8	907.6	907.4	906.7	906.5	906.3	905.1	903.7	904.0	903.5	902.3
15°	908.8	908.1	907.8	906.7	906.5	906.1	904.6	904.0	904.0	903.2	901.8
17.5°	909.3	908.8	908.8	907.6	907.0	906.8	905.1	904.2	905.1	903.5	902.5
20°	910.9	910.4	910.6	909.8	908.8	908.8	907.6	907.0	907.4	907.0	904.2
22.5°	913.8	913.8	914.4	914.1	913.9	914.1	913.1	913.1	913.4	913.4	911.1
25°	922.4	922.1	922.6	922.7	922.9	924.7	923.9	923.6	924.9	924.9	922.7
27.5°	938.4	938.0	938.4	939.0	940.2	942.5	942.0	942.7	944.8	944.2	942.3
30°	957.1	956.6	957.8	959.4	960.3	963.8	962.3	966.1	967.9	969.3	967.9
32.5°	984.2	984.2	986.5	987.5	989.7	993.3	993.8	996.8	999.1	1001.6	999.8
35°	1020.3	1019.9	1021.7	1023.4	1026.2	1029.4	1030.7	1034.7	1038.2	1040.0	1036.8
37.5°	1075.6	1073.0	1076.3	1077.2	1079.5	1080.2	1083.7	1088.7	1092.5	1092.0	1089.7
40°	1150.6	1150.1	1148.8	1147.4	1150.9	1152.1	1152.1	1158.9	1164.9	1163.9	1163.6
42.5°	1238.0	1235.9	1234.3	1234.3	1236.3	1236.8	1244.6	1249.6	1253.9	1254.9	1253.9
45°	1332.0	1329.7	1330.4	1329.3	1330.1	1333.4	1337.8	1347.2	1355.2	1355.4	1351.2
47.5°	1433.1	1426.0	1431.6	1423.8	1428.6	1431.1	1442.4	1456.0	1470.1	1472.5	1468.8
50°	1535.5	1534.9	1534.3	1532.8	1535.1	1540.7	1554.5	1575.9	1589.4	1598.4	1592.4
52.5°	1647.7	1643.9	1642.2	1639.7	1642.0	1652.7	1672.1	1690.8	1715.0	1725.4	1717.1
55°	1756.8	1755.5	1749.0	1748.8	1753.6	1770.4	1791.5	1814.4	1840.8	1852.3	1849.3
57.5°	1868.9	1861.7	1859.6	1856.6	1866.1	1882.0	1907.9	1949.1	1976.5	1989.5	1982.0
60°	1978.4	1973.0	1968.7	1967.7	1974.2	1996.3	2033.6	2083.0	2117.0	2134.1	2122.0
62.5°	2096.2	2092.6	2087.6	2081.8	2095.6	2123.9	2170.3	2225.1	2275.0	2296.2	2277.8
65°	2242.4	2235.1	2229.6	2222.3	2233.6	2269.2	2327.4	2404.5	2471.6	2496.2	2483.1
67.5°	2396.8	2389.8	2390.5	2385.9	2406.0	2455.5	2530.4	2635.2	2725.2	2767.2	2742.5
70°	2531.4	2535.1	2536.2	2554.5	2589.2	2664.7	2789.2	2953.4	3089.8	3154.0	3127.6
71°	2491.7	2500.0	2512.8	2531.9	2591.7	2680.9	2851.1	3049.9	3212.7	3321.3	3284.9
72.5°	2379.1	2384.1	2390.7	2419.8	2487.5	2605.5	2780.7	3007.9	3217.3	3357.7	3315.5
75°	2216.2	2220.9	2223.3	2243.6	2305.2	2408.3	2568.6	2770.2	2954.9	3074.5	3062.7
77.5°	1970.4	1971.2	1988.8	2020.2	2089.3	2207.3	2376.1	2585.2	2758.9	2851.8	2792.7
80°	1414.9	1405.4	1423.5	1464.0	1549.4	1684.7	1857.6	2096.4	2289.1	2376.1	2284.6
82.5°	538.3	567.5	613.5	680.4	709.2	859.6	1020.9	1161.1	1323.5	1505.0	1459.5
85°	57.8	65.1	81.7	101.2	128.0	177.0	244.6	333.8	411.4	483.5	429.2
87.5°	21.6	22.1	24.7	28.4	28.9	30.2	32.2	37.4	34.9	30.2	24.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148634

CATALOG NUMBER: AVS-F04-LED-E-U-5XQ-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	908.8	908.8	908.8	908.8	908.8	908.8	908.8	908.8
2.5°	908.8	909.0	908.8	909.1	909.0	908.1	908.3	907.8
5°	908.6	907.8	908.1	908.3	908.1	908.6	907.8	908.3
7.5°	907.4	905.8	906.3	906.3	905.8	906.5	906.0	905.8
10°	904.8	902.8	903.8	903.3	903.0	903.2	903.3	903.2
12.5°	902.6	901.3	901.6	901.2	901.0	901.8	901.6	901.8
15°	902.1	900.0	899.8	899.3	899.5	900.0	900.1	900.7
17.5°	901.6	899.0	898.8	898.2	898.5	899.6	899.8	899.3
20°	903.0	901.0	900.5	900.0	899.8	901.0	900.7	900.7
22.5°	910.1	907.6	907.4	905.3	904.6	905.3	904.8	904.8
25°	921.3	918.3	917.3	914.6	912.5	912.5	911.8	911.3
27.5°	941.8	937.2	936.2	934.0	931.2	931.7	930.2	929.9
30°	965.4	961.3	957.8	954.6	951.3	950.1	948.3	948.0
32.5°	996.3	991.7	987.5	983.4	979.0	977.2	974.2	972.6
35°	1034.2	1028.2	1023.2	1020.4	1015.9	1013.6	1011.6	1013.9
37.5°	1087.3	1080.0	1077.5	1074.2	1071.2	1067.7	1068.4	1067.7
40°	1160.6	1154.1	1151.6	1145.8	1145.1	1141.0	1143.5	1141.0
42.5°	1251.4	1239.3	1237.5	1233.1	1231.5	1229.2	1230.3	1228.5
45°	1350.2	1339.3	1337.4	1330.1	1330.4	1325.0	1327.0	1327.0
47.5°	1461.2	1449.9	1440.6	1435.3	1433.4	1430.1	1431.8	1431.6
50°	1575.9	1560.5	1550.3	1539.9	1535.3	1536.6	1533.1	1539.2
52.5°	1699.0	1676.2	1661.6	1651.7	1643.2	1645.0	1645.5	1647.3
55°	1826.4	1797.3	1776.2	1763.3	1755.5	1756.1	1758.3	1760.4
57.5°	1954.6	1918.1	1889.5	1870.5	1865.4	1867.7	1867.7	1867.4
60°	2087.6	2043.8	2006.8	1985.3	1980.7	1979.5	1989.2	1986.0
62.5°	2230.4	2177.8	2139.6	2111.9	2105.4	2109.9	2118.8	2116.7
65°	2419.5	2346.9	2297.6	2270.3	2259.3	2263.7	2275.5	2275.1
67.5°	2663.6	2562.1	2497.0	2461.8	2453.7	2459.3	2465.8	2472.1
70°	3028.5	2883.5	2790.5	2714.4	2681.8	2675.4	2682.0	2682.3
71°	3156.9	2990.4	2842.3	2749.3	2695.8	2673.2	2674.9	2663.6
72.5°	3151.7	2946.4	2773.2	2676.0	2601.5	2583.4	2574.6	2561.0
75°	2939.3	2754.4	2604.0	2497.9	2426.3	2405.0	2389.4	2388.6
77.5°	2665.6	2529.1	2363.5	2251.2	2163.9	2128.5	2112.6	2112.1
80°	2142.8	1938.5	1817.4	1749.8	1644.5	1614.1	1581.9	1569.7
82.5°	1295.9	1012.6	823.4	731.6	680.8	560.7	503.2	476.1
85°	301.9	214.4	147.8	97.0	69.8	55.5	42.7	37.7
87.5°	20.4	16.1	14.3	11.5	8.8	8.6	5.3	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)