

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147576

Luminaire Tested: **AVS-F02-LED-E-U-5MQ-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P147576
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-5MQ-7050
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM
Light Source: (14) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5461.5 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B3 - U0 - G1

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P147576

CATALOG NUMBER: AVS-F02-LED-E-U-5MQ-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.1 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P147576

CATALOG NUMBER: AVS-F02-LED-E-U-5MQ-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P147576

CATALOG NUMBER: AVS-F02-LED-E-U-5MQ-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2730.8	0.0	2730.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2730.8	0.0	2730.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	5461.5	0.0	5461.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.3	0.7
10°-20°	122.8	2.2
20°-30°	237.5	4.3
30°-40°	459.8	8.4
40°-50°	830.2	15.2
50°-60°	1443.5	26.4
60°-70°	1638.8	30.0
70°-80°	635.4	11.6
80°-90°	57.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5461.5	100.0
0°-180°	5461.5	100.0

Coefficient of Utilization



REPORT NUMBER: P147576


CATALOG NUMBER: AVS-F02-LED-E-U-5MQ-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	198.3	3.6			
FM	(30°-60°)	1366.7	25.0			
FH	(60°-80°)	1137.1	20.8			G1/1800
FVH	(80°-90°)	28.7	0.5			G1/100
BL	(0°-30°)	198.3	3.6	B1/500		
BM	(30°-60°)	1366.7	25.0	B2/2500		
BH	(60°-80°)	1137.1	20.8	B3/2500		G1/1800
BVH	(80°-90°)	28.7	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1

Type V Short





REPORT NUMBER: P147576

CATALOG NUMBER: AVS-F02-LED-E-U-5MQ-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	362.6	362.6	362.6	362.6	362.6	362.6	362.6	362.6	362.6	362.6	362.6
2.5°	364.8	366.0	365.6	365.1	365.1	365.1	364.8	363.9	363.7	364.2	364.8
5°	373.3	373.3	373.3	373.3	372.7	372.7	372.2	371.6	371.8	371.3	371.0
7.5°	386.2	385.4	385.5	385.1	385.1	384.6	383.7	382.6	382.9	382.6	382.4
10°	401.5	401.9	400.9	401.8	400.4	400.1	399.0	398.3	398.1	397.3	397.3
12.5°	419.9	419.1	419.1	418.4	417.8	417.3	415.6	415.3	414.3	413.7	412.8
15°	437.1	436.9	435.6	434.6	434.2	433.8	431.7	430.6	430.3	428.8	427.8
17.5°	454.3	453.7	452.3	451.8	450.6	449.7	448.1	446.4	445.6	445.0	443.5
20°	472.7	472.1	470.7	469.6	468.2	466.9	464.5	463.0	462.2	461.3	460.2
22.5°	495.5	494.5	492.2	490.2	487.0	486.0	482.5	480.6	479.2	478.0	477.5
25°	520.4	520.6	517.5	515.0	511.3	508.3	504.0	501.8	500.3	499.3	498.9
27.5°	551.5	551.7	548.9	545.3	539.6	536.2	530.6	527.8	526.8	525.8	525.5
30°	600.6	598.0	593.2	587.4	582.2	574.9	566.6	563.9	561.0	560.2	560.2
32.5°	691.0	689.5	685.6	670.9	664.0	648.9	634.4	626.3	616.9	612.4	609.5
35°	754.2	753.6	750.5	745.4	741.1	738.0	729.6	728.2	726.4	726.5	728.7
37.5°	800.7	797.3	796.8	797.7	796.5	797.1	803.9	813.3	821.0	825.1	824.6
40°	869.6	864.9	867.8	865.7	863.2	862.6	864.9	868.6	872.2	872.1	871.3
42.5°	959.8	962.0	963.1	954.9	949.5	948.2	953.6	952.3	956.1	954.6	951.0
45°	1093.6	1092.2	1090.2	1080.3	1071.8	1065.1	1066.5	1064.5	1064.8	1062.5	1059.7
47.5°	1228.6	1233.4	1225.1	1220.3	1210.8	1206.0	1209.9	1206.4	1213.1	1201.1	1195.4
50°	1359.6	1362.9	1360.1	1353.4	1353.4	1360.1	1365.0	1371.2	1380.1	1366.6	1346.3
52.5°	1466.8	1469.6	1474.0	1479.6	1493.5	1507.8	1528.1	1549.8	1567.0	1564.6	1541.3
55°	1532.4	1535.8	1542.8	1562.3	1587.2	1625.0	1671.0	1721.5	1761.0	1780.3	1763.3
57.5°	1554.4	1556.9	1576.2	1599.6	1638.2	1694.4	1771.6	1858.8	1934.7	1983.0	1975.3
60°	1549.3	1549.3	1568.7	1600.9	1655.1	1729.7	1838.8	1959.6	2075.9	2148.2	2137.4
62.5°	1496.0	1498.8	1526.7	1565.4	1630.9	1720.1	1849.9	2004.5	2143.6	2233.5	2224.7
65°	1379.1	1380.9	1411.3	1457.2	1530.4	1636.0	1778.0	1949.1	2108.6	2195.0	2178.7
67.5°	1190.2	1192.1	1216.7	1268.6	1346.0	1456.4	1609.7	1798.0	1954.2	2022.6	1973.4
70°	946.7	952.3	968.3	1023.2	1082.0	1190.2	1331.4	1519.7	1667.0	1731.7	1677.5
72.5°	645.2	659.6	678.9	727.7	783.8	873.6	986.0	1144.7	1263.0	1337.7	1289.5
75°	363.4	383.7	389.6	426.7	473.0	543.8	625.9	739.8	859.3	919.9	861.8
77.5°	157.0	173.7	180.9	198.1	234.4	264.0	314.0	390.8	483.1	525.8	456.0
80°	77.3	81.2	84.5	89.7	99.9	109.5	133.3	166.8	204.8	214.3	170.6
82.5°	59.9	62.6	68.1	72.3	74.8	77.3	79.6	84.1	87.8	89.7	84.8
85°	42.1	45.8	51.6	56.5	59.3	61.3	63.2	64.7	61.2	56.0	58.8
87.5°	11.0	14.4	20.1	21.8	24.6	26.0	25.4	26.2	23.7	17.2	19.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147576

CATALOG NUMBER: AVS-F02-LED-E-U-5MQ-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	362.6	362.6	362.6	362.6	362.6	362.6	362.6	362.6
2.5°	364.6	364.2	364.6	364.6	364.6	364.2	364.2	364.2
5°	371.0	371.0	371.3	370.8	370.8	371.0	370.8	370.5
7.5°	382.1	381.8	381.7	381.6	381.8	381.5	381.6	381.1
10°	396.7	396.2	396.4	395.6	395.6	395.3	395.3	395.3
12.5°	412.5	411.6	411.9	411.2	409.7	409.9	410.4	409.9
15°	427.8	426.9	426.1	425.5	424.7	425.0	424.9	424.7
17.5°	443.3	441.7	441.3	440.5	440.2	440.2	440.2	440.5
20°	459.4	458.2	458.0	457.2	456.9	457.7	458.0	457.4
22.5°	476.6	476.1	476.7	476.1	476.9	477.5	477.7	477.2
25°	498.4	497.8	498.7	500.6	501.8	502.4	503.7	503.2
27.5°	526.3	525.8	527.7	530.6	532.2	535.1	536.5	537.0
30°	562.5	565.0	566.1	571.8	572.8	577.4	577.4	579.4
32.5°	614.9	619.8	628.2	637.1	649.1	657.8	657.9	662.4
35°	730.3	732.1	738.7	740.1	742.6	745.4	742.6	744.9
37.5°	818.5	809.8	803.5	794.8	789.4	789.4	790.1	789.4
40°	863.7	860.3	857.5	850.2	849.1	848.7	848.7	849.9
42.5°	944.5	936.4	931.8	925.6	923.5	923.0	922.7	923.3
45°	1049.5	1036.3	1024.1	1017.8	1012.5	1007.5	1009.1	1009.1
47.5°	1171.8	1151.2	1131.4	1120.6	1111.3	1107.2	1104.2	1103.4
50°	1320.6	1291.8	1266.4	1246.4	1232.7	1232.5	1234.0	1224.9
52.5°	1503.0	1457.5	1425.9	1398.8	1386.1	1384.7	1380.1	1375.1
55°	1705.2	1651.2	1599.0	1569.8	1553.3	1544.2	1538.9	1530.4
57.5°	1913.6	1841.0	1765.8	1719.3	1689.9	1669.5	1658.9	1654.1
60°	2074.2	1975.1	1876.0	1801.1	1752.3	1722.1	1703.4	1695.9
62.5°	2137.4	2003.1	1876.1	1777.7	1707.2	1665.4	1640.3	1629.2
65°	2062.1	1902.8	1758.2	1649.8	1571.0	1524.5	1497.0	1485.2
67.5°	1851.4	1710.8	1553.6	1445.7	1364.6	1318.5	1288.9	1280.2
70°	1552.1	1408.4	1258.2	1161.9	1089.6	1052.0	1021.3	1017.6
72.5°	1166.4	1042.5	913.7	834.1	776.0	713.8	698.0	705.9
75°	747.8	631.7	517.0	445.3	392.2	332.8	310.1	315.6
77.5°	354.1	274.2	197.9	153.1	128.5	109.8	105.1	102.2
80°	131.3	106.5	94.1	89.2	85.8	82.7	80.4	77.9
82.5°	85.0	83.0	80.4	79.6	77.1	73.2	65.8	62.7
85°	63.5	63.5	60.1	60.4	58.4	53.4	46.5	42.9
87.5°	18.7	16.7	15.2	14.1	13.9	12.4	9.0	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)