

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P153194

Luminaire Tested: **AVS-F04-LED-E-U-SLL-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P153194
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33681)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-SLL-7030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - 90° SPILL LIGHT ELIMINATOR LEFT
Light Source: (28) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8391.8 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type IV - Short - Non-Cutoff
BUG Rating: B1 - U0 - G3

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P153194

CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 20.9 fc
Type IV - Short - Non-Cutoff

REPORT NUMBER: P153194

CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P153194

CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1819.7	0.0	1819.7
	% Fixture	21.7	0.0	21.7
Street Side	Lumens	6572.1	0.0	6572.1
	% Fixture	78.3	0.0	78.3
Total	Lumens	8391.8	0.0	8391.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	1.2
10°-20°	319.7	3.8
20°-30°	568.0	6.8
30°-40°	894.5	10.7
40°-50°	1316.4	15.7
50°-60°	1748.5	20.8
60°-70°	1926.0	23.0
70°-80°	1208.4	14.4
80°-90°	307.8	3.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8391.8	100.0
0°-180°	8391.8	100.0

Coefficient of Utilization



REPORT NUMBER: P153194


CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	537.3	6.4			
FM	(30°-60°)	3049.8	36.3			
FH	(60°-80°)	2714.9	32.4			G2/5000
FVH	(80°-90°)	270.1	3.2			G3/500
BL	(0°-30°)	453.0	5.4	B1/500		
BM	(30°-60°)	909.5	10.8	B1/1000		
BH	(60°-80°)	419.5	5.0	B1/500		G1/500
BVH	(80°-90°)	37.7	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short





REPORT NUMBER: P153194

CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6
2.5°	1040.5	1042.5	1042.5	1041.6	1041.6	1043.5	1042.5	1041.6	1038.5	1042.5	1042.5
5°	1032.4	1034.5	1034.5	1036.5	1038.5	1040.5	1040.5	1042.5	1041.6	1045.5	1048.6
7.5°	1042.5	1044.6	1048.6	1053.6	1056.6	1063.6	1063.6	1068.7	1070.7	1073.7	1072.6
10°	1055.5	1060.6	1069.6	1077.7	1083.7	1091.8	1097.8	1104.9	1104.9	1107.9	1109.8
12.5°	1078.8	1083.7	1093.8	1103.8	1112.8	1122.9	1132.0	1139.1	1146.1	1148.1	1152.1
15°	1116.9	1122.9	1138.0	1152.1	1163.1	1176.3	1188.3	1202.4	1215.4	1218.4	1220.4
17.5°	1174.2	1186.3	1197.3	1222.5	1238.5	1255.6	1274.7	1294.8	1298.9	1320.0	1325.0
20°	1255.6	1270.8	1280.8	1311.9	1339.1	1361.2	1389.3	1412.4	1421.6	1441.7	1461.8
22.5°	1396.4	1393.4	1408.5	1439.6	1459.7	1503.9	1528.1	1552.2	1564.2	1594.4	1610.6
25°	1585.4	1601.5	1634.6	1637.7	1656.8	1708.1	1739.2	1763.3	1764.4	1773.4	1790.5
27.5°	1771.4	1837.7	1890.1	1918.1	1969.4	2016.7	2014.7	2048.8	1995.5	2006.6	2022.7
30°	1996.6	2107.2	2205.7	2272.0	2324.4	2379.6	2406.7	2425.8	2402.7	2392.6	2373.6
32.5°	2207.7	2362.5	2514.3	2631.9	2729.4	2820.9	2881.2	2908.4	2940.6	3022.0	3051.2
35°	2352.4	2571.6	2760.6	2930.6	3093.4	3239.2	3344.8	3405.1	3381.9	3370.9	3364.9
37.5°	2439.0	2706.3	2942.6	3182.9	3369.8	3588.0	3751.9	3910.7	3946.9	3883.5	3852.4
40°	2493.2	2809.8	3113.5	3397.0	3639.3	3920.7	4123.8	4362.1	4543.1	4567.2	4492.7
42.5°	2519.4	2879.3	3233.2	3553.8	3881.6	4226.4	4483.7	4772.2	5042.7	5228.7	5182.5
45°	2523.3	2924.5	3320.6	3695.5	4085.6	4494.8	4826.5	5146.2	5508.2	5826.8	5836.0
47.5°	2523.3	2958.7	3380.9	3798.1	4268.6	4728.1	5089.9	5468.0	5911.3	6288.3	6403.9
50°	2525.4	2981.8	3437.2	3878.5	4408.4	4925.1	5334.3	5780.6	6247.0	6657.3	6880.4
52.5°	2534.4	2998.9	3481.5	3935.9	4498.9	5063.8	5524.2	6039.0	6503.4	6924.7	7213.2
55°	2554.5	3023.0	3513.6	3971.0	4559.2	5154.3	5662.0	6216.0	6669.3	7096.6	7499.7
57.5°	2610.8	3065.3	3552.8	4002.2	4592.3	5213.6	5758.5	6292.3	6732.6	7178.0	7651.5
60°	2723.4	3154.7	3620.2	4064.6	4647.6	5323.2	5804.8	6241.0	6686.4	7153.9	7685.7
62.5°	2903.4	3294.4	3713.7	4170.1	4805.5	5493.1	5769.5	6088.3	6504.5	7014.2	7564.0
63°	2965.7	3324.6	3734.8	4193.2	4848.7	5524.2	5754.5	6043.0	6467.3	6969.9	7520.8
65°	3139.6	3458.3	3835.3	4309.8	5026.6	5555.4	5636.9	5807.8	6209.8	6717.6	7265.5
67.5°	3464.4	3783.0	4051.5	4506.8	5176.4	5432.7	5271.9	5293.1	5713.3	6239.1	6731.6
70°	3669.4	4049.4	4189.2	4532.0	5149.2	5250.8	4799.4	4519.9	4856.7	5455.9	5887.2
72.5°	3616.2	4052.4	4037.4	4197.2	4606.4	4700.9	4233.5	3793.1	3993.2	4440.5	4720.0
75°	3097.4	3619.2	3508.6	3476.4	3620.2	3682.5	3331.6	3264.2	3516.6	3765.0	3768.9
77.5°	2229.8	2803.8	2674.2	2488.2	2478.1	2621.9	2669.1	3110.5	3483.4	3679.5	3593.1
80°	1420.5	2042.8	1908.1	1583.4	1578.3	1765.4	2180.5	2780.7	3175.9	3285.4	3060.2
82.5°	742.0	1337.1	1388.4	1188.3	1360.2	1669.8	2075.0	2240.8	2390.7	2405.7	2140.3
85°	462.5	822.4	967.2	998.2	1228.5	1480.8	1477.8	1419.5	1353.2	1158.1	1047.6
87.5°	52.2	103.5	156.8	148.8	200.1	280.5	349.8	205.1	143.7	52.2	72.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153194

CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6
2.5°	1044.6	1045.5	1046.5	1046.5	1051.6	1050.6	1051.6	1053.6	1056.6	1058.7	1060.6
5°	1052.5	1052.5	1056.6	1059.6	1065.6	1069.6	1071.7	1077.7	1084.8	1082.7	1088.8
7.5°	1078.8	1077.7	1081.8	1083.7	1088.8	1095.9	1094.8	1099.8	1105.9	1107.9	1112.8
10°	1113.9	1110.9	1110.9	1108.9	1109.8	1107.9	1107.9	1107.9	1111.9	1110.9	1114.9
12.5°	1150.1	1149.1	1147.0	1141.0	1141.0	1133.0	1129.0	1123.9	1122.9	1116.0	1116.9
15°	1224.5	1224.5	1220.4	1208.4	1198.3	1191.3	1181.2	1174.2	1164.1	1151.1	1144.0
17.5°	1333.1	1319.0	1314.0	1311.9	1295.9	1289.8	1267.7	1244.6	1233.6	1215.4	1205.4
20°	1465.8	1462.8	1442.6	1432.5	1412.4	1384.4	1356.2	1326.0	1307.9	1285.8	1273.8
22.5°	1615.5	1593.5	1583.4	1568.3	1537.1	1505.0	1462.8	1422.5	1394.4	1379.3	1370.3
25°	1790.5	1768.4	1758.3	1738.2	1700.0	1665.8	1613.6	1566.3	1541.1	1516.1	1502.0
27.5°	2022.7	2001.6	1989.5	1937.3	1924.1	1867.9	1803.5	1739.2	1706.0	1668.8	1644.7
30°	2369.5	2370.6	2308.2	2244.9	2179.6	2082.1	2014.7	1942.3	1888.0	1834.7	1781.5
32.5°	2955.6	2805.9	2690.3	2554.5	2412.7	2309.2	2225.8	2139.4	2063.9	1986.5	1898.0
35°	3313.6	3241.1	3091.4	2843.1	2700.3	2574.6	2482.2	2377.6	2285.1	2148.4	2013.7
37.5°	3717.7	3549.8	3367.9	3230.2	3068.3	2922.5	2767.7	2649.0	2489.2	2305.2	2114.2
40°	4307.8	4067.6	3848.4	3663.4	3454.3	3301.5	3128.6	2956.7	2744.6	2478.1	2215.8
42.5°	4924.0	4675.8	4386.2	4146.0	3899.7	3720.7	3506.5	3265.3	2953.7	2623.9	2303.2
45°	5570.5	5238.8	4891.9	4598.3	4342.0	4119.8	3854.4	3534.7	3154.7	2754.6	2384.7
47.5°	6207.9	5826.8	5413.7	5098.0	4764.2	4492.7	4167.0	3762.9	3311.5	2878.2	2466.0
50°	6769.8	6402.9	5905.3	5504.1	5166.3	4831.6	4425.4	3938.9	3435.2	2984.8	2539.5
52.5°	7254.4	6938.8	6415.0	5908.3	5519.3	5143.2	4633.6	4080.6	3559.9	3083.3	2599.8
55°	7610.3	7400.2	6917.6	6289.3	5829.8	5381.6	4809.4	4217.3	3677.5	3161.8	2639.0
57.5°	7878.8	7762.1	7347.9	6648.2	6115.4	5612.7	4991.4	4381.2	3794.1	3229.1	2657.1
60°	8025.5	8057.7	7673.7	6961.9	6367.8	5805.7	5173.4	4520.9	3880.5	3268.3	2647.0
62.5°	8011.4	8208.5	7917.9	7154.9	6514.5	5920.3	5296.1	4586.3	3868.5	3206.0	2555.5
63°	7984.2	8213.5	7945.1	7168.0	6523.5	5924.4	5299.1	4577.2	3843.3	3175.9	2519.4
65°	7750.1	8097.9	7922.0	7108.6	6443.1	5849.0	5235.8	4446.5	3666.4	3014.0	2333.4
67.5°	7122.7	7558.0	7507.8	6689.4	6062.1	5537.3	4912.0	4025.3	3229.1	2615.9	1977.5
70°	6086.2	6495.4	6504.5	5817.8	5294.0	4779.3	4259.6	3275.3	2559.6	2027.8	1474.8
72.5°	4664.7	4928.1	5019.6	4567.2	4216.4	3854.4	3388.0	2377.6	1824.7	1379.3	960.1
75°	3612.1	3539.8	3538.8	3347.8	3205.0	3028.1	2515.3	1604.5	1198.3	896.8	587.2
77.5°	3247.2	2925.5	2613.9	2384.7	2270.1	2210.7	1649.7	967.2	706.7	515.8	337.8
80°	2678.1	2203.6	1780.4	1533.2	1434.6	1503.0	919.9	522.8	387.0	293.6	219.2
82.5°	1846.7	1533.2	1165.2	965.1	828.4	866.6	470.5	267.5	179.0	163.8	135.8
85°	962.1	843.4	711.8	611.2	539.9	474.5	244.2	127.7	74.4	65.4	59.3
87.5°	0.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153194

CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6
2.5°	1063.6	1062.6	1064.7	1065.6	1068.7	1070.7	1071.7	1069.6	1072.6	1075.6	1073.7
5°	1091.8	1098.9	1099.8	1102.8	1102.8	1108.9	1108.9	1108.9	1107.9	1108.9	1106.8
7.5°	1116.0	1125.0	1126.0	1129.9	1131.0	1138.0	1135.0	1137.0	1137.0	1132.0	1129.9
10°	1119.0	1128.0	1133.0	1138.0	1145.1	1154.1	1154.1	1159.2	1159.2	1155.1	1154.1
12.5°	1119.9	1126.9	1132.0	1139.1	1149.1	1162.2	1169.2	1176.3	1179.3	1178.2	1175.2
15°	1141.0	1141.0	1142.1	1148.1	1155.1	1171.2	1181.2	1189.3	1194.3	1192.3	1187.3
17.5°	1196.4	1188.3	1182.3	1172.2	1174.2	1182.3	1188.3	1195.3	1196.4	1194.3	1186.3
20°	1260.7	1250.7	1235.5	1219.5	1211.4	1205.4	1201.3	1201.3	1198.3	1188.3	1175.2
22.5°	1352.1	1339.1	1318.0	1293.9	1277.7	1258.7	1235.5	1213.5	1189.3	1165.2	1137.0
25°	1478.9	1460.7	1438.7	1401.5	1367.3	1327.0	1279.8	1230.5	1173.3	1122.9	1081.8
27.5°	1606.5	1566.3	1509.0	1457.7	1394.4	1334.1	1266.7	1206.4	1133.0	1072.6	1027.5
30°	1712.0	1635.6	1553.3	1471.8	1388.4	1306.9	1226.5	1154.1	1073.7	1012.3	968.1
32.5°	1793.5	1688.0	1573.4	1466.7	1364.2	1264.7	1172.2	1091.8	1010.4	947.0	899.8
35°	1868.9	1722.1	1576.4	1444.7	1318.0	1214.4	1109.8	1022.4	936.0	869.6	818.3
37.5°	1925.2	1738.2	1558.2	1403.4	1257.6	1142.1	1035.4	946.0	857.5	785.2	726.8
40°	1961.3	1728.2	1519.1	1344.1	1186.3	1064.7	956.1	863.5	778.1	698.7	628.3
42.5°	1990.6	1715.1	1479.8	1289.8	1129.9	997.3	885.7	786.1	699.7	613.3	535.9
45°	2033.8	1725.2	1462.8	1251.6	1079.7	940.0	817.3	713.8	623.3	538.9	464.5
47.5°	2076.0	1730.2	1437.6	1204.4	1016.4	880.6	756.0	655.4	563.0	485.6	417.2
50°	2114.2	1727.2	1398.4	1144.0	955.0	821.3	700.7	600.2	508.7	437.3	373.0
52.5°	2132.3	1710.1	1350.2	1085.7	905.8	769.1	646.4	548.9	458.4	391.1	331.7
55°	2130.3	1665.8	1286.8	1030.5	851.5	713.8	593.2	496.6	415.2	352.8	301.6
57.5°	2100.1	1597.4	1219.5	969.1	780.1	645.4	530.8	437.3	368.9	316.7	273.5
60°	2036.8	1509.9	1131.0	879.7	690.7	560.9	453.4	373.0	317.7	277.5	249.3
62.5°	1918.1	1384.4	1020.4	755.0	570.1	451.4	357.9	305.6	264.4	240.3	227.3
63°	1883.0	1350.2	973.2	724.9	541.9	426.2	337.8	283.5	253.4	232.2	220.2
65°	1708.1	1182.3	814.3	585.1	421.2	328.7	271.4	230.3	212.1	203.1	202.1
67.5°	1383.3	929.9	576.1	401.1	286.5	237.3	208.1	191.0	183.0	180.9	183.0
70°	971.2	587.2	365.9	266.4	212.1	191.0	177.9	170.9	165.9	166.8	168.9
72.5°	619.3	351.8	251.3	202.1	179.0	167.9	161.9	159.9	158.9	157.8	157.8
75°	352.8	234.2	193.1	174.9	162.9	153.8	148.8	146.7	147.8	148.8	146.7
77.5°	233.3	193.1	171.9	159.9	148.8	138.8	135.8	134.7	136.7	138.8	138.8
80°	183.9	171.9	159.9	147.8	129.6	122.7	124.7	125.7	124.7	125.7	122.7
82.5°	129.6	127.7	130.7	125.7	107.6	101.6	99.5	100.5	98.5	98.5	96.5
85°	60.3	60.3	63.3	63.3	61.3	62.3	67.4	73.4	76.4	73.4	69.3
87.5°	0.0	0.0	0.0	0.0	0.0	9.0	18.1	26.1	28.2	35.2	34.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153194

CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6
2.5°	1070.7	1072.6	1071.7	1070.7	1072.6	1070.7	1071.7	1070.7	1070.7	1069.6	1069.6
5°	1104.9	1107.9	1101.9	1100.8	1098.9	1093.8	1093.8	1091.8	1091.8	1087.8	1084.8
7.5°	1126.9	1128.0	1122.9	1122.0	1116.9	1111.9	1107.9	1103.8	1102.8	1099.8	1093.8
10°	1148.1	1146.1	1142.1	1137.0	1132.0	1125.0	1119.9	1114.9	1113.9	1108.9	1101.9
12.5°	1166.2	1165.2	1157.1	1152.1	1144.0	1137.0	1131.0	1125.0	1122.0	1116.0	1105.9
15°	1178.2	1172.2	1162.2	1153.1	1144.0	1136.1	1129.0	1122.0	1119.0	1111.9	1101.9
17.5°	1173.3	1162.2	1149.1	1138.0	1126.0	1116.0	1109.8	1102.8	1097.8	1093.8	1079.7
20°	1155.1	1139.1	1119.0	1105.9	1089.7	1076.7	1072.6	1065.6	1061.7	1046.5	1028.5
22.5°	1107.9	1084.8	1059.6	1040.5	1022.4	1009.3	999.3	992.2	982.2	973.2	945.0
25°	1048.6	1022.4	996.3	973.2	949.0	928.9	910.8	893.8	888.7	869.6	842.5
27.5°	991.3	962.1	936.0	908.8	877.6	852.5	821.3	797.2	781.1	761.0	735.9
30°	929.9	900.7	865.6	829.4	793.2	766.0	730.9	701.8	681.7	660.5	637.4
32.5°	852.5	817.3	775.1	734.9	701.8	669.5	634.4	606.2	586.1	567.0	544.9
35°	764.0	717.8	672.5	628.3	593.2	566.0	534.8	513.7	499.7	482.6	459.5
37.5°	662.5	610.3	562.0	527.8	496.6	470.5	448.4	435.3	420.2	411.2	397.1
40°	560.0	508.7	461.5	430.3	404.1	389.0	377.0	374.0	363.9	351.8	342.8
42.5°	469.5	420.2	374.0	348.8	331.7	327.8	321.7	321.7	316.7	307.7	301.6
45°	408.2	356.9	316.7	298.5	289.5	288.5	285.5	285.5	284.5	280.5	273.5
47.5°	363.9	317.7	286.5	275.4	273.5	271.4	268.4	267.5	266.4	263.4	259.4
50°	323.7	284.5	264.4	259.4	260.4	257.4	254.3	251.3	250.4	247.4	243.3
52.5°	286.5	258.3	245.3	242.3	242.3	242.3	240.3	240.3	238.2	237.3	233.3
55°	265.4	244.2	237.3	236.3	235.2	234.2	232.2	232.2	230.3	229.2	224.1
57.5°	247.4	234.2	230.3	228.2	227.3	225.2	224.1	224.1	224.1	224.1	218.1
60°	233.3	227.3	226.2	224.1	223.2	219.2	217.1	216.2	217.1	218.1	212.1
62.5°	218.1	217.1	216.2	214.1	213.2	209.1	206.1	204.0	206.1	208.1	207.0
63°	214.1	213.2	213.2	212.1	211.1	206.1	203.1	201.0	203.1	205.1	205.1
65°	200.1	201.0	201.0	200.1	199.1	196.1	192.0	190.1	191.0	194.0	195.0
67.5°	185.0	186.0	185.0	186.0	185.0	183.0	180.0	177.9	176.9	177.9	179.0
70°	170.9	173.0	171.9	170.9	169.9	169.9	167.9	164.9	163.8	162.9	162.9
72.5°	158.9	158.9	156.8	156.8	155.9	155.9	153.8	150.8	149.8	149.8	147.8
75°	145.8	145.8	142.8	142.8	140.7	141.8	139.7	136.7	135.8	135.8	134.7
77.5°	137.7	134.7	129.6	128.7	127.7	127.7	126.6	123.6	122.7	122.7	121.7
80°	121.7	115.6	110.6	109.5	110.6	112.6	112.6	110.6	110.6	110.6	110.6
82.5°	94.5	92.5	89.4	87.5	87.5	90.5	94.5	96.5	98.5	100.5	100.5
85°	69.3	70.4	69.3	66.3	65.4	68.4	72.3	76.4	77.4	81.5	80.4
87.5°	37.2	38.2	35.2	34.2	37.2	39.2	43.2	44.2	46.2	47.3	48.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153194

CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6
2.5°	1068.7	1067.7	1068.7	1066.6	1066.6	1064.7	1062.6	1061.7	1059.6	1058.7	1056.6
5°	1086.7	1083.7	1080.7	1079.7	1075.6	1071.7	1068.7	1063.6	1059.6	1052.5	1050.6
7.5°	1098.9	1091.8	1087.8	1086.7	1080.7	1077.7	1070.7	1064.7	1058.7	1049.5	1046.5
10°	1103.8	1096.8	1089.7	1086.7	1079.7	1074.7	1067.7	1058.7	1053.6	1044.6	1042.5
12.5°	1109.8	1096.8	1085.7	1077.7	1067.7	1056.6	1049.5	1044.6	1037.5	1032.4	1030.5
15°	1098.9	1081.8	1064.7	1049.5	1033.5	1021.5	1014.4	1006.3	998.2	995.2	995.2
17.5°	1068.7	1046.5	1017.4	998.2	981.2	968.1	959.1	951.1	950.1	946.0	948.0
20°	1006.3	977.2	949.0	934.9	924.9	916.9	907.8	903.8	900.7	894.7	892.7
22.5°	919.9	895.8	875.6	865.6	857.5	847.5	839.5	827.4	824.4	818.3	815.3
25°	824.4	805.3	788.2	781.1	776.1	762.1	757.0	740.9	729.8	722.8	726.8
27.5°	728.9	714.8	698.7	689.6	686.6	673.6	668.5	650.5	641.3	641.3	631.3
30°	630.4	617.3	607.3	597.2	595.1	579.1	566.0	559.0	548.9	544.9	537.8
32.5°	537.8	524.8	516.8	511.7	503.6	490.6	477.5	465.5	449.4	443.3	440.3
35°	452.4	442.4	432.3	428.3	417.2	403.1	387.0	377.0	357.9	350.9	347.9
37.5°	387.0	375.0	368.0	356.9	345.8	330.8	318.7	309.6	302.6	299.6	299.6
40°	334.8	325.7	317.7	308.6	299.6	291.5	285.5	283.5	282.5	282.5	284.5
42.5°	295.5	287.6	283.5	278.4	275.4	275.4	274.4	275.4	276.5	277.5	280.5
45°	269.4	264.4	262.4	261.3	263.4	265.4	266.4	268.4	272.4	274.4	275.4
47.5°	255.3	251.3	250.4	251.3	254.3	258.3	262.4	265.4	268.4	269.4	270.5
50°	241.2	236.3	234.2	236.3	240.3	246.3	249.3	254.3	256.4	258.3	256.4
52.5°	229.2	225.2	224.1	224.1	228.2	232.2	236.3	240.3	241.2	241.2	240.3
55°	219.2	216.2	213.2	215.1	218.1	222.2	228.2	231.2	233.3	234.2	234.2
57.5°	211.1	208.1	205.1	207.0	210.2	214.1	220.2	223.2	225.2	228.2	229.2
60°	205.1	201.0	198.0	201.0	204.0	210.2	215.1	218.1	223.2	224.1	224.1
62.5°	199.1	195.0	190.1	193.1	193.1	196.1	201.0	205.1	210.2	212.1	212.1
63°	198.0	194.0	189.0	191.0	191.0	193.1	197.0	201.0	207.0	209.1	208.1
65°	190.1	189.0	183.9	183.9	182.0	183.9	186.9	191.0	194.0	197.0	197.0
67.5°	176.9	176.0	174.9	174.9	174.9	176.9	179.0	182.0	185.0	186.9	186.0
70°	161.9	161.9	161.9	162.9	162.9	164.9	165.9	164.9	167.9	169.9	168.9
72.5°	148.8	147.8	146.7	148.8	147.8	147.8	149.8	148.8	151.8	151.8	152.8
75°	134.7	133.7	133.7	134.7	132.7	130.7	131.7	131.7	132.7	132.7	134.7
77.5°	122.7	122.7	122.7	121.7	119.6	118.7	117.6	117.6	117.6	117.6	118.7
80°	111.6	111.6	111.6	110.6	108.6	106.5	104.6	103.5	102.6	97.5	97.5
82.5°	100.5	100.5	100.5	100.5	99.5	97.5	94.5	86.4	82.5	78.4	79.4
85°	79.4	81.5	83.4	86.4	85.5	85.5	79.4	69.3	63.3	59.3	60.3
87.5°	51.3	45.3	45.3	44.2	42.2	40.2	40.2	34.2	28.2	25.2	26.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153194
CATALOG NUMBER: AVS-F04-LED-E-U-SLL-7030

REPORT N
CATALOG

CANDELA DISTRIBUTION (continued):

CANDELA

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°	
0°	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	0°
2.5°	1056.6	1054.6	1052.5	1052.5	1049.5	1049.5	1047.6	1051.6	1047.6	1044.6	1044.6	2.5°
5°	1048.6	1046.5	1040.5	1039.5	1035.4	1035.4	1035.4	1033.5	1033.5	1031.5	1030.5	5°
7.5°	1043.5	1038.5	1033.5	1030.5	1030.5	1028.5	1032.4	1030.5	1031.5	1031.5	1032.4	7.5°
10°	1039.5	1035.4	1033.5	1032.4	1032.4	1035.4	1038.5	1039.5	1038.5	1039.5	1039.5	10°
12.5°	1029.4	1031.5	1032.4	1036.5	1041.6	1047.6	1054.6	1055.5	1057.6	1057.6	1059.6	12.5°
15°	997.3	1002.3	1008.3	1018.4	1031.5	1044.6	1057.6	1068.7	1078.8	1083.7	1087.8	15°
17.5°	952.0	957.1	968.1	979.2	996.3	1015.3	1037.5	1056.6	1077.7	1096.8	1116.0	17.5°
20°	890.7	898.8	901.8	921.9	942.0	968.1	994.3	1024.5	1060.6	1096.8	1134.0	20°
22.5°	811.3	820.3	834.4	850.5	871.6	903.8	934.9	982.2	1030.5	1081.8	1140.0	22.5°
25°	722.8	732.8	745.0	762.1	783.1	817.3	862.6	912.8	972.1	1039.5	1111.9	25°
27.5°	631.3	641.3	651.4	663.5	687.7	723.8	777.1	829.4	894.7	968.1	1052.5	27.5°
30°	539.9	540.8	546.9	562.0	587.2	634.4	673.6	739.0	807.3	884.7	982.2	30°
32.5°	439.4	438.3	445.4	458.4	482.6	527.8	576.1	639.4	706.7	804.2	904.8	32.5°
35°	349.8	349.8	362.9	376.0	403.1	435.3	477.5	533.8	613.3	703.7	804.2	35°
37.5°	302.6	309.6	317.7	330.8	351.8	377.0	414.2	463.4	525.8	612.2	704.8	37.5°
40°	287.6	291.5	298.5	310.7	328.7	351.8	379.0	416.2	464.5	533.8	618.2	40°
42.5°	281.5	282.5	286.5	295.5	311.6	334.8	362.9	396.1	432.3	481.6	554.9	42.5°
45°	275.4	274.4	276.5	283.5	296.6	322.7	354.9	391.1	427.3	468.5	528.8	45°
47.5°	270.5	270.5	270.5	273.5	285.5	311.6	348.8	391.1	434.3	480.5	539.9	47.5°
50°	256.4	255.3	255.3	257.4	266.4	294.6	338.8	390.1	446.3	506.6	574.0	50°
52.5°	240.3	240.3	241.2	242.3	250.4	278.4	327.8	390.1	460.4	540.8	625.3	52.5°
55°	235.2	236.3	237.3	236.3	242.3	266.4	315.6	384.0	466.4	568.0	680.6	55°
57.5°	231.2	233.3	233.3	232.2	236.3	256.4	303.6	372.0	461.5	578.0	719.8	57.5°
60°	225.2	225.2	225.2	222.2	224.1	242.3	285.5	352.8	445.4	569.0	725.8	60°
62.5°	212.1	212.1	210.2	209.1	208.1	222.2	261.3	324.8	416.2	544.9	710.8	62.5°
63°	209.1	208.1	208.1	205.1	205.1	218.1	256.4	320.7	408.2	538.9	704.8	63°
65°	198.0	198.0	198.0	196.1	195.0	205.1	236.3	292.5	377.0	510.7	674.6	65°
67.5°	186.0	186.9	185.0	183.9	183.0	189.0	213.2	257.4	328.7	451.4	618.2	67.5°
70°	168.9	169.9	169.9	168.9	167.9	171.9	186.9	221.1	272.4	376.0	526.8	70°
72.5°	153.8	155.9	155.9	157.8	157.8	160.8	166.8	183.9	218.1	293.6	414.2	72.5°
75°	137.7	138.8	140.7	142.8	140.7	139.7	140.7	153.8	170.9	217.1	295.5	75°
77.5°	123.6	126.6	126.6	125.7	122.7	120.6	120.6	126.6	140.7	164.9	211.1	77.5°
80°	102.6	107.6	108.6	105.6	102.6	102.6	104.6	108.6	117.6	135.8	159.9	80°
82.5°	82.5	87.5	88.5	89.4	88.5	91.5	91.5	92.5	97.5	111.6	130.7	82.5°
85°	63.3	67.4	70.4	71.4	72.3	73.4	72.3	67.4	70.4	79.4	88.5	85°
87.5°	28.2	29.1	27.2	28.2	27.2	28.2	29.1	24.1	23.1	31.2	32.1	87.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	90°



NUMBER: P153194

NUMBER: AVS-F04-LED-E-U-SLL-7030

DISTRIBUTION (continued):

330°	335°	340°	345°	350°	355°	360°
1054.6	1054.6	1054.6	1054.6	1054.6	1054.6	1054.6
1043.5	1043.5	1044.6	1042.5	1042.5	1043.5	1040.5
1027.5	1031.5	1031.5	1031.5	1029.4	1031.5	1032.4
1031.5	1034.5	1036.5	1036.5	1035.4	1039.5	1042.5
1036.5	1041.6	1043.5	1043.5	1043.5	1048.6	1055.5
1055.5	1059.6	1062.6	1062.6	1064.7	1070.7	1078.8
1090.8	1095.9	1095.9	1094.8	1100.8	1107.9	1116.9
1129.9	1144.0	1151.1	1150.1	1155.1	1164.1	1174.2
1167.2	1206.4	1223.5	1235.5	1240.6	1252.6	1255.6
1198.3	1263.7	1311.0	1351.2	1370.3	1382.3	1396.4
1187.3	1275.8	1360.2	1442.6	1500.9	1560.3	1585.4
1142.1	1252.6	1363.2	1483.8	1589.4	1695.0	1771.4
1086.7	1219.5	1368.3	1539.2	1706.0	1867.9	1996.6
1023.4	1188.3	1379.3	1590.5	1809.5	2021.7	2207.7
944.0	1129.0	1352.1	1595.4	1853.8	2111.2	2352.4
843.4	1048.6	1288.8	1559.3	1855.9	2150.4	2439.0
742.9	947.0	1208.4	1506.9	1829.7	2159.5	2493.2
672.5	856.6	1126.9	1440.6	1787.5	2145.4	2519.4
624.4	791.2	1054.6	1380.3	1742.2	2120.2	2523.3
620.3	763.0	1007.4	1336.1	1706.0	2098.1	2523.3
654.5	778.1	991.3	1314.0	1691.0	2091.1	2525.4
718.8	838.4	1020.4	1331.1	1703.0	2100.1	2534.4
796.2	929.9	1098.9	1390.4	1754.3	2130.3	2554.5
866.6	1035.4	1232.5	1505.0	1847.8	2206.7	2610.8
907.8	1126.0	1374.3	1665.8	2007.7	2358.4	2723.4
912.8	1176.3	1499.9	1840.7	2201.7	2532.4	2903.4
908.8	1180.2	1516.1	1873.9	2242.9	2575.6	2965.7
886.7	1181.2	1561.2	1990.6	2385.6	2757.6	3139.6
830.4	1149.1	1577.3	2082.1	2565.6	2996.9	3464.4
732.8	1057.6	1530.2	2084.0	2634.9	3130.6	3669.4
589.1	883.7	1326.0	1896.1	2452.0	2998.9	3616.2
431.3	649.4	1002.3	1468.8	2000.6	2496.3	3097.4
286.5	420.2	675.5	1046.5	1434.6	1796.5	2229.8
197.0	260.4	395.1	629.3	877.6	1053.6	1420.5
144.8	171.9	219.2	321.7	422.3	519.8	742.0
90.5	98.5	109.5	158.9	227.3	306.6	462.5
24.1	25.2	23.1	31.2	49.2	47.3	52.2
0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)