

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147586

Luminaire Tested: **AVS-F03-LED-E-U-5MQ-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P147586
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F03-LED-E-U-5MQ-7050
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM
Light Source: (21) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8192.3 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B3 - U0 - G1

Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P147586

CATALOG NUMBER: AVS-F03-LED-E-U-5MQ-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 6.2 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P147586

CATALOG NUMBER: AVS-F03-LED-E-U-5MQ-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P147586

CATALOG NUMBER: AVS-F03-LED-E-U-5MQ-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4096.2	0.0	4096.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4096.2	0.0	4096.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	8192.3	0.0	8192.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	0.7
10°-20°	184.2	2.2
20°-30°	356.2	4.3
30°-40°	689.7	8.4
40°-50°	1245.3	15.2
50°-60°	2165.3	26.4
60°-70°	2458.2	30.0
70°-80°	953.0	11.6
80°-90°	86.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8192.3	100.0
0°-180°	8192.3	100.0

Coefficient of Utilization



REPORT NUMBER: P147586


CATALOG NUMBER: AVS-F03-LED-E-U-5MQ-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	297.5	3.6			
FM	(30°-60°)	2050.1	25.0			
FH	(60°-80°)	1705.6	20.8			G1/1800
FVH	(80°-90°)	43.0	0.5			G1/100
BL	(0°-30°)	297.5	3.6	B1/500		
BM	(30°-60°)	2050.1	25.0	B2/2500		
BH	(60°-80°)	1705.6	20.8	B3/2500		G1/1800
BVH	(80°-90°)	43.0	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1

Type V Short





REPORT NUMBER: P147586

CATALOG NUMBER: AVS-F03-LED-E-U-5MQ-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8
2.5°	547.2	548.9	548.5	547.6	547.6	547.6	547.2	545.9	545.5	546.3	547.2
5°	560.0	560.0	560.0	560.0	559.1	559.1	558.1	557.3	557.8	556.9	556.5
7.5°	579.5	578.1	578.1	577.6	577.7	576.9	575.5	573.9	574.3	573.9	573.5
10°	602.3	602.7	601.5	602.7	600.6	600.2	598.4	597.6	597.2	595.9	595.9
12.5°	629.8	628.6	628.5	627.7	626.8	625.9	623.4	623.0	621.3	620.5	619.3
15°	655.6	655.2	653.5	651.8	651.4	650.6	647.7	645.9	645.4	643.3	641.7
17.5°	681.6	680.6	678.5	677.7	676.0	674.6	672.2	669.6	668.4	667.6	665.4
20°	709.0	708.2	706.0	704.4	702.2	700.5	696.8	694.5	693.3	692.0	690.4
22.5°	743.3	741.6	738.2	735.3	730.6	728.9	723.8	720.8	718.8	717.1	716.3
25°	780.5	781.0	776.4	772.5	767.0	762.4	756.1	752.6	750.5	748.8	748.4
27.5°	827.2	827.7	823.4	817.8	809.3	804.4	795.9	791.5	790.3	788.6	788.2
30°	900.9	897.0	889.8	881.0	873.4	862.4	850.1	845.8	841.6	840.3	840.3
32.5°	1036.5	1034.2	1028.4	1006.3	996.2	973.3	951.7	939.5	925.4	918.7	914.4
35°	1131.3	1130.4	1125.8	1118.1	1111.7	1107.2	1094.4	1092.2	1089.7	1089.7	1093.2
37.5°	1201.1	1196.1	1195.2	1196.5	1194.8	1195.6	1205.8	1219.8	1231.7	1237.5	1236.7
40°	1304.5	1297.3	1301.5	1298.5	1294.7	1293.9	1297.3	1302.8	1308.3	1308.3	1306.9
42.5°	1439.6	1443.0	1444.8	1432.4	1424.4	1422.3	1430.3	1428.6	1434.1	1431.9	1426.5
45°	1640.4	1638.2	1635.2	1620.4	1607.8	1597.5	1599.8	1596.8	1597.1	1593.8	1589.5
47.5°	1842.8	1849.9	1837.7	1830.5	1816.2	1808.9	1814.9	1809.7	1819.5	1801.8	1793.3
50°	2039.4	2044.4	2040.2	2030.1	2030.1	2040.2	2047.4	2056.7	2070.3	2049.9	2019.5
52.5°	2200.2	2204.6	2210.9	2219.3	2240.1	2261.7	2292.2	2324.8	2350.7	2346.8	2312.1
55°	2298.4	2303.6	2314.2	2343.4	2380.7	2437.4	2506.5	2582.4	2641.6	2670.5	2645.0
57.5°	2331.6	2335.3	2364.1	2399.4	2457.4	2541.7	2657.2	2788.2	2902.1	2974.5	2963.1
60°	2323.9	2323.9	2353.2	2401.5	2482.8	2594.6	2758.1	2939.4	3113.8	3222.3	3206.2
62.5°	2243.9	2248.1	2290.1	2348.1	2446.3	2580.1	2774.9	3006.7	3215.5	3350.2	3337.0
65°	2068.6	2071.5	2116.9	2185.9	2295.5	2454.0	2666.9	2923.7	3163.0	3292.6	3268.0
67.5°	1785.3	1788.2	1825.1	1903.0	2019.1	2184.7	2414.6	2697.1	2931.3	3033.8	2960.1
70°	1420.1	1428.6	1452.3	1534.9	1623.0	1785.3	1996.9	2279.5	2500.5	2597.5	2516.2
72.5°	967.8	989.4	1018.2	1091.4	1175.8	1310.5	1479.0	1717.0	1894.5	2006.7	1934.3
75°	545.1	575.5	584.5	640.0	709.4	815.8	939.0	1109.6	1288.8	1379.9	1292.6
77.5°	235.4	260.4	271.5	297.4	351.5	396.1	471.0	586.1	724.7	788.6	683.9
80°	116.1	122.1	126.6	134.7	149.8	164.4	199.9	250.4	307.0	321.5	255.9
82.5°	89.7	94.1	102.1	108.4	112.2	116.1	119.5	126.2	131.8	134.7	127.0
85°	63.1	68.6	77.5	84.8	88.9	91.9	94.9	97.0	91.9	83.9	88.1
87.5°	16.6	21.6	30.1	32.5	36.9	39.1	38.1	39.4	35.5	25.9	28.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147586

CATALOG NUMBER: AVS-F03-LED-E-U-5MQ-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8
2.5°	546.7	546.3	546.8	546.7	546.8	546.3	546.3	546.3
5°	556.5	556.5	556.9	556.1	556.2	556.5	556.1	555.6
7.5°	573.1	572.6	572.6	572.2	572.6	572.2	572.2	571.8
10°	595.0	594.2	594.6	593.4	593.4	593.0	593.0	593.0
12.5°	618.9	617.5	617.9	616.7	614.5	614.9	615.3	615.0
15°	641.7	640.4	639.2	638.3	637.0	637.4	637.4	637.0
17.5°	665.0	662.4	662.0	660.7	660.3	660.3	660.3	660.7
20°	689.1	687.5	687.0	685.7	685.3	686.6	687.0	686.1
22.5°	714.9	714.1	714.9	714.1	715.3	716.3	716.7	715.8
25°	747.6	746.7	748.0	750.9	752.6	753.5	755.6	754.7
27.5°	789.4	788.6	791.6	795.9	798.3	802.6	804.8	805.6
30°	843.7	847.5	849.2	857.6	859.3	866.1	866.1	869.1
32.5°	922.5	929.7	942.4	955.4	973.7	986.8	986.8	993.6
35°	1095.3	1098.2	1108.0	1110.1	1114.0	1118.1	1114.0	1117.3
37.5°	1227.9	1214.7	1205.4	1192.3	1184.2	1184.2	1185.1	1184.2
40°	1295.5	1290.6	1286.2	1275.2	1273.6	1273.2	1273.2	1274.8
42.5°	1416.8	1404.5	1397.7	1388.4	1385.4	1384.5	1384.0	1385.0
45°	1574.3	1554.4	1536.2	1526.8	1518.8	1511.2	1513.8	1513.7
47.5°	1757.7	1726.8	1697.1	1681.0	1667.0	1660.7	1656.5	1655.2
50°	1980.9	1937.6	1899.6	1869.4	1849.1	1848.7	1850.9	1837.3
52.5°	2254.5	2186.3	2138.9	2098.2	2079.2	2077.0	2070.3	2062.6
55°	2557.7	2476.9	2398.5	2354.8	2329.9	2316.3	2308.3	2295.5
57.5°	2870.4	2761.5	2648.8	2578.9	2534.8	2504.5	2488.3	2481.0
60°	3111.3	2962.7	2814.0	2701.8	2628.4	2583.2	2555.2	2543.7
62.5°	3206.2	3004.6	2814.0	2666.5	2560.7	2498.0	2460.3	2443.8
65°	3093.1	2854.2	2637.3	2474.7	2356.6	2286.6	2245.6	2227.8
67.5°	2777.2	2566.2	2330.4	2168.5	2046.9	1977.9	1933.5	1920.3
70°	2328.2	2112.6	1887.3	1742.8	1634.4	1578.0	1531.9	1526.4
72.5°	1749.6	1563.7	1370.6	1251.2	1163.9	1070.7	1047.0	1058.9
75°	1121.6	947.5	775.5	668.0	588.3	499.3	465.1	473.5
77.5°	531.1	411.2	297.0	229.5	192.7	164.8	157.5	153.4
80°	196.9	159.7	141.0	133.8	128.7	124.1	120.6	116.9
82.5°	127.5	124.6	120.7	119.4	115.6	109.6	98.7	94.0
85°	95.3	95.3	90.2	90.7	87.7	80.0	69.8	64.4
87.5°	28.0	25.0	22.8	21.1	20.7	18.7	13.6	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)