

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148092

Luminaire Tested: **AVS-E02-LED-E-U-5WQ-7060**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148092
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-5WQ-7060
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (42) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6533.8 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G1

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148092

CATALOG NUMBER: AVS-E02-LED-E-U-5WQ-7060

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.9 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P148092

CATALOG NUMBER: AVS-E02-LED-E-U-5WQ-7060

Luminous Intensity Polar Plot



REPORT NUMBER: P148092

CATALOG NUMBER: AVS-E02-LED-E-U-5WQ-7060


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3266.9	0.0	3266.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3266.9	0.0	3266.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	6533.8	0.0	6533.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.1	0.5
10°-20°	120.3	1.8
20°-30°	243.6	3.7
30°-40°	408.4	6.3
40°-50°	720.4	11.0
50°-60°	1270.5	19.4
60°-70°	1939.6	29.7
70°-80°	1620.8	24.8
80°-90°	176.1	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6533.8	100.0
0°-180°	6533.8	100.0

Coefficient of Utilization



REPORT NUMBER: P148092


CATALOG NUMBER: AVS-E02-LED-E-U-5WQ-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	199.0	3.0			
FM	(30°-60°)	1199.7	18.4			
FH	(60°-80°)	1780.2	27.2			G1/1800
FVH	(80°-90°)	88.1	1.3			G1/100
BL	(0°-30°)	199.0	3.0	B1/500		
BM	(30°-60°)	1199.7	18.4	B2/2500		
BH	(60°-80°)	1780.2	27.2	B3/2500		G1/1800
BVH	(80°-90°)	88.1	1.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1

Type V Short





REPORT NUMBER: P148092

CATALOG NUMBER: AVS-E02-LED-E-U-5WQ-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3
2.5°	342.1	342.7	342.1	342.1	342.1	342.1	342.1	341.3	341.3	341.3	342.1
5°	348.9	349.5	348.9	349.5	349.5	349.5	349.5	348.9	348.9	348.9	348.9
7.5°	359.8	359.8	359.8	360.5	359.8	359.8	360.5	359.8	359.8	359.8	359.8
10°	375.5	374.9	374.9	374.9	374.9	374.9	375.5	375.5	375.5	374.9	374.9
12.5°	394.7	394.0	394.7	394.7	395.4	395.4	395.4	395.4	395.4	395.4	394.7
15°	417.9	417.9	417.9	418.7	420.0	420.0	419.4	420.0	420.0	420.0	420.0
17.5°	443.9	445.3	443.9	444.7	445.3	444.7	446.0	446.7	447.4	446.7	444.7
20°	470.7	471.3	471.3	471.3	471.3	472.6	473.4	473.4	475.4	474.7	474.1
22.5°	496.0	497.3	497.3	498.0	498.0	500.1	500.1	500.1	501.5	502.8	501.5
25°	522.6	522.0	522.0	523.3	524.0	526.7	526.7	528.1	530.2	530.9	529.4
27.5°	546.5	545.9	545.9	548.0	548.6	552.0	552.0	554.8	556.2	556.8	555.4
30°	571.9	571.9	571.2	573.3	575.3	578.0	579.4	582.2	584.1	584.9	583.5
32.5°	602.0	600.6	601.3	602.7	604.0	606.7	608.8	612.2	615.0	615.6	614.3
35°	636.2	634.1	634.8	636.2	638.2	642.4	645.8	647.8	651.9	653.3	650.6
37.5°	673.8	674.5	673.8	677.2	680.6	685.4	689.5	692.2	696.4	698.4	696.4
40°	727.2	725.1	727.2	730.6	736.1	742.2	750.5	752.4	756.6	760.7	755.9
42.5°	796.3	794.9	799.7	802.4	808.6	815.4	825.7	831.2	837.3	840.0	836.0
45°	886.5	886.5	892.0	892.7	902.3	911.2	925.6	932.4	944.0	944.0	944.0
47.5°	986.4	990.6	994.0	1000.8	1007.7	1024.0	1038.4	1053.5	1064.5	1065.8	1063.7
50°	1089.7	1093.8	1104.0	1113.7	1128.7	1149.2	1165.0	1184.8	1194.4	1202.6	1199.9
52.5°	1203.9	1204.7	1217.0	1229.2	1251.2	1273.8	1299.1	1319.6	1336.7	1344.2	1338.0
55°	1329.1	1330.5	1341.5	1354.5	1379.1	1405.1	1436.6	1457.7	1479.7	1493.4	1483.1
57.5°	1464.6	1465.3	1476.3	1491.9	1521.3	1547.4	1577.5	1607.6	1628.1	1640.4	1633.6
60°	1614.4	1617.8	1626.0	1645.9	1673.9	1701.2	1731.4	1758.0	1782.0	1795.0	1788.2
62.5°	1774.5	1777.9	1789.5	1805.3	1829.8	1860.0	1888.7	1922.9	1942.8	1957.1	1946.8
65°	1881.9	1888.1	1906.5	1927.7	1963.9	2003.0	2036.5	2083.0	2106.9	2124.0	2114.5
67.5°	1888.7	1892.1	1914.7	1946.8	1995.4	2054.3	2122.7	2195.2	2242.4	2265.0	2248.5
69°	1842.2	1846.9	1868.9	1905.2	1959.2	2027.6	2109.0	2199.3	2271.8	2305.3	2289.5
70°	1789.5	1799.8	1823.7	1863.4	1916.1	1987.9	2072.0	2168.5	2253.4	2299.2	2287.6
72.5°	1678.8	1681.5	1697.2	1728.6	1769.0	1828.5	1907.9	1998.9	2079.6	2145.3	2154.8
75°	1489.9	1498.8	1510.5	1531.6	1552.1	1595.2	1648.6	1710.9	1758.0	1808.7	1810.8
77.5°	1126.0	1152.6	1161.6	1166.3	1175.2	1209.4	1256.0	1309.9	1349.0	1357.2	1355.9
80°	505.5	541.1	549.3	588.3	612.2	669.0	740.2	822.9	878.3	884.5	869.4
82.5°	99.2	106.0	123.8	154.6	210.7	244.2	290.8	348.9	402.3	433.1	414.5
85°	32.8	34.9	40.3	44.5	51.3	58.1	70.5	87.6	108.8	120.4	107.4
87.5°	13.0	13.0	15.0	16.4	17.8	17.8	17.8	16.4	15.8	13.0	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148092

CATALOG NUMBER: AVS-E02-LED-E-U-5WQ-7060

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3
2.5°	341.3	341.3	341.3	341.3	341.3	341.3	341.3	341.3
5°	348.9	348.2	348.2	347.5	347.5	347.5	347.5	347.5
7.5°	359.2	358.4	357.7	358.4	357.7	357.7	357.7	357.7
10°	374.9	373.5	372.8	372.1	372.1	372.1	371.4	371.4
12.5°	393.4	393.4	392.6	392.0	390.6	391.3	390.6	389.2
15°	418.7	417.3	416.6	416.0	414.5	414.5	414.5	413.9
17.5°	443.9	442.6	442.6	440.5	439.9	439.9	439.9	440.5
20°	472.0	469.9	468.6	467.3	465.8	466.5	465.2	466.5
22.5°	500.1	497.3	496.0	493.9	491.8	491.8	491.2	489.8
25°	527.5	524.0	522.6	520.6	517.8	517.8	516.5	515.1
27.5°	553.4	549.9	548.6	544.6	541.8	541.1	539.7	539.1
30°	582.2	578.0	576.0	571.9	567.8	567.0	565.1	565.1
32.5°	612.2	608.2	606.7	600.6	597.2	597.2	595.9	594.5
35°	649.8	643.7	642.4	636.2	631.4	631.4	630.1	630.7
37.5°	694.3	689.5	684.8	680.0	674.5	673.8	672.4	671.1
40°	753.9	748.4	742.9	736.1	731.3	729.9	727.9	727.2
42.5°	833.2	827.8	816.8	811.3	806.5	802.4	801.8	801.0
45°	934.4	927.6	920.1	909.8	903.6	894.7	893.4	889.9
47.5°	1056.2	1043.2	1030.3	1021.3	1011.7	1001.5	999.4	994.0
50°	1185.5	1175.2	1153.4	1139.0	1123.9	1113.7	1106.8	1104.8
52.5°	1324.4	1305.2	1283.3	1264.1	1242.3	1228.6	1216.3	1212.8
55°	1469.4	1442.0	1414.6	1392.1	1370.2	1353.8	1342.2	1336.7
57.5°	1614.4	1584.4	1554.2	1529.5	1511.1	1489.9	1478.2	1475.5
60°	1765.6	1736.9	1706.1	1681.5	1658.9	1640.4	1633.6	1620.5
62.5°	1925.7	1895.5	1866.8	1842.9	1814.2	1801.1	1789.5	1782.0
65°	2083.0	2048.1	2011.8	1986.5	1957.8	1939.4	1925.0	1914.7
67.5°	2204.8	2152.1	2103.5	2061.1	2022.1	1993.4	1974.9	1965.3
69°	2239.0	2173.3	2111.1	2055.6	2009.8	1977.6	1957.1	1947.6
70°	2234.8	2162.4	2094.0	2033.1	1983.1	1948.9	1929.1	1911.3
72.5°	2108.3	2042.0	1966.0	1899.7	1854.5	1821.7	1801.9	1792.2
75°	1799.1	1754.6	1699.9	1648.6	1615.8	1596.6	1572.0	1572.6
77.5°	1309.9	1311.4	1274.4	1221.8	1184.8	1177.9	1167.0	1156.1
80°	812.6	747.7	705.3	648.5	606.7	570.5	554.8	520.6
82.5°	374.9	292.7	227.2	171.7	132.0	103.3	90.3	73.9
85°	83.4	63.6	52.6	42.4	36.3	33.5	27.4	25.3
87.5°	11.6	10.3	9.5	8.9	7.6	5.5	4.1	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)