

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155821

Luminaire Tested: **AVS-E02-LED-E-U-T3-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155821
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-T3-7050
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (42) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6328.9 lumens
Efficiency: N/A
Efficacy: 121.5 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P155821

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 6.8 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155821

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P155821

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2185.6	0.0	2185.6
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	4143.3	0.0	4143.3
	% Fixture	65.5	0.0	65.5
Total	Lumens	6328.9	0.0	6328.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	1.0
10°-20°	192.8	3.0
20°-30°	331.3	5.2
30°-40°	538.0	8.5
40°-50°	898.2	14.2
50°-60°	1414.3	22.3
60°-70°	1928.6	30.5
70°-80°	834.9	13.2
80°-90°	125.5	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6328.9	100.0
0°-180°	6328.9	100.0

Coefficient of Utilization



REPORT NUMBER: P155821


CATALOG NUMBER: AVS-E02-LED-E-U-T3-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	296.1	4.7			
FM	(30°-60°)	1767.4	27.9			
FH	(60°-80°)	1976.7	31.2			G2/5000
FVH	(80°-90°)	103.1	1.6			G2/225
BL	(0°-30°)	293.4	4.6	B1/500		
BM	(30°-60°)	1083.0	17.1	B2/2500		
BH	(60°-80°)	786.7	12.4	B2/1000		G2/1000
BVH	(80°-90°)	22.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P155821

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0
2.5°	684.8	687.5	684.8	685.4	686.1	685.4	684.8	684.8	682.7	684.0	685.4
5°	682.0	684.0	683.4	684.0	684.8	684.0	683.4	684.0	682.7	683.4	685.4
7.5°	678.5	677.9	678.5	680.0	681.3	681.3	681.3	682.0	681.3	681.3	683.4
10°	668.3	669.0	670.4	672.4	673.2	675.1	675.1	677.2	677.9	679.3	682.0
12.5°	655.3	656.1	657.4	658.8	662.2	665.6	665.6	670.4	672.4	675.9	680.6
15°	645.8	646.4	647.8	649.2	651.9	655.3	657.4	662.9	666.3	672.4	679.3
17.5°	651.2	650.6	651.9	652.6	652.6	655.3	655.3	659.5	663.5	669.0	677.9
20°	666.9	666.9	668.3	668.3	667.7	669.0	666.3	666.3	666.9	669.7	675.9
22.5°	682.7	682.0	684.8	686.1	686.8	688.8	686.1	685.4	682.0	680.0	682.0
25°	697.7	697.1	700.5	702.6	706.0	708.0	708.0	708.0	705.3	701.9	699.8
27.5°	721.0	721.0	724.5	726.5	729.2	733.4	735.3	735.3	736.1	731.3	727.9
30°	760.0	760.7	761.3	764.1	766.8	768.2	771.0	773.0	775.0	772.3	766.8
32.5°	806.5	802.4	802.4	806.5	809.9	814.1	815.4	818.1	822.3	820.2	819.5
35°	862.0	860.5	859.2	860.5	864.7	869.4	874.9	879.7	877.0	881.0	879.1
37.5°	944.0	945.4	946.1	946.1	945.4	946.7	949.5	954.3	953.0	954.3	957.0
40°	1079.5	1074.7	1069.8	1070.6	1063.7	1065.1	1054.2	1059.0	1059.6	1054.8	1056.9
42.5°	1214.9	1217.6	1219.7	1225.2	1220.4	1217.6	1207.4	1207.4	1201.9	1197.1	1195.8
45°	1361.3	1366.7	1367.5	1378.4	1374.3	1383.2	1390.7	1388.7	1379.8	1379.1	1369.5
47.5°	1478.2	1487.2	1496.8	1509.7	1520.0	1539.8	1563.1	1574.7	1581.6	1587.0	1576.1
50°	1565.8	1569.9	1594.6	1615.1	1637.6	1670.5	1702.7	1744.4	1777.9	1793.7	1808.7
52.5°	1613.1	1623.3	1649.9	1682.2	1721.8	1771.1	1823.0	1889.4	1946.8	1985.2	2019.4
55°	1623.3	1633.6	1663.6	1704.7	1758.8	1825.1	1899.7	1989.9	2076.2	2150.1	2221.9
57.5°	1594.6	1606.2	1638.3	1685.6	1749.1	1829.8	1923.6	2042.0	2160.9	2280.7	2386.7
60°	1541.9	1556.3	1585.7	1632.2	1702.7	1793.7	1905.8	2054.3	2221.1	2404.5	2607.7
62.5°	1455.0	1470.1	1497.4	1548.7	1621.2	1721.8	1851.8	2036.5	2272.4	2561.1	2921.7
65°	1315.4	1322.3	1355.9	1407.8	1472.1	1582.9	1725.9	1948.9	2256.1	2657.6	3154.2
66°	1252.5	1264.1	1284.7	1326.4	1388.0	1491.9	1635.6	1862.1	2193.8	2624.1	3148.1
67.5°	1154.0	1162.9	1176.6	1204.7	1242.3	1318.9	1455.0	1669.1	2003.6	2454.4	3017.4
70°	933.1	937.2	955.6	965.2	978.2	1003.5	1052.7	1176.0	1436.6	1860.0	2435.3
72.5°	636.2	647.8	667.7	695.0	730.6	764.8	788.1	803.8	859.9	1109.5	1622.6
75°	466.5	478.9	504.1	540.4	602.7	673.8	747.7	781.9	758.7	726.5	903.6
77.5°	270.9	287.4	308.5	343.4	400.8	495.2	621.9	734.0	809.9	814.7	773.7
80°	114.2	116.3	129.3	147.0	182.7	249.0	347.5	508.9	677.2	790.8	817.5
82.5°	26.0	32.1	41.0	48.6	59.5	82.1	121.8	202.5	366.0	573.9	748.4
85°	9.5	9.5	13.0	19.2	21.9	24.7	32.1	51.3	87.6	161.5	336.6
87.5°	0.0	0.7	1.3	1.3	2.7	3.4	5.5	7.6	6.8	6.1	20.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155821

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0
2.5°	684.0	683.4	682.0	682.0	682.0	682.0	680.6	681.3	680.0	680.6	680.6
5°	683.4	683.4	682.7	681.3	682.0	682.0	682.7	681.3	681.3	682.0	681.3
7.5°	683.4	682.7	682.7	682.7	683.4	682.7	683.4	683.4	683.4	684.0	684.0
10°	683.4	683.4	684.8	685.4	685.4	686.1	688.2	688.2	688.8	689.5	690.9
12.5°	684.0	686.8	688.8	690.9	691.6	693.0	696.4	696.4	697.7	699.8	700.5
15°	684.8	688.8	693.0	694.3	695.8	698.4	701.9	703.2	705.3	707.4	708.7
17.5°	684.0	689.5	694.3	696.4	698.4	701.9	706.0	707.4	710.1	712.8	715.5
20°	683.4	690.9	698.4	701.1	703.9	708.7	714.2	717.6	720.3	724.5	727.2
22.5°	687.5	696.4	706.6	710.8	715.5	721.7	729.2	733.4	736.8	740.8	742.9
25°	700.5	707.4	719.7	726.5	732.6	742.9	753.2	757.9	762.1	765.5	766.1
27.5°	722.4	724.5	739.5	748.4	757.3	773.7	786.0	789.4	796.9	799.7	799.0
30°	757.9	754.5	766.8	780.5	793.5	816.1	831.2	840.0	846.8	846.8	841.5
32.5°	809.2	803.8	807.3	822.9	838.0	870.8	888.6	900.2	905.0	903.6	892.0
35°	876.3	872.8	870.8	883.1	907.0	945.4	968.6	974.8	982.3	980.9	965.9
37.5°	955.6	953.0	953.0	967.3	990.6	1047.4	1072.6	1076.7	1076.1	1065.1	1037.1
40°	1049.3	1048.0	1041.9	1050.1	1069.8	1143.7	1177.9	1183.4	1176.0	1158.1	1125.3
42.5°	1184.1	1176.0	1156.8	1161.6	1176.6	1248.4	1292.8	1308.0	1300.4	1282.6	1229.2
45°	1359.9	1351.1	1318.9	1314.8	1323.0	1385.9	1443.4	1446.8	1445.5	1422.9	1359.9
47.5°	1566.5	1552.8	1518.7	1507.7	1505.0	1563.1	1618.5	1623.9	1620.5	1587.0	1502.9
50°	1790.3	1770.4	1747.8	1740.3	1729.3	1771.1	1827.2	1827.9	1814.2	1767.7	1689.0
52.5°	2028.9	2022.1	2018.0	2010.5	2005.7	2042.0	2076.2	2055.6	2035.1	1986.5	1918.1
55°	2269.7	2297.8	2326.5	2329.2	2337.5	2376.5	2375.8	2319.7	2304.7	2277.9	2210.3
57.5°	2525.6	2629.5	2719.9	2747.9	2775.2	2847.8	2840.9	2785.5	2766.4	2733.6	2677.4
60°	2873.8	3154.2	3414.9	3477.1	3520.2	3607.2	3598.9	3513.4	3553.1	3550.4	3477.8
62.5°	3361.6	3828.1	4218.7	4314.4	4344.6	4354.1	4302.1	4209.7	4248.8	4292.5	4069.5
65°	3691.9	4240.5	4641.5	4715.3	4719.4	4605.2	4489.5	4380.8	4371.2	4333.6	4014.8
66°	3699.5	4261.0	4663.3	4735.1	4709.8	4553.9	4407.5	4298.0	4250.8	4168.1	3837.6
67.5°	3566.7	4133.2	4566.2	4642.1	4586.7	4365.7	4163.9	4023.0	3930.7	3796.6	3505.2
70°	2995.5	3557.2	4090.8	4232.3	4250.2	3920.4	3640.6	3475.0	3350.6	3166.5	2915.5
72.5°	2227.4	2734.9	3205.6	3341.0	3410.1	3146.7	2910.7	2784.9	2614.5	2420.9	2242.4
75°	1396.2	1754.6	2069.9	2165.1	2100.1	1896.3	1754.6	1702.0	1534.4	1418.8	1337.3
77.5°	798.3	910.5	935.9	899.6	822.9	630.1	448.1	331.8	288.0	318.8	351.6
80°	779.2	714.2	569.1	500.7	453.6	311.9	183.3	125.9	104.7	107.4	116.3
82.5°	844.1	905.7	745.6	608.2	510.4	344.8	190.2	101.2	68.4	80.7	91.0
85°	548.6	763.4	687.5	579.4	469.2	294.8	156.7	52.6	34.9	45.8	62.9
87.5°	55.4	60.9	52.0	70.5	52.6	24.7	12.3	7.6	6.8	8.2	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155821

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7050

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0	682.0
2.5°	681.3	681.3	682.0	682.7	683.4	684.0	684.0	684.0	684.0	685.4	684.8
5°	682.7	684.0	685.4	686.1	687.5	687.5	689.5	688.8	688.8	690.9	691.6
7.5°	685.4	687.5	690.3	689.5	692.2	691.6	693.0	693.0	690.9	691.6	690.3
10°	691.6	694.3	695.8	693.7	694.3	691.6	690.9	687.5	683.4	681.3	678.5
12.5°	701.9	704.6	704.6	701.1	697.1	690.9	686.1	678.5	672.4	669.0	665.6
15°	710.8	713.5	712.8	707.4	701.1	691.6	684.8	675.9	666.9	661.5	658.0
17.5°	717.6	719.0	716.9	709.4	702.6	693.7	686.8	677.2	666.9	660.1	654.0
20°	727.9	726.5	721.7	712.1	704.6	696.4	690.9	682.7	671.1	662.2	653.3
22.5°	742.9	737.4	728.5	718.2	710.8	703.2	697.7	688.8	677.2	666.3	656.1
25°	762.7	751.8	739.5	728.5	721.7	713.5	707.4	697.7	685.4	673.2	660.8
27.5°	791.5	772.3	756.6	747.0	739.5	729.2	721.7	709.4	696.4	682.0	668.3
30°	823.6	797.6	782.6	775.0	766.8	755.9	744.2	728.5	713.5	697.7	681.3
32.5°	865.4	833.9	819.5	812.0	801.0	787.4	773.7	755.9	734.7	714.2	694.3
35°	920.1	887.9	872.8	861.2	846.2	828.4	808.6	784.7	755.9	728.5	703.2
37.5°	978.9	944.0	929.6	917.3	894.7	871.5	843.4	808.6	769.5	733.4	701.9
40°	1053.5	1021.3	1002.8	981.7	954.9	914.6	870.8	820.2	770.3	725.8	688.8
42.5°	1147.9	1115.8	1088.4	1054.8	1008.3	946.1	883.8	818.1	757.9	707.4	667.7
45°	1273.1	1234.1	1186.8	1128.1	1052.7	965.9	884.5	805.2	734.7	678.5	636.2
47.5°	1426.3	1366.7	1289.4	1190.3	1082.2	971.4	873.6	779.2	698.4	637.5	590.4
50°	1608.3	1514.5	1387.3	1241.6	1097.2	963.2	846.2	740.2	647.2	582.2	526.0
52.5°	1816.2	1663.0	1475.5	1278.5	1096.6	935.9	799.7	681.3	580.1	507.6	454.2
55°	2060.4	1832.6	1566.5	1305.9	1077.4	885.2	728.5	598.5	497.3	430.3	381.0
57.5°	2418.2	2107.7	1725.2	1348.3	1039.1	807.3	632.1	499.4	410.5	346.8	305.1
60°	3072.1	2566.6	2011.2	1433.8	980.3	693.0	519.2	393.4	318.8	267.5	239.4
62.5°	3564.7	2921.7	2165.8	1414.6	862.0	552.0	385.2	286.6	234.6	199.8	182.0
65°	3494.2	2811.5	2000.9	1218.3	675.9	389.2	255.9	194.9	161.5	145.0	134.7
66°	3334.8	2667.9	1857.9	1096.6	584.1	323.5	210.7	163.5	138.9	127.3	120.4
67.5°	3032.4	2401.0	1602.1	898.9	448.7	234.6	158.7	129.3	112.8	108.1	103.3
70°	2520.8	1914.7	1124.7	523.3	229.1	130.7	100.5	90.3	86.2	85.5	84.1
72.5°	1931.8	1355.1	662.2	247.7	119.1	86.8	78.0	74.6	73.2	73.2	73.9
75°	1184.1	761.3	292.7	121.0	83.4	73.2	69.1	67.8	67.0	67.8	67.0
77.5°	395.4	242.2	125.2	91.7	76.0	67.8	65.0	63.6	63.6	63.6	63.6
80°	121.0	105.4	95.8	84.9	71.8	64.4	60.2	59.5	60.2	60.9	58.9
82.5°	91.0	86.2	80.7	75.2	65.0	57.5	56.1	56.1	56.1	54.1	51.3
85°	67.0	66.3	54.7	51.3	47.9	47.9	47.9	47.9	45.8	42.4	39.7
87.5°	12.3	11.6	12.3	13.0	19.2	20.5	20.5	21.9	23.9	22.6	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155821

CATALOG NUMBER: AVS-E02-LED-E-U-T3-7050

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	682.0	682.0	682.0	682.0	682.0
2.5°	684.8	684.0	686.1	684.8	685.4
5°	690.9	690.3	691.6	690.3	692.2
7.5°	688.8	687.5	686.8	687.5	688.2
10°	674.5	673.2	672.4	671.7	672.4
12.5°	662.2	659.5	659.5	658.0	658.8
15°	653.3	651.2	650.6	649.2	649.8
17.5°	649.2	645.8	644.4	643.0	643.0
20°	646.4	642.4	640.3	639.0	638.2
22.5°	646.4	640.3	637.5	636.2	635.5
25°	649.2	641.7	637.5	635.5	634.8
27.5°	654.6	645.1	640.3	637.5	637.5
30°	664.2	651.9	645.1	641.7	640.9
32.5°	673.8	657.4	647.8	643.7	642.4
35°	678.5	657.4	645.8	639.0	637.5
37.5°	673.2	648.5	634.1	623.8	621.9
40°	656.1	630.1	614.3	604.8	603.3
42.5°	633.5	608.2	589.6	582.8	580.7
45°	602.7	572.5	554.1	544.6	545.2
47.5°	549.9	519.2	502.8	493.9	495.2
50°	487.8	457.6	443.3	433.7	435.8
52.5°	419.4	392.0	378.3	373.5	372.1
55°	347.5	326.3	316.7	311.3	309.2
57.5°	281.9	266.7	259.9	253.1	253.8
60°	222.3	214.8	212.7	205.2	204.6
62.5°	175.1	170.4	168.3	162.8	163.5
65°	132.7	131.3	132.7	129.3	130.7
66°	119.7	120.4	120.4	118.3	119.7
67.5°	103.3	104.7	106.7	104.7	106.0
70°	85.5	86.8	88.3	88.3	88.3
72.5°	74.6	76.0	76.6	76.6	76.6
75°	68.4	69.1	69.7	68.4	68.4
77.5°	64.4	64.4	62.9	62.3	61.6
80°	58.1	57.5	55.4	54.1	54.1
82.5°	48.6	47.2	45.8	43.7	43.7
85°	36.9	35.5	34.2	31.5	30.1
87.5°	19.2	19.8	19.2	15.8	13.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)