

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148607

Luminaire Tested: **AVS-F01-LED-E-U-5XQ-7060**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148607
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F01-LED-E-U-5XQ-7060
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (7) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2694 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B2 - U0 - G1

Input Watts (W): 25.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148607

CATALOG NUMBER: AVS-F01-LED-E-U-5XQ-7060

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.6 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148607

CATALOG NUMBER: AVS-F01-LED-E-U-5XQ-7060

Luminous Intensity Polar Plot



REPORT NUMBER: P148607

CATALOG NUMBER: AVS-F01-LED-E-U-5XQ-7060


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1347.0	0.0	1347.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1347.0	0.0	1347.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	2694.0	0.0	2694.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.3	0.9
10°-20°	72.0	2.7
20°-30°	120.5	4.5
30°-40°	183.7	6.8
40°-50°	293.3	10.9
50°-60°	451.0	16.7
60°-70°	656.7	24.4
70°-80°	739.8	27.5
80°-90°	152.7	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2694.0	100.0
0°-180°	2694.0	100.0

Coefficient of Utilization



REPORT NUMBER: P148607


CATALOG NUMBER: AVS-F01-LED-E-U-5XQ-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	108.4	4.0			
FM	(30°-60°)	464.0	17.2			
FH	(60°-80°)	698.2	25.9			G1/1800
FVH	(80°-90°)	76.4	2.8			G1/100
BL	(0°-30°)	108.4	4.0	B0/110		
BM	(30°-60°)	464.0	17.2	B1/1000		
BH	(60°-80°)	698.2	25.9	B2/1000		G1/1800
BVH	(80°-90°)	76.4	2.8			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type V Short





REPORT NUMBER: P148607

CATALOG NUMBER: AVS-F01-LED-E-U-5XQ-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	255.2	255.2	255.2	255.2	255.2	255.2	255.2	255.2	255.2	255.2	255.2
2.5°	255.6	255.8	255.8	255.6	255.8	255.6	255.4	255.4	254.9	255.1	255.5
5°	255.8	255.5	255.5	255.4	255.3	255.5	255.3	255.1	255.1	255.2	255.0
7.5°	255.5	255.2	255.1	255.0	255.1	255.1	254.9	254.7	254.9	254.7	254.4
10°	255.1	254.9	255.0	254.7	254.7	254.7	254.4	254.2	254.3	254.1	253.8
12.5°	255.2	254.9	254.8	254.7	254.6	254.5	254.2	253.8	253.9	253.8	253.5
15°	255.2	255.0	254.9	254.7	254.6	254.5	254.1	253.9	253.9	253.7	253.3
17.5°	255.3	255.2	255.2	254.9	254.7	254.7	254.2	254.0	254.2	253.8	253.5
20°	255.9	255.8	255.8	255.5	255.2	255.2	254.9	254.7	254.8	254.7	254.0
22.5°	256.7	256.7	256.8	256.8	256.7	256.8	256.5	256.5	256.5	256.6	255.9
25°	259.1	259.1	259.2	259.2	259.3	259.7	259.5	259.5	259.8	259.8	259.1
27.5°	263.6	263.4	263.6	263.7	264.0	264.7	264.6	264.8	265.3	265.2	264.7
30°	268.8	268.6	269.0	269.4	269.7	270.7	270.3	271.3	271.9	272.2	271.9
32.5°	276.5	276.5	277.1	277.4	277.9	279.0	279.1	280.0	280.6	281.2	280.8
35°	286.6	286.4	286.9	287.5	288.2	289.1	289.5	290.6	291.6	292.1	291.2
37.5°	302.1	301.3	302.3	302.6	303.2	303.4	304.4	305.8	306.9	306.7	306.1
40°	323.1	323.0	322.7	322.3	323.2	323.5	323.6	325.5	327.2	326.8	326.8
42.5°	347.7	347.2	346.7	346.6	347.3	347.4	349.5	351.0	352.1	352.4	352.1
45°	374.1	373.5	373.7	373.3	373.5	374.5	375.8	378.3	380.6	380.7	379.5
47.5°	402.5	400.5	402.1	399.9	401.2	402.0	405.1	408.9	412.8	413.6	412.5
50°	431.3	431.1	431.0	430.5	431.1	432.7	436.6	442.6	446.4	448.9	447.3
52.5°	462.8	461.8	461.2	460.5	461.1	464.2	469.6	474.8	481.7	484.6	482.3
55°	493.5	493.1	491.3	491.2	492.4	497.2	503.1	509.5	517.0	520.2	519.4
57.5°	524.9	522.9	522.3	521.5	524.1	528.6	535.9	547.4	555.1	558.8	556.7
60°	555.6	554.1	553.0	552.6	554.5	560.7	571.2	585.1	594.6	599.4	596.1
62.5°	588.8	587.8	586.3	584.7	588.6	596.5	609.5	624.9	639.0	644.9	639.8
65°	629.8	627.8	626.2	624.1	627.3	637.4	653.7	675.3	694.2	701.1	697.4
67.5°	673.2	671.3	671.4	670.2	675.8	689.6	710.7	740.1	765.4	777.2	770.3
70°	711.0	712.0	712.3	717.5	727.3	748.4	783.4	829.4	867.8	885.8	878.4
71°	699.8	702.2	705.7	711.1	727.9	753.0	800.8	856.6	902.4	932.8	922.6
72.5°	668.2	669.6	671.5	679.6	698.7	731.8	781.0	844.8	903.6	943.1	931.2
75°	622.5	623.8	624.5	630.2	647.5	676.4	721.5	778.0	829.9	863.5	860.2
77.5°	553.4	553.6	558.5	567.5	586.8	619.9	667.4	726.1	774.9	801.0	784.4
80°	397.4	394.7	399.8	411.2	435.1	473.2	521.8	588.8	642.9	667.4	641.7
82.5°	151.3	159.4	172.3	191.1	199.2	241.5	286.7	326.1	371.7	422.7	409.9
85°	16.3	18.2	23.0	28.4	36.0	49.7	68.7	93.7	115.5	135.8	120.6
87.5°	6.0	6.2	6.9	8.0	8.1	8.4	9.0	10.5	9.8	8.5	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148607

CATALOG NUMBER: AVS-F01-LED-E-U-5XQ-7060

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	255.2	255.2	255.2	255.2	255.2	255.2	255.2	255.2
2.5°	255.2	255.3	255.2	255.3	255.3	255.0	255.1	254.9
5°	255.1	254.9	255.0	255.1	255.0	255.2	254.9	255.1
7.5°	254.8	254.4	254.5	254.5	254.4	254.6	254.5	254.4
10°	254.1	253.6	253.9	253.7	253.6	253.7	253.7	253.7
12.5°	253.5	253.1	253.3	253.2	253.1	253.3	253.2	253.3
15°	253.4	252.8	252.6	252.5	252.6	252.7	252.8	253.1
17.5°	253.3	252.4	252.4	252.3	252.4	252.6	252.6	252.5
20°	253.7	253.1	252.8	252.8	252.7	253.1	253.0	253.1
22.5°	255.5	254.9	254.8	254.3	254.1	254.3	254.1	254.1
25°	258.9	257.9	257.6	256.9	256.4	256.3	256.2	256.0
27.5°	264.5	263.2	263.0	262.4	261.6	261.7	261.2	261.1
30°	271.1	269.9	269.0	268.1	267.2	266.8	266.3	266.3
32.5°	279.8	278.5	277.3	276.3	274.9	274.4	273.6	273.2
35°	290.5	288.8	287.4	286.6	285.3	284.7	284.1	284.8
37.5°	305.4	303.3	302.6	301.7	300.8	299.9	300.1	299.9
40°	326.0	324.1	323.4	321.9	321.7	320.5	321.1	320.4
42.5°	351.5	348.1	347.6	346.3	345.9	345.3	345.5	345.1
45°	379.3	376.2	375.5	373.6	373.7	372.1	372.6	372.7
47.5°	410.4	407.3	404.6	403.1	402.6	401.7	402.2	402.1
50°	442.6	438.3	435.4	432.5	431.2	431.6	430.6	432.3
52.5°	477.2	470.8	466.7	463.9	461.6	462.0	462.2	462.6
55°	513.0	504.8	498.9	495.2	493.1	493.3	493.9	494.4
57.5°	549.0	538.8	530.7	525.4	523.9	524.6	524.6	524.6
60°	586.3	574.1	563.6	557.6	556.3	556.0	558.8	557.7
62.5°	626.4	611.6	600.9	593.2	591.3	592.6	595.1	594.5
65°	679.6	659.2	645.4	637.6	634.5	635.8	639.1	639.0
67.5°	748.1	719.6	701.3	691.4	689.1	690.8	692.5	694.3
70°	850.6	809.9	783.7	762.4	753.2	751.5	753.3	753.4
71°	886.6	839.9	798.3	772.2	757.1	750.8	751.3	748.2
72.5°	885.2	827.6	778.9	751.5	730.7	725.6	723.1	719.3
75°	825.6	773.6	731.4	701.6	681.5	675.4	671.1	670.9
77.5°	748.7	710.4	663.8	632.3	607.8	597.8	593.4	593.3
80°	601.9	544.5	510.5	491.4	461.9	453.4	444.4	440.8
82.5°	363.9	284.4	231.3	205.5	191.2	157.5	141.3	133.7
85°	84.8	60.2	41.5	27.3	19.6	15.5	12.0	10.6
87.5°	5.7	4.6	4.0	3.2	2.5	2.4	1.5	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)