

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148111

Luminaire Tested: **AVS-E04-LED-E-U-5WQ-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148111
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E04-LED-E-U-5WQ-7050
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (84) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13067.6 lumens
Efficiency: N/A
Efficacy: 134.4 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2

Input Watts (W): 97.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148111

CATALOG NUMBER: AVS-E04-LED-E-U-5WQ-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 2 fc
Type V - Short - Semi-Cutoff

REPORT NUMBER: P148111

CATALOG NUMBER: AVS-E04-LED-E-U-5WQ-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P148111

CATALOG NUMBER: AVS-E04-LED-E-U-5WQ-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6533.8	0.0	6533.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6533.8	0.0	6533.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	13067.6	0.0	13067.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.2	0.5
10°-20°	240.6	1.8
20°-30°	487.2	3.7
30°-40°	816.9	6.3
40°-50°	1440.9	11.0
50°-60°	2540.9	19.4
60°-70°	3879.3	29.7
70°-80°	3241.5	24.8
80°-90°	352.2	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13067.6	100.0
0°-180°	13067.6	100.0

Coefficient of Utilization



REPORT NUMBER: P148111


CATALOG NUMBER: AVS-E04-LED-E-U-5WQ-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	398.0	3.0			
FM	(30°-60°)	2399.3	18.4			
FH	(60°-80°)	3560.4	27.2			G2/5000
FVH	(80°-90°)	176.1	1.3			G2/225
BL	(0°-30°)	398.0	3.0	B1/500		
BM	(30°-60°)	2399.3	18.4	B2/2500		
BH	(60°-80°)	3560.4	27.2	B4/5000		G2/5000
BVH	(80°-90°)	176.1	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short





REPORT NUMBER: P148111

CATALOG NUMBER: AVS-E04-LED-E-U-5WQ-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	678.5	678.5	678.5	678.5	678.5	678.5	678.5	678.5	678.5	678.5	678.5
2.5°	684.0	685.4	684.0	684.0	684.0	684.0	684.0	682.7	682.7	682.7	684.0
5°	697.7	699.2	697.7	699.2	699.2	699.2	699.2	697.7	697.7	697.7	697.7
7.5°	719.7	719.7	719.7	721.0	719.7	719.7	721.0	719.7	719.7	719.7	719.7
10°	751.1	749.7	749.7	749.7	749.7	749.7	751.1	751.1	751.1	749.7	749.7
12.5°	789.4	788.1	789.4	789.4	790.8	790.8	790.8	790.8	790.8	790.8	789.4
15°	836.0	836.0	836.0	837.3	840.0	840.0	838.7	840.0	840.0	840.0	840.0
17.5°	887.9	890.7	887.9	889.3	890.7	889.3	892.0	893.4	894.7	893.4	889.3
20°	941.2	942.7	942.7	942.7	942.7	945.4	946.7	946.7	950.9	949.5	948.1
22.5°	991.9	994.6	994.6	996.0	996.0	1000.1	1000.1	1000.1	1002.8	1005.6	1002.8
25°	1045.3	1043.9	1043.9	1046.6	1048.0	1053.5	1053.5	1056.2	1060.3	1061.7	1059.0
27.5°	1093.2	1091.8	1091.8	1095.9	1097.2	1104.0	1104.0	1109.5	1112.3	1113.7	1110.9
30°	1143.7	1143.7	1142.4	1146.5	1150.6	1156.1	1158.9	1164.2	1168.4	1169.7	1167.0
32.5°	1203.9	1201.2	1202.6	1205.3	1208.1	1213.6	1217.6	1224.5	1229.9	1231.3	1228.6
35°	1272.3	1268.3	1269.6	1272.3	1276.5	1284.7	1291.5	1295.6	1303.8	1306.5	1301.1
37.5°	1347.7	1349.0	1347.7	1354.5	1361.3	1370.9	1379.1	1384.6	1392.7	1396.9	1392.7
40°	1454.3	1450.3	1454.3	1461.1	1472.1	1484.5	1500.8	1505.0	1513.2	1521.3	1511.8
42.5°	1592.5	1589.7	1599.4	1604.9	1617.1	1630.8	1651.3	1662.3	1674.6	1680.1	1671.9
45°	1773.2	1773.2	1784.0	1785.4	1804.6	1822.4	1851.1	1864.8	1888.1	1888.1	1888.1
47.5°	1972.8	1981.0	1987.9	2001.6	2015.2	2048.1	2076.8	2106.9	2128.8	2131.6	2127.5
50°	2179.5	2187.7	2208.2	2227.4	2257.4	2298.4	2329.9	2369.6	2388.8	2405.2	2399.7
52.5°	2407.9	2409.3	2433.9	2458.5	2502.3	2547.5	2598.1	2639.2	2673.4	2688.4	2676.1
55°	2658.3	2661.0	2682.9	2708.9	2758.1	2810.2	2873.1	2915.5	2959.3	2986.6	2966.1
57.5°	2929.2	2930.6	2952.4	2983.9	3042.7	3094.7	3154.9	3215.1	3256.2	3280.8	3267.2
60°	3228.8	3235.6	3252.0	3291.7	3347.9	3402.6	3462.8	3516.2	3564.0	3590.1	3576.3
62.5°	3548.9	3555.8	3579.1	3610.6	3659.8	3720.0	3777.4	3845.8	3885.5	3914.3	3893.7
65°	3763.7	3776.1	3813.1	3855.4	3928.0	4005.9	4073.0	4166.0	4213.9	4248.1	4228.9
67.5°	3777.4	3784.2	3829.4	3893.7	3990.9	4108.5	4245.4	4390.4	4484.8	4529.9	4497.1
69°	3684.4	3694.0	3737.7	3810.3	3918.3	4055.1	4217.9	4398.5	4543.6	4610.7	4579.2
70°	3579.1	3599.6	3647.5	3726.8	3832.1	3975.9	4144.1	4337.0	4506.6	4598.3	4575.0
72.5°	3357.4	3362.9	3394.4	3457.3	3538.0	3657.0	3815.8	3997.7	4159.2	4290.5	4309.6
75°	2979.8	2997.6	3020.8	3063.3	3104.4	3190.5	3297.2	3421.8	3516.2	3617.4	3621.5
77.5°	2251.9	2305.3	2323.1	2332.6	2350.5	2418.9	2511.9	2620.0	2697.9	2714.4	2711.6
80°	1011.1	1082.2	1098.7	1176.6	1224.5	1338.0	1480.3	1645.9	1756.7	1769.0	1738.9
82.5°	198.3	212.0	247.7	309.2	421.3	488.4	581.5	697.7	804.5	866.0	829.1
85°	65.7	69.7	80.7	88.9	102.6	116.3	140.9	175.1	217.5	240.8	214.8
87.5°	26.0	26.0	30.1	32.8	35.5	35.5	35.5	32.8	31.5	26.0	23.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148111

CATALOG NUMBER: AVS-E04-LED-E-U-5WQ-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	678.5	678.5	678.5	678.5	678.5	678.5	678.5	678.5
2.5°	682.7	682.7	682.7	682.7	682.7	682.7	682.7	682.7
5°	697.7	696.4	696.4	695.0	695.0	695.0	695.0	695.0
7.5°	718.2	716.9	715.5	716.9	715.5	715.5	715.5	715.5
10°	749.7	747.0	745.6	744.2	744.2	744.2	742.9	742.9
12.5°	786.6	786.6	785.3	783.9	781.2	782.6	781.2	778.4
15°	837.3	834.6	833.2	831.8	829.1	829.1	829.1	827.8
17.5°	887.9	885.2	885.2	881.0	879.7	879.7	879.7	881.0
20°	944.0	939.9	937.2	934.4	931.7	933.1	930.4	933.1
22.5°	1000.1	994.6	991.9	987.8	983.7	983.7	982.3	979.6
25°	1054.8	1048.0	1045.3	1041.1	1035.6	1035.6	1033.0	1030.3
27.5°	1106.8	1100.0	1097.2	1089.0	1083.5	1082.2	1079.5	1078.1
30°	1164.2	1156.1	1152.0	1143.7	1135.5	1134.2	1130.1	1130.1
32.5°	1224.5	1216.3	1213.6	1201.2	1194.4	1194.4	1191.6	1188.9
35°	1299.7	1287.5	1284.7	1272.3	1262.8	1262.8	1260.1	1261.5
37.5°	1388.7	1379.1	1369.5	1359.9	1349.0	1347.7	1344.9	1342.2
40°	1507.7	1496.8	1485.8	1472.1	1462.6	1459.8	1455.8	1454.3
42.5°	1666.4	1655.4	1633.6	1622.6	1613.1	1604.9	1603.4	1602.1
45°	1868.9	1855.2	1840.1	1819.6	1807.4	1789.5	1786.8	1780.0
47.5°	2112.4	2086.4	2060.4	2042.6	2023.5	2003.0	1998.9	1987.9
50°	2371.0	2350.5	2306.7	2277.9	2247.9	2227.4	2213.7	2209.5
52.5°	2648.7	2610.4	2566.6	2528.3	2484.6	2457.2	2432.5	2425.7
55°	2938.8	2884.0	2829.3	2784.1	2740.4	2707.6	2684.2	2673.4
57.5°	3228.8	3168.6	3108.4	3059.2	3022.2	2979.8	2956.6	2951.1
60°	3531.2	3473.7	3412.1	3362.9	3317.7	3280.8	3267.2	3241.1
62.5°	3851.3	3791.1	3733.7	3685.8	3628.3	3602.3	3579.1	3564.0
65°	4166.0	4096.2	4023.7	3973.1	3915.6	3878.7	3849.9	3829.4
67.5°	4409.5	4304.1	4207.0	4122.2	4044.2	3986.7	3949.8	3930.7
69°	4477.9	4346.6	4222.1	4111.3	4019.6	3955.3	3914.3	3895.1
70°	4469.7	4324.7	4187.9	4066.1	3966.2	3897.8	3858.1	3822.6
72.5°	4216.6	4083.9	3932.0	3799.3	3709.0	3643.3	3603.7	3584.6
75°	3598.2	3509.3	3399.8	3297.2	3231.5	3193.3	3143.9	3145.4
77.5°	2620.0	2622.7	2548.8	2443.5	2369.6	2356.0	2334.1	2312.1
80°	1625.4	1495.3	1410.6	1297.0	1213.6	1141.0	1109.5	1041.1
82.5°	749.7	585.6	454.2	343.4	264.0	206.6	180.6	147.8
85°	166.9	127.3	105.4	84.9	72.5	67.0	54.7	50.6
87.5°	23.2	20.5	19.2	17.8	15.0	11.0	8.2	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)