

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P149177

Luminaire Tested: **AVS-F01-LED-E-U-RW-7060**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P149177
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33677)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F01-LED-E-U-RW-7060
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - RECTANGULAR WIDE
Light Source: (7) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2646.2 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type V - Medium - Full Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 25.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P149177

CATALOG NUMBER: AVS-F01-LED-E-U-RW-7060

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.1 fc
 Type V - Medium - Full Cutoff

REPORT NUMBER: P149177

CATALOG NUMBER: AVS-F01-LED-E-U-RW-7060

Luminous Intensity Polar Plot



REPORT NUMBER: P149177

CATALOG NUMBER: AVS-F01-LED-E-U-RW-7060

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1323.1	0.0	1323.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1323.1	0.0	1323.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	2646.2	0.0	2646.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	1.8
10°-20°	153.4	5.8
20°-30°	248.6	9.4
30°-40°	309.8	11.7
40°-50°	387.1	14.6
50°-60°	478.0	18.1
60°-70°	593.9	22.4
70°-80°	394.3	14.9
80°-90°	32.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2646.2	100.0
0°-180°	2646.2	100.0

Coefficient of Utilization



REPORT NUMBER: P149177


CATALOG NUMBER: AVS-F01-LED-E-U-RW-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	225.3	8.5			
FM	(30°-60°)	587.4	22.2			
FH	(60°-80°)	494.1	18.7			G0/660
FVH	(80°-90°)	16.3	0.6			G1/100
BL	(0°-30°)	225.3	8.5	B1/500		
BM	(30°-60°)	587.4	22.2	B1/1000		
BH	(60°-80°)	494.1	18.7	B1/500		G0/660
BVH	(80°-90°)	16.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type V Medium





REPORT NUMBER: P149177

CATALOG NUMBER: AVS-F01-LED-E-U-RW-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	67°	68°
0°	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9
2.5°	498.1	498.5	498.2	498.8	498.6	498.6	498.4	497.8	497.7	497.6	497.6
5°	502.8	502.2	503.2	504.0	503.8	503.8	503.8	503.7	503.7	503.6	503.6
7.5°	508.0	507.8	508.4	510.7	510.8	511.8	512.8	513.4	513.4	513.5	513.5
10°	512.4	512.5	513.8	517.1	518.8	521.5	524.2	526.4	526.5	526.7	526.8
12.5°	515.9	516.0	518.2	523.2	527.3	532.4	538.2	541.4	541.7	542.0	542.3
15°	516.2	516.6	520.2	528.6	536.8	545.2	552.0	556.3	556.6	556.8	557.0
17.5°	512.5	512.8	519.0	531.3	545.0	557.9	565.2	567.1	567.2	567.3	567.4
20°	502.8	503.6	512.4	530.6	551.4	568.4	575.8	573.2	572.9	572.6	572.3
22.5°	487.4	487.2	498.6	523.2	552.7	576.6	583.2	576.2	575.3	574.5	573.6
25°	462.2	463.9	477.4	506.6	545.6	578.4	588.4	577.7	576.5	575.3	574.1
27.5°	435.0	436.0	450.2	481.7	528.7	572.0	591.0	580.8	579.5	578.1	576.8
30°	403.2	404.5	419.8	452.6	501.8	555.6	590.2	587.8	586.3	584.7	583.2
32.5°	372.2	373.5	387.2	423.2	473.4	533.2	586.0	597.9	596.3	594.7	593.1
35°	340.0	342.0	358.8	395.2	446.0	508.2	579.5	610.8	609.9	609.0	608.1
37.5°	313.2	313.7	329.8	368.0	420.6	484.4	571.0	627.0	627.6	628.3	628.9
40°	283.5	286.2	302.3	342.6	397.6	464.2	562.8	649.0	652.4	655.8	659.1
42.5°	256.8	257.1	273.5	315.1	372.6	448.0	558.2	675.5	682.7	689.9	697.2
45°	228.7	229.8	244.6	284.9	343.8	428.8	558.1	706.2	717.7	729.2	740.7
47.5°	202.1	202.6	218.2	255.7	310.8	402.0	557.1	739.1	754.8	770.4	786.1
50°	176.8	176.4	191.7	227.7	278.1	366.8	548.5	776.3	796.1	815.9	835.7
52.5°	147.6	149.6	165.6	200.0	248.5	331.0	523.4	817.2	840.8	864.5	888.2
55°	119.2	120.0	137.1	169.3	218.4	297.8	479.6	854.8	882.7	910.6	938.5
57.5°	87.9	90.4	105.3	137.1	187.9	269.6	424.0	874.2	908.2	942.1	976.1
60°	62.0	64.0	77.2	103.9	154.4	240.2	376.0	863.3	907.5	951.6	995.8
62.5°	48.2	49.8	60.4	77.8	120.4	210.6	341.8	828.2	888.3	948.4	1008.4
65°	42.4	43.8	53.4	62.3	90.0	180.6	323.0	791.0	870.4	949.8	1029.3
67.5°	38.2	40.0	48.3	54.5	73.2	157.6	318.0	767.6	857.6	947.5	1037.5
69°	36.4	38.1	45.6	50.8	68.0	149.4	309.6	730.8	820.2	909.6	999.1
70°	35.2	36.7	43.6	49.0	66.4	143.8	295.5	684.7	772.5	860.4	948.2
72.5°	32.8	33.5	39.6	44.8	61.6	116.2	227.2	508.6	584.7	660.8	737.0
75°	28.9	29.8	35.4	40.6	48.0	72.2	143.8	314.6	371.4	428.3	485.1
77.5°	25.0	25.7	30.6	38.7	37.2	45.0	86.0	175.1	208.1	241.0	274.0
80°	20.0	20.9	25.3	38.4	30.8	35.0	61.8	122.4	131.3	140.2	149.1
82.5°	14.8	15.4	19.8	31.0	23.6	26.4	47.2	103.8	106.8	109.9	113.0
85°	7.4	7.6	12.6	18.9	15.0	13.6	26.6	71.0	73.0	75.0	76.9
87.5°	1.3	1.3	2.8	3.2	3.7	2.3	3.4	12.1	12.5	12.9	13.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P149177

CATALOG NUMBER: AVS-F01-LED-E-U-RW-7060

CANDELA DISTRIBUTION (continued):

	69°	70°	71°	72°	73°	74°	75°	76°	77°	78°	79°
0°	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9
2.5°	497.5	497.4	497.2	497.3	497.5	497.4	497.6	497.6	497.7	497.2	497.1
5°	503.5	503.5	503.4	503.4	503.5	503.5	503.6	503.8	503.8	503.4	503.3
7.5°	513.6	513.6	513.8	513.6	513.9	513.8	513.4	513.9	514.2	514.3	514.6
10°	527.0	527.1	527.6	527.5	528.0	527.9	528.0	528.5	528.8	528.9	529.2
12.5°	542.5	542.8	543.1	543.3	543.8	543.5	544.2	544.5	544.9	545.8	545.4
15°	557.2	557.5	558.3	558.3	558.8	559.0	559.6	559.9	560.0	560.6	560.7
17.5°	567.4	567.5	567.8	567.7	568.1	568.0	568.4	568.6	569.0	569.3	570.0
20°	572.1	571.8	571.7	571.5	571.2	570.8	570.9	571.1	571.2	571.5	572.0
22.5°	572.8	572.0	571.1	570.6	569.7	568.9	568.2	568.3	568.4	568.3	568.6
25°	572.9	571.7	570.4	568.8	567.6	565.9	564.6	564.5	564.1	564.1	564.3
27.5°	575.5	574.1	572.2	570.3	567.8	565.6	563.5	562.7	561.9	561.4	561.2
30°	581.6	580.0	577.8	575.3	572.6	569.2	566.1	565.2	564.0	563.1	562.2
32.5°	591.5	589.9	587.4	584.9	581.1	577.8	574.8	573.2	571.6	570.0	568.4
35°	607.2	606.3	604.1	601.9	599.2	596.6	593.8	592.0	589.4	588.2	586.2
37.5°	629.6	630.2	630.2	630.5	629.7	628.4	626.4	624.6	623.7	620.2	617.9
40°	662.5	665.9	669.0	671.3	673.4	675.6	677.4	676.3	676.6	675.7	674.4
42.5°	704.4	711.6	718.2	724.8	729.6	737.0	742.2	743.8	748.0	749.6	752.6
45°	752.2	763.8	774.8	785.0	794.6	805.2	815.6	823.3	831.7	841.3	850.8
47.5°	801.8	817.5	833.8	847.1	860.9	876.6	890.4	902.0	917.2	931.2	946.6
50°	855.6	875.4	893.9	910.4	928.1	946.2	965.2	982.2	1002.6	1025.0	1049.3
52.5°	911.9	935.6	957.1	977.7	998.5	1019.3	1039.4	1063.4	1088.7	1118.2	1148.6
55°	966.4	994.4	1018.7	1041.7	1065.5	1088.7	1109.4	1141.6	1172.6	1207.9	1247.5
57.5°	1010.1	1044.0	1072.2	1099.4	1126.2	1151.0	1176.4	1212.8	1252.2	1293.4	1343.6
60°	1040.0	1084.1	1120.0	1152.8	1185.8	1216.8	1246.0	1293.6	1340.5	1391.8	1454.3
62.5°	1068.5	1128.6	1175.4	1220.1	1264.5	1304.4	1340.8	1400.6	1461.8	1525.2	1599.5
65°	1108.7	1188.1	1257.1	1319.4	1380.9	1439.5	1494.0	1569.7	1647.0	1730.5	1819.2
67.5°	1127.4	1217.4	1307.2	1391.2	1469.2	1543.5	1613.4	1704.9	1796.0	1892.8	2000.0
69°	1088.5	1177.9	1273.9	1365.6	1451.9	1530.7	1606.3	1699.8	1794.5	1893.3	2001.4
70°	1036.0	1123.8	1220.7	1316.6	1399.2	1481.2	1559.6	1652.3	1748.2	1847.3	1960.5
72.5°	813.1	889.2	983.7	1076.8	1159.6	1242.0	1318.1	1412.9	1509.5	1613.6	1720.7
75°	541.9	598.8	669.2	755.5	831.4	904.2	977.9	1058.2	1152.5	1238.2	1336.2
77.5°	306.9	339.9	380.8	436.9	491.4	535.0	587.6	625.3	680.0	727.3	777.1
80°	158.0	166.9	179.1	192.6	200.2	199.0	206.8	199.1	200.8	194.5	187.7
82.5°	116.1	119.2	124.7	127.4	127.1	118.3	108.8	95.8	84.2	72.1	61.0
85°	78.9	80.9	82.3	84.4	83.8	80.0	71.4	60.1	49.0	39.3	31.4
87.5°	13.6	14.0	13.9	15.1	15.2	14.0	11.5	9.8	8.3	6.2	4.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P149177

CATALOG NUMBER: AVS-F01-LED-E-U-RW-7060

CANDELA DISTRIBUTION (continued):

	80°	81°	82°	83°	84°	85°	86°	87°	88°	89°	90°
0°	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9	495.9
2.5°	497.0	496.9	497.3	497.0	497.0	497.0	496.8	497.1	497.0	496.6	496.1
5°	503.4	503.0	502.9	503.2	503.5	502.8	503.3	503.7	503.0	503.2	502.9
7.5°	514.3	514.2	514.0	514.3	514.4	514.1	514.3	513.8	513.6	514.0	514.5
10°	528.8	528.7	529.0	529.0	529.6	529.3	529.2	529.6	529.3	529.0	529.1
12.5°	546.0	545.5	546.2	546.2	546.7	546.7	546.6	546.6	546.6	546.1	545.8
15°	561.2	560.6	560.8	561.9	561.8	562.0	562.0	561.7	561.6	561.4	561.7
17.5°	570.3	570.0	570.1	570.7	571.0	571.0	571.0	571.0	570.8	571.0	571.2
20°	572.0	572.0	572.2	572.8	573.4	573.0	573.0	573.3	573.0	573.4	573.5
22.5°	568.8	569.0	569.4	570.0	570.2	570.2	570.2	570.4	570.6	570.6	570.9
25°	564.3	564.6	565.0	565.6	566.2	566.1	566.1	566.4	566.3	566.6	566.7
27.5°	560.9	561.2	561.6	562.2	562.9	562.9	562.8	563.2	563.2	563.3	563.6
30°	561.2	560.8	561.2	561.4	561.8	561.8	561.8	562.0	562.0	562.0	562.2
32.5°	567.4	566.2	565.7	565.6	565.7	565.3	565.1	564.8	564.6	564.6	564.5
35°	583.5	581.5	581.4	580.2	579.1	578.0	578.2	577.3	577.6	576.8	576.3
37.5°	616.6	614.2	615.7	613.2	611.8	610.6	609.4	607.6	606.7	608.0	607.9
40°	675.7	674.2	673.6	674.2	672.8	673.5	670.3	669.5	667.7	668.9	670.6
42.5°	757.4	756.4	761.8	762.8	763.3	764.2	764.8	760.1	759.9	759.0	756.2
45°	858.4	864.2	864.0	870.6	870.8	868.8	869.7	867.6	866.7	863.6	867.4
47.5°	962.2	973.4	977.7	979.0	984.4	985.8	980.6	978.9	981.9	976.8	977.5
50°	1073.5	1085.7	1095.6	1102.2	1106.0	1106.2	1102.5	1101.6	1104.3	1094.7	1099.2
52.5°	1183.1	1201.4	1220.1	1230.0	1237.0	1237.6	1240.5	1237.0	1238.4	1236.2	1240.7
55°	1291.1	1322.8	1344.7	1364.1	1376.4	1387.0	1387.9	1391.8	1392.1	1396.7	1392.0
57.5°	1396.7	1431.2	1469.4	1503.8	1522.8	1534.8	1546.0	1561.4	1564.8	1563.0	1566.0
60°	1521.4	1574.9	1626.7	1666.2	1699.0	1730.6	1747.5	1771.6	1775.4	1786.0	1776.9
62.5°	1678.9	1756.6	1826.8	1880.0	1930.0	1979.1	2016.0	2034.6	2046.0	2067.8	2060.6
65°	1920.6	2013.8	2106.8	2183.0	2253.1	2311.4	2367.6	2394.4	2424.0	2455.1	2460.7
67.5°	2119.7	2235.0	2339.9	2432.8	2517.6	2582.4	2640.9	2687.3	2723.5	2746.4	2748.2
69°	2128.7	2248.5	2362.5	2462.2	2550.7	2619.6	2681.1	2732.8	2768.0	2791.4	2797.6
70°	2085.4	2208.2	2329.6	2430.2	2520.9	2591.4	2656.6	2705.9	2745.1	2769.0	2777.3
72.5°	1842.6	1973.5	2103.4	2191.5	2284.2	2368.0	2420.2	2470.5	2525.9	2533.0	2556.0
75°	1452.5	1562.6	1663.2	1730.8	1808.0	1883.3	1934.6	1947.8	1976.8	2013.2	2000.2
77.5°	841.7	875.6	940.6	957.2	943.0	975.8	986.6	963.6	962.4	983.8	941.3
80°	186.4	175.9	189.1	179.2	179.6	179.9	176.9	175.8	177.9	175.8	172.8
82.5°	51.7	50.0	50.2	49.7	50.7	50.0	49.6	50.7	50.6	50.4	51.4
85°	24.9	24.6	24.2	24.0	23.4	22.6	21.6	21.6	22.2	21.4	21.8
87.5°	3.2	3.1	3.1	3.6	3.2	2.7	2.7	2.7	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)