

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147566

Luminaire Tested: **AVS-F01-LED-E-U-5MQ-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P147566
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F01-LED-E-U-5MQ-7050
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM
Light Source: (7) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2730.8 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B2 - U0 - G1

Input Watts (W): 25.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P147566

CATALOG NUMBER: AVS-F01-LED-E-U-5MQ-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.1 fc
Type V - Short - Full Cutoff

REPORT NUMBER: P147566

CATALOG NUMBER: AVS-F01-LED-E-U-5MQ-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P147566

CATALOG NUMBER: AVS-F01-LED-E-U-5MQ-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1365.4	0.0	1365.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1365.4	0.0	1365.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	2730.8	0.0	2730.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	0.7
10°-20°	61.4	2.2
20°-30°	118.7	4.3
30°-40°	229.9	8.4
40°-50°	415.1	15.2
50°-60°	721.8	26.4
60°-70°	819.4	30.0
70°-80°	317.7	11.6
80°-90°	28.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2730.8	100.0
0°-180°	2730.8	100.0

Coefficient of Utilization



REPORT NUMBER: P147566


CATALOG NUMBER: AVS-F01-LED-E-U-5MQ-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	99.2	3.6			
FM	(30°-60°)	683.4	25.0			
FH	(60°-80°)	568.5	20.8			G0/660
FVH	(80°-90°)	14.3	0.5			G1/100
BL	(0°-30°)	99.2	3.6	B0/110		
BM	(30°-60°)	683.4	25.0	B1/1000		
BH	(60°-80°)	568.5	20.8	B2/1000		G0/660
BVH	(80°-90°)	14.3	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type V Short





REPORT NUMBER: P147566

CATALOG NUMBER: AVS-F01-LED-E-U-5MQ-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	181.2	181.2	181.2	181.2	181.2	181.2	181.2	181.2	181.2	181.2	181.2
2.5°	182.4	183.0	182.9	182.6	182.6	182.6	182.4	182.0	181.9	182.2	182.4
5°	186.7	186.7	186.7	186.7	186.3	186.3	186.1	185.7	185.9	185.7	185.5
7.5°	193.2	192.7	192.7	192.5	192.5	192.3	191.9	191.3	191.5	191.3	191.1
10°	200.8	200.8	200.4	200.9	200.2	200.0	199.5	199.2	199.1	198.7	198.7
12.5°	209.9	209.5	209.4	209.2	208.9	208.7	207.9	207.7	207.0	206.8	206.4
15°	218.5	218.4	217.8	217.3	217.2	216.8	215.9	215.3	215.1	214.5	213.9
17.5°	227.2	226.8	226.1	225.9	225.3	224.9	224.0	223.2	222.8	222.5	221.8
20°	236.3	236.1	235.3	234.8	234.1	233.6	232.2	231.5	231.1	230.7	230.1
22.5°	247.8	247.3	246.0	245.2	243.5	242.9	241.2	240.3	239.6	239.0	238.8
25°	260.2	260.3	258.9	257.5	255.8	254.1	252.0	250.9	250.2	249.5	249.5
27.5°	275.8	275.9	274.4	272.5	269.8	268.2	265.3	263.8	263.4	262.9	262.8
30°	300.3	299.1	296.6	293.7	291.2	287.5	283.3	282.0	280.5	280.1	280.1
32.5°	345.5	344.8	342.8	335.4	332.1	324.5	317.2	313.2	308.5	306.2	304.9
35°	377.1	376.8	375.2	372.6	370.6	369.1	364.8	364.1	363.3	363.2	364.4
37.5°	400.4	398.7	398.3	398.9	398.3	398.5	401.9	406.6	410.6	412.5	412.2
40°	434.8	432.4	433.8	432.8	431.6	431.3	432.4	434.3	436.1	436.1	435.6
42.5°	479.8	481.0	481.6	477.5	474.8	474.1	476.8	476.2	478.0	477.3	475.4
45°	546.8	546.1	545.1	540.1	536.0	532.4	533.3	532.2	532.4	531.3	529.8
47.5°	614.3	616.6	612.6	610.2	605.4	603.0	605.0	603.3	606.5	600.6	597.7
50°	679.8	681.5	680.0	676.7	676.7	680.0	682.5	685.6	690.2	683.3	673.2
52.5°	733.5	734.8	737.0	739.8	746.7	753.9	764.0	774.9	783.5	782.3	770.8
55°	766.2	767.9	771.4	781.1	793.6	812.4	835.4	860.7	880.5	890.2	881.7
57.5°	777.2	778.4	788.0	799.8	819.1	847.3	885.8	929.3	967.4	991.5	987.7
60°	774.7	774.7	784.4	800.5	827.7	864.9	919.4	979.8	1037.9	1074.1	1068.7
62.5°	748.0	749.4	763.4	782.7	815.4	860.1	925.0	1002.3	1071.9	1116.7	1112.3
65°	689.5	690.5	705.6	728.7	765.2	818.0	889.0	974.5	1054.3	1097.5	1089.3
67.5°	595.0	596.1	608.3	634.3	673.0	728.3	804.9	899.1	977.1	1011.3	986.7
70°	473.4	476.2	484.1	511.7	540.9	595.0	665.7	759.8	833.6	865.9	838.8
72.5°	322.6	329.7	339.4	363.8	391.9	436.8	493.0	572.3	631.5	668.9	644.8
75°	181.8	191.9	194.8	213.3	236.5	271.9	313.0	369.8	429.6	460.0	430.9
77.5°	78.5	86.8	90.6	99.1	117.2	132.0	157.0	195.3	241.6	262.9	228.0
80°	38.8	40.6	42.2	44.9	49.9	54.7	66.6	83.5	102.4	107.2	85.3
82.5°	29.9	31.3	34.0	36.1	37.4	38.8	39.8	42.1	43.9	44.9	42.4
85°	21.0	22.9	25.9	28.2	29.6	30.7	31.7	32.3	30.7	28.0	29.3
87.5°	5.6	7.3	10.1	10.9	12.3	13.1	12.6	13.2	11.9	8.6	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147566

CATALOG NUMBER: AVS-F01-LED-E-U-5MQ-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	181.2	181.2	181.2	181.2	181.2	181.2	181.2	181.2
2.5°	182.3	182.1	182.3	182.2	182.3	182.2	182.2	182.1
5°	185.5	185.5	185.7	185.4	185.4	185.5	185.4	185.2
7.5°	191.1	190.9	190.9	190.7	190.9	190.7	190.7	190.6
10°	198.3	198.1	198.1	197.8	197.7	197.7	197.6	197.6
12.5°	206.2	205.8	206.0	205.6	204.8	205.0	205.2	205.0
15°	213.9	213.5	213.1	212.8	212.3	212.4	212.4	212.3
17.5°	221.7	220.8	220.7	220.2	220.1	220.1	220.1	220.2
20°	229.6	229.1	229.0	228.6	228.4	228.8	229.0	228.7
22.5°	238.3	238.0	238.3	238.0	238.5	238.8	238.9	238.5
25°	249.1	248.9	249.3	250.4	250.9	251.2	251.8	251.6
27.5°	263.2	262.9	263.8	265.3	266.1	267.6	268.2	268.5
30°	281.2	282.5	283.1	285.8	286.4	288.7	288.7	289.7
32.5°	307.6	309.8	314.2	318.5	324.6	328.9	328.9	331.2
35°	365.1	366.0	369.3	370.1	371.4	372.6	371.3	372.4
37.5°	409.3	404.9	401.9	397.4	394.7	394.7	395.0	394.7
40°	431.9	430.2	428.8	425.1	424.5	424.4	424.4	425.0
42.5°	472.2	468.2	465.9	462.8	461.8	461.6	461.3	461.7
45°	524.8	518.1	512.1	509.0	506.3	503.7	504.6	504.6
47.5°	585.9	575.5	565.7	560.3	555.6	553.6	552.1	551.7
50°	660.3	645.8	633.2	623.2	616.4	616.2	617.0	612.4
52.5°	751.5	728.7	713.0	699.5	693.1	692.3	690.2	687.6
55°	852.5	825.6	799.6	784.9	776.6	772.1	769.4	765.2
57.5°	956.8	920.4	882.9	859.7	844.9	834.8	829.4	827.0
60°	1037.1	987.6	938.0	900.6	876.1	861.0	851.8	847.9
62.5°	1068.7	1001.5	938.0	888.9	853.6	832.7	820.1	814.6
65°	1031.0	951.4	879.2	824.9	785.5	762.3	748.6	742.6
67.5°	925.7	855.3	776.8	722.9	682.3	659.3	644.6	640.1
70°	776.1	704.2	629.0	580.9	544.9	526.0	510.7	508.8
72.5°	583.2	521.2	456.9	417.0	388.0	356.9	349.0	353.0
75°	373.9	315.9	258.4	222.6	196.1	166.4	155.0	157.8
77.5°	177.0	137.1	99.1	76.5	64.2	54.9	52.4	51.1
80°	65.7	53.3	46.9	44.6	42.9	41.5	40.2	39.0
82.5°	42.5	41.5	40.2	39.8	38.5	36.6	33.0	31.3
85°	31.7	31.7	30.1	30.3	29.2	26.7	23.3	21.5
87.5°	9.3	8.3	7.7	7.0	6.8	6.1	4.6	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)