

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148117

Luminaire Tested: **AVS-F04-LED-E-U-5WQ-7060**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148117
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-5WQ-7060
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (28) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10787.7 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148117

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ-7060

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 1.6 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P148117

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ-7060

Luminous Intensity Polar Plot



REPORT NUMBER: P148117

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ-7060


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5393.8	0.0	5393.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5393.8	0.0	5393.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	10787.7	0.0	10787.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	0.5
10°-20°	198.6	1.8
20°-30°	402.2	3.7
30°-40°	674.3	6.3
40°-50°	1189.5	11.0
50°-60°	2097.6	19.4
60°-70°	3202.4	29.7
70°-80°	2676.0	24.8
80°-90°	290.8	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10787.7	100.0
0°-180°	10787.7	100.0

Coefficient of Utilization



REPORT NUMBER: P148117


CATALOG NUMBER: AVS-F04-LED-E-U-5WQ-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	328.6	3.0			
FM	(30°-60°)	1980.7	18.4			
FH	(60°-80°)	2939.2	27.2			G2/5000
FVH	(80°-90°)	145.4	1.3			G2/225
BL	(0°-30°)	328.6	3.0	B1/500		
BM	(30°-60°)	1980.7	18.4	B2/2500		
BH	(60°-80°)	2939.2	27.2	B4/5000		G2/5000
BVH	(80°-90°)	145.4	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short





REPORT NUMBER: P148117

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	560.2	560.2	560.2	560.2	560.2	560.2	560.2	560.2	560.2	560.2	560.2
2.5°	564.8	565.8	564.8	564.8	564.8	564.8	564.8	563.6	563.6	563.6	564.8
5°	576.1	577.1	576.1	577.1	577.1	577.1	577.1	576.1	576.1	576.1	576.1
7.5°	594.1	594.1	594.1	595.2	594.1	594.1	595.2	594.1	594.1	594.1	594.1
10°	620.1	619.0	619.0	619.0	619.0	619.0	620.1	620.1	620.1	619.0	619.0
12.5°	651.7	650.6	651.7	651.7	652.8	652.8	652.8	652.8	652.8	652.8	651.7
15°	690.1	690.1	690.1	691.2	693.5	693.5	692.3	693.5	693.5	693.5	693.5
17.5°	733.0	735.2	733.0	734.1	735.2	734.1	736.4	737.5	738.7	737.5	734.1
20°	777.1	778.1	778.1	778.1	778.1	780.4	781.6	781.6	785.0	783.8	782.7
22.5°	818.9	821.1	821.1	822.3	822.3	825.6	825.6	825.6	827.9	830.2	827.9
25°	862.9	861.8	861.8	864.0	865.2	869.6	869.6	871.9	875.3	876.5	874.2
27.5°	902.4	901.2	901.2	904.7	905.8	911.5	911.5	916.0	918.2	919.4	917.1
30°	944.2	944.2	943.1	946.4	949.8	954.4	956.6	961.1	964.6	965.7	963.4
32.5°	993.9	991.6	992.7	995.0	997.3	1001.8	1005.2	1010.9	1015.3	1016.5	1014.2
35°	1050.4	1046.9	1048.1	1050.4	1053.8	1060.5	1066.2	1069.5	1076.4	1078.7	1074.1
37.5°	1112.5	1113.6	1112.5	1118.1	1123.8	1131.7	1138.4	1143.0	1149.7	1153.2	1149.7
40°	1200.6	1197.2	1200.6	1206.2	1215.2	1225.4	1239.0	1242.4	1249.1	1256.0	1248.0
42.5°	1314.6	1312.4	1320.3	1324.9	1335.0	1346.3	1363.2	1372.2	1382.4	1386.9	1380.2
45°	1463.7	1463.7	1472.7	1473.9	1489.7	1504.5	1528.1	1539.4	1558.7	1558.7	1558.7
47.5°	1628.6	1635.4	1641.0	1652.3	1663.6	1690.8	1714.5	1739.4	1757.4	1759.7	1756.3
50°	1799.2	1806.0	1822.9	1838.8	1863.5	1897.4	1923.4	1956.2	1972.0	1985.6	1981.0
52.5°	1987.8	1988.9	2009.2	2029.6	2065.7	2103.0	2144.8	2178.7	2206.9	2219.4	2209.2
55°	2194.5	2196.8	2214.8	2236.3	2276.9	2319.9	2371.8	2406.8	2443.0	2465.6	2448.6
57.5°	2418.1	2419.3	2437.3	2463.3	2511.8	2554.8	2604.5	2654.2	2688.1	2708.4	2697.1
60°	2665.5	2671.1	2684.7	2717.4	2763.7	2808.9	2858.5	2902.7	2942.2	2963.6	2952.3
62.5°	2929.7	2935.4	2954.6	2980.6	3021.2	3070.9	3118.3	3174.8	3207.6	3231.3	3214.4
65°	3107.0	3117.2	3147.8	3182.7	3242.6	3306.9	3362.3	3439.2	3478.7	3506.9	3491.1
67.5°	3118.3	3124.0	3161.2	3214.4	3294.5	3391.7	3504.7	3624.4	3702.3	3739.6	3712.4
69°	3041.6	3049.4	3085.6	3145.5	3234.7	3347.7	3482.1	3631.1	3750.9	3806.2	3780.2
70°	2954.6	2971.5	3011.1	3076.6	3163.5	3282.2	3421.0	3580.3	3720.3	3796.1	3776.8
72.5°	2771.6	2776.2	2802.2	2854.1	2920.7	3019.0	3149.9	3300.2	3433.5	3541.9	3557.7
75°	2459.9	2474.6	2493.8	2528.8	2562.7	2633.9	2722.0	2824.7	2902.7	2986.2	2989.6
77.5°	1859.1	1903.1	1917.8	1925.7	1940.4	1996.9	2073.7	2162.9	2227.3	2240.8	2238.5
80°	834.6	893.4	906.9	971.3	1010.9	1104.6	1222.1	1358.8	1450.2	1460.3	1435.5
82.5°	163.7	175.0	204.5	255.2	347.9	403.2	480.0	576.1	664.1	714.9	684.5
85°	54.2	57.6	66.6	73.4	84.7	96.0	116.4	144.6	179.6	198.8	177.3
87.5°	21.5	21.5	24.9	27.2	29.3	29.3	29.3	27.2	26.0	21.5	19.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148117

CATALOG NUMBER: AVS-F04-LED-E-U-5WQ-7060

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	560.2	560.2	560.2	560.2	560.2	560.2	560.2	560.2
2.5°	563.6	563.6	563.6	563.6	563.6	563.6	563.6	563.6
5°	576.1	574.9	574.9	573.8	573.8	573.8	573.8	573.8
7.5°	593.0	591.8	590.7	591.8	590.7	590.7	590.7	590.7
10°	619.0	616.7	615.5	614.4	614.4	614.4	613.3	613.3
12.5°	649.4	649.4	648.3	647.2	644.9	646.0	644.9	642.7
15°	691.2	688.9	687.9	686.7	684.5	684.5	684.5	683.3
17.5°	733.0	730.8	730.8	727.4	726.2	726.2	726.2	727.4
20°	779.3	776.0	773.7	771.4	769.1	770.3	768.0	770.3
22.5°	825.6	821.1	818.9	815.4	812.0	812.0	811.0	808.7
25°	870.8	865.2	862.9	859.5	855.0	855.0	852.7	850.5
27.5°	913.7	908.1	905.8	899.1	894.5	893.4	891.1	889.9
30°	961.1	954.4	951.0	944.2	937.4	936.3	933.0	933.0
32.5°	1010.9	1004.0	1001.8	991.6	986.0	986.0	983.7	981.5
35°	1073.0	1062.8	1060.5	1050.4	1042.5	1042.5	1040.2	1041.3
37.5°	1146.4	1138.4	1130.6	1122.7	1113.6	1112.5	1110.3	1108.0
40°	1244.7	1235.6	1226.5	1215.2	1207.4	1205.1	1201.8	1200.6
42.5°	1375.6	1366.6	1348.5	1339.5	1331.6	1324.9	1323.7	1322.6
45°	1542.8	1531.5	1519.1	1502.2	1492.0	1477.3	1475.0	1469.4
47.5°	1743.8	1722.4	1700.9	1686.2	1670.5	1653.5	1650.1	1641.0
50°	1957.3	1940.4	1904.2	1880.5	1855.6	1838.8	1827.5	1824.0
52.5°	2186.6	2154.9	2118.9	2087.2	2051.1	2028.5	2008.1	2002.5
55°	2426.0	2380.8	2335.6	2298.4	2262.3	2235.1	2216.0	2206.9
57.5°	2665.5	2615.8	2566.1	2525.4	2494.9	2459.9	2440.7	2436.2
60°	2915.0	2867.7	2816.8	2776.2	2738.9	2708.4	2697.1	2675.6
62.5°	3179.4	3129.6	3082.2	3042.7	2995.2	2973.8	2954.6	2942.2
65°	3439.2	3381.6	3321.7	3279.9	3232.4	3202.0	3178.2	3161.2
67.5°	3640.2	3553.2	3473.1	3403.0	3338.7	3291.2	3260.7	3244.9
69°	3696.7	3588.2	3485.4	3394.0	3318.2	3265.2	3231.3	3215.5
70°	3689.8	3570.2	3457.2	3356.7	3274.2	3217.7	3185.0	3155.6
72.5°	3480.9	3371.4	3246.0	3136.5	3061.9	3007.7	2974.9	2959.1
75°	2970.4	2897.0	2806.6	2722.0	2667.8	2636.1	2595.4	2596.6
77.5°	2162.9	2165.1	2104.1	2017.2	1956.2	1944.9	1926.8	1908.7
80°	1341.8	1234.5	1164.5	1070.7	1001.8	942.0	916.0	859.5
82.5°	619.0	483.4	374.9	283.5	218.0	170.6	149.1	122.0
85°	137.8	105.1	86.9	70.1	59.9	55.3	45.2	41.8
87.5°	19.2	16.9	15.9	14.7	12.4	9.0	6.7	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)