

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152588

Luminaire Tested: **AVS-E01-LED-E-U-SL4-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152588
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E01-LED-E-U-SL4-8030
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (21) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2493.3 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 24.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152588

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.3 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152588

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P152588

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	517.6	0.0	517.6
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	1975.7	0.0	1975.7
	% Fixture	79.2	0.0	79.2
Total	Lumens	2493.3	0.0	2493.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	2.0
10°-20°	136.1	5.5
20°-30°	201.4	8.1
30°-40°	254.5	10.2
40°-50°	287.9	11.5
50°-60°	409.6	16.4
60°-70°	762.9	30.6
70°-80°	349.7	14.0
80°-90°	41.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2493.3	100.0
0°-180°	2493.3	100.0

Coefficient of Utilization



REPORT NUMBER: P152588


CATALOG NUMBER: AVS-E01-LED-E-U-SL4-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	227.0	9.1			
FM	(30°-60°)	730.4	29.3			
FH	(60°-80°)	987.4	39.6			G1/1800
FVH	(80°-90°)	30.8	1.2			G1/100
BL	(0°-30°)	160.1	6.4	B1/500		
BM	(30°-60°)	221.6	8.9	B1/1000		
BH	(60°-80°)	125.1	5.0	B1/500		G1/500
BVH	(80°-90°)	10.7	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P152588

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0
2.5°	540.1	541.6	539.9	539.6	539.6	539.3	537.6	537.3	535.1	535.3	536.0
5°	544.0	544.7	543.5	543.2	542.7	541.6	540.1	538.4	536.8	535.1	533.7
7.5°	548.1	547.5	546.6	546.6	545.8	544.0	541.2	539.1	535.3	533.4	530.9
10°	553.7	552.8	551.7	551.1	549.7	547.2	543.2	540.1	535.6	531.7	527.5
12.5°	559.0	558.8	557.0	556.2	554.0	551.4	546.6	541.9	536.0	529.7	524.1
15°	568.6	567.5	565.8	564.0	560.4	557.0	549.7	544.0	535.6	527.5	518.8
17.5°	585.2	583.2	581.6	577.8	573.4	567.5	556.8	547.2	535.6	523.8	514.0
20°	615.5	611.3	609.1	604.2	596.4	585.7	569.1	553.7	536.5	521.3	508.1
22.5°	649.8	647.0	643.9	640.8	628.5	613.1	590.5	567.5	541.6	520.2	503.3
25°	688.4	684.8	683.1	677.7	666.2	648.5	617.8	585.7	553.1	524.7	503.3
27.5°	722.7	721.7	721.3	715.1	704.1	683.3	647.0	608.5	568.8	534.0	507.6
30°	754.0	752.8	752.2	748.9	736.3	711.5	672.1	628.8	586.0	546.9	515.4
32.5°	787.2	783.5	781.9	775.3	761.0	732.0	687.0	642.0	599.5	559.6	524.1
35°	814.2	811.1	807.7	798.4	778.1	743.8	693.5	646.5	604.9	566.6	528.6
37.5°	833.9	830.8	826.0	814.2	789.1	747.8	693.2	645.1	602.9	565.5	529.4
40°	842.6	839.5	834.4	819.5	791.1	745.5	687.9	638.7	597.0	559.6	526.1
42.5°	839.2	837.0	830.5	816.2	784.9	735.4	677.2	626.5	585.7	550.1	518.4
45°	826.2	824.6	818.3	803.2	770.9	719.1	661.5	611.3	572.2	538.1	508.4
47.5°	806.8	806.3	800.1	785.2	753.2	702.8	645.1	596.4	558.8	526.6	499.9
50°	785.5	782.7	779.6	765.8	736.5	688.7	633.3	587.2	551.1	522.4	496.3
52.5°	772.0	771.1	768.3	756.0	727.8	680.5	628.0	583.7	550.6	521.6	494.3
55°	891.8	893.8	867.9	814.2	766.9	703.0	643.9	600.9	564.4	535.1	515.1
57.5°	1319.2	1310.5	1266.0	1159.4	1039.0	880.0	765.5	696.1	650.7	655.8	665.9
60°	1536.9	1535.2	1527.0	1485.7	1405.5	1284.6	1150.4	996.5	947.6	952.8	956.8
62.5°	1634.2	1636.8	1643.0	1627.5	1606.4	1571.2	1504.2	1442.4	1376.8	1352.3	1286.8
65°	1679.3	1683.7	1697.8	1706.5	1714.7	1720.9	1747.4	1819.9	1867.8	1778.2	1570.2
67.5°	1586.1	1607.8	1654.2	1699.5	1740.0	1797.7	1887.2	2055.6	2173.0	2063.0	1761.1
70°	1156.3	1185.8	1239.0	1379.1	1528.7	1659.6	1832.8	2089.4	2266.4	2181.5	1808.4
72.5°	725.0	733.2	756.8	808.3	919.4	1087.4	1390.4	1775.2	1979.5	1911.6	1528.5
75°	460.0	462.8	462.0	473.8	492.6	529.2	649.0	1048.5	1356.1	1250.3	851.9
77.5°	274.0	278.2	279.9	283.6	292.5	305.5	315.3	356.7	568.6	552.0	309.2
80°	229.5	233.0	230.2	229.3	223.6	219.7	224.5	219.7	203.9	196.4	180.9
82.5°	121.6	121.2	120.4	128.6	145.2	158.1	168.0	165.7	149.9	127.8	108.3
85°	66.6	68.9	68.9	71.7	69.2	69.5	71.7	75.6	70.1	58.5	47.9
87.5°	5.6	8.7	7.0	8.7	11.8	8.4	8.2	8.2	7.0	5.1	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152588

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0
2.5°	534.5	534.0	532.8	532.0	532.0	530.6	529.7	529.2	528.9	527.8	527.8
5°	532.8	530.9	528.9	527.5	526.6	525.3	523.0	521.9	520.4	519.4	518.8
7.5°	529.2	525.5	522.4	520.2	517.4	515.1	512.3	509.7	507.3	506.1	505.6
10°	523.5	518.8	514.0	509.7	505.8	501.9	498.2	494.6	491.5	489.2	486.9
12.5°	518.2	510.9	504.7	498.5	492.3	487.6	482.5	477.1	472.6	468.4	467.3
15°	510.9	502.5	494.6	486.9	479.4	471.5	465.3	459.4	452.1	447.4	443.6
17.5°	504.1	494.0	484.5	475.4	466.1	458.0	448.7	440.8	433.6	426.2	420.8
20°	496.8	485.9	475.8	465.6	455.4	445.1	434.4	424.2	415.2	406.5	397.8
22.5°	490.4	479.1	469.2	458.2	447.0	435.2	422.8	410.2	399.8	388.5	378.3
25°	486.4	474.1	463.9	453.3	440.8	427.9	413.9	399.0	386.2	373.4	361.2
27.5°	486.4	470.4	460.0	449.3	436.6	422.8	407.4	391.1	376.7	362.4	347.5
30°	490.7	471.0	456.9	445.6	432.6	417.8	400.6	383.4	367.7	350.8	336.5
32.5°	494.6	472.0	454.6	440.3	425.4	410.8	393.3	375.0	357.6	341.6	326.3
35°	497.1	472.0	450.4	432.1	415.2	400.9	383.7	365.5	347.8	332.0	317.9
37.5°	497.4	469.8	443.6	422.8	405.1	390.2	373.9	356.7	339.9	325.2	313.4
40°	494.6	465.3	436.9	413.0	394.4	379.3	364.4	348.8	333.7	321.6	311.4
42.5°	489.5	460.5	430.5	405.1	385.7	369.9	356.2	342.9	329.7	319.3	310.9
45°	482.0	454.1	424.6	400.3	381.2	364.6	351.1	340.1	328.9	320.1	311.7
47.5°	475.1	451.8	426.5	403.4	383.4	366.3	352.5	343.2	334.5	328.6	317.1
50°	473.8	450.7	427.4	406.0	385.7	368.3	356.2	351.4	348.8	345.2	327.5
52.5°	469.8	450.4	433.6	421.8	408.8	400.6	388.0	392.4	389.6	376.7	344.7
55°	511.2	516.8	532.5	555.0	575.9	580.6	579.3	573.9	545.5	469.2	386.0
57.5°	702.8	734.5	764.4	777.6	776.0	761.0	750.3	728.6	687.6	594.7	467.6
60°	968.9	974.0	958.2	934.8	895.4	862.6	827.4	786.8	727.3	636.4	517.6
62.5°	1214.0	1145.9	1075.9	1009.9	950.1	897.7	848.8	792.2	714.6	619.8	511.2
65°	1386.9	1242.9	1132.3	1037.8	953.2	880.0	819.0	745.5	658.0	572.5	473.8
67.5°	1476.2	1255.3	1085.7	954.0	833.9	732.5	651.3	579.8	514.8	477.4	414.7
70°	1376.6	1065.4	829.1	680.2	536.5	430.2	339.9	285.3	266.4	301.9	314.0
72.5°	1025.7	693.5	493.2	381.5	292.3	233.0	178.7	140.4	114.2	119.9	155.5
75°	485.0	299.4	211.6	160.9	128.0	106.0	86.6	79.4	66.4	55.1	51.8
77.5°	188.8	137.6	113.7	83.3	59.1	47.6	40.5	39.1	40.0	38.9	38.2
80°	143.7	97.3	61.0	44.8	38.5	34.0	30.1	29.0	29.5	31.0	32.3
82.5°	80.2	50.1	37.1	32.3	29.0	24.8	22.5	20.8	21.1	22.8	25.9
85°	31.0	24.1	22.2	21.3	20.0	16.1	13.8	14.1	16.1	19.2	19.2
87.5°	3.4	3.4	4.5	3.4	3.4	3.4	3.1	3.6	3.9	5.1	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152588

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0	532.0
2.5°	527.3	527.3	527.3	526.6	526.9	525.8	525.8	525.0	526.3	525.5	525.3
5°	519.1	518.8	517.6	517.6	517.6	517.6	518.4	516.3	517.9	517.9	517.1
7.5°	505.3	505.3	502.2	503.8	503.3	504.1	505.3	504.1	505.8	506.9	506.1
10°	486.1	486.1	483.6	485.6	484.8	486.7	488.7	487.6	488.7	490.4	490.9
12.5°	465.1	463.9	461.7	462.5	462.5	463.6	464.5	465.9	467.3	469.5	470.7
15°	440.5	438.9	436.1	436.1	434.4	434.9	436.6	437.2	440.0	443.1	446.7
17.5°	415.5	411.3	408.2	404.6	401.8	404.0	406.0	407.4	409.6	414.4	416.9
20°	391.9	383.4	377.5	372.7	369.6	371.1	373.6	375.3	377.3	378.3	379.3
22.5°	368.5	359.0	350.8	344.9	339.9	341.2	340.1	339.3	340.7	337.0	336.8
25°	348.3	337.0	326.0	319.1	312.8	310.9	305.0	303.5	299.6	296.5	294.3
27.5°	333.7	319.1	306.9	298.8	288.9	281.7	274.0	266.4	262.2	257.1	254.6
30°	322.1	306.6	292.3	278.5	265.6	254.3	244.1	234.3	227.6	220.3	215.5
32.5°	311.4	297.1	279.7	260.8	243.3	230.7	217.5	206.2	195.5	186.0	179.0
35°	304.1	288.1	265.9	242.8	223.1	208.2	194.1	178.0	165.2	152.7	145.2
37.5°	300.2	280.5	253.2	227.6	205.7	188.8	171.3	152.7	137.0	125.5	114.0
40°	297.1	272.8	242.0	214.1	191.0	170.8	150.5	128.6	111.1	99.1	90.1
42.5°	293.7	264.5	232.1	203.4	177.8	154.2	129.7	106.3	89.7	81.3	77.4
45°	290.1	257.1	222.8	193.3	164.9	136.2	108.0	86.3	76.5	73.7	73.7
47.5°	289.2	252.3	216.1	183.4	150.3	115.3	88.1	74.5	71.7	72.3	73.5
50°	292.5	251.0	210.2	171.9	130.8	93.4	74.5	70.1	70.6	72.3	74.0
52.5°	300.7	252.0	203.9	155.9	107.8	77.1	68.9	68.6	70.4	72.8	74.5
55°	314.5	252.0	192.1	131.9	86.1	69.2	66.9	68.1	70.4	72.5	74.0
57.5°	344.0	249.5	171.3	105.5	72.0	66.4	66.4	67.8	69.7	72.0	73.2
60°	379.3	246.1	142.1	81.6	65.0	64.1	66.1	67.8	69.5	71.5	72.5
62.5°	381.5	237.4	112.5	67.6	61.3	62.7	65.8	68.1	68.6	70.1	71.5
65°	350.6	207.0	89.4	60.5	59.7	61.9	65.0	66.6	66.9	67.6	68.9
67.5°	306.9	168.8	72.3	57.1	57.9	60.5	62.2	63.6	64.5	65.8	66.1
70°	252.0	135.6	61.9	53.8	54.6	57.4	58.8	60.2	61.9	63.6	62.7
72.5°	178.7	105.5	54.3	50.1	51.2	53.8	55.4	56.6	57.9	59.7	58.5
75°	76.0	73.7	46.9	45.3	46.9	48.7	50.4	52.0	53.5	54.3	54.3
77.5°	38.9	43.3	40.5	40.5	41.7	43.3	44.8	46.4	47.3	48.1	49.2
80°	33.0	33.5	34.0	35.1	36.3	38.0	39.4	40.8	41.0	41.3	42.0
82.5°	27.3	28.4	29.0	30.7	31.5	32.0	33.0	33.0	33.5	33.5	32.6
85°	19.7	21.1	22.0	22.2	22.0	22.2	22.5	23.1	24.5	24.5	23.3
87.5°	5.6	5.4	6.7	7.0	7.6	8.7	9.8	11.8	12.3	13.0	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152588

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	532.0	532.0	532.0	532.0
2.5°	525.0	525.5	524.4	524.7
5°	517.1	518.2	516.8	518.4
7.5°	506.9	508.6	508.4	508.1
10°	492.3	494.6	494.6	495.4
12.5°	473.8	475.1	476.3	476.9
15°	448.7	451.3	452.6	452.6
17.5°	418.7	420.3	421.1	420.0
20°	380.3	379.8	380.1	377.3
22.5°	336.2	337.0	334.5	335.0
25°	292.8	291.5	292.5	290.9
27.5°	251.0	251.2	248.1	249.5
30°	211.0	209.6	205.7	207.7
32.5°	172.4	168.8	164.6	162.1
35°	136.2	130.6	128.6	127.8
37.5°	106.9	100.7	98.8	96.5
40°	85.0	82.7	81.9	82.4
42.5°	76.3	76.3	76.8	77.1
45°	74.0	74.8	75.6	76.0
47.5°	74.3	75.1	76.3	76.5
50°	74.8	75.6	76.5	76.8
52.5°	75.1	75.1	75.6	76.0
55°	74.5	74.3	74.5	74.8
57.5°	73.5	72.8	73.2	74.0
60°	72.8	72.0	72.5	73.2
62.5°	71.5	71.2	71.7	72.0
65°	68.4	68.6	69.5	69.5
67.5°	65.6	65.8	66.1	66.4
70°	62.2	62.5	63.0	63.3
72.5°	58.2	59.4	60.2	61.3
75°	55.1	56.3	57.9	59.1
77.5°	49.8	50.7	52.6	54.0
80°	42.2	42.0	42.2	43.0
82.5°	32.3	32.3	32.0	31.8
85°	22.8	22.5	21.7	21.7
87.5°	12.3	12.1	11.8	11.3
90°	0.0	0.0	0.0	0.0

(END OF REPORT)