

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P150896

Luminaire Tested: **AVS-F02-LED-E-U-SL3-HSS-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P150896
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33727)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-SL3-HSS-7050
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ SPILL LIGHT CONTROL AND
HOUSE SIDE SHIELD
Light Source: (14) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2937.4 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type III - Short - Non-Cutoff
BUG Rating: B0 - U0 - G1

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P150896

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.8 fc
 Type III - Short - Non-Cutoff

REPORT NUMBER: P150896

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P150896

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	63.7	0.0	63.7
	% Fixture	2.2	0.0	2.2
Street Side	Lumens	2873.7	0.0	2873.7
	% Fixture	97.8	0.0	97.8
Total	Lumens	2937.4	0.0	2937.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.9	0.3
10°-20°	42.1	1.4
20°-30°	90.8	3.1
30°-40°	193.8	6.6
40°-50°	428.7	14.6
50°-60°	726.5	24.7
60°-70°	969.4	33.0
70°-80°	427.0	14.5
80°-90°	49.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2937.4	100.0
0°-180°	2937.4	100.0

Coefficient of Utilization



REPORT NUMBER: P150896


CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	122.7	4.2			
FM	(30°-60°)	1321.0	45.0			
FH	(60°-80°)	1382.8	47.1			G1/1800
FVH	(80°-90°)	47.2	1.6			G1/100
BL	(0°-30°)	20.1	0.7	B0/110		
BM	(30°-60°)	27.9	1.0	B0/220		
BH	(60°-80°)	13.7	0.5	B0/110		G0/110
BVH	(80°-90°)	2.0	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type III Short





REPORT NUMBER: P150896

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	67°	68°
0°	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7
2.5°	111.8	111.3	109.0	109.0	105.6	103.3	100.5	97.7	97.7	97.1	96.6
5°	148.0	144.6	144.0	137.8	132.7	125.4	118.5	109.5	108.4	107.3	106.7
7.5°	188.1	187.5	182.4	175.0	164.9	151.3	137.8	123.1	120.8	119.7	117.5
10°	240.0	237.2	230.4	218.0	202.7	184.7	162.6	139.5	136.7	134.4	133.3
12.5°	289.7	284.7	280.6	264.9	245.7	219.1	192.5	159.3	157.0	154.2	149.6
15°	336.0	331.5	324.7	311.2	289.7	256.4	225.3	184.7	179.0	175.0	171.7
17.5°	372.1	369.3	361.5	346.2	323.0	293.7	256.4	210.7	206.1	201.0	194.8
20°	406.6	402.7	390.3	369.3	344.5	321.9	293.1	244.6	238.3	232.1	225.3
22.5°	439.4	435.4	415.0	380.6	354.1	344.5	334.3	282.9	273.4	268.3	261.5
25°	485.1	476.6	445.0	390.3	354.6	362.0	379.5	332.6	323.6	316.3	305.5
27.5°	546.6	535.3	485.7	404.4	356.9	381.1	431.4	393.1	383.4	374.9	363.1
30°	616.1	608.8	549.4	438.2	373.3	409.4	489.6	469.8	458.5	448.4	434.3
32.5°	686.1	676.0	617.2	502.6	417.3	464.2	562.5	559.1	544.4	534.8	519.6
35°	747.7	742.6	699.2	608.2	517.8	560.2	659.6	663.5	650.6	640.4	623.4
37.5°	789.4	789.4	781.0	721.7	677.6	709.3	802.5	803.0	790.1	766.8	758.4
40°	811.0	817.1	847.7	859.0	856.7	897.3	989.9	979.8	969.0	957.2	928.9
42.5°	855.0	860.6	925.6	1003.5	1054.3	1108.0	1171.8	1168.4	1155.4	1134.0	1108.0
45°	929.5	936.9	1014.2	1137.9	1242.4	1318.7	1359.3	1343.4	1330.5	1310.2	1296.6
47.5°	1024.4	1038.5	1126.0	1279.1	1405.0	1531.0	1573.3	1531.5	1520.2	1504.5	1482.4
50°	1125.5	1139.1	1232.2	1407.3	1549.5	1699.8	1770.4	1699.8	1683.4	1678.3	1653.5
52.5°	1213.1	1224.4	1314.1	1506.1	1660.3	1836.5	1939.3	1846.0	1834.2	1817.3	1799.2
55°	1265.0	1274.0	1358.1	1553.6	1735.3	1959.6	2102.5	2020.5	2003.0	1996.3	1970.3
57.5°	1282.5	1291.5	1367.2	1559.8	1776.1	2071.9	2300.6	2303.5	2282.6	2258.3	2250.4
60°	1282.5	1292.6	1356.5	1544.5	1815.5	2191.7	2565.0	2800.4	2755.2	2750.8	2722.0
62.5°	1229.4	1239.0	1303.3	1497.6	1868.6	2353.2	2933.2	3348.8	3335.8	3306.4	3259.0
65°	1114.2	1119.8	1183.1	1377.9	1848.3	2501.7	3252.2	3713.6	3692.6	3635.1	3574.1
66°	1062.3	1066.7	1126.0	1309.5	1781.7	2522.1	3308.7	3759.3	3724.9	3676.3	3607.5
67.5°	987.2	995.0	1036.8	1182.5	1621.9	2451.4	3273.1	3727.2	3697.2	3638.4	3569.5
70°	659.1	653.4	800.7	907.5	1235.6	1997.4	2936.6	3346.5	3347.0	3319.4	3291.7
72.5°	312.8	316.3	359.2	558.5	808.7	1334.4	2337.4	2671.1	2709.5	2659.8	2625.4
75°	224.8	229.8	255.9	341.7	482.3	800.7	1515.1	1868.1	1869.2	1781.1	1702.6
77.5°	65.5	68.3	96.0	210.7	361.5	540.4	870.3	1038.5	1014.2	951.0	891.7
80°	27.2	27.2	28.2	67.2	145.2	367.0	608.8	799.7	796.8	772.5	737.5
82.5°	10.2	10.8	13.6	27.7	34.4	90.4	406.0	694.0	692.3	657.9	633.1
85°	1.1	1.1	3.4	11.8	13.0	16.9	81.3	306.1	304.4	306.1	268.3
87.5°	0.0	0.0	0.5	1.1	1.7	2.3	3.4	11.8	13.0	12.4	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150896

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7050

CANDELA DISTRIBUTION (continued):

	69°	70°	71°	72°	73°	74°	75°	76°	77°	78°	79°
0°	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7
2.5°	96.6	95.4	95.4	94.9	94.9	94.9	94.3	93.8	93.8	93.2	92.6
5°	105.6	104.5	103.9	102.8	102.2	101.7	100.5	100.0	98.9	98.2	97.7
7.5°	116.4	114.1	113.5	111.8	110.2	109.0	107.9	106.2	105.1	102.8	102.2
10°	129.8	127.0	124.8	122.6	120.8	118.0	116.4	114.1	111.8	110.2	108.4
12.5°	147.4	143.4	140.0	137.8	133.9	130.5	127.0	125.4	120.8	118.5	115.8
15°	166.6	162.1	158.1	153.6	150.8	145.2	140.6	135.5	133.3	129.3	124.8
17.5°	191.4	184.1	177.9	173.4	167.8	162.1	157.0	151.9	145.2	140.6	134.9
20°	218.0	211.8	203.3	195.4	188.6	181.9	174.5	167.8	161.6	154.2	147.4
22.5°	251.8	242.8	232.6	224.8	215.8	208.4	198.2	189.2	179.0	169.4	161.6
25°	294.8	282.9	273.4	262.1	251.3	240.0	227.6	216.3	203.3	194.3	180.7
27.5°	347.9	336.6	323.6	308.9	298.1	281.2	264.9	250.8	235.4	221.3	206.1
30°	415.6	399.3	385.7	371.6	350.2	333.8	314.5	295.3	274.4	260.3	237.2
32.5°	497.0	479.5	459.1	438.8	419.1	395.9	372.1	348.4	325.3	299.3	275.5
35°	596.4	575.4	552.3	530.3	499.8	474.9	445.0	412.2	386.2	356.4	326.4
37.5°	727.9	693.5	673.2	649.9	608.8	574.9	541.6	508.8	463.1	431.4	389.1
40°	892.8	872.5	839.2	801.9	764.7	720.0	674.8	631.4	578.2	534.2	485.1
42.5°	1086.5	1056.6	1022.7	969.0	931.2	878.7	827.4	769.7	704.8	648.3	590.7
45°	1268.4	1232.7	1206.8	1153.2	1113.6	1051.5	989.4	928.4	853.3	780.4	713.8
47.5°	1464.9	1435.5	1392.6	1349.1	1309.0	1239.0	1171.8	1097.8	1018.8	932.3	845.9
50°	1637.7	1614.5	1585.2	1532.6	1488.0	1429.3	1350.3	1269.5	1169.5	1083.7	985.4
52.5°	1784.5	1766.4	1725.2	1688.0	1647.9	1592.5	1521.9	1444.6	1336.7	1242.4	1130.6
55°	1957.8	1944.9	1908.7	1885.6	1850.1	1796.9	1730.9	1659.2	1545.1	1442.3	1315.8
57.5°	2242.0	2231.8	2200.1	2190.6	2155.5	2109.2	2027.9	1951.1	1817.8	1690.2	1545.6
60°	2712.3	2692.0	2645.7	2622.0	2548.0	2485.9	2380.3	2274.7	2113.8	1951.1	1777.2
62.5°	3216.1	3159.1	3070.9	2995.2	2890.3	2782.4	2641.1	2479.7	2291.1	2097.9	1898.0
65°	3487.7	3390.6	3279.3	3159.1	3022.9	2864.2	2686.3	2492.6	2289.9	2086.1	1874.8
66°	3518.8	3409.2	3291.2	3157.3	3006.0	2837.1	2656.5	2453.2	2242.5	2043.7	1832.5
67.5°	3479.8	3365.2	3240.3	3091.8	2928.1	2753.0	2563.2	2352.0	2149.3	1947.7	1742.2
70°	3207.0	3093.0	2981.7	2825.3	2650.8	2474.6	2295.0	2059.0	1866.9	1681.8	1498.8
72.5°	2561.0	2483.6	2373.5	2239.7	2069.6	1863.0	1713.4	1502.2	1335.5	1156.0	1014.2
75°	1600.4	1491.4	1355.3	1184.8	1054.9	887.2	799.7	639.3	544.4	461.3	381.1
77.5°	818.2	736.4	640.9	545.0	453.0	361.5	279.6	197.6	133.3	92.6	68.9
80°	676.0	603.7	524.7	437.1	355.8	276.2	198.8	135.5	86.4	56.5	44.0
82.5°	558.5	497.5	426.9	345.6	275.0	216.9	150.8	98.2	61.0	39.5	31.1
85°	237.7	215.8	166.6	132.1	99.4	73.4	51.4	34.4	24.2	19.8	18.0
87.5°	10.2	11.3	10.8	8.5	6.2	6.2	5.6	4.6	4.6	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150896

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7050

CANDELA DISTRIBUTION (continued):

	80°	81°	82°	83°	84°	85°	95°	105°	115°	125°	135°
0°	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.7
2.5°	92.6	92.0	91.5	91.5	90.9	90.4	86.9	84.1	80.7	78.4	76.3
5°	96.6	96.0	94.9	94.3	93.2	92.6	85.3	79.1	74.0	70.1	67.2
7.5°	100.5	100.0	98.2	96.6	96.0	94.9	83.0	75.1	68.3	63.8	61.0
10°	105.6	103.9	102.2	100.0	98.2	96.6	80.7	70.6	63.2	59.3	56.5
12.5°	113.0	110.2	107.3	104.5	102.2	99.4	79.6	66.6	59.3	54.8	51.9
15°	121.5	117.5	114.1	110.7	106.7	103.9	77.4	63.2	56.0	51.4	48.0
17.5°	129.3	124.8	119.7	114.6	110.7	106.7	75.1	59.9	52.5	48.0	44.7
20°	140.6	133.9	127.7	121.5	115.8	110.7	71.7	56.5	49.7	44.7	41.2
22.5°	153.1	145.2	137.2	128.7	121.5	114.6	68.9	53.7	46.8	41.8	37.8
25°	168.8	159.3	148.5	137.8	129.3	120.3	66.1	50.8	44.0	39.0	35.0
27.5°	190.9	177.3	165.5	151.9	139.0	128.7	63.8	48.6	41.2	36.2	32.2
30°	220.8	201.0	182.4	167.8	152.4	137.8	61.6	45.7	39.0	33.4	28.8
32.5°	254.1	231.0	209.5	187.5	168.3	151.3	59.3	43.5	36.2	30.5	26.5
35°	295.3	266.0	237.2	211.8	188.6	166.0	57.0	41.2	33.9	27.7	23.7
37.5°	354.6	317.9	280.1	247.4	217.4	187.5	55.3	39.0	31.1	24.9	20.9
40°	436.0	388.5	342.2	297.6	258.7	221.3	53.1	36.7	28.8	22.6	18.7
42.5°	524.0	466.4	405.5	355.2	301.6	254.7	50.8	34.4	26.5	20.3	16.4
45°	633.6	561.9	487.9	419.6	354.1	293.7	48.6	32.2	23.7	18.0	14.1
47.5°	753.4	661.9	578.2	492.4	414.5	342.2	45.7	30.5	21.5	15.9	12.4
50°	876.5	779.9	674.3	576.6	483.9	390.8	42.9	27.7	19.2	14.1	10.2
52.5°	1009.1	895.0	787.3	665.8	557.9	454.6	40.1	25.4	17.5	12.4	8.5
55°	1178.0	1050.4	923.8	787.8	657.9	528.6	37.3	22.6	15.2	10.8	6.7
57.5°	1390.4	1239.0	1083.7	930.1	772.5	625.7	35.0	19.8	13.0	9.0	5.6
60°	1590.8	1414.1	1226.0	1049.2	871.4	700.2	31.6	17.5	11.3	7.4	5.6
62.5°	1694.7	1493.2	1290.4	1095.5	905.8	726.8	28.2	14.7	9.6	6.2	5.1
65°	1669.3	1463.7	1267.3	1070.7	884.9	709.8	24.9	13.0	8.5	5.6	5.1
66°	1632.6	1429.3	1231.6	1044.8	867.4	691.8	23.1	12.4	7.9	5.6	4.6
67.5°	1552.4	1355.9	1167.3	993.4	819.4	657.3	20.9	11.3	7.4	5.1	4.6
70°	1325.9	1147.5	996.7	842.0	700.2	554.0	16.9	9.6	6.2	4.6	4.6
72.5°	877.6	756.2	655.6	564.1	471.5	365.9	14.1	7.9	5.1	4.6	3.9
75°	330.9	299.3	257.0	231.0	201.6	176.8	11.3	5.1	3.9	3.9	3.9
77.5°	58.8	54.2	48.0	44.0	40.6	37.3	9.0	3.4	3.4	3.9	3.9
80°	39.5	36.7	33.4	30.5	28.2	25.4	6.2	2.8	3.4	3.4	3.9
82.5°	28.2	26.5	24.9	22.6	20.9	18.7	3.9	2.8	3.4	3.4	3.4
85°	16.9	15.9	14.7	13.6	11.8	11.3	2.8	2.8	2.8	3.4	3.4
87.5°	4.6	3.9	4.6	4.6	3.4	3.9	2.3	2.3	2.3	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150896

CATALOG NUMBER: AVS-F02-LED-E-U-SL3-HSS-7050

CANDELA DISTRIBUTION (continued):

	145°	155°	165°	175°	180°
0°	88.7	88.7	88.7	88.7	88.7
2.5°	75.1	75.1	74.0	75.6	75.6
5°	65.0	65.0	64.4	65.0	65.0
7.5°	59.3	58.8	58.8	58.8	59.3
10°	54.2	53.7	53.7	53.7	53.7
12.5°	49.7	49.1	48.6	49.1	49.1
15°	45.7	44.7	44.7	44.7	44.7
17.5°	42.4	41.2	40.6	40.6	40.6
20°	39.0	37.3	37.3	37.3	37.3
22.5°	35.5	33.9	33.9	33.9	33.9
25°	32.2	30.5	30.5	30.5	30.5
27.5°	29.3	27.7	27.7	27.7	27.7
30°	26.0	24.9	24.9	25.4	24.9
32.5°	23.7	22.1	22.1	22.6	22.6
35°	20.9	19.8	19.8	19.8	19.8
37.5°	18.0	16.9	16.9	16.9	16.9
40°	15.9	14.7	14.1	14.7	14.7
42.5°	13.6	12.4	11.8	11.8	11.8
45°	11.8	10.2	9.6	10.2	10.2
47.5°	9.6	8.5	8.5	9.0	9.0
50°	7.4	7.4	7.9	9.0	9.0
52.5°	6.7	6.7	7.9	9.0	9.0
55°	6.2	6.7	7.9	8.5	9.0
57.5°	5.6	6.7	7.9	8.5	8.5
60°	5.6	6.2	7.4	8.5	8.5
62.5°	5.1	5.6	6.7	7.9	7.9
65°	5.1	5.6	6.7	7.9	7.9
66°	5.1	5.6	6.7	7.9	7.9
67.5°	5.1	5.6	6.7	7.9	7.9
70°	5.1	5.6	6.7	7.4	7.4
72.5°	4.6	5.1	6.2	7.4	7.4
75°	4.6	5.1	6.2	7.4	7.4
77.5°	4.6	5.1	6.2	7.4	7.4
80°	4.6	5.1	6.2	6.7	7.4
82.5°	3.9	5.1	5.6	6.7	6.7
85°	3.9	4.6	5.6	6.2	6.7
87.5°	3.4	3.9	4.6	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)