

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152598

Luminaire Tested: **AVS-E02-LED-E-U-SL4-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152598
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-SL4-8030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (42) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4986.5 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152598

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 10.7 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152598

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P152598

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1035.1	0.0	1035.1
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	3951.4	0.0	3951.4
	% Fixture	79.2	0.0	79.2
Total	Lumens	4986.5	0.0	4986.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.4	2.0
10°-20°	272.1	5.5
20°-30°	402.8	8.1
30°-40°	509.1	10.2
40°-50°	575.7	11.5
50°-60°	819.3	16.4
60°-70°	1525.8	30.6
70°-80°	699.3	14.0
80°-90°	83.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4986.5	100.0
0°-180°	4986.5	100.0

Coefficient of Utilization



REPORT NUMBER: P152598


CATALOG NUMBER: AVS-E02-LED-E-U-SL4-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	454.1	9.1			
FM	(30°-60°)	1460.9	29.3			
FH	(60°-80°)	1974.8	39.6			G2/5000
FVH	(80°-90°)	61.6	1.2			G1/100
BL	(0°-30°)	320.3	6.4	B1/500		
BM	(30°-60°)	443.2	8.9	B1/1000		
BH	(60°-80°)	250.2	5.0	B1/500		G1/500
BVH	(80°-90°)	21.4	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P152598

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1080.3	1083.1	1079.8	1079.2	1079.2	1078.7	1075.2	1074.7	1070.2	1070.8	1071.9
5°	1088.2	1089.3	1087.0	1086.5	1085.4	1083.1	1080.3	1076.9	1073.6	1070.2	1067.4
7.5°	1096.1	1094.9	1093.3	1093.3	1091.6	1088.2	1082.6	1078.0	1070.8	1066.8	1061.8
10°	1107.4	1105.6	1103.4	1102.3	1099.5	1094.4	1086.5	1080.3	1071.3	1063.4	1055.0
12.5°	1118.0	1117.4	1114.1	1112.3	1107.9	1102.8	1093.3	1083.7	1071.9	1059.5	1048.2
15°	1137.1	1134.9	1131.5	1128.1	1120.8	1114.1	1099.5	1088.2	1071.3	1055.0	1037.5
17.5°	1170.4	1166.4	1163.0	1155.8	1146.7	1134.9	1113.5	1094.4	1071.3	1047.7	1028.0
20°	1231.1	1222.7	1218.1	1208.6	1192.8	1171.5	1138.2	1107.4	1073.0	1042.6	1016.2
22.5°	1299.8	1294.1	1288.0	1281.8	1257.0	1226.0	1181.0	1134.9	1083.1	1040.3	1006.6
25°	1376.8	1369.5	1366.1	1355.4	1332.3	1296.9	1235.6	1171.5	1106.2	1049.3	1006.6
27.5°	1445.5	1443.2	1442.7	1430.3	1408.3	1366.7	1294.1	1217.0	1137.7	1068.0	1015.0
30°	1508.0	1505.7	1504.6	1497.8	1472.4	1423.0	1344.1	1257.5	1172.0	1093.8	1030.8
32.5°	1574.3	1567.0	1563.6	1550.7	1522.0	1464.0	1374.0	1284.0	1199.1	1119.2	1048.2
35°	1628.3	1622.2	1615.4	1596.8	1556.3	1487.7	1386.9	1293.0	1209.7	1133.2	1057.2
37.5°	1667.8	1661.6	1652.0	1628.3	1578.2	1495.5	1386.4	1290.2	1205.8	1131.0	1059.0
40°	1685.2	1679.0	1668.8	1639.1	1582.2	1491.1	1375.8	1277.2	1194.0	1119.2	1052.1
42.5°	1678.4	1673.9	1660.9	1632.2	1569.8	1470.8	1354.3	1253.1	1171.5	1100.0	1037.0
45°	1652.5	1649.1	1636.8	1606.4	1541.7	1438.1	1322.8	1222.7	1144.5	1076.4	1016.7
47.5°	1613.7	1612.5	1600.2	1570.4	1506.2	1405.5	1290.2	1192.8	1117.4	1053.3	999.9
50°	1571.0	1565.3	1559.2	1531.6	1473.1	1377.4	1266.5	1174.3	1102.3	1044.9	992.5
52.5°	1543.9	1542.3	1536.6	1511.9	1455.6	1361.0	1255.9	1167.6	1101.1	1043.2	988.6
55°	1783.6	1787.6	1735.9	1628.3	1533.8	1406.1	1288.0	1201.9	1128.7	1070.2	1030.3
57.5°	2638.3	2620.8	2532.0	2318.8	2077.9	1760.0	1531.0	1392.0	1301.5	1311.6	1331.8
60°	3073.8	3070.5	3054.1	2971.4	2811.1	2569.1	2300.7	1993.0	1895.0	1905.7	1913.6
62.5°	3268.5	3273.6	3285.9	3255.0	3212.7	3142.5	3008.5	2884.8	2753.7	2704.7	2573.6
65°	3358.5	3367.6	3395.6	3413.1	3429.4	3441.8	3494.7	3639.9	3735.5	3556.6	3140.2
67.5°	3172.3	3215.6	3308.4	3399.1	3480.1	3595.4	3774.3	4111.4	4346.0	4126.0	3522.3
70°	2312.5	2371.6	2477.9	2758.1	3057.5	3319.2	3665.7	4178.9	4532.7	4362.9	3616.8
72.5°	1449.9	1466.3	1513.6	1616.5	1838.8	2174.7	2780.6	3550.4	3958.9	3823.3	3056.9
75°	920.0	925.6	923.9	947.6	985.2	1058.3	1298.0	2097.0	2712.0	2500.4	1703.7
77.5°	548.1	556.5	559.9	567.2	585.2	611.1	630.8	713.5	1137.1	1103.9	618.3
80°	459.2	465.9	460.2	458.5	447.4	439.5	449.0	439.5	408.0	392.7	361.8
82.5°	243.1	242.5	240.8	257.1	290.4	316.2	336.0	331.4	299.9	255.4	216.6
85°	133.4	137.8	137.8	143.5	138.4	139.0	143.5	151.4	140.1	117.0	95.6
87.5°	11.3	17.4	14.1	17.4	23.6	16.9	16.3	16.3	14.1	10.2	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152598

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1069.0	1068.0	1065.7	1064.0	1064.0	1061.1	1059.5	1058.3	1057.8	1055.5	1055.5
5°	1065.7	1061.8	1057.8	1055.0	1053.3	1050.5	1046.0	1043.7	1040.9	1038.7	1037.5
7.5°	1058.3	1051.1	1044.9	1040.3	1034.7	1030.3	1024.6	1019.6	1014.5	1012.2	1011.1
10°	1047.2	1037.5	1028.0	1019.6	1011.7	1003.8	996.5	989.1	983.0	978.4	974.0
12.5°	1036.4	1021.8	1009.4	997.0	984.7	975.1	965.0	954.3	945.3	936.8	934.6
15°	1021.8	1004.9	989.1	974.0	958.8	943.0	930.7	918.9	904.1	894.6	887.4
17.5°	1008.3	988.1	968.9	950.9	932.3	916.1	897.4	881.7	867.0	852.4	841.8
20°	993.7	971.7	951.5	931.2	911.0	890.2	868.7	848.5	830.5	813.1	795.6
22.5°	980.7	958.2	938.5	916.6	894.1	870.5	845.7	820.3	799.6	777.0	756.8
25°	972.8	948.1	927.9	906.4	881.7	855.9	827.7	797.8	772.5	746.6	722.5
27.5°	972.8	940.7	920.0	898.5	873.3	845.7	814.7	782.1	753.4	724.7	694.9
30°	981.2	941.9	913.8	891.3	865.4	835.5	801.2	766.9	735.4	701.7	673.0
32.5°	989.1	944.1	909.2	880.5	850.8	821.5	786.6	750.1	715.1	683.1	652.6
35°	994.2	944.1	900.8	864.2	830.5	801.8	767.5	730.9	695.4	663.9	635.9
37.5°	994.8	939.7	887.4	845.7	810.3	780.4	747.8	713.5	679.7	650.5	626.8
40°	989.1	930.7	873.8	826.0	788.8	758.4	728.6	697.7	667.4	643.1	622.9
42.5°	979.1	921.0	860.8	810.3	771.4	739.9	712.3	685.9	659.5	638.7	621.8
45°	963.8	908.1	849.0	800.6	762.4	729.2	702.2	680.2	657.7	640.3	623.4
47.5°	950.4	903.6	853.0	806.8	766.9	732.5	705.0	686.4	669.0	657.2	634.1
50°	947.6	901.3	854.7	811.9	771.4	736.5	712.3	702.8	697.7	690.4	654.9
52.5°	939.7	900.8	867.0	843.4	817.5	801.2	776.0	784.9	779.3	753.4	689.2
55°	1022.4	1033.6	1065.1	1110.2	1151.8	1161.3	1158.5	1147.9	1091.0	938.5	772.0
57.5°	1405.5	1469.1	1528.7	1555.2	1551.8	1522.0	1500.6	1457.3	1375.1	1189.4	935.1
60°	1937.8	1948.0	1916.4	1869.7	1791.0	1725.1	1654.8	1573.8	1454.5	1272.7	1035.3
62.5°	2427.9	2291.7	2151.6	2020.0	1900.1	1795.4	1697.5	1584.5	1429.1	1239.6	1022.4
65°	2773.9	2485.8	2264.7	2075.6	1906.3	1760.0	1637.9	1491.1	1316.1	1145.0	947.6
67.5°	2952.3	2510.6	2171.3	1908.0	1667.8	1465.2	1302.6	1159.7	1029.6	954.8	829.3
70°	2753.1	2130.8	1658.1	1360.5	1073.0	860.3	679.7	570.6	532.8	603.7	628.0
72.5°	2051.5	1386.9	986.3	763.0	584.6	465.9	357.3	280.7	228.4	239.7	311.2
75°	970.1	598.7	423.1	321.9	256.1	212.1	173.3	158.7	132.7	110.3	103.5
77.5°	377.5	275.1	227.4	166.5	118.1	95.1	81.0	78.2	79.9	77.6	76.5
80°	287.6	194.7	122.1	89.4	77.1	68.1	60.2	57.9	59.1	61.9	64.7
82.5°	160.3	100.1	74.3	64.7	57.9	49.5	45.0	41.7	42.2	45.6	51.8
85°	61.9	48.4	44.5	42.8	40.0	32.0	27.6	28.1	32.0	38.2	38.2
87.5°	6.7	6.7	9.0	6.7	6.7	6.7	6.2	7.4	7.9	10.2	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152598

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1054.4	1054.4	1054.4	1053.3	1053.9	1051.6	1051.6	1049.9	1052.7	1051.1	1050.5
5°	1038.1	1037.5	1035.3	1035.3	1035.3	1035.3	1037.0	1032.4	1035.9	1035.9	1034.2
7.5°	1010.6	1010.6	1004.4	1007.8	1006.6	1008.3	1010.6	1008.3	1011.7	1013.9	1012.2
10°	972.2	972.2	967.3	971.2	969.4	973.4	977.3	975.1	977.3	980.7	981.9
12.5°	930.1	927.9	923.3	925.0	925.0	927.3	928.9	931.8	934.6	939.1	941.3
15°	881.1	877.7	872.1	872.1	868.7	869.8	873.3	874.4	880.0	886.2	893.5
17.5°	831.1	822.6	816.4	809.1	803.5	808.0	811.9	814.7	819.3	828.8	833.9
20°	783.8	766.9	755.1	745.5	739.4	742.2	747.3	750.6	754.5	756.8	758.4
22.5°	737.1	717.9	701.7	689.8	679.7	682.5	680.2	678.5	681.3	674.1	673.5
25°	696.6	674.1	652.1	638.0	625.7	621.8	609.9	607.2	599.3	593.1	588.5
27.5°	667.4	638.0	613.9	597.5	577.8	563.2	548.1	532.8	524.4	514.3	509.2
30°	644.2	613.3	584.6	557.0	531.2	508.6	488.4	468.7	455.2	440.5	431.0
32.5°	622.9	594.2	559.3	521.6	486.7	461.3	434.9	412.4	391.1	371.9	357.8
35°	608.2	576.2	531.7	485.6	446.2	416.4	388.2	356.2	330.3	305.5	290.4
37.5°	600.3	560.9	506.4	455.2	411.3	377.5	342.7	305.5	274.0	251.0	227.9
40°	594.2	545.8	483.9	428.2	382.1	341.6	301.0	257.1	222.3	198.0	180.0
42.5°	587.5	528.9	464.1	406.8	355.6	308.3	259.4	212.6	179.5	162.6	154.7
45°	580.1	514.3	445.6	386.5	329.7	272.3	216.1	172.7	153.1	147.5	147.5
47.5°	578.4	504.7	432.1	366.8	300.4	230.7	176.1	149.1	143.5	144.6	146.8
50°	585.2	501.9	420.3	343.8	261.7	186.8	149.1	140.1	141.2	144.6	148.0
52.5°	601.5	504.1	408.0	311.7	215.5	154.2	137.8	137.3	140.6	145.7	149.1
55°	629.0	504.1	384.2	263.9	172.1	138.4	133.9	136.2	140.6	145.2	148.0
57.5°	688.1	499.1	342.7	211.0	144.0	132.7	132.7	135.6	139.6	144.0	146.3
60°	758.4	492.3	284.1	163.2	129.9	128.3	132.2	135.6	139.0	142.9	145.2
62.5°	763.0	474.9	225.1	135.0	122.7	125.5	131.7	136.2	137.3	140.1	142.9
65°	701.0	414.1	179.0	120.9	119.3	123.8	129.9	133.4	133.9	135.0	137.8
67.5°	613.9	337.6	144.6	114.2	116.0	120.9	124.4	127.2	128.8	131.7	132.2
70°	504.1	271.2	123.8	107.5	109.1	114.8	117.6	120.4	123.8	127.2	125.5
72.5°	357.3	211.0	108.6	100.1	102.4	107.5	110.9	113.1	116.0	119.3	117.0
75°	151.9	147.5	94.0	90.6	94.0	97.3	100.7	104.0	106.9	108.6	108.6
77.5°	77.6	86.6	81.0	81.0	83.3	86.6	89.4	92.8	94.5	96.2	98.4
80°	65.8	66.9	68.1	70.4	72.5	76.0	78.8	81.6	82.2	82.7	83.8
82.5°	54.6	56.8	57.9	61.3	63.0	64.1	65.8	65.8	66.9	66.9	65.3
85°	39.4	42.2	43.9	44.5	43.9	44.5	45.0	46.1	48.9	48.9	46.7
87.5°	11.3	10.7	13.5	14.1	15.2	17.4	19.7	23.6	24.8	25.9	25.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152598

CATALOG NUMBER: AVS-E02-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1064.0	1064.0	1064.0	1064.0
2.5°	1049.9	1051.1	1048.8	1049.3
5°	1034.2	1036.4	1033.6	1037.0
7.5°	1013.9	1017.3	1016.7	1016.2
10°	984.7	989.1	989.1	990.9
12.5°	947.6	950.4	952.5	953.7
15°	897.4	902.5	905.3	905.3
17.5°	837.2	840.6	842.3	840.1
20°	760.7	759.6	760.1	754.5
22.5°	672.3	674.1	669.0	670.2
25°	585.7	582.9	585.2	581.8
27.5°	501.9	502.5	496.3	499.1
30°	422.0	419.2	411.3	415.2
32.5°	344.9	337.6	329.1	324.0
35°	272.3	261.0	257.1	255.4
37.5°	213.8	201.5	197.5	193.0
40°	169.9	165.4	163.7	164.9
42.5°	152.4	152.4	153.6	154.2
45°	148.0	149.6	151.4	151.9
47.5°	148.5	150.3	152.4	153.1
50°	149.6	151.4	153.1	153.6
52.5°	150.3	150.3	151.4	151.9
55°	149.1	148.5	149.1	149.6
57.5°	146.8	145.7	146.3	148.0
60°	145.7	144.0	145.2	146.3
62.5°	142.9	142.4	143.5	144.0
65°	136.7	137.3	139.0	139.0
67.5°	131.1	131.7	132.2	132.7
70°	124.4	124.9	126.0	126.6
72.5°	116.5	118.8	120.4	122.7
75°	110.3	112.5	116.0	118.1
77.5°	99.6	101.2	105.2	108.0
80°	84.4	83.8	84.4	86.1
82.5°	64.7	64.7	64.1	63.6
85°	45.6	45.0	43.3	43.3
87.5°	24.8	24.1	23.6	22.5
90°	0.0	0.0	0.0	0.0

(END OF REPORT)