

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155818

Luminaire Tested: **AVS-E02-LED-E-U-T3-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155818
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-T3-8030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (42) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5205.6 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P155818

CATALOG NUMBER: AVS-E02-LED-E-U-T3-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.6 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155818

CATALOG NUMBER: AVS-E02-LED-E-U-T3-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P155818

CATALOG NUMBER: AVS-E02-LED-E-U-T3-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1797.7	0.0	1797.7
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	3407.9	0.0	3407.9
	% Fixture	65.5	0.0	65.5
Total	Lumens	5205.6	0.0	5205.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.0
10°-20°	158.6	3.0
20°-30°	272.5	5.2
30°-40°	442.5	8.5
40°-50°	738.8	14.2
50°-60°	1163.3	22.3
60°-70°	1586.3	30.5
70°-80°	686.7	13.2
80°-90°	103.3	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5205.6	100.0
0°-180°	5205.6	100.0

Coefficient of Utilization



REPORT NUMBER: P155818


CATALOG NUMBER: AVS-E02-LED-E-U-T3-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	243.5	4.7			
FM	(30°-60°)	1453.8	27.9			
FH	(60°-80°)	1625.9	31.2			G1/1800
FVH	(80°-90°)	84.8	1.6			G1/100
BL	(0°-30°)	241.3	4.6	B1/500		
BM	(30°-60°)	890.8	17.1	B1/1000		
BH	(60°-80°)	647.1	12.4	B2/1000		G2/1000
BVH	(80°-90°)	18.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P155818

CATALOG NUMBER: AVS-E02-LED-E-U-T3-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9
2.5°	563.2	565.5	563.2	563.8	564.4	563.8	563.2	563.2	561.6	562.7	563.8
5°	560.9	562.7	562.1	562.7	563.2	562.7	562.1	562.7	561.6	562.1	563.8
7.5°	558.1	557.6	558.1	559.3	560.4	560.4	560.4	560.9	560.4	560.4	562.1
10°	549.7	550.3	551.4	553.1	553.7	555.3	555.3	557.0	557.6	558.8	560.9
12.5°	539.1	539.6	540.7	541.9	544.7	547.5	547.5	551.4	553.1	556.0	559.9
15°	531.2	531.7	532.8	534.0	536.2	539.1	540.7	545.2	548.1	553.1	558.8
17.5°	535.6	535.1	536.2	536.8	536.8	539.1	539.1	542.4	545.8	550.3	557.6
20°	548.6	548.6	549.7	549.7	549.1	550.3	548.1	548.1	548.6	550.9	556.0
22.5°	561.6	560.9	563.2	564.4	564.9	566.6	564.4	563.8	560.9	559.3	560.9
25°	573.9	573.4	576.2	577.8	580.6	582.4	582.4	582.4	580.1	577.3	575.6
27.5°	593.1	593.1	595.9	597.5	599.8	603.2	604.9	604.9	605.4	601.5	598.7
30°	625.1	625.7	626.2	628.5	630.8	631.9	634.1	635.9	637.5	635.2	630.8
32.5°	663.4	660.0	660.0	663.4	666.2	669.5	670.7	673.0	676.3	674.6	674.1
35°	708.9	707.9	706.7	707.9	711.2	715.1	719.7	723.6	721.3	724.7	723.0
37.5°	776.5	777.6	778.1	778.1	777.6	778.8	780.9	784.9	783.8	784.9	787.2
40°	887.9	883.9	880.0	880.5	874.9	876.1	867.0	871.0	871.6	867.7	869.3
42.5°	999.3	1001.6	1003.2	1007.8	1003.8	1001.6	993.1	993.1	988.6	984.7	983.5
45°	1119.7	1124.1	1124.8	1133.8	1130.4	1137.7	1143.9	1142.2	1134.9	1134.3	1126.4
47.5°	1216.0	1223.2	1231.1	1241.8	1250.3	1266.5	1285.7	1295.2	1300.8	1305.4	1296.4
50°	1288.0	1291.3	1311.6	1328.4	1347.0	1374.0	1400.4	1434.8	1462.4	1475.3	1487.7
52.5°	1326.7	1335.2	1357.1	1383.6	1416.2	1456.7	1499.5	1554.1	1601.3	1632.8	1660.9
55°	1335.2	1343.6	1368.4	1402.2	1446.6	1501.1	1562.5	1636.8	1707.7	1768.4	1827.6
57.5°	1311.6	1321.1	1347.6	1386.4	1438.8	1505.1	1582.2	1679.6	1777.4	1876.0	1963.1
60°	1268.2	1280.1	1304.2	1342.5	1400.4	1475.3	1567.6	1689.6	1826.9	1977.7	2144.9
62.5°	1196.8	1209.1	1231.7	1273.9	1333.5	1416.2	1523.1	1675.0	1869.1	2106.6	2403.1
65°	1082.0	1087.7	1115.2	1157.9	1210.9	1302.0	1419.6	1603.0	1855.6	2185.9	2594.4
66°	1030.3	1039.8	1056.7	1091.0	1141.7	1227.2	1345.3	1531.6	1804.5	2158.3	2589.3
67.5°	949.2	956.5	967.8	990.9	1021.8	1084.8	1196.8	1372.8	1648.1	2018.9	2481.9
70°	767.5	770.9	786.0	793.9	804.6	825.4	865.9	967.3	1181.6	1529.8	2003.1
72.5°	523.3	532.8	549.1	571.7	600.9	629.0	648.2	661.1	707.3	912.6	1334.6
75°	383.7	393.9	414.7	444.5	495.8	554.2	615.0	643.1	624.0	597.5	743.3
77.5°	222.8	236.3	253.8	282.5	329.7	407.4	511.5	603.7	666.2	670.2	636.4
80°	94.0	95.6	106.3	120.9	150.3	204.8	285.8	418.7	557.0	650.5	672.3
82.5°	21.3	26.4	33.8	40.0	48.9	67.6	100.1	166.5	301.0	472.0	615.5
85°	7.9	7.9	10.7	15.8	18.0	20.2	26.4	42.2	72.0	132.7	276.8
87.5°	0.0	0.5	1.1	1.1	2.3	2.8	4.5	6.2	5.6	5.1	16.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155818

CATALOG NUMBER: AVS-E02-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9
2.5°	562.7	562.1	560.9	560.9	560.9	560.9	559.9	560.4	559.3	559.9	559.9
5°	562.1	562.1	561.6	560.4	560.9	560.9	561.6	560.4	560.4	560.9	560.4
7.5°	562.1	561.6	561.6	561.6	562.1	561.6	562.1	562.1	562.1	562.7	562.7
10°	562.1	562.1	563.2	563.8	563.8	564.4	566.0	566.0	566.6	567.2	568.3
12.5°	562.7	564.9	566.6	568.3	568.8	569.9	572.7	572.7	573.9	575.6	576.2
15°	563.2	566.6	569.9	571.1	572.2	574.5	577.3	578.4	580.1	581.8	582.9
17.5°	562.7	567.2	571.1	572.7	574.5	577.3	580.6	581.8	584.0	586.3	588.5
20°	562.1	568.3	574.5	576.7	579.0	582.9	587.5	590.3	592.4	595.9	598.1
22.5°	565.5	572.7	581.2	584.6	588.5	593.6	599.8	603.2	606.0	609.3	611.1
25°	576.2	581.8	591.9	597.5	602.6	611.1	619.5	623.4	626.8	629.6	630.2
27.5°	594.2	595.9	608.2	615.5	622.9	636.4	646.5	649.3	655.5	657.7	657.2
30°	623.4	620.6	630.8	642.0	652.6	671.3	683.6	691.0	696.6	696.6	692.1
32.5°	665.6	661.1	663.9	676.9	689.2	716.3	730.9	740.4	744.4	743.3	733.7
35°	720.7	717.9	716.3	726.4	746.1	777.6	796.7	801.8	808.0	806.8	794.5
37.5°	786.0	783.8	783.8	795.6	814.7	861.5	882.3	885.6	885.1	876.1	853.0
40°	863.1	862.0	856.9	863.7	880.0	940.7	968.9	973.4	967.3	952.5	925.6
42.5°	974.0	967.3	951.5	955.4	967.8	1026.8	1063.4	1075.9	1069.6	1055.0	1011.1
45°	1118.5	1111.3	1084.8	1081.5	1088.2	1140.0	1187.3	1190.1	1188.9	1170.4	1118.5
47.5°	1288.5	1277.2	1249.1	1240.1	1237.8	1285.7	1331.3	1335.8	1333.0	1305.4	1236.2
50°	1472.4	1456.2	1437.6	1431.4	1422.4	1456.7	1502.9	1503.4	1492.1	1453.9	1389.2
52.5°	1668.8	1663.2	1659.9	1653.7	1649.7	1679.6	1707.7	1690.8	1673.9	1634.0	1577.7
55°	1866.9	1889.9	1913.6	1915.9	1922.6	1954.7	1954.1	1908.0	1895.6	1873.7	1817.9
57.5°	2077.3	2162.9	2237.1	2260.2	2282.7	2342.4	2336.7	2291.2	2275.4	2248.4	2202.3
60°	2363.7	2594.4	2808.8	2860.0	2895.4	2966.9	2960.2	2889.8	2922.5	2920.2	2860.5
62.5°	2764.9	3148.6	3469.9	3548.7	3573.5	3581.3	3538.5	3462.6	3494.7	3530.7	3347.3
65°	3036.7	3488.0	3817.6	3878.4	3881.8	3787.9	3692.7	3603.3	3595.4	3564.5	3302.3
66°	3042.9	3504.8	3835.6	3894.7	3873.9	3745.6	3625.2	3535.2	3496.4	3428.3	3156.5
67.5°	2933.7	3399.6	3755.8	3818.2	3772.6	3590.9	3424.9	3309.0	3233.1	3122.8	2883.1
70°	2463.9	2925.8	3364.7	3481.1	3495.9	3224.6	2994.5	2858.3	2756.0	2604.6	2398.0
72.5°	1832.0	2249.5	2636.6	2748.1	2804.9	2588.3	2394.1	2290.6	2150.5	1991.3	1844.4
75°	1148.4	1443.2	1702.6	1780.8	1727.4	1559.7	1443.2	1399.9	1262.1	1166.9	1100.0
77.5°	656.6	748.9	769.7	739.9	676.9	518.2	368.5	272.8	236.9	262.2	289.2
80°	640.8	587.5	468.1	411.9	373.1	256.6	150.8	103.5	86.1	88.3	95.6
82.5°	694.3	745.0	613.3	500.2	419.8	283.6	156.4	83.3	56.3	66.4	74.8
85°	451.3	628.0	565.5	476.6	386.0	242.5	128.8	43.3	28.7	37.7	51.8
87.5°	45.6	50.1	42.8	57.9	43.3	20.2	10.2	6.2	5.6	6.7	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155818

CATALOG NUMBER: AVS-E02-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9	560.9
2.5°	560.4	560.4	560.9	561.6	562.1	562.7	562.7	562.7	562.7	563.8	563.2
5°	561.6	562.7	563.8	564.4	565.5	565.5	567.2	566.6	566.6	568.3	568.8
7.5°	563.8	565.5	567.8	567.2	569.4	568.8	569.9	569.9	568.3	568.8	567.8
10°	568.8	571.1	572.2	570.6	571.1	568.8	568.3	565.5	562.1	560.4	558.1
12.5°	577.3	579.6	579.6	576.7	573.4	568.3	564.4	558.1	553.1	550.3	547.5
15°	584.6	586.8	586.3	581.8	576.7	568.8	563.2	556.0	548.6	544.0	541.2
17.5°	590.3	591.4	589.6	583.5	577.8	570.6	564.9	557.0	548.6	543.0	537.9
20°	598.7	597.5	593.6	585.7	579.6	572.7	568.3	561.6	552.0	544.7	537.3
22.5°	611.1	606.5	599.3	590.8	584.6	578.4	573.9	566.6	557.0	548.1	539.6
25°	627.4	618.3	608.2	599.3	593.6	586.8	581.8	573.9	563.8	553.7	543.5
27.5°	651.0	635.2	622.3	614.4	608.2	599.8	593.6	583.5	572.7	560.9	549.7
30°	677.4	656.1	643.7	637.5	630.8	621.8	612.1	599.3	586.8	573.9	560.4
32.5°	711.8	685.9	674.1	667.9	658.9	647.7	636.4	621.8	604.2	587.5	571.1
35°	756.8	730.4	717.9	708.4	696.1	681.3	665.1	645.4	621.8	599.3	578.4
37.5°	805.2	776.5	764.7	754.5	736.0	716.8	693.8	665.1	633.0	603.2	577.3
40°	866.5	840.1	824.9	807.5	785.5	752.2	716.3	674.6	633.6	597.0	566.6
42.5°	944.1	917.7	895.2	867.7	829.3	778.1	726.9	673.0	623.4	581.8	549.1
45°	1047.2	1015.0	976.2	927.9	865.9	794.5	727.6	662.3	604.2	558.1	523.3
47.5°	1173.2	1124.1	1060.6	979.1	890.2	799.0	718.5	640.8	574.5	524.4	485.6
50°	1322.8	1245.7	1141.0	1021.2	902.5	792.2	696.1	608.8	532.2	478.9	432.6
52.5°	1493.9	1367.9	1213.7	1051.6	902.0	769.7	657.7	560.4	477.1	417.5	373.6
55°	1694.7	1507.4	1288.5	1074.1	886.2	728.1	599.3	492.3	409.0	353.9	313.4
57.5°	1989.0	1733.6	1419.1	1109.0	854.7	663.9	519.9	410.8	337.6	285.3	251.0
60°	2526.9	2111.1	1654.2	1179.4	806.3	569.9	427.0	323.5	262.2	220.0	196.9
62.5°	2932.0	2403.1	1781.3	1163.6	708.9	454.1	316.8	235.8	193.0	164.2	149.6
65°	2874.1	2312.5	1645.8	1002.1	556.0	320.1	210.5	160.3	132.7	119.3	110.9
66°	2743.0	2194.4	1528.2	902.0	480.5	266.1	173.3	134.5	114.2	104.7	99.1
67.5°	2494.3	1974.9	1317.7	739.4	369.1	193.0	130.6	106.3	92.8	88.9	85.0
70°	2073.4	1574.9	925.0	430.5	188.5	107.5	82.7	74.3	70.9	70.4	69.2
72.5°	1588.9	1114.6	544.7	203.7	97.9	71.5	64.1	61.3	60.2	60.2	60.7
75°	974.0	626.2	240.8	99.6	68.6	60.2	56.8	55.8	55.1	55.8	55.1
77.5°	325.2	199.2	103.0	75.4	62.5	55.8	53.5	52.3	52.3	52.3	52.3
80°	99.6	86.6	78.8	69.7	59.1	52.8	49.5	48.9	49.5	50.1	48.4
82.5°	74.8	70.9	66.4	61.9	53.5	47.3	46.1	46.1	46.1	44.5	42.2
85°	55.1	54.6	45.0	42.2	39.4	39.4	39.4	39.4	37.7	34.9	32.6
87.5°	10.2	9.5	10.2	10.7	15.8	16.9	16.9	18.0	19.7	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155818

CATALOG NUMBER: AVS-E02-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	560.9	560.9	560.9	560.9	560.9
2.5°	563.2	562.7	564.4	563.2	563.8
5°	568.3	567.8	568.8	567.8	569.4
7.5°	566.6	565.5	564.9	565.5	566.0
10°	554.8	553.7	553.1	552.5	553.1
12.5°	544.7	542.4	542.4	541.2	541.9
15°	537.3	535.6	535.1	534.0	534.5
17.5°	534.0	531.2	530.1	528.9	528.9
20°	531.7	528.3	526.6	525.5	525.0
22.5°	531.7	526.6	524.4	523.3	522.7
25°	534.0	527.8	524.4	522.7	522.2
27.5°	538.4	530.6	526.6	524.4	524.4
30°	546.3	536.2	530.6	527.8	527.3
32.5°	554.2	540.7	532.8	529.4	528.3
35°	558.1	540.7	531.2	525.5	524.4
37.5°	553.7	533.4	521.6	513.2	511.5
40°	539.6	518.2	505.3	497.4	496.3
42.5°	521.0	500.2	485.0	479.4	477.7
45°	495.8	471.0	455.8	447.9	448.4
47.5°	452.3	427.0	413.6	406.2	407.4
50°	401.1	376.4	364.6	356.7	358.4
52.5°	344.9	322.4	311.2	307.3	306.1
55°	285.8	268.4	260.5	256.1	254.3
57.5°	231.8	219.5	213.8	208.2	208.7
60°	182.9	176.7	175.0	168.8	168.2
62.5°	144.0	140.1	138.4	133.9	134.5
65°	109.1	108.0	109.1	106.3	107.5
66°	98.4	99.1	99.1	97.3	98.4
67.5°	85.0	86.1	87.8	86.1	87.3
70°	70.4	71.5	72.5	72.5	72.5
72.5°	61.3	62.5	63.0	63.0	63.0
75°	56.3	56.8	57.4	56.3	56.3
77.5°	52.8	52.8	51.8	51.2	50.7
80°	47.9	47.3	45.6	44.5	44.5
82.5°	40.0	38.9	37.7	36.0	36.0
85°	30.4	29.2	28.1	25.9	24.8
87.5°	15.8	16.3	15.8	13.0	11.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)