

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148098

Luminaire Tested: **AVS-E03-LED-E-U-5WQ-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148098
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-5WQ-8030
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (63) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8061.3 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G2

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148098

CATALOG NUMBER: AVS-E03-LED-E-U-5WQ-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.9 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P148098

CATALOG NUMBER: AVS-E03-LED-E-U-5WQ-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P148098

CATALOG NUMBER: AVS-E03-LED-E-U-5WQ-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4030.6	0.0	4030.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4030.6	0.0	4030.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	8061.3	0.0	8061.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.0	0.5
10°-20°	148.4	1.8
20°-30°	300.6	3.7
30°-40°	503.9	6.3
40°-50°	888.8	11.0
50°-60°	1567.5	19.4
60°-70°	2393.1	29.7
70°-80°	1999.7	24.8
80°-90°	217.3	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8061.3	100.0
0°-180°	8061.3	100.0

Coefficient of Utilization



REPORT NUMBER: P148098


CATALOG NUMBER: AVS-E03-LED-E-U-5WQ-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	245.5	3.0			
FM	(30°-60°)	1480.1	18.4			
FH	(60°-80°)	2196.4	27.2			G2/5000
FVH	(80°-90°)	108.6	1.3			G2/225
BL	(0°-30°)	245.5	3.0	B1/500		
BM	(30°-60°)	1480.1	18.4	B2/2500		
BH	(60°-80°)	2196.4	27.2	B3/2500		G2/5000
BVH	(80°-90°)	108.6	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P148098

CATALOG NUMBER: AVS-E03-LED-E-U-5WQ-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7
2.5°	422.0	422.8	422.0	422.0	422.0	422.0	422.0	421.1	421.1	421.1	422.0
5°	430.5	431.3	430.5	431.3	431.3	431.3	431.3	430.5	430.5	430.5	430.5
7.5°	443.9	443.9	443.9	444.8	443.9	443.9	444.8	443.9	443.9	443.9	443.9
10°	463.3	462.5	462.5	462.5	462.5	462.5	463.3	463.3	463.3	462.5	462.5
12.5°	486.9	486.1	486.9	486.9	487.9	487.9	487.9	487.9	487.9	487.9	486.9
15°	515.6	515.6	515.6	516.5	518.2	518.2	517.4	518.2	518.2	518.2	518.2
17.5°	547.8	549.4	547.8	548.6	549.4	548.6	550.3	551.1	552.0	551.1	548.6
20°	580.6	581.6	581.6	581.6	581.6	583.2	584.0	584.0	586.5	585.7	584.9
22.5°	611.9	613.6	613.6	614.4	614.4	617.0	617.0	617.0	618.7	620.3	618.7
25°	644.8	643.9	643.9	645.7	646.5	649.8	649.8	651.6	654.1	654.9	653.3
27.5°	674.3	673.5	673.5	676.1	676.9	681.1	681.1	684.5	686.1	687.0	685.3
30°	705.6	705.6	704.8	707.3	709.8	713.2	714.8	718.2	720.7	721.7	719.9
32.5°	742.7	741.0	741.9	743.5	745.3	748.6	751.2	755.3	758.8	759.6	757.9
35°	784.9	782.4	783.2	784.9	787.5	792.5	796.7	799.3	804.4	806.0	802.6
37.5°	831.3	832.1	831.3	835.5	839.8	845.7	850.8	854.1	859.2	861.8	859.2
40°	897.2	894.6	897.2	901.3	908.1	915.8	925.9	928.4	933.5	938.5	932.6
42.5°	982.4	980.7	986.6	990.1	997.6	1006.0	1018.7	1025.5	1033.1	1036.4	1031.4
45°	1093.8	1093.8	1100.5	1101.5	1113.3	1124.1	1142.0	1150.4	1164.7	1164.7	1164.7
47.5°	1217.0	1222.1	1226.3	1234.7	1243.2	1263.4	1281.1	1299.8	1313.3	1314.9	1312.4
50°	1344.5	1349.5	1362.2	1374.0	1392.5	1417.9	1437.3	1461.8	1473.6	1483.7	1480.3
52.5°	1485.4	1486.2	1501.5	1516.7	1543.6	1571.5	1602.7	1628.1	1649.1	1658.4	1650.9
55°	1639.9	1641.6	1655.0	1671.1	1701.5	1733.6	1772.3	1798.5	1825.6	1842.4	1829.7
57.5°	1806.9	1807.9	1821.3	1840.7	1877.0	1909.1	1946.2	1983.4	2008.7	2023.9	2015.4
60°	1991.8	1996.1	2006.2	2030.7	2065.3	2099.0	2136.2	2169.0	2198.5	2214.6	2206.2
62.5°	2189.3	2193.6	2207.9	2227.3	2257.7	2294.8	2330.3	2372.4	2396.9	2414.6	2402.0
65°	2321.9	2329.4	2352.2	2378.3	2423.1	2471.2	2512.5	2569.9	2599.5	2620.6	2608.8
67.5°	2330.3	2334.5	2362.3	2402.0	2462.0	2534.5	2618.9	2708.4	2766.6	2794.4	2774.2
69°	2272.8	2278.8	2305.8	2350.5	2417.2	2501.6	2602.1	2713.5	2802.9	2844.2	2824.9
70°	2207.9	2220.5	2250.1	2299.1	2364.0	2452.6	2556.5	2675.4	2780.1	2836.7	2822.3
72.5°	2071.2	2074.5	2094.0	2132.7	2182.6	2256.0	2353.9	2466.1	2565.7	2646.7	2658.5
75°	1838.2	1849.2	1863.5	1889.7	1915.0	1968.2	2034.0	2110.8	2169.0	2231.5	2234.1
77.5°	1389.2	1422.2	1433.1	1439.0	1449.9	1492.1	1549.5	1616.3	1664.4	1674.5	1672.7
80°	623.7	667.6	677.7	725.8	755.3	825.4	913.2	1015.3	1083.7	1091.3	1072.7
82.5°	122.4	130.8	152.7	190.8	260.0	301.3	358.7	430.5	496.3	534.2	511.5
85°	40.5	43.0	49.8	54.8	63.3	71.7	86.9	108.0	134.2	148.5	132.5
87.5°	16.1	16.1	18.5	20.2	22.0	22.0	22.0	20.2	19.4	16.1	14.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148098

CATALOG NUMBER: AVS-E03-LED-E-U-5WQ-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7
2.5°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1
5°	430.5	429.6	429.6	428.7	428.7	428.7	428.7	428.7
7.5°	443.1	442.3	441.5	442.3	441.5	441.5	441.5	441.5
10°	462.5	460.8	460.0	459.2	459.2	459.2	458.2	458.2
12.5°	485.3	485.3	484.5	483.6	482.0	482.8	482.0	480.2
15°	516.5	514.8	514.0	513.2	511.5	511.5	511.5	510.6
17.5°	547.8	546.0	546.0	543.5	542.7	542.7	542.7	543.5
20°	582.4	579.8	578.1	576.5	574.7	575.6	573.9	575.6
22.5°	617.0	613.6	611.9	609.3	606.8	606.8	606.0	604.2
25°	650.7	646.5	644.8	642.3	638.9	638.9	637.2	635.5
27.5°	682.8	678.5	676.9	671.8	668.4	667.6	665.9	665.1
30°	718.2	713.2	710.7	705.6	700.5	699.7	697.1	697.1
32.5°	755.3	750.3	748.6	741.0	736.8	736.8	735.1	733.5
35°	801.8	794.2	792.5	784.9	779.0	779.0	777.3	778.1
37.5°	856.7	850.8	844.9	839.0	832.1	831.3	829.6	828.0
40°	930.1	923.3	916.6	908.1	902.2	900.5	898.0	897.2
42.5°	1028.0	1021.2	1007.8	1000.9	995.0	990.1	989.1	988.3
45°	1152.8	1144.5	1135.1	1122.5	1114.9	1103.9	1102.3	1098.0
47.5°	1303.1	1287.0	1271.1	1260.1	1248.3	1235.6	1233.1	1226.3
50°	1462.6	1449.9	1423.0	1405.3	1386.6	1374.0	1365.6	1363.0
52.5°	1634.0	1610.4	1583.3	1559.7	1532.6	1515.9	1500.6	1496.4
55°	1812.8	1779.2	1745.4	1717.5	1690.5	1670.3	1656.0	1649.1
57.5°	1991.8	1954.7	1917.5	1887.2	1864.4	1838.2	1823.8	1820.5
60°	2178.3	2142.9	2104.9	2074.5	2046.6	2023.9	2015.4	1999.4
62.5°	2375.9	2338.7	2303.2	2273.7	2238.2	2222.3	2207.9	2198.5
65°	2569.9	2526.9	2482.2	2451.0	2415.5	2392.7	2375.0	2362.3
67.5°	2720.2	2655.2	2595.2	2542.9	2494.8	2459.4	2436.6	2424.8
69°	2762.4	2681.3	2604.6	2536.2	2479.7	2440.0	2414.6	2402.8
70°	2757.3	2667.9	2583.4	2508.3	2446.7	2404.6	2380.1	2358.1
72.5°	2601.1	2519.3	2425.6	2343.7	2288.1	2247.6	2223.1	2211.3
75°	2219.7	2164.9	2097.3	2034.0	1993.5	1969.8	1939.5	1940.3
77.5°	1616.3	1617.9	1572.3	1507.4	1461.8	1453.4	1439.9	1426.3
80°	1002.7	922.5	870.2	800.1	748.6	703.9	684.5	642.3
82.5°	462.5	361.2	280.2	211.8	162.9	127.5	111.4	91.2
85°	103.0	78.4	65.0	52.3	44.8	41.3	33.8	31.2
87.5°	14.3	12.6	11.8	11.0	9.3	6.7	5.1	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)