

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155828

Luminaire Tested: **AVS-E03-LED-E-U-T3-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155828
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E03-LED-E-U-T3-8030
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (63) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7808.4 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 75.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P155828

CATALOG NUMBER: AVS-E03-LED-E-U-T3-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 8.4 fc
Type III - Short - Semi-Cutoff

REPORT NUMBER: P155828

CATALOG NUMBER: AVS-E03-LED-E-U-T3-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P155828

CATALOG NUMBER: AVS-E03-LED-E-U-T3-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2696.5	0.0	2696.5
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	5111.9	0.0	5111.9
	% Fixture	65.5	0.0	65.5
Total	Lumens	7808.4	0.0	7808.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.6	1.0
10°-20°	237.9	3.0
20°-30°	408.8	5.2
30°-40°	663.8	8.5
40°-50°	1108.1	14.2
50°-60°	1744.9	22.3
60°-70°	2379.4	30.5
70°-80°	1030.0	13.2
80°-90°	154.9	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7808.4	100.0
0°-180°	7808.4	100.0

Coefficient of Utilization



REPORT NUMBER: P155828


CATALOG NUMBER: AVS-E03-LED-E-U-T3-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	365.3	4.7			
FM	(30°-60°)	2180.6	27.9			
FH	(60°-80°)	2438.8	31.2			G2/5000
FVH	(80°-90°)	127.2	1.6			G2/225
BL	(0°-30°)	362.0	4.6	B1/500		
BM	(30°-60°)	1336.2	17.1	B2/2500		
BH	(60°-80°)	970.6	12.4	B2/1000		G2/1000
BVH	(80°-90°)	27.7	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P155828

CATALOG NUMBER: AVS-E03-LED-E-U-T3-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5
2.5°	844.9	848.2	844.9	845.7	846.5	845.7	844.9	844.9	842.3	844.0	845.7
5°	841.5	844.0	843.1	844.0	844.9	844.0	843.1	844.0	842.3	843.1	845.7
7.5°	837.2	836.4	837.2	839.0	840.6	840.6	840.6	841.5	840.6	840.6	843.1
10°	824.6	825.4	827.2	829.6	830.5	833.1	833.1	835.5	836.4	838.1	841.5
12.5°	808.5	809.4	811.1	812.7	817.0	821.2	821.2	827.2	829.6	833.9	839.8
15°	796.7	797.6	799.3	800.9	804.4	808.5	811.1	817.8	822.1	829.6	838.1
17.5°	803.5	802.6	804.4	805.2	805.2	808.5	808.5	813.6	818.7	825.4	836.4
20°	822.9	822.9	824.6	824.6	823.7	825.4	822.1	822.1	822.9	826.2	833.9
22.5°	842.3	841.5	844.9	846.5	847.4	849.9	846.5	845.7	841.5	839.0	841.5
25°	860.8	860.0	864.2	866.7	871.0	873.6	873.6	873.6	870.2	865.9	863.4
27.5°	889.5	889.5	893.8	896.3	899.7	904.8	907.3	907.3	908.1	902.2	898.0
30°	937.7	938.5	939.4	942.7	946.1	947.8	951.2	953.7	956.3	952.8	946.1
32.5°	995.0	990.1	990.1	995.0	999.3	1004.4	1006.0	1009.4	1014.5	1011.9	1011.1
35°	1063.4	1061.8	1060.1	1061.8	1066.8	1072.7	1079.5	1085.4	1082.0	1087.0	1084.6
37.5°	1164.7	1166.4	1167.3	1167.3	1166.4	1168.1	1171.5	1177.4	1175.6	1177.4	1180.7
40°	1331.8	1325.9	1320.0	1320.8	1312.4	1314.1	1300.6	1306.5	1307.4	1301.5	1303.9
42.5°	1499.0	1502.3	1504.9	1511.6	1505.7	1502.3	1489.6	1489.6	1482.9	1477.0	1475.3
45°	1679.6	1686.3	1687.2	1700.6	1695.5	1706.5	1715.9	1713.3	1702.3	1701.5	1689.6
47.5°	1823.8	1834.8	1846.6	1862.7	1875.3	1899.8	1928.5	1942.9	1951.3	1958.0	1944.6
50°	1931.9	1937.0	1967.4	1992.6	2020.5	2061.0	2100.7	2152.2	2193.6	2213.0	2231.5
52.5°	1990.2	2002.8	2035.8	2075.3	2124.4	2185.1	2249.2	2331.1	2402.0	2449.2	2491.5
55°	2002.8	2015.4	2052.5	2103.2	2169.9	2251.8	2343.7	2455.1	2561.6	2652.6	2741.2
57.5°	1967.4	1981.7	2021.3	2079.6	2158.1	2257.7	2373.3	2519.3	2666.2	2813.9	2944.7
60°	1902.4	1920.1	1956.4	2013.8	2100.7	2213.0	2351.4	2534.5	2740.4	2966.6	3217.3
62.5°	1795.1	1813.8	1847.5	1910.8	2000.2	2124.4	2284.7	2512.5	2803.7	3159.9	3604.7
65°	1623.0	1631.4	1672.7	1736.9	1816.3	1953.0	2129.4	2404.6	2783.5	3278.9	3891.6
66°	1545.4	1559.7	1585.0	1636.5	1712.4	1840.7	2018.0	2297.3	2706.6	3237.5	3884.0
67.5°	1423.8	1434.8	1451.7	1486.2	1532.6	1627.3	1795.1	2059.4	2472.0	3028.3	3722.8
70°	1151.2	1156.3	1179.1	1190.9	1206.9	1238.1	1298.9	1450.8	1772.3	2294.8	3004.6
72.5°	784.9	799.3	823.7	857.5	901.3	943.6	972.2	991.7	1060.9	1368.9	2002.0
75°	575.6	590.8	622.1	666.7	743.5	831.3	922.5	964.7	936.0	896.3	1114.9
77.5°	334.2	354.5	380.6	423.7	494.6	611.1	767.2	905.6	999.3	1005.2	954.5
80°	140.9	143.5	159.5	181.5	225.4	307.3	428.7	628.0	835.5	975.6	1008.6
82.5°	32.0	39.7	50.7	59.9	73.5	101.2	150.3	249.8	451.5	708.1	923.3
85°	11.8	11.8	16.1	23.6	27.0	30.4	39.7	63.3	108.0	199.2	415.2
87.5°	0.0	0.8	1.7	1.7	3.4	4.2	6.7	9.3	8.4	7.6	25.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155828

CATALOG NUMBER: AVS-E03-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5
2.5°	844.0	843.1	841.5	841.5	841.5	841.5	839.8	840.6	839.0	839.8	839.8
5°	843.1	843.1	842.3	840.6	841.5	841.5	842.3	840.6	840.6	841.5	840.6
7.5°	843.1	842.3	842.3	842.3	843.1	842.3	843.1	843.1	843.1	844.0	844.0
10°	843.1	843.1	844.9	845.7	845.7	846.5	849.0	849.0	849.9	850.8	852.4
12.5°	844.0	847.4	849.9	852.4	853.3	854.9	859.2	859.2	860.8	863.4	864.2
15°	844.9	849.9	854.9	856.7	858.3	861.8	865.9	867.7	870.2	872.6	874.4
17.5°	844.0	850.8	856.7	859.2	861.8	865.9	871.0	872.6	876.1	879.5	882.8
20°	843.1	852.4	861.8	865.1	868.5	874.4	881.1	885.4	888.7	893.8	897.2
22.5°	848.2	859.2	871.8	876.9	882.8	890.4	899.7	904.8	909.0	914.1	916.6
25°	864.2	872.6	887.9	896.3	903.9	916.6	929.2	935.1	940.2	944.5	945.3
27.5°	891.3	893.8	912.3	923.3	934.3	954.5	969.7	974.0	983.2	986.6	985.8
30°	935.1	930.9	946.1	963.0	979.1	1006.8	1025.5	1036.4	1044.9	1044.9	1038.1
32.5°	998.4	991.7	996.0	1015.3	1033.9	1074.4	1096.4	1110.7	1116.6	1114.9	1100.5
35°	1081.1	1076.9	1074.4	1089.6	1119.2	1166.4	1195.1	1202.7	1212.0	1210.3	1191.7
37.5°	1179.1	1175.6	1175.6	1193.4	1222.1	1292.1	1323.4	1328.4	1327.6	1314.1	1279.5
40°	1294.7	1293.0	1285.4	1295.5	1320.0	1411.2	1453.4	1460.1	1450.8	1428.9	1388.4
42.5°	1460.9	1450.8	1427.2	1433.1	1451.7	1540.3	1595.1	1613.7	1604.5	1582.5	1516.7
45°	1677.8	1666.8	1627.3	1622.2	1632.2	1709.9	1780.8	1785.1	1783.3	1755.5	1677.8
47.5°	1932.7	1915.9	1873.7	1860.2	1856.8	1928.5	1996.9	2003.6	1999.4	1958.0	1854.2
50°	2208.7	2184.2	2156.4	2147.2	2133.6	2185.1	2254.3	2255.1	2238.2	2180.8	2083.8
52.5°	2503.3	2494.8	2489.7	2480.5	2474.6	2519.3	2561.6	2536.2	2510.9	2451.0	2366.5
55°	2800.3	2834.9	2870.4	2873.8	2883.9	2932.0	2931.2	2862.0	2843.4	2810.5	2726.9
57.5°	3116.1	3244.4	3355.8	3390.4	3424.0	3513.6	3505.1	3436.7	3413.1	3372.5	3303.4
60°	3545.6	3891.6	4213.2	4290.1	4343.2	4450.4	4440.2	4334.7	4383.7	4380.3	4290.9
62.5°	4147.4	4723.0	5204.9	5323.0	5360.2	5372.0	5307.9	5193.9	5242.1	5296.1	5020.9
65°	4555.0	5231.9	5726.5	5817.6	5822.7	5681.8	5539.1	5404.9	5393.1	5346.6	4953.4
66°	4564.4	5257.2	5753.5	5842.1	5810.9	5618.4	5437.8	5302.8	5244.6	5142.5	4734.8
67.5°	4400.5	5099.4	5633.7	5727.4	5659.0	5386.3	5137.4	4963.5	4849.5	4684.1	4324.6
70°	3695.9	4388.7	5047.0	5221.8	5243.7	4836.9	4491.7	4287.5	4133.9	3906.8	3597.1
72.5°	2748.1	3374.3	3954.9	4122.1	4207.3	3882.4	3591.2	3435.9	3225.7	2986.8	2766.6
75°	1722.6	2164.9	2553.9	2671.2	2591.1	2339.6	2164.9	2099.9	1893.1	1750.5	1650.1
77.5°	985.0	1123.3	1154.6	1109.8	1015.3	777.3	552.8	409.3	355.3	393.3	433.8
80°	961.3	881.1	702.2	617.8	559.6	384.9	226.2	155.3	129.1	132.5	143.5
82.5°	1041.5	1117.4	920.0	750.3	629.6	425.4	234.6	124.9	84.4	99.6	112.2
85°	676.9	941.9	848.2	714.8	579.0	363.7	193.3	65.0	43.0	56.6	77.6
87.5°	68.4	75.1	64.1	86.9	65.0	30.4	15.2	9.3	8.4	10.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155828

CATALOG NUMBER: AVS-E03-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5	841.5
2.5°	840.6	840.6	841.5	842.3	843.1	844.0	844.0	844.0	844.0	845.7	844.9
5°	842.3	844.0	845.7	846.5	848.2	848.2	850.8	849.9	849.9	852.4	853.3
7.5°	845.7	848.2	851.6	850.8	854.1	853.3	854.9	854.9	852.4	853.3	851.6
10°	853.3	856.7	858.3	855.9	856.7	853.3	852.4	848.2	843.1	840.6	837.2
12.5°	865.9	869.3	869.3	865.1	860.0	852.4	846.5	837.2	829.6	825.4	821.2
15°	876.9	880.3	879.5	872.6	865.1	853.3	844.9	833.9	822.9	816.2	811.9
17.5°	885.4	887.0	884.5	875.2	866.7	855.9	847.4	835.5	822.9	814.4	806.8
20°	898.0	896.3	890.4	878.5	869.3	859.2	852.4	842.3	828.0	817.0	806.0
22.5°	916.6	909.8	898.9	886.2	876.9	867.7	860.8	849.9	835.5	822.1	809.4
25°	941.0	927.6	912.3	898.9	890.4	880.3	872.6	860.8	845.7	830.5	815.3
27.5°	976.5	952.8	933.5	921.7	912.3	899.7	890.4	875.2	859.2	841.5	824.6
30°	1016.2	984.1	965.5	956.3	946.1	932.6	918.2	898.9	880.3	860.8	840.6
32.5°	1067.7	1028.8	1011.1	1001.9	988.3	971.4	954.5	932.6	906.4	881.1	856.7
35°	1135.1	1095.5	1076.9	1062.6	1044.0	1022.1	997.6	968.1	932.6	898.9	867.7
37.5°	1207.8	1164.7	1146.9	1131.8	1103.9	1075.2	1040.6	997.6	949.5	904.8	865.9
40°	1299.8	1260.1	1237.3	1211.1	1178.2	1128.4	1074.4	1011.9	950.4	895.4	849.9
42.5°	1416.2	1376.6	1342.8	1301.5	1244.0	1167.3	1090.5	1009.4	935.1	872.6	823.7
45°	1570.7	1522.6	1464.4	1391.7	1298.9	1191.7	1091.3	993.4	906.4	837.2	784.9
47.5°	1759.7	1686.3	1590.9	1468.5	1335.2	1198.4	1077.8	961.3	861.8	786.6	728.4
50°	1984.2	1868.6	1711.6	1531.8	1353.8	1188.3	1044.0	913.2	798.4	718.2	649.0
52.5°	2240.8	2051.7	1820.5	1577.4	1353.0	1154.6	986.6	840.6	715.8	626.2	560.4
55°	2542.1	2261.0	1932.7	1611.2	1329.3	1092.1	898.9	738.4	613.6	530.9	470.1
57.5°	2983.5	2600.3	2128.5	1663.5	1282.1	996.0	779.9	616.1	506.4	427.9	376.4
60°	3790.4	3166.6	2481.3	1769.0	1209.4	854.9	640.6	485.3	393.3	330.1	295.4
62.5°	4398.0	3604.7	2672.1	1745.4	1063.4	681.1	475.1	353.7	289.5	246.4	224.5
65°	4311.1	3468.8	2468.7	1503.1	833.9	480.2	315.6	240.5	199.2	179.0	166.2
66°	4114.4	3291.6	2292.2	1353.0	720.7	399.2	260.0	201.8	171.3	157.0	148.5
67.5°	3741.5	2962.4	1976.6	1109.0	553.7	289.5	195.9	159.5	139.3	133.4	127.5
70°	3110.2	2362.3	1387.6	645.7	282.7	161.2	124.0	111.4	106.3	105.5	103.8
72.5°	2383.4	1671.9	817.0	305.5	146.8	107.2	96.2	92.0	90.3	90.3	91.2
75°	1460.9	939.4	361.2	149.4	103.0	90.3	85.3	83.5	82.7	83.5	82.7
77.5°	487.9	298.8	154.4	113.1	93.7	83.5	80.2	78.4	78.4	78.4	78.4
80°	149.4	129.9	118.1	104.7	88.6	79.4	74.3	73.5	74.3	75.1	72.5
82.5°	112.2	106.3	99.6	92.8	80.2	70.9	69.2	69.2	69.2	66.6	63.3
85°	82.7	81.9	67.6	63.3	59.1	59.1	59.1	59.1	56.6	52.3	48.9
87.5°	15.2	14.3	15.2	16.1	23.6	25.3	25.3	27.0	29.5	27.9	27.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155828

CATALOG NUMBER: AVS-E03-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	841.5	841.5	841.5	841.5	841.5
2.5°	844.9	844.0	846.5	844.9	845.7
5°	852.4	851.6	853.3	851.6	854.1
7.5°	849.9	848.2	847.4	848.2	849.0
10°	832.1	830.5	829.6	828.8	829.6
12.5°	817.0	813.6	813.6	811.9	812.7
15°	806.0	803.5	802.6	800.9	801.8
17.5°	800.9	796.7	795.0	793.4	793.4
20°	797.6	792.5	789.9	788.3	787.5
22.5°	797.6	789.9	786.6	784.9	784.0
25°	800.9	791.7	786.6	784.0	783.2
27.5°	807.7	795.9	789.9	786.6	786.6
30°	819.5	804.4	795.9	791.7	790.8
32.5°	831.3	811.1	799.3	794.2	792.5
35°	837.2	811.1	796.7	788.3	786.6
37.5°	830.5	800.1	782.4	769.7	767.2
40°	809.4	777.3	757.9	746.1	744.4
42.5°	781.6	750.3	727.6	719.1	716.6
45°	743.5	706.4	683.6	671.8	672.6
47.5°	678.5	640.6	620.3	609.3	611.1
50°	601.8	564.7	546.9	535.1	537.6
52.5°	517.4	483.6	466.7	460.8	459.2
55°	428.7	402.6	390.8	384.0	381.5
57.5°	347.8	329.1	320.7	312.2	313.2
60°	274.3	265.0	262.5	253.2	252.3
62.5°	216.1	210.2	207.7	200.8	201.8
65°	163.7	162.1	163.7	159.5	161.2
66°	147.7	148.5	148.5	146.0	147.7
67.5°	127.5	129.1	131.7	129.1	130.8
70°	105.5	107.2	108.9	108.9	108.9
72.5°	92.0	93.7	94.5	94.5	94.5
75°	84.4	85.3	86.1	84.4	84.4
77.5°	79.4	79.4	77.6	76.8	76.0
80°	71.7	70.9	68.4	66.6	66.6
82.5°	59.9	58.2	56.6	54.0	54.0
85°	45.6	43.9	42.2	38.9	37.1
87.5°	23.6	24.5	23.6	19.4	16.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)