

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P150908

Luminaire Tested: **AVS-E04-LED-E-U-SL3-HSS-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P150908
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33727)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E04-LED-E-U-SL3-HSS-8030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (84) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5853.3 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type III - Short - Non-Cutoff
BUG Rating: B0 - U0 - G2

Input Watts (W): 97.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P150908

CATALOG NUMBER: AVS-E04-LED-E-U-SL3-HSS-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 9.7 fc
 Type III - Short - Non-Cutoff

REPORT NUMBER: P150908

CATALOG NUMBER: AVS-E04-LED-E-U-SL3-HSS-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P150908

CATALOG NUMBER: AVS-E04-LED-E-U-SL3-HSS-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	126.8	0.0	126.8
	% Fixture	2.2	0.0	2.2
Street Side	Lumens	5726.5	0.0	5726.5
	% Fixture	97.8	0.0	97.8
Total	Lumens	5853.3	0.0	5853.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.8	0.3
10°-20°	83.9	1.4
20°-30°	180.9	3.1
30°-40°	386.3	6.6
40°-50°	854.2	14.6
50°-60°	1447.6	24.7
60°-70°	1931.8	33.0
70°-80°	850.9	14.5
80°-90°	98.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5853.3	100.0
0°-180°	5853.3	100.0

Coefficient of Utilization



REPORT NUMBER: P150908


CATALOG NUMBER: AVS-E04-LED-E-U-SL3-HSS-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	244.5	4.2			
FM	(30°-60°)	2632.4	45.0			
FH	(60°-80°)	2755.5	47.1			G2/5000
FVH	(80°-90°)	94.1	1.6			G1/100
BL	(0°-30°)	40.0	0.7	B0/110		
BM	(30°-60°)	55.7	1.0	B0/220		
BH	(60°-80°)	27.2	0.5	B0/110		G0/110
BVH	(80°-90°)	3.9	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short





REPORT NUMBER: P150908

CATALOG NUMBER: AVS-E04-LED-E-U-SL3-HSS-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	67°	68°
0°	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7
2.5°	222.8	221.7	217.2	217.2	210.5	205.9	200.3	194.7	194.7	193.6	192.4
5°	294.8	288.1	286.9	274.6	264.5	249.8	236.3	218.3	216.1	213.8	212.6
7.5°	374.7	373.6	363.5	348.8	328.6	301.6	274.6	245.3	240.8	238.5	234.1
10°	478.2	472.6	459.2	434.4	404.0	368.0	324.0	277.9	272.3	267.9	265.6
12.5°	577.3	567.2	559.3	527.8	489.5	436.6	383.7	317.3	312.8	307.3	298.2
15°	669.5	660.5	647.0	620.1	577.3	510.9	449.0	368.0	356.7	348.8	342.1
17.5°	741.6	736.0	720.2	689.8	643.7	585.2	510.9	419.8	410.8	400.6	388.2
20°	810.3	802.4	777.6	736.0	686.4	641.5	584.0	487.3	474.9	462.5	449.0
22.5°	875.5	867.7	827.2	758.4	705.6	686.4	666.2	563.8	544.7	534.5	521.0
25°	966.6	949.7	886.7	777.6	706.7	721.3	756.2	662.8	644.8	630.2	608.8
27.5°	1089.3	1066.8	967.8	805.7	711.2	759.6	859.8	783.2	764.0	747.3	723.6
30°	1227.8	1213.1	1094.9	873.3	743.8	815.9	975.6	936.3	913.8	893.5	865.4
32.5°	1367.3	1347.0	1229.9	1001.6	831.6	925.0	1120.8	1114.1	1084.8	1065.7	1035.3
35°	1489.9	1479.8	1393.2	1212.0	1031.9	1116.3	1314.4	1322.3	1296.4	1276.2	1242.4
37.5°	1573.2	1573.2	1556.3	1438.1	1350.4	1413.4	1599.1	1600.2	1574.3	1528.2	1511.3
40°	1616.0	1628.3	1689.1	1711.6	1707.2	1788.2	1972.6	1952.4	1931.1	1907.5	1851.2
42.5°	1703.7	1715.0	1844.4	1999.7	2100.9	2207.9	2335.0	2328.3	2302.4	2259.7	2207.9
45°	1852.2	1866.9	2021.0	2267.6	2475.8	2627.7	2708.6	2677.1	2651.3	2610.8	2583.7
47.5°	2041.3	2069.4	2243.9	2548.8	2799.8	3050.8	3135.1	3051.9	3029.3	2997.8	2954.0
50°	2242.8	2269.7	2455.4	2804.4	3087.9	3387.3	3527.9	3387.3	3354.6	3344.5	3294.9
52.5°	2417.2	2439.7	2618.7	3001.2	3308.4	3659.6	3864.4	3678.7	3655.0	3621.2	3585.3
55°	2520.7	2538.8	2706.4	3095.8	3458.1	3904.9	4189.5	4026.4	3991.5	3978.0	3926.2
57.5°	2555.6	2573.6	2724.4	3108.2	3539.2	4128.8	4584.6	4590.2	4548.5	4500.2	4484.5
60°	2555.6	2575.9	2703.0	3077.7	3617.9	4367.4	5111.2	5580.5	5490.5	5481.5	5424.0
62.5°	2449.8	2468.9	2597.2	2984.4	3723.7	4689.2	5844.9	6673.2	6647.3	6588.7	6494.2
65°	2220.2	2231.5	2357.5	2745.8	3683.2	4985.2	6480.7	7400.1	7358.4	7243.7	7122.2
66°	2116.7	2125.7	2243.9	2609.6	3550.4	5025.7	6593.3	7491.3	7422.6	7325.8	7188.6
67.5°	1967.0	1982.8	2066.1	2356.4	3231.9	4885.0	6522.4	7427.2	7367.5	7250.5	7113.2
70°	1313.3	1302.0	1595.8	1808.4	2462.2	3980.3	5851.7	6668.7	6669.7	6614.6	6559.5
72.5°	623.4	630.2	715.8	1113.0	1611.5	2659.2	4657.7	5322.8	5399.3	5300.3	5231.6
75°	447.9	458.0	509.7	680.8	961.0	1595.8	3019.3	3722.6	3724.8	3549.2	3392.8
77.5°	130.6	136.2	191.3	419.8	720.2	1076.9	1734.1	2069.4	2021.0	1895.0	1776.9
80°	54.0	54.0	56.3	133.9	289.2	731.5	1213.1	1593.5	1587.9	1539.5	1469.6
82.5°	20.2	21.3	27.0	55.1	68.6	180.0	809.1	1383.0	1379.7	1311.0	1261.5
85°	2.3	2.3	6.7	23.6	25.9	33.8	162.1	609.9	606.5	609.9	534.5
87.5°	0.0	0.0	1.1	2.3	3.4	4.5	6.7	23.6	25.9	24.8	22.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150908

CATALOG NUMBER: AVS-E04-LED-E-U-SL3-HSS-8030

CANDELA DISTRIBUTION (continued):

	69°	70°	71°	72°	73°	74°	75°	76°	77°	78°	79°
0°	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7
2.5°	192.4	190.2	190.2	189.0	189.0	189.0	188.0	186.8	186.8	185.7	184.6
5°	210.5	208.2	207.0	204.8	203.7	202.6	200.3	199.2	196.9	195.9	194.7
7.5°	231.8	227.4	226.2	222.8	219.5	217.2	214.9	211.6	209.3	204.8	203.7
10°	258.9	253.2	248.7	244.1	240.8	235.2	231.8	227.4	222.8	219.5	216.1
12.5°	293.7	285.8	279.1	274.6	266.7	260.0	253.2	249.8	240.8	236.3	230.7
15°	332.0	323.0	315.1	306.1	300.4	289.2	280.2	270.1	265.6	257.7	248.7
17.5°	381.5	366.8	354.5	345.5	334.2	323.0	312.8	302.7	289.2	280.2	268.9
20°	434.4	422.0	405.1	389.3	375.9	362.4	347.8	334.2	321.9	307.3	293.7
22.5°	501.9	483.9	463.6	447.9	429.8	415.2	395.0	377.0	356.7	337.6	321.9
25°	587.5	563.8	544.7	522.2	500.7	478.2	453.5	431.0	405.1	387.2	360.1
27.5°	693.2	670.7	644.8	615.5	594.2	560.4	527.8	499.7	469.2	441.1	410.8
30°	828.2	795.6	768.6	740.4	697.7	665.1	626.8	588.5	546.9	518.8	472.6
32.5°	990.3	955.4	914.9	874.4	835.0	788.8	741.6	694.3	648.2	596.4	549.1
35°	1188.3	1146.7	1100.5	1056.7	996.0	946.4	886.7	821.5	769.7	710.1	650.5
37.5°	1450.6	1381.9	1341.3	1295.2	1213.1	1145.6	1079.2	1013.9	922.8	859.8	775.3
40°	1779.2	1738.7	1672.2	1597.9	1523.7	1434.8	1344.8	1258.1	1152.3	1064.6	966.6
42.5°	2165.1	2105.5	2037.9	1931.1	1855.6	1751.0	1648.6	1533.8	1404.4	1291.9	1177.1
45°	2527.5	2456.6	2404.8	2297.9	2219.2	2095.3	1971.6	1850.1	1700.3	1555.2	1422.4
47.5°	2919.1	2860.5	2775.0	2688.4	2608.5	2468.9	2335.0	2187.7	2030.1	1857.9	1685.7
50°	3263.4	3217.3	3158.8	3054.1	2965.2	2848.2	2690.7	2529.7	2330.6	2159.5	1963.7
52.5°	3556.1	3520.0	3437.8	3363.6	3283.7	3173.4	3032.7	2878.5	2663.6	2475.8	2252.8
55°	3901.5	3875.6	3803.6	3757.4	3686.5	3580.7	3449.1	3306.2	3078.9	2874.1	2622.0
57.5°	4467.6	4447.3	4384.2	4365.1	4295.3	4203.1	4041.0	3888.0	3622.4	3368.1	3080.0
60°	5404.9	5364.5	5272.1	5224.9	5077.4	4953.7	4743.2	4532.7	4212.1	3888.0	3541.3
62.5°	6408.7	6295.0	6119.5	5968.7	5759.4	5544.5	5263.1	4941.2	4565.4	4180.5	3782.2
65°	6949.9	6756.5	6534.7	6295.0	6023.8	5707.7	5353.2	4967.2	4563.2	4156.9	3736.1
66°	7011.9	6793.6	6558.3	6291.7	5990.1	5653.6	5293.5	4888.4	4468.6	4072.5	3651.7
67.5°	6934.2	6705.8	6457.1	6161.1	5834.8	5485.9	5107.9	4686.9	4283.0	3881.2	3471.6
70°	6390.7	6163.4	5941.7	5629.9	5282.3	4931.2	4573.3	4102.9	3720.3	3351.2	2986.6
72.5°	5103.3	4949.1	4729.7	4463.0	4124.4	3712.4	3414.2	2993.4	2661.3	2303.5	2021.0
75°	3189.1	2972.0	2700.7	2360.9	2102.1	1767.9	1593.5	1273.9	1084.8	919.4	759.6
77.5°	1630.6	1467.5	1277.2	1085.9	902.5	720.2	557.0	393.9	265.6	184.6	137.3
80°	1347.0	1203.0	1045.4	871.0	708.9	550.3	396.1	270.1	172.1	112.5	87.8
82.5°	1113.0	991.4	850.8	688.7	548.1	432.1	300.4	195.9	121.6	78.8	61.9
85°	473.8	429.8	332.0	263.3	198.0	146.3	102.4	68.6	48.4	39.4	36.0
87.5°	20.2	22.5	21.3	16.9	12.3	12.3	11.3	9.0	9.0	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150908

CATALOG NUMBER: AVS-E04-LED-E-U-SL3-HSS-8030

CANDELA DISTRIBUTION (continued):

	80°	81°	82°	83°	84°	85°	95°	105°	115°	125°	135°
0°	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7
2.5°	184.6	183.4	182.3	182.3	181.1	180.0	173.3	167.7	160.9	156.4	151.9
5°	192.4	191.3	189.0	188.0	185.7	184.6	169.9	157.5	147.5	139.6	133.9
7.5°	200.3	199.2	195.9	192.4	191.3	189.0	165.4	149.6	136.2	127.2	121.6
10°	210.5	207.0	203.7	199.2	195.9	192.4	160.9	140.6	126.0	118.1	112.5
12.5°	225.1	219.5	213.8	208.2	203.7	198.0	158.7	132.7	118.1	109.1	103.5
15°	242.0	234.1	227.4	220.5	212.6	207.0	154.2	126.0	111.4	102.4	95.6
17.5°	257.7	248.7	238.5	228.4	220.5	212.6	149.6	119.3	104.7	95.6	88.9
20°	280.2	266.7	254.3	242.0	230.7	220.5	142.9	112.5	99.1	88.9	82.2
22.5°	305.0	289.2	273.5	256.6	242.0	228.4	137.3	106.9	93.4	83.3	75.4
25°	336.5	317.3	296.0	274.6	257.7	239.7	131.7	101.2	87.8	77.6	69.7
27.5°	380.3	353.4	329.7	302.7	276.8	256.6	127.2	96.8	82.2	72.0	64.1
30°	440.0	400.6	363.5	334.2	303.8	274.6	122.7	91.2	77.6	66.4	57.4
32.5°	506.4	460.2	417.5	373.6	335.3	301.6	118.1	86.6	72.0	60.7	52.8
35°	588.5	530.1	472.6	422.0	375.9	330.9	113.7	82.2	67.6	55.1	47.3
37.5°	706.7	633.6	558.1	492.8	433.3	373.6	110.3	77.6	61.9	49.5	41.7
40°	868.7	774.2	682.0	593.1	515.4	441.1	105.8	73.2	57.4	45.0	37.1
42.5°	1044.2	929.5	808.0	707.9	600.9	507.6	101.2	68.6	52.8	40.5	32.6
45°	1262.6	1119.7	972.2	836.1	705.6	585.2	96.8	64.1	47.3	36.0	28.1
47.5°	1501.1	1318.9	1152.3	981.2	826.0	682.0	91.2	60.7	42.8	31.5	24.8
50°	1746.5	1554.1	1343.6	1148.9	964.4	778.8	85.5	55.1	38.2	28.1	20.2
52.5°	2011.0	1783.6	1568.7	1326.7	1111.8	905.9	79.9	50.7	34.9	24.8	16.9
55°	2347.5	2093.1	1841.0	1569.8	1311.0	1053.3	74.3	45.0	30.4	21.3	13.5
57.5°	2770.6	2468.9	2159.5	1853.4	1539.5	1246.8	69.7	39.4	25.9	18.0	11.3
60°	3170.1	2817.8	2443.1	2090.9	1736.4	1395.4	63.0	34.9	22.5	14.6	11.3
62.5°	3377.1	2975.3	2571.4	2183.1	1805.0	1448.3	56.3	29.2	19.2	12.3	10.2
65°	3326.4	2916.8	2525.2	2133.6	1763.4	1414.5	49.5	25.9	16.9	11.3	10.2
66°	3253.3	2848.2	2454.3	2081.9	1728.5	1378.5	46.1	24.8	15.8	11.3	9.0
67.5°	3093.5	2701.9	2326.0	1979.5	1632.8	1309.8	41.7	22.5	14.6	10.2	9.0
70°	2642.3	2286.6	1986.2	1677.8	1395.4	1103.9	33.8	19.2	12.3	9.0	9.0
72.5°	1748.7	1506.8	1306.5	1124.1	939.7	729.2	28.1	15.8	10.2	9.0	7.9
75°	659.5	596.4	512.0	460.2	401.8	352.2	22.5	10.2	7.9	7.9	7.9
77.5°	117.0	108.0	95.6	87.8	81.0	74.3	18.0	6.7	6.7	7.9	7.9
80°	78.8	73.2	66.4	60.7	56.3	50.7	12.3	5.6	6.7	6.7	7.9
82.5°	56.3	52.8	49.5	45.0	41.7	37.1	7.9	5.6	6.7	6.7	6.7
85°	33.8	31.5	29.2	27.0	23.6	22.5	5.6	5.6	5.6	6.7	6.7
87.5°	9.0	7.9	9.0	9.0	6.7	7.9	4.5	4.5	4.5	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150908

CATALOG NUMBER: AVS-E04-LED-E-U-SL3-HSS-8030

CANDELA DISTRIBUTION (continued):

	145°	155°	165°	175°	180°
0°	176.7	176.7	176.7	176.7	176.7
2.5°	149.6	149.6	147.5	150.8	150.8
5°	129.4	129.4	128.3	129.4	129.4
7.5°	118.1	117.0	117.0	117.0	118.1
10°	108.0	106.9	106.9	106.9	106.9
12.5°	99.1	97.9	96.8	97.9	97.9
15°	91.2	88.9	88.9	88.9	88.9
17.5°	84.4	82.2	81.0	81.0	81.0
20°	77.6	74.3	74.3	74.3	74.3
22.5°	70.9	67.6	67.6	67.6	67.6
25°	64.1	60.7	60.7	60.7	60.7
27.5°	58.5	55.1	55.1	55.1	55.1
30°	51.8	49.5	49.5	50.7	49.5
32.5°	47.3	43.9	43.9	45.0	45.0
35°	41.7	39.4	39.4	39.4	39.4
37.5°	36.0	33.8	33.8	33.8	33.8
40°	31.5	29.2	28.1	29.2	29.2
42.5°	27.0	24.8	23.6	23.6	23.6
45°	23.6	20.2	19.2	20.2	20.2
47.5°	19.2	16.9	16.9	18.0	18.0
50°	14.6	14.6	15.8	18.0	18.0
52.5°	13.5	13.5	15.8	18.0	18.0
55°	12.3	13.5	15.8	16.9	18.0
57.5°	11.3	13.5	15.8	16.9	16.9
60°	11.3	12.3	14.6	16.9	16.9
62.5°	10.2	11.3	13.5	15.8	15.8
65°	10.2	11.3	13.5	15.8	15.8
66°	10.2	11.3	13.5	15.8	15.8
67.5°	10.2	11.3	13.5	15.8	15.8
70°	10.2	11.3	13.5	14.6	14.6
72.5°	9.0	10.2	12.3	14.6	14.6
75°	9.0	10.2	12.3	14.6	14.6
77.5°	9.0	10.2	12.3	14.6	14.6
80°	9.0	10.2	12.3	13.5	14.6
82.5°	7.9	10.2	11.3	13.5	13.5
85°	7.9	9.0	11.3	12.3	13.5
87.5°	6.7	7.9	9.0	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)