

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156863

Luminaire Tested: **AVS-F02-LED-E-U-T4-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156863
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-T4-8030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (14) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4211.1 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156863

CATALOG NUMBER: AVS-F02-LED-E-U-T4-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.8 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156863

CATALOG NUMBER: AVS-F02-LED-E-U-T4-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P156863

CATALOG NUMBER: AVS-F02-LED-E-U-T4-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	898.6	0.0	898.6
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	3312.6	0.0	3312.6
	% Fixture	78.7	0.0	78.7
Total	Lumens	4211.1	0.0	4211.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.3
10°-20°	163.6	3.9
20°-30°	281.9	6.7
30°-40°	426.5	10.1
40°-50°	552.7	13.1
50°-60°	762.1	18.1
60°-70°	1184.0	28.1
70°-80°	688.5	16.3
80°-90°	97.9	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4211.1	100.0
0°-180°	4211.1	100.0

Coefficient of Utilization



REPORT NUMBER: P156863


CATALOG NUMBER: AVS-F02-LED-E-U-T4-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	258.9	6.1			
FM	(30°-60°)	1351.8	32.1			
FH	(60°-80°)	1626.8	38.6			G1/1800
FVH	(80°-90°)	75.1	1.8			G1/100
BL	(0°-30°)	240.5	5.7	B1/500		
BM	(30°-60°)	389.5	9.2	B1/1000		
BH	(60°-80°)	245.8	5.8	B1/500		G1/500
BVH	(80°-90°)	22.8	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P156863

CATALOG NUMBER: AVS-F02-LED-E-U-T4-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0
2.5°	544.9	546.7	545.3	545.8	545.8	546.2	546.2	546.7	546.2	547.7	548.6
5°	535.1	536.1	535.5	536.5	537.4	539.3	538.9	541.1	541.6	543.0	545.3
7.5°	531.4	530.5	530.9	532.3	533.3	534.2	535.1	537.0	538.3	541.6	543.4
10°	535.1	534.6	535.1	536.1	536.1	536.5	535.5	537.4	538.3	541.1	543.0
12.5°	550.5	550.5	549.5	549.5	548.6	547.7	545.3	543.9	543.4	543.9	544.9
15°	575.0	574.1	572.2	570.9	569.0	565.7	562.5	559.7	557.8	555.0	554.1
17.5°	599.2	597.8	596.0	594.1	591.7	588.5	583.4	580.1	575.0	571.8	569.9
20°	627.0	624.2	622.0	619.6	615.0	614.1	608.9	603.4	597.3	589.9	589.0
22.5°	663.3	658.7	655.9	654.5	649.8	648.4	640.1	632.1	624.8	615.0	612.6
25°	700.0	695.3	694.0	692.1	688.8	686.9	679.1	670.3	660.5	647.0	644.2
27.5°	735.8	736.2	732.5	733.9	733.0	729.7	721.9	713.0	705.6	689.7	686.5
30°	780.3	777.5	775.6	778.4	775.2	775.6	768.7	764.0	752.0	742.7	736.2
32.5°	826.8	826.3	829.1	831.0	830.5	829.5	824.0	819.4	808.7	795.2	792.4
35°	890.5	893.3	895.5	903.9	903.9	909.9	904.4	898.8	886.2	869.9	864.5
37.5°	933.6	934.5	943.8	955.0	968.9	982.0	985.7	987.0	982.0	969.8	961.5
40°	973.1	974.9	989.8	1007.0	1027.5	1053.0	1068.3	1075.3	1076.7	1071.1	1053.0
42.5°	1012.5	1015.3	1030.7	1055.8	1084.1	1116.7	1143.6	1160.7	1170.5	1170.5	1159.8
45°	1058.5	1062.3	1079.0	1106.4	1139.4	1180.3	1217.4	1250.4	1266.2	1267.2	1256.9
47.5°	1113.0	1116.2	1135.6	1163.5	1197.4	1238.8	1285.7	1323.3	1352.6	1354.4	1346.1
50°	1183.0	1187.7	1203.9	1229.0	1263.8	1305.7	1352.6	1405.1	1435.8	1443.2	1434.3
52.5°	1276.0	1276.9	1290.4	1313.6	1347.5	1387.5	1437.1	1494.3	1534.7	1540.7	1526.3
55°	1404.1	1402.8	1411.6	1436.7	1462.2	1493.4	1544.9	1609.0	1654.1	1663.3	1648.5
57.5°	1578.3	1577.0	1584.4	1590.5	1638.2	1668.5	1719.1	1780.4	1824.0	1851.0	1825.5
60°	1848.2	1846.8	1858.9	1894.2	1929.9	1974.1	2023.3	2096.7	2158.0	2165.9	2140.8
62.5°	2043.7	2050.7	2077.2	2118.5	2191.0	2277.4	2367.5	2464.1	2589.9	2629.9	2617.8
65°	1975.4	1989.4	2026.1	2088.8	2185.4	2304.8	2446.0	2621.1	2789.7	2884.0	2881.2
66°	1914.2	1929.5	1974.5	2034.9	2137.1	2267.7	2421.9	2612.7	2801.3	2905.4	2911.9
67.5°	1802.7	1819.9	1864.0	1935.5	2034.9	2173.8	2339.7	2547.3	2760.4	2881.7	2898.9
70°	1585.8	1605.3	1637.3	1696.3	1794.3	1918.3	2093.0	2278.8	2502.2	2641.1	2662.0
72.5°	1325.7	1342.8	1378.7	1426.9	1507.3	1585.3	1722.3	1859.4	2019.2	2177.5	2162.2
75°	951.7	959.2	980.5	1033.1	1076.3	1146.3	1256.5	1368.8	1478.0	1550.5	1560.7
77.5°	494.7	514.2	544.4	602.5	649.3	712.5	784.0	868.6	948.5	1014.9	996.8
80°	323.7	332.1	359.1	388.8	423.1	463.5	511.4	543.0	553.2	549.0	553.2
82.5°	186.7	202.1	237.8	260.6	286.1	300.1	338.1	374.4	394.8	369.2	360.0
85°	23.7	30.7	96.6	121.7	139.4	160.2	171.8	193.7	180.7	161.7	197.0
87.5°	5.1	4.7	6.5	13.9	14.4	12.1	22.8	24.1	14.8	7.5	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156863

CATALOG NUMBER: AVS-F02-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0
2.5°	549.5	549.9	550.9	552.2	553.2	554.1	555.0	556.5	557.4	558.3	560.2
5°	547.2	549.0	550.9	552.7	555.0	558.8	561.1	563.0	564.9	568.5	569.9
7.5°	545.8	549.0	551.8	555.0	558.8	562.1	566.2	568.5	571.3	573.7	576.5
10°	544.9	549.5	552.2	556.9	561.1	564.4	569.0	571.8	575.0	577.8	579.2
12.5°	546.7	549.0	551.8	556.5	561.6	566.2	571.3	573.7	576.5	578.8	579.2
15°	554.6	554.6	555.0	558.8	563.9	567.6	571.8	574.1	575.5	576.9	576.9
17.5°	569.0	565.7	563.4	563.9	567.2	569.4	571.8	571.8	570.9	570.4	569.4
20°	585.7	581.6	576.9	573.7	572.7	570.9	569.4	564.9	561.1	557.8	555.5
22.5°	609.8	603.4	596.9	590.9	585.3	578.3	570.4	561.1	552.2	546.2	542.5
25°	639.6	634.5	626.6	617.3	610.4	597.3	587.2	573.7	562.5	554.6	548.1
27.5°	681.9	675.9	668.4	660.0	649.8	635.4	622.9	607.0	593.6	582.0	573.7
30°	734.4	726.4	720.9	710.7	703.7	687.5	674.9	655.4	629.4	610.8	599.2
32.5°	788.3	779.4	774.8	766.8	759.0	749.2	730.2	700.0	666.5	636.4	616.4
35°	860.2	851.0	842.6	835.6	824.0	805.9	789.1	753.0	706.9	664.7	631.2
37.5°	950.8	935.4	914.6	896.9	876.5	850.5	825.0	787.8	735.3	680.5	635.9
40°	1047.5	1020.5	990.8	957.8	922.5	884.9	855.5	817.9	759.0	694.0	632.6
42.5°	1148.2	1105.5	1064.1	1017.7	968.5	923.8	885.8	844.5	776.6	697.6	619.6
45°	1248.1	1200.2	1137.5	1076.7	1014.4	959.2	916.5	869.9	792.8	699.1	602.5
47.5°	1330.8	1281.6	1209.9	1133.8	1060.0	997.3	947.0	896.9	814.7	708.8	598.2
50°	1418.1	1358.1	1278.8	1188.6	1105.0	1034.9	981.5	929.4	845.4	733.9	611.7
52.5°	1513.3	1444.6	1351.7	1250.9	1159.4	1080.8	1022.8	969.4	884.4	769.2	637.3
55°	1629.4	1545.4	1444.6	1330.8	1232.7	1145.9	1081.8	1018.7	930.9	811.0	669.3
57.5°	1806.8	1703.7	1590.5	1460.8	1352.1	1249.4	1172.8	1099.9	1002.8	873.3	713.0
60°	2127.9	2017.7	1870.5	1713.5	1585.8	1465.9	1353.6	1262.9	1143.6	995.9	809.6
62.5°	2587.7	2441.3	2244.9	2025.2	1857.9	1685.2	1558.3	1423.6	1275.4	1116.2	923.4
65°	2843.1	2665.7	2402.8	2147.8	1932.7	1745.1	1583.9	1427.9	1263.4	1111.1	949.8
66°	2874.7	2689.8	2416.8	2148.3	1922.5	1729.7	1560.2	1398.5	1230.5	1085.1	938.8
67.5°	2861.8	2672.6	2391.2	2107.9	1878.4	1671.2	1496.2	1328.4	1160.7	1025.2	901.6
70°	2648.5	2469.2	2192.8	1918.3	1700.5	1496.2	1328.9	1164.0	1010.3	894.1	803.1
72.5°	2199.4	2046.1	1805.9	1590.5	1419.5	1250.9	1109.2	951.7	821.7	735.8	681.9
75°	1587.7	1494.7	1276.0	1152.4	1002.4	890.5	753.0	659.6	566.2	524.5	515.1
77.5°	1002.8	877.9	739.0	608.5	500.2	414.8	322.8	274.1	228.5	223.8	270.4
80°	507.7	457.1	352.1	280.5	236.0	190.9	151.0	114.3	79.9	96.2	115.2
82.5°	332.5	277.3	217.4	178.9	155.6	129.1	100.3	69.6	51.1	57.6	79.0
85°	179.8	153.3	123.5	97.5	79.0	70.6	47.4	33.5	33.0	35.3	45.1
87.5°	13.1	13.1	10.3	9.3	11.2	9.3	8.4	8.4	7.9	8.4	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156863

CATALOG NUMBER: AVS-F02-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0	555.0
2.5°	561.1	562.5	563.0	565.3	566.6	567.6	568.5	568.5	569.0	570.4	570.9
5°	571.8	574.1	576.9	578.8	579.7	582.5	583.4	583.4	584.4	586.2	587.6
7.5°	578.3	581.6	584.4	585.3	587.2	588.1	589.4	590.4	590.4	592.2	593.2
10°	580.6	582.5	585.3	585.3	587.2	587.2	588.5	589.0	589.0	590.9	592.2
12.5°	580.6	581.6	583.8	583.8	585.3	585.7	587.6	589.0	589.4	591.7	593.6
15°	577.8	578.8	580.6	581.0	584.4	586.2	590.4	593.2	593.2	595.4	596.4
17.5°	569.9	572.2	576.0	579.7	585.7	589.9	595.0	597.3	595.4	594.1	592.6
20°	556.9	561.1	569.9	579.2	589.9	595.4	598.2	596.0	589.4	582.9	578.8
22.5°	543.9	552.2	567.2	581.0	593.2	596.9	595.4	587.2	576.5	568.5	563.0
25°	549.9	559.7	574.1	586.6	594.5	593.6	588.1	576.5	564.9	554.6	545.3
27.5°	575.0	585.7	593.6	597.8	596.9	590.4	581.6	568.5	554.6	541.1	528.1
30°	598.8	604.4	606.1	602.9	595.4	584.8	573.7	558.8	540.2	523.5	508.6
32.5°	609.4	603.8	595.0	586.2	574.1	564.9	549.5	533.3	510.1	490.1	475.1
35°	609.4	587.2	564.9	546.2	528.1	516.5	498.9	477.0	455.6	439.0	427.4
37.5°	596.0	553.2	516.5	486.3	463.5	451.0	424.6	405.1	386.9	381.3	373.9
40°	571.3	508.2	455.2	415.8	386.9	368.3	341.9	328.4	321.5	318.7	317.2
42.5°	538.3	458.0	387.4	338.7	307.5	286.6	268.9	260.6	260.1	259.7	259.7
45°	503.0	404.1	321.5	263.3	236.0	217.4	209.0	205.8	208.6	208.1	208.6
47.5°	481.2	363.2	261.0	199.3	178.3	166.3	162.1	163.5	165.8	164.9	164.9
50°	478.4	342.3	220.6	155.1	139.4	133.3	132.3	132.3	133.8	132.8	132.3
52.5°	488.6	339.1	199.7	133.3	120.7	115.6	114.7	114.3	113.8	111.0	108.7
55°	506.3	346.5	193.7	127.8	114.7	109.1	107.8	106.8	105.0	101.2	97.1
57.5°	541.6	369.7	199.3	130.6	116.6	111.9	110.6	110.6	106.8	100.8	94.7
60°	626.6	428.7	222.1	141.2	125.4	120.7	121.7	121.2	115.6	106.8	97.5
62.5°	736.2	505.8	251.7	156.1	136.6	135.6	140.3	139.4	130.1	116.6	103.1
65°	786.8	542.1	260.1	159.3	138.9	143.1	152.3	151.4	139.8	121.2	104.0
66°	787.8	542.1	256.4	156.6	135.6	140.7	150.1	149.5	137.9	119.4	102.2
67.5°	768.7	527.2	245.7	151.0	129.1	132.8	141.2	140.7	130.1	114.7	98.4
70°	697.2	471.9	218.3	141.2	120.3	118.4	121.2	119.4	112.4	101.8	90.6
72.5°	597.3	396.2	190.5	133.8	114.3	106.8	105.0	103.6	98.0	92.0	85.0
75°	470.6	313.6	167.3	128.2	108.7	99.0	95.6	93.8	90.2	85.9	80.3
77.5°	290.3	224.4	145.8	120.7	104.6	94.7	92.4	89.6	84.0	79.0	74.8
80°	129.6	138.9	119.8	105.4	93.4	84.6	80.8	76.7	71.1	67.8	65.5
82.5°	86.4	89.6	86.8	79.0	70.6	63.6	58.0	58.0	57.1	54.3	53.4
85°	55.2	55.8	53.9	48.8	45.5	41.3	39.1	39.5	41.3	40.8	40.4
87.5°	12.5	12.5	14.8	13.9	16.3	17.2	18.5	20.0	22.8	22.8	24.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156863

CATALOG NUMBER: AVS-F02-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	555.0	555.0	555.0	555.0	555.0
2.5°	571.3	572.2	573.2	571.8	572.2
5°	587.6	587.2	589.4	588.1	589.0
7.5°	592.6	593.2	595.0	595.0	595.4
10°	593.2	594.1	596.4	597.8	598.8
12.5°	595.4	597.3	601.0	602.0	602.0
15°	597.3	598.2	600.6	601.6	602.5
17.5°	590.9	589.0	589.9	590.4	589.9
20°	574.6	572.7	572.2	570.4	571.3
22.5°	556.9	551.8	548.6	544.9	544.9
25°	535.5	527.7	521.1	514.6	516.1
27.5°	515.5	505.4	498.9	494.7	493.8
30°	496.1	485.4	479.4	474.2	474.2
32.5°	463.5	456.2	448.2	445.0	444.6
35°	418.5	413.9	407.4	406.0	403.6
37.5°	367.9	366.5	360.9	360.4	358.1
40°	314.9	315.9	314.0	313.1	311.7
42.5°	262.0	266.6	265.7	265.2	264.2
45°	211.3	214.6	215.0	216.5	218.8
47.5°	166.3	167.3	168.2	167.7	168.2
50°	130.1	127.8	127.3	125.9	127.3
52.5°	105.0	101.2	99.4	97.5	96.6
55°	92.4	88.7	86.8	85.9	85.0
57.5°	89.2	85.5	82.7	80.8	80.3
60°	90.2	84.6	80.8	78.5	78.0
62.5°	92.4	85.0	79.9	77.6	77.1
65°	92.0	84.0	79.4	76.7	76.2
66°	90.6	83.1	78.5	76.2	75.8
67.5°	88.3	81.8	77.6	75.8	74.8
70°	84.0	79.9	76.7	74.3	73.4
72.5°	80.3	77.1	74.3	72.0	71.5
75°	76.2	73.4	70.6	68.7	68.3
77.5°	71.1	68.3	66.4	65.1	64.6
80°	62.7	60.8	59.0	57.1	57.1
82.5°	52.0	50.7	48.8	47.4	46.9
85°	39.9	39.9	38.5	37.2	36.7
87.5°	23.7	23.2	23.2	21.9	21.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)