

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P150917

Luminaire Tested: **AVS-F04-LED-E-U-SL3-HSS-7060**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P150917
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33727)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-SL3-HSS-7060
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (28) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5874.7 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type III - Short - Non-Cutoff
BUG Rating: B0 - U0 - G2

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P150917

CATALOG NUMBER: AVS-F04-LED-E-U-SL3-HSS-7060

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 9.7 fc
 Type III - Short - Non-Cutoff

REPORT NUMBER: P150917

CATALOG NUMBER: AVS-F04-LED-E-U-SL3-HSS-7060

Luminous Intensity Polar Plot



REPORT NUMBER: P150917

CATALOG NUMBER: AVS-F04-LED-E-U-SL3-HSS-7060


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	127.3	0.0	127.3
	% Fixture	2.2	0.0	2.2
Street Side	Lumens	5747.4	0.0	5747.4
	% Fixture	97.8	0.0	97.8
Total	Lumens	5874.7	0.0	5874.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.9	0.3
10°-20°	84.2	1.4
20°-30°	181.5	3.1
30°-40°	387.7	6.6
40°-50°	857.3	14.6
50°-60°	1452.9	24.7
60°-70°	1938.8	33.0
70°-80°	854.0	14.5
80°-90°	98.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5874.7	100.0
0°-180°	5874.7	100.0

Coefficient of Utilization



REPORT NUMBER: P150917


CATALOG NUMBER: AVS-F04-LED-E-U-SL3-HSS-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	245.4	4.2			
FM	(30°-60°)	2642.0	45.0			
FH	(60°-80°)	2765.5	47.1			G2/5000
FVH	(80°-90°)	94.4	1.6			G1/100
BL	(0°-30°)	40.2	0.7	B0/110		
BM	(30°-60°)	55.9	1.0	B0/220		
BH	(60°-80°)	27.3	0.5	B0/110		G0/110
BVH	(80°-90°)	3.9	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short





REPORT NUMBER: P150917

CATALOG NUMBER: AVS-F04-LED-E-U-SL3-HSS-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	67°	68°
0°	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3
2.5°	223.6	222.5	218.0	218.0	211.2	206.7	201.0	195.4	195.4	194.3	193.2
5°	296.0	289.1	288.0	275.5	265.4	250.8	237.2	219.1	216.9	214.6	213.5
7.5°	376.1	374.9	364.8	350.2	329.8	302.7	275.5	246.2	241.7	239.5	234.9
10°	480.0	474.4	460.8	436.0	405.5	369.3	325.3	279.0	273.4	268.8	266.5
12.5°	579.4	569.2	561.3	529.7	491.3	438.2	385.2	318.5	314.0	308.3	299.3
15°	672.0	663.0	649.4	622.3	579.4	512.7	450.7	369.3	358.0	350.2	343.3
17.5°	744.2	738.7	722.8	692.3	646.0	587.4	512.7	421.2	412.2	402.1	389.6
20°	813.2	805.3	780.4	738.7	688.9	643.7	586.2	489.0	476.6	464.2	450.7
22.5°	878.7	870.8	830.2	761.2	708.2	688.9	668.6	565.8	546.6	536.5	522.9
25°	970.2	953.3	889.9	780.4	709.3	723.9	759.0	665.3	647.2	632.4	611.0
27.5°	1093.3	1070.7	971.3	808.7	713.8	762.4	862.9	786.1	766.8	749.9	726.2
30°	1232.2	1217.5	1099.0	876.5	746.5	818.9	979.2	939.7	917.1	896.8	868.5
32.5°	1372.2	1351.9	1234.5	1005.2	834.6	928.4	1124.9	1118.1	1088.8	1069.5	1039.1
35°	1495.3	1485.2	1398.2	1216.4	1035.6	1120.4	1319.2	1327.0	1301.1	1280.8	1246.9
37.5°	1579.0	1579.0	1562.0	1443.4	1355.3	1418.5	1605.0	1606.0	1580.1	1533.8	1516.8
40°	1621.9	1634.3	1695.2	1717.8	1713.4	1794.7	1979.9	1959.6	1938.1	1914.4	1857.9
42.5°	1709.9	1721.2	1851.2	2007.0	2108.7	2216.0	2343.6	2336.8	2310.8	2267.9	2216.0
45°	1859.1	1873.8	2028.5	2275.9	2484.8	2637.2	2718.5	2686.9	2660.9	2620.3	2593.2
47.5°	2048.8	2077.0	2252.1	2558.1	2810.1	3061.9	3146.6	3063.0	3040.4	3008.8	2964.8
50°	2251.0	2278.0	2464.5	2814.5	3099.2	3399.6	3540.7	3399.6	3366.8	3356.7	3306.9
52.5°	2426.0	2448.6	2628.2	3012.2	3320.5	3673.0	3878.4	3692.1	3668.4	3634.5	3598.3
55°	2529.9	2548.0	2716.3	3107.0	3470.8	3919.2	4204.9	4041.1	4006.1	3992.5	3940.6
57.5°	2565.0	2583.0	2734.4	3119.5	3552.0	4143.9	4601.3	4606.9	4565.2	4516.6	4500.8
60°	2565.0	2585.3	2712.8	3089.0	3631.1	4383.3	5129.8	5600.8	5510.5	5501.5	5443.8
62.5°	2458.8	2477.9	2606.7	2995.2	3737.3	4706.3	5866.3	6697.5	6671.6	6612.8	6517.9
65°	2228.4	2239.7	2366.1	2755.9	3696.7	5003.4	6504.5	7427.2	7385.4	7270.2	7148.2
66°	2124.5	2133.5	2252.1	2619.2	3563.3	5044.0	6617.3	7518.7	7449.7	7352.6	7214.8
67.5°	1974.3	1990.1	2073.7	2365.1	3243.7	4902.9	6546.2	7454.3	7394.4	7277.0	7139.2
70°	1318.0	1306.7	1601.6	1815.0	2471.2	3994.8	5873.1	6693.1	6694.2	6638.9	6583.5
72.5°	625.7	632.4	718.3	1117.0	1617.3	2668.8	4674.7	5342.2	5419.1	5319.6	5250.8
75°	449.5	459.7	511.6	683.3	964.6	1601.6	3030.3	3736.2	3738.4	3562.3	3405.3
77.5°	131.0	136.7	192.0	421.2	722.8	1080.8	1740.4	2077.0	2028.5	1902.0	1783.4
80°	54.2	54.2	56.5	134.4	290.3	734.1	1217.5	1599.3	1593.7	1545.1	1475.0
82.5°	20.3	21.5	27.2	55.3	68.9	180.7	812.0	1388.1	1384.7	1315.8	1266.1
85°	2.3	2.3	6.7	23.7	26.0	33.9	162.6	612.1	608.8	612.1	536.5
87.5°	0.0	0.0	1.1	2.3	3.4	4.6	6.7	23.7	26.0	24.9	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150917

CATALOG NUMBER: AVS-F04-LED-E-U-SL3-HSS-7060

CANDELA DISTRIBUTION (continued):

	69°	70°	71°	72°	73°	74°	75°	76°	77°	78°	79°
0°	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3
2.5°	193.2	190.9	190.9	189.7	189.7	189.7	188.6	187.5	187.5	186.3	185.2
5°	211.2	208.9	207.8	205.6	204.5	203.3	201.0	199.9	197.6	196.5	195.4
7.5°	232.6	228.2	227.0	223.6	220.2	218.0	215.8	212.3	210.1	205.6	204.5
10°	259.8	254.1	249.6	245.1	241.7	236.1	232.6	228.2	223.6	220.2	216.9
12.5°	294.8	286.8	280.1	275.5	267.7	260.9	254.1	250.8	241.7	237.2	231.5
15°	333.2	324.1	316.3	307.3	301.6	290.3	281.2	271.1	266.5	258.7	249.6
17.5°	382.9	368.2	355.8	346.7	335.4	324.1	314.0	303.8	290.3	281.2	269.9
20°	436.0	423.5	406.6	390.8	377.2	363.6	349.0	335.4	323.0	308.3	294.8
22.5°	503.7	485.7	465.3	449.5	431.4	416.8	396.5	378.3	358.0	338.9	323.0
25°	589.5	565.8	546.6	524.0	502.6	480.0	455.1	432.5	406.6	388.5	361.5
27.5°	695.8	673.2	647.2	617.8	596.4	562.5	529.7	501.5	471.0	442.7	412.2
30°	831.3	798.5	771.4	743.2	700.2	667.5	629.1	590.7	548.9	520.6	474.4
32.5°	993.9	958.9	918.2	877.6	838.0	791.7	744.2	696.9	650.6	598.5	551.2
35°	1192.6	1150.9	1104.6	1060.5	999.6	949.8	889.9	824.5	772.5	712.6	652.8
37.5°	1455.9	1386.9	1346.3	1300.0	1217.5	1149.7	1083.1	1017.6	926.1	862.9	778.1
40°	1785.6	1745.0	1678.3	1603.8	1529.2	1440.0	1349.6	1262.7	1156.6	1068.4	970.2
42.5°	2173.1	2113.2	2045.4	1938.1	1862.5	1757.4	1654.6	1539.4	1409.5	1296.6	1181.3
45°	2536.7	2465.6	2413.6	2306.3	2227.3	2103.0	1978.8	1856.8	1706.5	1560.8	1427.6
47.5°	2929.7	2871.0	2785.2	2698.2	2618.0	2477.9	2343.6	2195.6	2037.5	1864.7	1691.9
50°	3275.3	3229.0	3170.4	3065.3	2976.1	2858.5	2700.5	2539.0	2339.1	2167.4	1970.9
52.5°	3569.0	3532.8	3450.5	3375.9	3295.6	3185.0	3043.8	2889.1	2673.4	2484.8	2261.1
55°	3915.8	3889.7	3817.5	3771.2	3700.0	3593.9	3461.8	3318.2	3090.2	2884.6	2631.6
57.5°	4483.8	4463.5	4400.3	4381.0	4311.1	4218.4	4055.8	3902.2	3635.6	3380.4	3091.3
60°	5424.7	5384.0	5291.4	5243.9	5096.0	4971.8	4760.5	4549.3	4227.5	3902.2	3554.3
62.5°	6432.1	6318.0	6141.9	5990.6	5780.4	5564.8	5282.4	4959.4	4582.1	4195.9	3796.1
65°	6975.3	6781.1	6558.7	6318.0	6045.9	5728.5	5372.7	4985.3	4579.9	4172.1	3749.7
66°	7037.5	6818.4	6582.4	6314.7	6012.0	5674.3	5312.8	4906.2	4485.0	4087.5	3665.0
67.5°	6959.6	6730.3	6480.7	6183.6	5856.2	5506.0	5126.5	4704.1	4298.7	3895.4	3484.4
70°	6414.1	6185.9	5963.4	5650.6	5301.6	4949.2	4590.1	4117.9	3733.9	3363.4	2997.5
72.5°	5122.0	4967.3	4747.0	4479.4	4139.4	3726.0	3426.7	3004.2	2671.1	2311.9	2028.5
75°	3200.8	2982.8	2710.7	2369.5	2109.7	1774.3	1599.3	1278.5	1088.8	922.8	762.4
77.5°	1636.6	1472.7	1281.9	1089.9	905.8	722.8	559.1	395.3	266.5	185.2	137.8
80°	1351.9	1207.4	1049.2	874.2	711.5	552.3	397.5	271.1	172.8	113.0	88.1
82.5°	1117.0	995.0	853.9	691.2	550.1	433.7	301.6	196.5	122.0	79.1	62.1
85°	475.4	431.4	333.2	264.2	198.8	146.8	102.8	68.9	48.6	39.5	36.2
87.5°	20.3	22.6	21.5	16.9	12.4	12.4	11.3	9.0	9.0	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150917

CATALOG NUMBER: AVS-F04-LED-E-U-SL3-HSS-7060

CANDELA DISTRIBUTION (continued):

	80°	81°	82°	83°	84°	85°	95°	105°	115°	125°	135°
0°	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3
2.5°	185.2	184.1	183.0	183.0	181.9	180.7	173.9	168.3	161.6	157.0	152.4
5°	193.2	192.0	189.7	188.6	186.3	185.2	170.6	158.1	148.0	140.0	134.4
7.5°	201.0	199.9	196.5	193.2	192.0	189.7	166.0	150.3	136.7	127.7	122.0
10°	211.2	207.8	204.5	199.9	196.5	193.2	161.6	141.1	126.5	118.5	113.0
12.5°	225.9	220.2	214.6	208.9	204.5	198.8	159.3	133.3	118.5	109.5	103.9
15°	242.8	234.9	228.2	221.3	213.5	207.8	154.7	126.5	111.8	102.8	96.0
17.5°	258.7	249.6	239.5	229.3	221.3	213.5	150.3	119.7	105.1	96.0	89.2
20°	281.2	267.7	255.2	242.8	231.5	221.3	143.4	113.0	99.4	89.2	82.5
22.5°	306.1	290.3	274.4	257.5	242.8	229.3	137.8	107.3	93.8	83.6	75.6
25°	337.7	318.5	297.0	275.5	258.7	240.5	132.1	101.7	88.1	77.9	70.1
27.5°	381.8	354.6	330.9	303.8	277.8	257.5	127.7	97.1	82.5	72.3	64.4
30°	441.7	402.1	364.8	335.4	305.0	275.5	123.1	91.5	77.9	66.6	57.6
32.5°	508.3	462.0	419.1	374.9	336.6	302.7	118.5	86.9	72.3	61.0	53.1
35°	590.7	531.9	474.4	423.5	377.2	332.0	114.1	82.5	67.8	55.3	47.5
37.5°	709.3	635.9	560.2	494.7	434.8	374.9	110.7	77.9	62.1	49.7	41.8
40°	871.9	777.1	684.5	595.2	517.3	442.7	106.2	73.4	57.6	45.2	37.3
42.5°	1048.1	933.0	811.0	710.4	603.1	509.3	101.7	68.9	53.1	40.6	32.7
45°	1267.3	1123.8	975.9	839.2	708.2	587.4	97.1	64.4	47.5	36.2	28.2
47.5°	1506.6	1323.7	1156.6	984.9	829.0	684.5	91.5	61.0	42.9	31.6	24.9
50°	1752.8	1559.8	1348.5	1153.2	967.9	781.6	85.8	55.3	38.4	28.2	20.3
52.5°	2018.3	1790.2	1574.4	1331.6	1115.9	909.2	80.2	50.8	35.0	24.9	16.9
55°	2356.0	2100.7	1847.8	1575.5	1315.8	1057.2	74.5	45.2	30.5	21.5	13.6
57.5°	2780.6	2477.9	2167.4	1860.2	1545.1	1251.4	70.1	39.5	26.0	18.0	11.3
60°	3181.7	2828.1	2452.0	2098.4	1742.7	1400.5	63.2	35.0	22.6	14.7	11.3
62.5°	3389.4	2986.2	2580.7	2191.1	1811.6	1453.6	56.5	29.3	19.2	12.4	10.2
65°	3338.7	2927.5	2534.4	2141.5	1769.8	1419.7	49.7	26.0	16.9	11.3	10.2
66°	3265.2	2858.5	2463.3	2089.4	1734.8	1383.5	46.3	24.9	15.9	11.3	9.0
67.5°	3104.8	2711.8	2334.5	1986.6	1638.9	1314.6	41.8	22.6	14.7	10.2	9.0
70°	2651.9	2295.0	1993.5	1683.9	1400.5	1108.0	33.9	19.2	12.4	9.0	9.0
72.5°	1755.1	1512.3	1311.3	1128.3	943.1	731.9	28.2	15.9	10.2	9.0	7.9
75°	661.9	598.5	513.9	462.0	403.2	353.5	22.6	10.2	7.9	7.9	7.9
77.5°	117.5	108.4	96.0	88.1	81.3	74.5	18.0	6.7	6.7	7.9	7.9
80°	79.1	73.4	66.6	61.0	56.5	50.8	12.4	5.6	6.7	6.7	7.9
82.5°	56.5	53.1	49.7	45.2	41.8	37.3	7.9	5.6	6.7	6.7	6.7
85°	33.9	31.6	29.3	27.2	23.7	22.6	5.6	5.6	5.6	6.7	6.7
87.5°	9.0	7.9	9.0	9.0	6.7	7.9	4.6	4.6	4.6	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150917

CATALOG NUMBER: AVS-F04-LED-E-U-SL3-HSS-7060

CANDELA DISTRIBUTION (continued):

	145°	155°	165°	175°	180°
0°	177.3	177.3	177.3	177.3	177.3
2.5°	150.3	150.3	148.0	151.3	151.3
5°	129.8	129.8	128.7	129.8	129.8
7.5°	118.5	117.5	117.5	117.5	118.5
10°	108.4	107.3	107.3	107.3	107.3
12.5°	99.4	98.2	97.1	98.2	98.2
15°	91.5	89.2	89.2	89.2	89.2
17.5°	84.7	82.5	81.3	81.3	81.3
20°	77.9	74.5	74.5	74.5	74.5
22.5°	71.2	67.8	67.8	67.8	67.8
25°	64.4	61.0	61.0	61.0	61.0
27.5°	58.8	55.3	55.3	55.3	55.3
30°	51.9	49.7	49.7	50.8	49.7
32.5°	47.5	44.0	44.0	45.2	45.2
35°	41.8	39.5	39.5	39.5	39.5
37.5°	36.2	33.9	33.9	33.9	33.9
40°	31.6	29.3	28.2	29.3	29.3
42.5°	27.2	24.9	23.7	23.7	23.7
45°	23.7	20.3	19.2	20.3	20.3
47.5°	19.2	16.9	16.9	18.0	18.0
50°	14.7	14.7	15.9	18.0	18.0
52.5°	13.6	13.6	15.9	18.0	18.0
55°	12.4	13.6	15.9	16.9	18.0
57.5°	11.3	13.6	15.9	16.9	16.9
60°	11.3	12.4	14.7	16.9	16.9
62.5°	10.2	11.3	13.6	15.9	15.9
65°	10.2	11.3	13.6	15.9	15.9
66°	10.2	11.3	13.6	15.9	15.9
67.5°	10.2	11.3	13.6	15.9	15.9
70°	10.2	11.3	13.6	14.7	14.7
72.5°	9.0	10.2	12.4	14.7	14.7
75°	9.0	10.2	12.4	14.7	14.7
77.5°	9.0	10.2	12.4	14.7	14.7
80°	9.0	10.2	12.4	13.6	14.7
82.5°	7.9	10.2	11.3	13.6	13.6
85°	7.9	9.0	11.3	12.4	13.6
87.5°	6.7	7.9	9.0	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)