

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147588

Luminaire Tested: **AVS-E04-LED-E-U-5MQ-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P147588
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E04-LED-E-U-5MQ-8030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM
Light Source: (84) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10883.3 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B3 - U0 - G2

Input Watts (W): 97.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P147588

CATALOG NUMBER: AVS-E04-LED-E-U-5MQ-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 2 fc
Type V - Short - Full Cutoff

REPORT NUMBER: P147588

CATALOG NUMBER: AVS-E04-LED-E-U-5MQ-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P147588

CATALOG NUMBER: AVS-E04-LED-E-U-5MQ-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5441.7	0.0	5441.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5441.7	0.0	5441.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	10883.3	0.0	10883.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	0.7
10°-20°	244.7	2.2
20°-30°	473.2	4.3
30°-40°	916.2	8.4
40°-50°	1654.3	15.2
50°-60°	2876.6	26.4
60°-70°	3265.6	30.0
70°-80°	1266.1	11.6
80°-90°	114.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10883.3	100.0
0°-180°	10883.3	100.0

Coefficient of Utilization



REPORT NUMBER: P147588


CATALOG NUMBER: AVS-E04-LED-E-U-5MQ-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	395.2	3.6			
FM	(30°-60°)	2723.5	25.0			
FH	(60°-80°)	2265.9	20.8			G2/5000
FVH	(80°-90°)	57.1	0.5			G1/100
BL	(0°-30°)	395.2	3.6	B1/500		
BM	(30°-60°)	2723.5	25.0	B3/5000		
BH	(60°-80°)	2265.9	20.8	B3/2500		G2/5000
BVH	(80°-90°)	57.1	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P147588

CATALOG NUMBER: AVS-E04-LED-E-U-5MQ-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	722.5	722.5	722.5	722.5	722.5	722.5	722.5	722.5	722.5	722.5	722.5
2.5°	726.9	729.2	728.7	727.6	727.6	727.5	726.9	725.3	724.8	725.8	726.9
5°	743.8	743.8	743.8	743.8	742.7	742.7	741.6	740.5	740.9	739.9	739.3
7.5°	769.7	768.1	768.1	767.5	767.5	766.3	764.7	762.4	762.9	762.5	761.9
10°	800.1	800.6	799.0	800.7	797.8	797.3	795.0	794.0	793.4	791.7	791.7
12.5°	836.7	835.0	835.0	833.9	832.7	831.6	828.2	827.7	825.5	824.2	822.6
15°	871.0	870.5	868.2	865.9	865.4	864.2	860.3	858.0	857.5	854.7	852.4
17.5°	905.3	904.2	901.3	900.3	898.0	896.4	893.0	889.5	887.9	886.8	883.9
20°	941.9	940.7	937.9	935.8	932.8	930.6	925.6	922.7	921.0	919.4	917.1
22.5°	987.5	985.3	980.7	976.8	970.6	968.3	961.7	957.7	954.8	952.5	951.5
25°	1036.9	1037.5	1031.3	1026.3	1019.1	1012.8	1004.4	999.8	997.1	994.8	994.2
27.5°	1098.9	1099.5	1093.9	1086.5	1075.2	1068.5	1057.2	1051.6	1049.9	1047.7	1047.0
30°	1196.8	1191.7	1182.2	1170.4	1160.2	1145.6	1129.2	1123.6	1118.0	1116.3	1116.3
32.5°	1376.8	1374.1	1366.1	1336.9	1323.4	1293.0	1264.4	1248.0	1229.4	1220.4	1214.7
35°	1502.9	1501.8	1495.5	1485.4	1477.0	1470.8	1453.9	1451.1	1447.7	1447.7	1452.2
37.5°	1595.6	1589.0	1587.8	1589.5	1587.3	1588.4	1601.9	1620.5	1636.3	1644.1	1643.0
40°	1733.1	1723.5	1729.1	1725.2	1720.0	1719.0	1723.4	1730.8	1738.0	1738.0	1736.4
42.5°	1912.5	1917.0	1919.2	1903.0	1892.2	1889.3	1900.1	1897.8	1905.2	1902.4	1895.0
45°	2179.2	2176.4	2172.4	2152.7	2135.9	2122.4	2125.2	2121.2	2121.8	2117.3	2111.7
47.5°	2448.1	2457.7	2441.5	2431.8	2412.6	2403.1	2411.0	2404.2	2417.2	2393.6	2382.3
50°	2709.2	2716.1	2710.3	2696.8	2696.8	2710.3	2720.0	2732.2	2750.3	2723.3	2682.8
52.5°	2923.1	2928.6	2937.1	2948.3	2976.0	3004.6	3045.2	3088.4	3122.7	3117.7	3071.6
55°	3053.6	3060.3	3074.4	3113.2	3162.7	3238.1	3329.8	3430.6	3509.3	3547.6	3513.8
57.5°	3097.4	3102.5	3140.7	3187.5	3264.6	3376.6	3530.2	3704.0	3855.3	3951.6	3936.4
60°	3087.3	3087.4	3126.2	3190.3	3298.3	3446.8	3664.0	3904.9	4136.7	4280.7	4259.3
62.5°	2980.9	2986.5	3042.3	3119.4	3249.9	3427.8	3686.5	3994.4	4271.7	4450.6	4433.2
65°	2748.0	2752.0	2812.2	2903.8	3049.5	3260.1	3543.0	3884.0	4202.0	4374.1	4341.6
67.5°	2371.6	2375.5	2424.5	2528.1	2682.3	2902.2	3207.7	3583.0	3894.2	4030.4	3932.4
70°	1886.6	1897.8	1929.3	2039.1	2156.1	2371.6	2653.0	3028.2	3322.0	3450.8	3342.8
72.5°	1285.6	1314.4	1352.5	1449.9	1561.9	1740.9	1964.8	2281.0	2516.8	2665.9	2569.7
75°	724.1	764.7	776.5	850.2	942.5	1083.7	1247.5	1474.2	1712.1	1833.2	1717.2
77.5°	312.8	346.1	360.7	395.0	466.9	526.1	625.7	778.7	962.7	1047.7	908.6
80°	154.2	162.1	168.3	178.9	199.2	218.2	265.6	332.4	407.9	427.0	339.9
82.5°	119.3	125.0	135.5	144.0	149.1	154.2	158.7	167.7	174.9	178.9	168.8
85°	83.8	91.2	103.0	112.5	118.1	122.1	126.0	128.9	122.1	111.4	117.0
87.5°	22.0	28.7	40.0	43.3	48.9	51.8	50.7	52.3	47.3	34.4	38.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147588

CATALOG NUMBER: AVS-E04-LED-E-U-5MQ-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	722.5	722.5	722.5	722.5	722.5	722.5	722.5	722.5
2.5°	726.4	725.8	726.4	726.3	726.4	725.8	725.8	725.8
5°	739.3	739.3	739.9	738.8	738.8	739.3	738.8	738.2
7.5°	761.2	760.7	760.7	760.2	760.7	760.2	760.2	759.6
10°	790.6	789.4	789.9	788.3	788.3	787.8	787.8	787.8
12.5°	822.1	820.3	820.9	819.3	816.4	816.9	817.5	817.0
15°	852.4	850.8	849.1	847.9	846.2	846.8	846.8	846.2
17.5°	883.4	880.0	879.4	877.7	877.1	877.2	877.2	877.7
20°	915.4	913.2	912.6	911.0	910.4	912.1	912.5	911.5
22.5°	949.7	948.6	949.8	948.6	950.3	951.5	952.0	950.9
25°	993.2	991.9	993.6	997.5	999.8	1001.0	1003.7	1002.7
27.5°	1048.8	1047.7	1051.6	1057.2	1060.6	1066.2	1069.0	1070.2
30°	1120.8	1125.8	1128.1	1139.5	1141.7	1150.7	1150.7	1154.6
32.5°	1225.5	1235.0	1251.9	1269.3	1293.5	1311.0	1311.0	1320.0
35°	1455.0	1459.0	1471.9	1474.7	1479.8	1485.4	1479.8	1484.2
37.5°	1631.2	1613.7	1601.3	1583.8	1573.3	1573.3	1574.3	1573.2
40°	1721.2	1714.4	1708.8	1694.1	1691.9	1691.4	1691.4	1693.6
42.5°	1882.1	1865.7	1856.8	1844.4	1840.4	1839.4	1838.8	1839.9
45°	2091.4	2065.0	2040.7	2028.4	2017.6	2007.7	2011.0	2011.0
47.5°	2335.0	2293.9	2254.5	2233.2	2214.6	2206.2	2200.5	2198.9
50°	2631.6	2574.2	2523.5	2483.5	2456.6	2456.0	2458.9	2440.8
52.5°	2995.0	2904.5	2841.5	2787.4	2762.1	2759.3	2750.3	2740.2
55°	3397.9	3290.5	3186.3	3128.4	3095.1	3077.2	3066.5	3049.6
57.5°	3813.2	3668.6	3519.0	3426.1	3367.6	3327.0	3305.7	3296.1
60°	4133.3	3935.8	3738.3	3589.2	3491.8	3431.7	3394.5	3379.4
62.5°	4259.3	3991.5	3738.3	3542.5	3401.9	3318.5	3268.5	3246.5
65°	4109.1	3791.7	3503.6	3287.6	3130.7	3037.8	2983.3	2959.6
67.5°	3689.3	3409.1	3095.8	2880.8	2719.3	2627.6	2568.5	2551.1
70°	3093.0	2806.5	2507.2	2315.3	2171.3	2096.5	2035.2	2027.9
72.5°	2324.4	2077.3	1820.7	1662.1	1546.1	1422.4	1390.9	1406.6
75°	1489.9	1258.7	1030.3	887.3	781.6	663.4	617.8	629.0
77.5°	705.6	546.3	394.4	305.0	256.0	218.9	209.3	203.7
80°	261.7	212.0	187.4	177.8	171.0	164.8	160.3	155.3
82.5°	169.3	165.4	160.3	158.7	153.6	145.7	131.1	124.9
85°	126.6	126.6	119.8	120.4	116.5	106.3	92.8	85.5
87.5°	37.1	33.2	30.5	28.2	27.6	24.8	18.0	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)