

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148093

Luminaire Tested: **AVS-F02-LED-E-U-5WQ-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148093
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-5WQ-8030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (14) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4436.5 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G1

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P148093

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.7 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P148093

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P148093

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2218.3	0.0	2218.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2218.3	0.0	2218.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	4436.5	0.0	4436.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.1	0.5
10°-20°	81.7	1.8
20°-30°	165.4	3.7
30°-40°	277.3	6.3
40°-50°	489.2	11.0
50°-60°	862.7	19.4
60°-70°	1317.0	29.7
70°-80°	1100.5	24.8
80°-90°	119.6	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4436.5	100.0
0°-180°	4436.5	100.0

Coefficient of Utilization



REPORT NUMBER: P148093


CATALOG NUMBER: AVS-F02-LED-E-U-5WQ-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	135.1	3.0			
FM	(30°-60°)	814.6	18.4			
FH	(60°-80°)	1208.8	27.2			G1/1800
FVH	(80°-90°)	59.8	1.3			G1/100
BL	(0°-30°)	135.1	3.0	B1/500		
BM	(30°-60°)	814.6	18.4	B1/1000		
BH	(60°-80°)	1208.8	27.2	B3/2500		G1/1800
BVH	(80°-90°)	59.8	1.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1

Type V Short





REPORT NUMBER: P148093

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	230.4	230.4	230.4	230.4	230.4	230.4	230.4	230.4	230.4	230.4	230.4
2.5°	232.2	232.7	232.2	232.2	232.2	232.2	232.2	231.8	231.8	231.8	232.2
5°	236.9	237.3	236.9	237.3	237.3	237.3	237.3	236.9	236.9	236.9	236.9
7.5°	244.4	244.4	244.4	244.8	244.4	244.4	244.8	244.4	244.4	244.4	244.4
10°	255.0	254.5	254.5	254.5	254.5	254.5	255.0	255.0	255.0	254.5	254.5
12.5°	268.0	267.6	268.0	268.0	268.5	268.5	268.5	268.5	268.5	268.5	268.0
15°	283.8	283.8	283.8	284.2	285.2	285.2	284.8	285.2	285.2	285.2	285.2
17.5°	301.5	302.4	301.5	302.0	302.4	302.0	302.8	303.3	303.7	303.3	302.0
20°	319.6	320.0	320.0	320.0	320.0	320.9	321.5	321.5	322.8	322.4	321.9
22.5°	336.8	337.7	337.7	338.1	338.1	339.6	339.6	339.6	340.5	341.5	340.5
25°	354.9	354.4	354.4	355.3	355.8	357.6	357.6	358.5	360.0	360.4	359.5
27.5°	371.1	370.7	370.7	372.0	372.5	374.8	374.8	376.7	377.6	378.1	377.2
30°	388.3	388.3	387.9	389.2	390.7	392.5	393.5	395.2	396.7	397.1	396.2
32.5°	408.7	407.8	408.3	409.2	410.2	412.0	413.4	415.8	417.6	418.0	417.1
35°	432.0	430.6	431.1	432.0	433.4	436.2	438.4	439.9	442.7	443.6	441.8
37.5°	457.5	458.0	457.5	459.9	462.2	465.4	468.2	470.1	472.8	474.2	472.8
40°	493.8	492.3	493.8	496.1	499.8	503.9	509.5	511.0	513.7	516.5	513.3
42.5°	540.6	539.7	543.0	544.9	549.0	553.7	560.6	564.4	568.5	570.4	567.6
45°	602.0	602.0	605.7	606.1	612.6	618.7	628.5	633.1	641.0	641.0	641.0
47.5°	669.8	672.5	674.9	679.6	684.1	695.3	705.1	715.3	722.8	723.6	722.3
50°	739.9	742.7	749.6	756.2	766.4	780.3	791.0	804.5	811.0	816.6	814.7
52.5°	817.5	817.9	826.3	834.7	849.5	864.9	882.1	896.0	907.6	912.7	908.5
55°	902.5	903.4	910.9	919.7	936.4	954.1	975.4	989.8	1004.7	1014.0	1007.0
57.5°	994.5	994.9	1002.4	1013.1	1033.1	1050.7	1071.1	1091.5	1105.5	1113.9	1109.2
60°	1096.2	1098.5	1104.1	1117.5	1136.6	1155.2	1175.6	1193.8	1209.9	1218.9	1214.2
62.5°	1204.9	1207.3	1215.1	1225.8	1242.5	1262.9	1282.5	1305.7	1319.2	1328.9	1322.0
65°	1277.8	1282.0	1294.5	1308.9	1333.6	1360.0	1382.8	1414.4	1430.7	1442.3	1435.8
67.5°	1282.5	1284.8	1300.1	1322.0	1354.9	1394.8	1441.3	1490.6	1522.6	1537.9	1526.7
69°	1250.9	1254.1	1269.0	1293.6	1330.3	1376.8	1432.0	1493.4	1542.6	1565.3	1554.6
70°	1215.1	1222.1	1238.3	1265.3	1301.0	1349.8	1406.9	1472.4	1530.1	1561.1	1553.3
72.5°	1139.9	1141.8	1152.4	1173.8	1201.1	1241.6	1295.4	1357.2	1412.0	1456.7	1463.1
75°	1011.7	1017.7	1025.6	1040.0	1053.9	1083.2	1119.4	1161.7	1193.8	1228.1	1229.5
77.5°	764.6	782.7	788.7	791.9	798.0	821.2	852.8	889.5	916.0	921.6	920.6
80°	343.2	367.5	373.0	399.5	415.8	454.3	502.6	558.8	596.4	600.6	590.4
82.5°	67.4	72.0	84.0	105.0	143.1	165.8	197.4	236.9	273.2	294.0	281.5
85°	22.3	23.7	27.4	30.2	34.8	39.5	47.9	59.5	73.9	81.8	73.0
87.5°	8.8	8.8	10.3	11.2	12.1	12.1	12.1	11.2	10.7	8.8	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148093

CATALOG NUMBER: AVS-F02-LED-E-U-5WQ-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	230.4	230.4	230.4	230.4	230.4	230.4	230.4	230.4
2.5°	231.8	231.8	231.8	231.8	231.8	231.8	231.8	231.8
5°	236.9	236.5	236.5	236.0	236.0	236.0	236.0	236.0
7.5°	243.8	243.4	242.9	243.4	242.9	242.9	242.9	242.9
10°	254.5	253.6	253.2	252.6	252.6	252.6	252.2	252.2
12.5°	267.0	267.0	266.6	266.1	265.2	265.7	265.2	264.2
15°	284.2	283.3	282.9	282.4	281.5	281.5	281.5	281.0
17.5°	301.5	300.5	300.5	299.2	298.7	298.7	298.7	299.2
20°	320.5	319.1	318.1	317.2	316.3	316.8	315.9	316.8
22.5°	339.6	337.7	336.8	335.3	334.0	334.0	333.5	332.5
25°	358.1	355.8	354.9	353.5	351.6	351.6	350.7	349.7
27.5°	375.8	373.5	372.5	369.7	367.9	367.5	366.5	366.0
30°	395.2	392.5	391.1	388.3	385.5	385.1	383.6	383.6
32.5°	415.8	413.0	412.0	407.8	405.5	405.5	404.6	403.6
35°	441.2	437.1	436.2	432.0	428.7	428.7	427.8	428.3
37.5°	471.5	468.2	465.0	461.7	458.0	457.5	456.6	455.6
40°	511.9	508.2	504.5	499.8	496.6	495.6	494.2	493.8
42.5°	565.7	562.1	554.6	550.9	547.7	544.9	544.4	543.9
45°	634.5	629.8	624.8	617.8	613.6	607.6	606.6	604.4
47.5°	717.2	708.4	699.5	693.5	686.9	680.0	678.7	674.9
50°	805.0	798.0	783.1	773.4	763.1	756.2	751.5	750.2
52.5°	899.3	886.2	871.4	858.3	843.5	834.2	825.9	823.5
55°	997.7	979.2	960.5	945.3	930.4	919.3	911.3	907.6
57.5°	1096.2	1075.8	1055.3	1038.5	1026.0	1011.7	1003.7	1001.9
60°	1198.9	1179.4	1158.4	1141.8	1126.4	1113.9	1109.2	1100.4
62.5°	1307.6	1287.2	1267.6	1251.3	1231.8	1223.0	1215.1	1209.9
65°	1414.4	1390.7	1366.1	1348.9	1329.3	1316.8	1307.0	1300.1
67.5°	1497.1	1461.2	1428.3	1399.5	1373.1	1353.6	1340.9	1334.5
69°	1520.3	1475.6	1433.4	1395.8	1364.7	1342.8	1328.9	1322.4
70°	1517.5	1468.3	1421.8	1380.4	1346.5	1323.3	1309.8	1297.8
72.5°	1431.6	1386.5	1334.9	1289.8	1259.3	1236.9	1223.4	1217.0
75°	1221.7	1191.4	1154.3	1119.4	1097.1	1084.1	1067.4	1067.9
77.5°	889.5	890.5	865.4	829.5	804.5	799.9	792.4	785.0
80°	551.8	507.7	478.9	440.3	412.0	387.4	376.7	353.5
82.5°	254.5	198.8	154.2	116.6	89.6	70.2	61.3	50.2
85°	56.7	43.2	35.8	28.8	24.7	22.8	18.5	17.2
87.5°	7.9	6.9	6.5	6.0	5.1	3.7	2.8	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)