

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156873

Luminaire Tested: **AVS-F03-LED-E-U-T4-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156873
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F03-LED-E-U-T4-8030
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (21) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6316.7 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156873

CATALOG NUMBER: AVS-F03-LED-E-U-T4-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 8.7 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156873

CATALOG NUMBER: AVS-F03-LED-E-U-T4-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P156873

CATALOG NUMBER: AVS-F03-LED-E-U-T4-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1347.8	0.0	1347.8
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	4968.9	0.0	4968.9
	% Fixture	78.7	0.0	78.7
Total	Lumens	6316.7	0.0	6316.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.8	1.3
10°-20°	245.5	3.9
20°-30°	422.8	6.7
30°-40°	639.7	10.1
40°-50°	829.1	13.1
50°-60°	1143.1	18.1
60°-70°	1776.0	28.1
70°-80°	1032.8	16.3
80°-90°	146.9	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6316.7	100.0
0°-180°	6316.7	100.0

Coefficient of Utilization



REPORT NUMBER: P156873


CATALOG NUMBER: AVS-F03-LED-E-U-T4-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	388.4	6.1			
FM	(30°-60°)	2027.7	32.1			
FH	(60°-80°)	2440.1	38.6			G2/5000
FVH	(80°-90°)	112.7	1.8			G2/225
BL	(0°-30°)	360.8	5.7	B1/500		
BM	(30°-60°)	584.3	9.2	B1/1000		
BH	(60°-80°)	368.6	5.8	B1/500		G1/500
BVH	(80°-90°)	34.1	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P156873

CATALOG NUMBER: AVS-F03-LED-E-U-T4-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6
2.5°	817.3	820.1	817.9	818.7	818.7	819.4	819.4	820.1	819.4	821.5	822.8
5°	802.6	804.0	803.3	804.8	806.1	808.9	808.2	811.7	812.4	814.5	817.9
7.5°	797.1	795.6	796.4	798.4	799.9	801.2	802.6	805.4	807.6	812.4	815.1
10°	802.6	802.0	802.6	804.0	804.0	804.8	803.3	806.1	807.6	811.7	814.5
12.5°	825.6	825.6	824.2	824.2	822.8	821.5	817.9	815.9	815.1	815.9	817.3
15°	862.6	861.1	858.3	856.3	853.5	848.6	843.7	839.6	836.8	832.6	831.2
17.5°	898.8	896.7	893.9	891.1	887.7	882.8	875.1	870.3	862.6	857.7	854.9
20°	940.6	936.4	933.0	929.4	922.5	921.0	913.5	905.1	896.0	884.9	883.4
22.5°	994.9	988.0	983.8	981.7	974.7	972.6	960.1	948.3	937.1	922.5	919.0
25°	1049.9	1043.0	1040.9	1038.1	1033.3	1030.5	1018.7	1005.4	990.8	970.6	966.3
27.5°	1103.6	1104.4	1098.8	1100.8	1099.5	1094.6	1082.7	1069.5	1058.3	1034.6	1029.7
30°	1170.5	1166.3	1163.5	1167.8	1162.9	1163.5	1153.1	1146.1	1128.0	1114.1	1104.4
32.5°	1240.2	1239.5	1243.6	1246.4	1245.8	1244.4	1236.0	1229.0	1213.1	1192.8	1188.6
35°	1335.6	1339.8	1343.3	1355.9	1355.9	1364.9	1356.6	1348.2	1329.3	1305.0	1296.6
37.5°	1400.4	1401.9	1415.8	1432.5	1453.4	1472.8	1478.4	1480.5	1472.8	1454.8	1442.3
40°	1459.7	1462.5	1484.8	1510.6	1541.1	1579.5	1602.5	1613.0	1615.0	1606.6	1579.5
42.5°	1518.9	1523.1	1546.0	1583.7	1626.2	1674.9	1715.3	1741.1	1755.8	1755.8	1739.8
45°	1587.9	1593.5	1618.5	1659.6	1709.1	1770.4	1826.1	1875.6	1899.3	1900.7	1885.4
47.5°	1669.4	1674.3	1703.5	1745.3	1796.2	1858.2	1928.6	1985.0	2028.9	2031.7	2019.2
50°	1774.6	1781.6	1805.9	1843.5	1895.9	1958.5	2028.9	2107.7	2153.6	2164.8	2151.5
52.5°	1913.9	1915.3	1935.5	1970.4	2021.2	2081.1	2155.8	2241.3	2302.0	2311.1	2289.4
55°	2106.2	2104.1	2117.4	2155.0	2193.4	2240.0	2317.3	2413.5	2481.0	2495.0	2472.7
57.5°	2367.5	2365.4	2376.6	2385.6	2457.4	2502.7	2578.7	2670.6	2736.1	2776.5	2738.1
60°	2772.3	2770.3	2788.3	2841.2	2894.9	2961.1	3035.0	3145.1	3237.0	3248.9	3211.3
62.5°	3065.6	3076.1	3115.8	3177.8	3286.5	3416.1	3551.3	3696.2	3885.0	3944.9	3926.8
65°	2963.2	2984.1	3039.2	3133.3	3278.1	3457.2	3669.0	3931.7	4184.6	4326.0	4321.9
66°	2871.3	2894.2	2961.9	3052.4	3205.7	3401.5	3632.7	3919.2	4202.0	4358.0	4367.9
67.5°	2704.0	2729.8	2796.0	2903.3	3052.4	3260.7	3509.4	3820.9	4140.7	4322.6	4348.3
70°	2378.7	2407.9	2456.0	2544.5	2691.5	2877.5	3139.5	3418.1	3753.3	3961.7	3993.0
72.5°	1988.5	2014.3	2067.9	2140.4	2260.9	2377.9	2583.5	2789.0	3028.7	3266.3	3243.3
75°	1427.6	1438.8	1470.8	1549.5	1614.3	1719.6	1884.7	2053.3	2217.0	2325.7	2341.0
77.5°	742.1	771.3	816.6	903.6	974.0	1068.8	1176.1	1302.9	1422.7	1522.4	1495.2
80°	485.6	498.1	538.5	583.2	634.7	695.3	767.2	814.5	829.8	823.5	829.8
82.5°	280.1	303.1	356.7	390.9	429.2	450.1	507.3	561.6	592.2	553.9	540.0
85°	35.5	46.0	144.9	182.6	209.0	240.4	257.8	290.6	271.0	242.5	295.4
87.5°	7.7	6.9	9.7	20.9	21.6	18.1	34.1	36.3	22.3	11.2	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156873

CATALOG NUMBER: AVS-F03-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6
2.5°	824.2	825.0	826.3	828.4	829.8	831.2	832.6	834.7	836.1	837.5	840.3
5°	820.7	823.5	826.3	829.1	832.6	838.1	841.7	844.5	847.3	852.8	854.9
7.5°	818.7	823.5	827.8	832.6	838.1	843.0	849.3	852.8	857.0	860.5	864.7
10°	817.3	824.2	828.4	835.3	841.7	846.5	853.5	857.7	862.6	866.7	868.8
12.5°	820.1	823.5	827.8	834.7	842.4	849.3	857.0	860.5	864.7	868.1	868.8
15°	831.9	831.9	832.6	838.1	845.8	851.4	857.7	861.1	863.2	865.4	865.4
17.5°	853.5	848.6	845.2	845.8	850.7	854.2	857.7	857.7	856.3	855.5	854.2
20°	878.5	872.3	865.4	860.5	859.1	856.3	854.2	847.3	841.7	836.8	833.3
22.5°	914.8	905.1	895.3	886.2	877.9	867.5	855.5	841.7	828.4	819.4	813.8
25°	959.4	951.7	939.9	926.0	915.5	896.0	880.7	860.5	843.7	831.9	822.2
27.5°	1022.8	1013.8	1002.6	990.1	974.7	953.2	934.3	910.7	890.5	873.1	860.5
30°	1101.6	1089.7	1081.3	1066.0	1055.5	1031.2	1012.3	983.1	944.0	916.2	898.8
32.5°	1182.4	1169.1	1162.2	1150.3	1138.4	1123.8	1095.2	1049.9	999.8	954.5	924.6
35°	1290.4	1276.4	1263.8	1253.5	1236.0	1208.8	1183.7	1129.4	1060.4	997.0	946.8
37.5°	1426.2	1403.2	1371.9	1345.4	1314.7	1275.8	1237.4	1181.7	1102.9	1020.7	953.8
40°	1571.1	1530.8	1486.1	1436.7	1383.7	1327.3	1283.4	1226.9	1138.4	1040.9	948.9
42.5°	1722.3	1658.2	1596.3	1526.5	1452.6	1385.8	1328.7	1266.6	1165.0	1046.5	929.4
45°	1872.1	1800.4	1706.3	1615.0	1521.7	1438.8	1374.6	1305.0	1189.3	1048.6	903.6
47.5°	1996.2	1922.3	1815.0	1700.7	1589.9	1495.9	1420.6	1345.4	1222.1	1063.2	897.4
50°	2127.2	2037.3	1918.1	1782.9	1657.5	1552.3	1472.2	1394.2	1268.1	1100.8	917.6
52.5°	2269.9	2166.8	2027.5	1876.3	1739.1	1621.3	1534.2	1454.1	1326.6	1153.8	956.0
55°	2444.1	2318.0	2166.8	1996.2	1849.1	1718.9	1622.7	1528.0	1396.3	1216.5	1004.0
57.5°	2710.3	2555.6	2385.6	2191.2	2028.2	1874.2	1759.3	1649.8	1504.2	1309.8	1069.5
60°	3191.7	3026.6	2805.8	2570.3	2378.7	2198.9	2030.3	1894.4	1715.3	1493.8	1214.4
62.5°	3881.6	3662.1	3367.4	3037.7	2786.9	2527.8	2337.5	2135.5	1913.3	1674.3	1385.1
65°	4264.8	3998.5	3604.2	3221.7	2899.1	2617.6	2375.9	2141.8	1895.1	1666.6	1424.9
66°	4312.1	4034.8	3625.1	3222.4	2883.8	2594.6	2340.3	2097.8	1845.7	1627.6	1408.1
67.5°	4292.5	4009.0	3586.8	3161.8	2817.6	2506.8	2244.1	1992.6	1741.1	1537.7	1352.3
70°	3972.7	3703.8	3289.3	2877.5	2550.8	2244.1	1993.4	1746.0	1515.4	1341.2	1204.7
72.5°	3299.1	3069.1	2708.9	2385.6	2129.2	1876.3	1663.8	1427.6	1232.5	1103.6	1022.8
75°	2381.5	2242.1	1913.9	1728.6	1503.5	1335.6	1129.4	989.3	849.3	786.6	772.6
77.5°	1504.2	1316.8	1108.5	912.7	750.4	622.2	484.2	411.1	342.8	335.9	405.5
80°	761.6	685.6	528.1	420.8	354.0	286.3	226.4	171.4	119.8	144.2	172.7
82.5°	498.9	416.0	326.1	268.3	233.4	193.7	150.5	104.6	76.7	86.4	118.4
85°	269.6	229.9	185.3	146.3	118.4	105.9	71.1	50.2	49.4	53.0	67.6
87.5°	19.5	19.5	15.3	13.9	16.7	13.9	12.5	12.5	11.8	12.5	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156873

CATALOG NUMBER: AVS-F03-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6	832.6
2.5°	841.7	843.7	844.5	847.9	850.1	851.4	852.8	852.8	853.5	855.5	856.3
5°	857.7	861.1	865.4	868.1	869.5	873.7	875.1	875.1	876.5	879.3	881.3
7.5°	867.5	872.3	876.5	877.9	880.7	882.1	884.1	885.6	885.6	888.3	889.7
10°	870.9	873.7	877.9	877.9	880.7	880.7	882.8	883.4	883.4	886.2	888.3
12.5°	870.9	872.3	875.8	875.8	877.9	878.5	881.3	883.4	884.1	887.7	890.5
15°	866.7	868.1	870.9	871.6	876.5	879.3	885.6	889.7	889.7	893.3	894.6
17.5°	854.9	858.3	863.9	869.5	878.5	884.9	892.5	896.0	893.3	891.1	889.0
20°	835.3	841.7	854.9	868.8	884.9	893.3	897.4	893.9	884.1	874.4	868.1
22.5°	815.9	828.4	850.7	871.6	889.7	895.3	893.3	880.7	864.7	852.8	844.5
25°	825.0	839.6	861.1	880.0	891.8	890.5	882.1	864.7	847.3	831.9	817.9
27.5°	862.6	878.5	890.5	896.7	895.3	885.6	872.3	852.8	831.9	811.7	792.2
30°	898.1	906.4	909.2	904.4	893.3	877.2	860.5	838.1	810.3	785.2	762.9
32.5°	914.1	905.8	892.5	879.3	861.1	847.3	824.2	799.9	765.0	735.0	712.7
35°	914.1	880.7	847.3	819.4	792.2	774.8	748.3	715.5	683.5	658.4	641.0
37.5°	893.9	829.8	774.8	729.5	695.3	676.6	636.8	607.6	580.4	572.0	560.8
40°	857.0	762.3	682.8	623.6	580.4	552.5	512.7	492.6	482.2	477.9	475.9
42.5°	807.6	686.9	581.0	507.9	461.2	429.8	403.4	390.9	390.2	389.4	389.4
45°	754.6	606.1	482.2	395.0	354.0	326.1	313.6	308.7	312.8	312.1	312.8
47.5°	721.9	544.9	391.6	298.9	267.6	249.4	243.2	245.3	248.7	247.4	247.4
50°	717.6	513.5	331.0	232.7	209.0	200.0	198.5	198.5	200.6	199.3	198.5
52.5°	733.0	508.6	299.6	200.0	181.1	173.5	172.1	171.4	170.7	166.5	163.0
55°	759.5	519.8	290.6	191.6	172.1	163.7	161.7	160.2	157.5	151.9	145.6
57.5°	812.4	554.6	298.9	195.8	174.9	167.9	165.8	165.8	160.2	151.2	142.2
60°	939.9	643.1	333.1	211.8	188.1	181.1	182.6	181.9	173.5	160.2	146.3
62.5°	1104.4	758.8	377.6	234.1	204.9	203.4	210.4	209.0	195.1	174.9	154.7
65°	1180.3	813.1	390.2	239.0	208.3	214.6	228.5	227.2	209.7	181.9	156.1
66°	1181.7	813.1	384.6	234.8	203.4	211.1	225.1	224.4	206.9	179.1	153.3
67.5°	1153.1	790.8	368.6	226.4	193.7	199.3	211.8	211.1	195.1	172.1	147.7
70°	1045.8	707.9	327.5	211.8	180.4	177.6	181.9	179.1	168.6	152.5	135.9
72.5°	896.0	594.3	285.7	200.6	171.4	160.2	157.5	155.3	147.0	137.9	127.5
75°	705.8	470.3	250.8	192.3	163.0	148.4	143.5	140.7	135.1	128.9	120.5
77.5°	435.4	336.5	218.8	181.1	156.8	142.2	138.7	134.5	126.1	118.4	112.1
80°	194.4	208.3	179.8	158.1	140.0	126.8	121.2	114.9	106.6	101.8	98.2
82.5°	129.6	134.5	130.3	118.4	105.9	95.4	87.0	87.0	85.7	81.6	80.1
85°	82.9	83.6	80.8	73.2	68.3	62.0	58.5	59.2	62.0	61.3	60.6
87.5°	18.9	18.9	22.3	20.9	24.4	25.8	27.9	29.9	34.1	34.1	36.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156873

CATALOG NUMBER: AVS-F03-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	832.6	832.6	832.6	832.6	832.6
2.5°	857.0	858.3	859.8	857.7	858.3
5°	881.3	880.7	884.1	882.1	883.4
7.5°	889.0	889.7	892.5	892.5	893.3
10°	889.7	891.1	894.6	896.7	898.1
12.5°	893.3	896.0	901.6	903.0	903.0
15°	896.0	897.4	900.8	902.3	903.6
17.5°	886.2	883.4	884.9	885.6	884.9
20°	861.9	859.1	858.3	855.5	857.0
22.5°	835.3	827.8	822.8	817.3	817.3
25°	803.3	791.5	781.8	772.0	774.1
27.5°	773.4	758.0	748.3	742.1	740.6
30°	744.1	728.1	719.1	711.4	711.4
32.5°	695.3	684.1	672.3	667.5	666.7
35°	627.8	620.8	611.1	608.9	605.5
37.5°	551.8	549.7	541.3	540.6	537.2
40°	472.4	473.8	471.0	469.6	467.5
42.5°	393.0	399.9	398.5	397.8	396.5
45°	317.0	321.9	322.6	324.7	328.2
47.5°	249.4	250.8	252.2	251.5	252.2
50°	195.1	191.6	190.9	188.8	190.9
52.5°	157.5	151.9	149.1	146.3	144.9
55°	138.7	133.1	130.3	128.9	127.5
57.5°	133.8	128.2	124.0	121.2	120.5
60°	135.1	126.8	121.2	117.7	117.1
62.5°	138.7	127.5	119.8	116.4	115.6
65°	137.9	126.1	119.2	114.9	114.3
66°	135.9	124.8	117.7	114.3	113.6
67.5°	132.3	122.6	116.4	113.6	112.1
70°	126.1	119.8	114.9	111.5	110.1
72.5°	120.5	115.6	111.5	108.0	107.3
75°	114.3	110.1	105.9	103.1	102.4
77.5°	106.6	102.4	99.6	97.5	96.9
80°	94.1	91.3	88.5	85.7	85.7
82.5°	78.0	76.0	73.2	71.1	70.4
85°	59.9	59.9	57.8	55.8	55.0
87.5°	35.5	34.8	34.8	32.7	32.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)