

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155843

Luminaire Tested: **AVS-F04-LED-E-U-T3-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155843
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-T3-8030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA
Light Source: (28) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8594.7 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P155843

CATALOG NUMBER: AVS-F04-LED-E-U-T3-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 9.3 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155843

CATALOG NUMBER: AVS-F04-LED-E-U-T3-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P155843

CATALOG NUMBER: AVS-F04-LED-E-U-T3-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2968.0	0.0	2968.0
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	5626.7	0.0	5626.7
	% Fixture	65.5	0.0	65.5
Total	Lumens	8594.7	0.0	8594.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	1.0
10°-20°	261.8	3.0
20°-30°	450.0	5.2
30°-40°	730.6	8.5
40°-50°	1219.7	14.2
50°-60°	1920.6	22.3
60°-70°	2619.0	30.5
70°-80°	1133.8	13.2
80°-90°	170.5	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8594.7	100.0
0°-180°	8594.7	100.0

Coefficient of Utilization



REPORT NUMBER: P155843


CATALOG NUMBER: AVS-F04-LED-E-U-T3-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	402.1	4.7			
FM	(30°-60°)	2400.2	27.9			
FH	(60°-80°)	2684.4	31.2			G2/5000
FVH	(80°-90°)	140.0	1.6			G2/225
BL	(0°-30°)	398.4	4.6	B1/500		
BM	(30°-60°)	1470.8	17.1	B2/2500		
BH	(60°-80°)	1068.4	12.4	B3/2500		G3/2500
BVH	(80°-90°)	30.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P155843

CATALOG NUMBER: AVS-F04-LED-E-U-T3-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2
2.5°	929.9	933.6	929.9	930.9	931.8	930.9	929.9	929.9	927.2	929.0	930.9
5°	926.2	929.0	928.1	929.0	929.9	929.0	928.1	929.0	927.2	928.1	930.9
7.5°	921.6	920.6	921.6	923.4	925.3	925.3	925.3	926.2	925.3	925.3	928.1
10°	907.6	908.5	910.4	913.2	914.1	916.9	916.9	919.7	920.6	922.5	926.2
12.5°	889.9	890.9	892.7	894.6	899.3	903.9	903.9	910.4	913.2	917.8	924.4
15°	877.0	877.9	879.8	881.6	885.3	889.9	892.7	900.2	904.9	913.2	922.5
17.5°	884.4	883.4	885.3	886.2	886.2	889.9	889.9	895.5	901.1	908.5	920.6
20°	905.8	905.8	907.6	907.6	906.7	908.5	904.9	904.9	905.8	909.4	917.8
22.5°	927.2	926.2	929.9	931.8	932.7	935.4	931.8	930.9	926.2	923.4	926.2
25°	947.6	946.6	951.3	954.1	958.8	961.5	961.5	961.5	957.8	953.2	950.4
27.5°	979.2	979.2	983.8	986.5	990.3	995.9	998.7	998.7	999.6	993.1	988.4
30°	1032.1	1033.1	1034.0	1037.7	1041.3	1043.2	1046.9	1049.7	1052.5	1048.8	1041.3
32.5°	1095.2	1089.7	1089.7	1095.2	1099.9	1105.5	1107.4	1111.1	1116.7	1113.9	1113.0
35°	1170.5	1168.7	1166.8	1168.7	1174.2	1180.7	1188.2	1194.7	1191.0	1196.5	1193.8
37.5°	1282.0	1283.8	1284.8	1284.8	1283.8	1285.7	1289.4	1296.0	1294.1	1296.0	1299.7
40°	1465.9	1459.4	1453.0	1453.9	1444.6	1446.4	1431.6	1438.0	1439.0	1432.5	1435.2
42.5°	1649.8	1653.6	1656.4	1663.8	1657.3	1653.6	1639.7	1639.7	1632.2	1625.7	1623.8
45°	1848.7	1856.1	1857.0	1871.9	1866.3	1878.4	1888.6	1885.8	1873.8	1872.8	1859.8
47.5°	2007.6	2019.6	2032.6	2050.3	2064.1	2091.1	2122.7	2138.5	2147.8	2155.2	2140.4
50°	2126.4	2132.0	2165.5	2193.4	2223.9	2268.6	2312.2	2368.9	2414.4	2435.8	2456.3
52.5°	2190.6	2204.5	2240.7	2284.4	2338.2	2405.2	2475.8	2565.8	2643.8	2695.9	2742.4
55°	2204.5	2218.4	2259.3	2315.0	2388.4	2478.5	2579.8	2702.4	2819.5	2919.8	3017.3
57.5°	2165.5	2181.2	2224.9	2289.0	2375.4	2485.0	2612.3	2773.1	2934.6	3097.2	3241.2
60°	2093.9	2113.5	2153.4	2216.6	2312.2	2435.8	2588.2	2789.7	3016.4	3265.4	3541.2
62.5°	1976.0	1996.4	2033.6	2103.2	2201.7	2338.2	2514.7	2765.6	3086.1	3478.1	3967.7
65°	1786.4	1795.8	1841.2	1911.8	1999.2	2149.6	2343.8	2646.6	3063.7	3609.1	4283.5
66°	1700.9	1716.8	1744.7	1801.2	1884.9	2026.1	2221.2	2528.7	2979.3	3563.5	4275.1
67.5°	1567.2	1579.3	1597.8	1636.0	1687.0	1791.1	1976.0	2266.7	2721.0	3333.2	4097.7
70°	1267.2	1272.7	1297.8	1310.8	1328.4	1362.8	1429.7	1596.9	1950.9	2525.9	3307.2
72.5°	863.9	879.8	906.7	943.8	992.1	1038.5	1070.2	1091.5	1167.8	1506.8	2203.5
75°	633.6	650.3	684.7	733.9	818.4	915.0	1015.3	1061.9	1030.3	986.5	1227.2
77.5°	367.9	390.2	419.0	466.3	544.4	672.5	844.5	996.8	1099.9	1106.4	1050.7
80°	155.1	157.9	175.5	199.7	248.1	338.1	471.9	691.2	919.7	1073.9	1110.2
82.5°	35.3	43.6	55.8	65.9	80.8	111.5	165.4	275.0	497.0	779.4	1016.3
85°	13.1	13.1	17.6	26.0	29.7	33.5	43.6	69.6	118.9	219.3	457.1
87.5°	0.0	0.9	1.9	1.9	3.7	4.7	7.5	10.3	9.3	8.4	27.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155843

CATALOG NUMBER: AVS-F04-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2
2.5°	929.0	928.1	926.2	926.2	926.2	926.2	924.4	925.3	923.4	924.4	924.4
5°	928.1	928.1	927.2	925.3	926.2	926.2	927.2	925.3	925.3	926.2	925.3
7.5°	928.1	927.2	927.2	927.2	928.1	927.2	928.1	928.1	928.1	929.0	929.0
10°	928.1	928.1	929.9	930.9	930.9	931.8	934.5	934.5	935.4	936.4	938.2
12.5°	929.0	932.7	935.4	938.2	939.2	941.0	945.7	945.7	947.6	950.4	951.3
15°	929.9	935.4	941.0	942.9	944.8	948.5	953.2	955.0	957.8	960.5	962.4
17.5°	929.0	936.4	942.9	945.7	948.5	953.2	958.8	960.5	964.2	968.0	971.7
20°	928.1	938.2	948.5	952.2	956.0	962.4	969.8	974.5	978.2	983.8	987.5
22.5°	933.6	945.7	959.6	965.2	971.7	980.1	990.3	995.9	1000.5	1006.1	1008.9
25°	951.3	960.5	977.3	986.5	994.9	1008.9	1022.8	1029.3	1034.9	1039.5	1040.4
27.5°	981.0	983.8	1004.2	1016.3	1028.4	1050.7	1067.4	1072.0	1082.3	1086.0	1085.1
30°	1029.3	1024.7	1041.3	1060.0	1077.6	1108.3	1128.7	1140.8	1150.1	1150.1	1142.7
32.5°	1099.0	1091.5	1096.2	1117.5	1138.0	1182.6	1206.7	1222.5	1229.0	1227.2	1211.4
35°	1190.1	1185.4	1182.6	1199.3	1231.8	1283.8	1315.4	1323.8	1334.0	1332.1	1311.7
37.5°	1297.8	1294.1	1294.1	1313.6	1345.2	1422.3	1456.7	1462.2	1461.2	1446.4	1408.3
40°	1425.1	1423.2	1414.8	1426.0	1453.0	1553.3	1599.7	1607.2	1596.9	1572.7	1528.2
42.5°	1608.1	1596.9	1570.9	1577.4	1597.8	1695.4	1755.8	1776.2	1766.0	1741.9	1669.4
45°	1846.8	1834.7	1791.1	1785.5	1796.7	1882.1	1960.1	1964.8	1962.9	1932.3	1846.8
47.5°	2127.4	2108.8	2062.4	2047.5	2043.7	2122.7	2197.9	2205.4	2200.7	2155.2	2040.9
50°	2431.2	2404.2	2373.6	2363.3	2348.5	2405.2	2481.3	2482.3	2463.6	2400.5	2293.7
52.5°	2755.3	2746.1	2740.5	2730.3	2723.7	2773.1	2819.5	2791.6	2763.7	2697.7	2604.9
55°	3082.4	3120.4	3159.5	3163.2	3174.3	3227.3	3226.3	3150.2	3129.7	3093.5	3001.6
57.5°	3429.8	3571.0	3693.7	3731.7	3768.9	3867.4	3858.0	3782.8	3756.8	3712.2	3636.1
60°	3902.7	4283.5	4637.5	4722.0	4780.5	4898.5	4887.4	4771.3	4825.1	4821.5	4722.9
62.5°	4565.0	5198.5	5729.0	5859.1	5900.0	5913.0	5842.4	5717.0	5769.9	5829.3	5526.5
65°	5013.7	5758.8	6303.1	6403.4	6409.0	6253.9	6096.9	5949.2	5936.2	5885.1	5452.2
66°	5023.9	5786.6	6332.8	6430.4	6396.1	6184.2	5985.4	5836.8	5772.6	5660.3	5211.6
67.5°	4843.7	5613.0	6200.9	6304.0	6228.8	5928.7	5654.7	5463.3	5337.9	5155.9	4760.1
70°	4068.0	4830.7	5555.3	5747.6	5771.7	5323.9	4944.0	4719.2	4550.2	4300.2	3959.3
72.5°	3024.8	3714.1	4353.2	4537.1	4631.0	4273.3	3952.8	3781.9	3550.6	3287.7	3045.2
75°	1896.1	2382.8	2811.1	2940.2	2852.0	2575.1	2382.8	2311.3	2083.7	1926.7	1816.2
77.5°	1084.1	1236.5	1270.9	1221.7	1117.5	855.5	608.5	450.6	391.1	433.0	477.5
80°	1058.1	969.8	773.0	680.0	616.0	423.6	249.0	170.9	142.2	145.8	157.9
82.5°	1146.3	1229.9	1012.5	825.9	693.1	468.2	258.2	137.5	92.8	109.6	123.5
85°	745.1	1036.8	933.6	786.8	637.3	400.4	212.7	71.5	47.4	62.3	85.5
87.5°	75.2	82.7	70.6	95.6	71.5	33.5	16.7	10.3	9.3	11.2	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155843

CATALOG NUMBER: AVS-F04-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2
2.5°	925.3	925.3	926.2	927.2	928.1	929.0	929.0	929.0	929.0	930.9	929.9
5°	927.2	929.0	930.9	931.8	933.6	933.6	936.4	935.4	935.4	938.2	939.2
7.5°	930.9	933.6	937.3	936.4	940.1	939.2	941.0	941.0	938.2	939.2	937.3
10°	939.2	942.9	944.8	942.0	942.9	939.2	938.2	933.6	928.1	925.3	921.6
12.5°	953.2	956.9	956.9	952.2	946.6	938.2	931.8	921.6	913.2	908.5	903.9
15°	965.2	968.9	968.0	960.5	952.2	939.2	929.9	917.8	905.8	898.3	893.7
17.5°	974.5	976.4	973.6	963.3	954.1	942.0	932.7	919.7	905.8	896.5	888.1
20°	988.4	986.5	980.1	967.0	956.9	945.7	938.2	927.2	911.3	899.3	887.2
22.5°	1008.9	1001.5	989.3	975.4	965.2	955.0	947.6	935.4	919.7	904.9	890.9
25°	1035.9	1020.9	1004.2	989.3	980.1	968.9	960.5	947.6	930.9	914.1	897.4
27.5°	1074.8	1048.8	1027.5	1014.4	1004.2	990.3	980.1	963.3	945.7	926.2	907.6
30°	1118.4	1083.2	1062.8	1052.5	1041.3	1026.5	1010.8	989.3	968.9	947.6	925.3
32.5°	1175.1	1132.4	1113.0	1102.7	1087.9	1069.2	1050.7	1026.5	997.7	969.8	942.9
35°	1249.4	1205.8	1185.4	1169.6	1149.1	1125.0	1098.0	1065.5	1026.5	989.3	955.0
37.5°	1329.3	1282.0	1262.5	1245.8	1215.1	1183.5	1145.4	1098.0	1045.1	995.9	953.2
40°	1430.7	1386.9	1361.9	1333.1	1296.9	1242.1	1182.6	1113.9	1046.0	985.7	935.4
42.5°	1558.9	1515.1	1478.0	1432.5	1369.3	1284.8	1200.2	1111.1	1029.3	960.5	906.7
45°	1728.8	1675.9	1611.8	1531.9	1429.7	1311.7	1201.1	1093.4	997.7	921.6	863.9
47.5°	1936.9	1856.1	1751.1	1616.5	1469.6	1319.2	1186.3	1058.1	948.5	865.8	801.8
50°	2184.0	2056.8	1883.9	1686.1	1490.1	1308.0	1149.1	1005.2	878.9	790.6	714.4
52.5°	2466.4	2258.3	2003.8	1736.3	1489.1	1270.9	1086.0	925.3	787.8	689.3	616.9
55°	2798.1	2488.7	2127.4	1773.5	1463.1	1202.1	989.3	812.8	675.3	584.4	517.4
57.5°	3283.9	2862.2	2342.9	1831.0	1411.1	1096.2	858.3	678.1	557.4	471.0	414.3
60°	4172.0	3485.5	2731.2	1947.2	1331.2	941.0	705.1	534.2	433.0	363.2	325.2
62.5°	4840.9	3967.7	2941.1	1921.1	1170.5	749.6	523.0	389.2	318.7	271.3	247.2
65°	4745.3	3818.1	2717.3	1654.5	917.8	528.6	347.5	264.8	219.3	197.0	183.0
66°	4528.8	3623.0	2523.1	1489.1	793.4	439.4	286.1	222.1	188.6	172.7	163.5
67.5°	4118.1	3260.7	2175.6	1220.7	609.4	318.7	215.5	175.5	153.3	146.7	140.3
70°	3423.3	2600.2	1527.3	710.7	311.2	177.4	136.6	122.6	117.1	116.2	114.3
72.5°	2623.4	1840.3	899.3	336.3	161.7	118.0	105.9	101.2	99.4	99.4	100.3
75°	1608.1	1034.0	397.6	164.5	113.4	99.4	93.8	92.0	91.1	92.0	91.1
77.5°	537.0	328.8	170.1	124.5	103.1	92.0	88.3	86.4	86.4	86.4	86.4
80°	164.5	143.1	130.1	115.2	97.5	87.4	81.8	80.8	81.8	82.7	79.9
82.5°	123.5	117.1	109.6	102.2	88.3	78.0	76.2	76.2	76.2	73.4	69.6
85°	91.1	90.2	74.3	69.6	65.1	65.1	65.1	65.1	62.3	57.6	53.9
87.5°	16.7	15.8	16.7	17.6	26.0	27.9	27.9	29.7	32.5	30.7	30.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155843

CATALOG NUMBER: AVS-F04-LED-E-U-T3-8030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	926.2	926.2	926.2	926.2	926.2
2.5°	929.9	929.0	931.8	929.9	930.9
5°	938.2	937.3	939.2	937.3	940.1
7.5°	935.4	933.6	932.7	933.6	934.5
10°	916.0	914.1	913.2	912.2	913.2
12.5°	899.3	895.5	895.5	893.7	894.6
15°	887.2	884.4	883.4	881.6	882.5
17.5°	881.6	877.0	875.1	873.3	873.3
20°	877.9	872.3	869.5	867.7	866.7
22.5°	877.9	869.5	865.8	863.9	863.0
25°	881.6	871.4	865.8	863.0	862.1
27.5°	889.0	876.1	869.5	865.8	865.8
30°	902.1	885.3	876.1	871.4	870.5
32.5°	915.0	892.7	879.8	874.2	872.3
35°	921.6	892.7	877.0	867.7	865.8
37.5°	914.1	880.7	861.1	847.3	844.5
40°	890.9	855.5	834.2	821.2	819.4
42.5°	860.2	825.9	800.8	791.5	788.7
45°	818.4	777.5	752.4	739.5	740.4
47.5°	746.9	705.1	682.8	670.7	672.5
50°	662.4	621.5	602.0	589.0	591.7
52.5°	569.4	532.3	513.7	507.3	505.4
55°	471.9	443.1	430.2	422.7	419.9
57.5°	382.7	362.3	353.1	343.7	344.7
60°	302.0	291.7	288.9	278.7	277.7
62.5°	237.8	231.3	228.5	221.1	222.1
65°	180.2	178.3	180.2	175.5	177.4
66°	162.6	163.5	163.5	160.7	162.6
67.5°	140.3	142.2	144.9	142.2	144.0
70°	116.2	118.0	119.8	119.8	119.8
72.5°	101.2	103.1	104.0	104.0	104.0
75°	92.8	93.8	94.7	92.8	92.8
77.5°	87.4	87.4	85.5	84.6	83.6
80°	79.0	78.0	75.2	73.4	73.4
82.5°	65.9	64.1	62.3	59.5	59.5
85°	50.2	48.3	46.4	42.7	40.8
87.5°	26.0	26.9	26.0	21.3	18.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)