

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156883

Luminaire Tested: **AVS-F04-LED-E-U-T4-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156883
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-T4-8030
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (28) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8422.3 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156883

CATALOG NUMBER: AVS-F04-LED-E-U-T4-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 11.6 fc
Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156883

CATALOG NUMBER: AVS-F04-LED-E-U-T4-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P156883

CATALOG NUMBER: AVS-F04-LED-E-U-T4-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1797.1	0.0	1797.1
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	6625.1	0.0	6625.1
	% Fixture	78.7	0.0	78.7
Total	Lumens	8422.3	0.0	8422.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.8	1.3
10°-20°	327.3	3.9
20°-30°	563.8	6.7
30°-40°	852.9	10.1
40°-50°	1105.5	13.1
50°-60°	1524.1	18.1
60°-70°	2368.0	28.1
70°-80°	1377.0	16.3
80°-90°	195.8	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8422.3	100.0
0°-180°	8422.3	100.0

Coefficient of Utilization



REPORT NUMBER: P156883


CATALOG NUMBER: AVS-F04-LED-E-U-T4-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	517.8	6.1			
FM	(30°-60°)	2703.5	32.1			
FH	(60°-80°)	3253.5	38.6			G2/5000
FVH	(80°-90°)	150.3	1.8			G2/225
BL	(0°-30°)	481.0	5.7	B1/500		
BM	(30°-60°)	779.0	9.2	B1/1000		
BH	(60°-80°)	491.5	5.8	B1/500		G1/500
BVH	(80°-90°)	45.5	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P156883

CATALOG NUMBER: AVS-F04-LED-E-U-T4-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2
2.5°	1089.7	1093.4	1090.7	1091.5	1091.5	1092.4	1092.4	1093.4	1092.4	1095.2	1097.1
5°	1070.2	1072.0	1071.1	1073.0	1074.8	1078.5	1077.6	1082.3	1083.2	1086.0	1090.7
7.5°	1062.8	1060.9	1061.9	1064.7	1066.4	1068.3	1070.2	1073.9	1076.7	1083.2	1086.9
10°	1070.2	1069.2	1070.2	1072.0	1072.0	1073.0	1071.1	1074.8	1076.7	1082.3	1086.0
12.5°	1100.8	1100.8	1099.0	1099.0	1097.1	1095.2	1090.7	1087.9	1086.9	1087.9	1089.7
15°	1150.1	1148.2	1144.5	1141.8	1138.0	1131.5	1125.0	1119.4	1115.8	1110.2	1108.3
17.5°	1198.3	1195.6	1191.9	1188.2	1183.5	1177.0	1166.8	1160.3	1150.1	1143.6	1139.9
20°	1254.1	1248.6	1243.9	1239.3	1229.9	1228.1	1217.9	1206.7	1194.7	1179.8	1177.9
22.5°	1326.6	1317.3	1311.7	1308.9	1299.7	1296.9	1280.1	1264.4	1249.4	1229.9	1225.3
25°	1400.0	1390.7	1387.9	1384.1	1377.7	1374.0	1358.1	1340.5	1321.0	1294.1	1288.5
27.5°	1471.5	1472.4	1465.0	1467.8	1465.9	1459.4	1443.6	1426.0	1411.1	1379.6	1373.1
30°	1560.7	1555.1	1551.4	1557.0	1550.5	1551.4	1537.5	1528.2	1504.0	1485.4	1472.4
32.5°	1653.6	1652.6	1658.2	1662.0	1661.0	1659.2	1648.0	1638.8	1617.3	1590.5	1584.9
35°	1780.8	1786.4	1791.1	1807.8	1807.8	1819.9	1808.7	1797.6	1772.5	1740.0	1728.8
37.5°	1867.3	1869.1	1887.7	1909.9	1937.8	1963.8	1971.3	1974.1	1963.8	1939.7	1923.0
40°	1946.2	1949.9	1979.7	2014.0	2054.9	2106.0	2136.7	2150.6	2153.4	2142.3	2106.0
42.5°	2025.2	2030.8	2061.5	2111.6	2168.3	2233.3	2287.2	2321.6	2341.0	2341.0	2319.7
45°	2117.1	2124.6	2158.0	2212.8	2278.8	2360.5	2434.8	2500.8	2532.4	2534.3	2513.8
47.5°	2225.8	2232.3	2271.4	2327.0	2394.9	2477.6	2571.4	2646.6	2705.2	2708.9	2692.2
50°	2366.1	2375.4	2407.9	2458.1	2527.8	2611.4	2705.2	2810.2	2871.5	2886.3	2868.7
52.5°	2551.9	2553.8	2580.7	2627.2	2694.9	2774.8	2874.3	2988.5	3069.3	3081.5	3052.6
55°	2808.3	2805.5	2823.2	2873.4	2924.5	2986.6	3089.7	3218.0	3308.1	3326.6	3297.0
57.5°	3156.7	3153.9	3168.7	3180.8	3276.5	3336.9	3438.1	3560.8	3648.1	3702.0	3650.9
60°	3696.4	3693.7	3717.8	3788.4	3859.9	3948.2	4046.6	4193.4	4316.1	4331.8	4281.7
62.5°	4087.6	4101.5	4154.4	4237.1	4382.0	4554.8	4735.0	4928.3	5180.0	5259.9	5235.8
65°	3951.0	3978.9	4052.2	4177.6	4370.9	4609.6	4892.0	5242.3	5579.5	5768.1	5762.5
66°	3828.3	3859.0	3949.1	4069.8	4274.2	4535.2	4843.7	5225.5	5602.7	5810.8	5823.7
67.5°	3605.4	3639.8	3728.0	3871.1	4069.8	4347.7	4679.3	5094.5	5520.9	5763.4	5797.7
70°	3171.5	3210.6	3274.6	3392.6	3588.6	3836.7	4186.0	4557.6	5004.5	5282.2	5323.9
72.5°	2651.3	2685.7	2757.2	2853.8	3014.5	3170.6	3444.7	3718.8	4038.2	4355.0	4324.5
75°	1903.5	1918.3	1961.0	2066.0	2152.4	2292.7	2512.8	2737.7	2956.1	3100.9	3121.3
77.5°	989.3	1028.4	1088.8	1204.9	1298.8	1425.1	1568.1	1737.2	1897.0	2029.8	1993.6
80°	647.5	664.2	718.1	777.5	846.3	927.2	1022.8	1086.0	1106.4	1098.0	1106.4
82.5°	373.5	404.1	475.6	521.1	572.2	600.1	676.3	748.8	789.6	738.5	720.0
85°	47.4	61.3	193.3	243.4	278.7	320.5	343.7	387.4	361.3	323.3	393.9
87.5°	10.3	9.3	13.1	27.9	28.8	24.1	45.5	48.3	29.7	14.8	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156883

CATALOG NUMBER: AVS-F04-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2
2.5°	1099.0	1099.9	1101.8	1104.6	1106.4	1108.3	1110.2	1113.0	1114.8	1116.7	1120.3
5°	1094.3	1098.0	1101.8	1105.5	1110.2	1117.5	1122.2	1125.9	1129.6	1137.1	1139.9
7.5°	1091.5	1098.0	1103.6	1110.2	1117.5	1124.0	1132.4	1137.1	1142.7	1147.3	1152.8
10°	1089.7	1099.0	1104.6	1113.9	1122.2	1128.7	1138.0	1143.6	1150.1	1155.6	1158.4
12.5°	1093.4	1098.0	1103.6	1113.0	1123.1	1132.4	1142.7	1147.3	1152.8	1157.5	1158.4
15°	1109.2	1109.2	1110.2	1117.5	1127.8	1135.2	1143.6	1148.2	1151.0	1153.8	1153.8
17.5°	1138.0	1131.5	1126.8	1127.8	1134.3	1139.0	1143.6	1143.6	1141.8	1140.8	1139.0
20°	1171.4	1163.1	1153.8	1147.3	1145.4	1141.8	1139.0	1129.6	1122.2	1115.8	1111.1
22.5°	1219.8	1206.7	1193.8	1181.7	1170.5	1156.6	1140.8	1122.2	1104.6	1092.4	1085.1
25°	1279.2	1269.0	1253.2	1234.6	1220.7	1194.7	1174.2	1147.3	1125.0	1109.2	1096.2
27.5°	1363.7	1351.7	1336.8	1320.1	1299.7	1270.9	1245.8	1214.2	1187.3	1164.0	1147.3
30°	1468.7	1453.0	1441.8	1421.3	1407.4	1374.9	1349.8	1310.8	1258.8	1221.7	1198.3
32.5°	1576.5	1558.9	1549.5	1533.8	1517.9	1498.4	1460.3	1400.0	1333.1	1272.7	1232.7
35°	1720.5	1701.9	1685.2	1671.2	1648.0	1611.8	1578.3	1505.9	1413.9	1329.3	1262.5
37.5°	1901.7	1871.0	1829.1	1793.9	1753.0	1700.9	1649.8	1575.5	1470.6	1360.9	1271.8
40°	2094.8	2040.9	1981.6	1915.5	1845.0	1769.7	1711.2	1636.0	1517.9	1387.9	1265.3
42.5°	2296.5	2211.0	2128.3	2035.4	1936.9	1847.8	1771.6	1688.9	1553.3	1395.3	1239.3
45°	2496.2	2400.5	2275.0	2153.4	2028.9	1918.3	1832.8	1740.0	1585.8	1398.1	1204.9
47.5°	2661.6	2563.1	2420.0	2267.7	2119.9	1994.5	1894.2	1793.9	1629.4	1417.6	1196.5
50°	2836.2	2716.4	2557.5	2377.3	2210.1	2069.7	1962.9	1858.9	1690.8	1467.8	1223.4
52.5°	3026.6	2889.1	2703.3	2501.8	2318.8	2161.8	2045.6	1938.8	1768.8	1538.3	1274.6
55°	3258.9	3090.7	2889.1	2661.6	2465.5	2291.8	2163.6	2037.3	1861.7	1622.0	1338.7
57.5°	3613.8	3407.5	3180.8	2921.7	2704.2	2499.0	2345.7	2199.8	2005.7	1746.5	1426.0
60°	4255.6	4035.5	3741.0	3427.0	3171.5	2931.8	2707.0	2525.9	2287.2	1991.7	1619.2
62.5°	5175.3	4882.7	4489.7	4050.4	3716.0	3370.4	3116.7	2847.4	2551.0	2232.3	1846.8
65°	5686.3	5331.4	4805.6	4295.6	3865.5	3490.2	3167.9	2855.6	2526.8	2222.1	1899.8
66°	5749.4	5379.7	4833.5	4296.6	3845.1	3459.5	3120.4	2797.2	2460.8	2170.1	1877.5
67.5°	5723.4	5345.4	4782.4	4215.8	3756.8	3342.5	2992.2	2656.9	2321.6	2050.3	1803.1
70°	5297.1	4938.4	4385.7	3836.7	3401.0	2992.2	2657.8	2328.0	2020.5	1788.3	1606.2
72.5°	4398.8	4092.1	3611.9	3180.8	2839.0	2501.8	2218.4	1903.5	1643.3	1471.5	1363.7
75°	3175.2	2989.4	2551.9	2304.8	2004.8	1780.8	1505.9	1319.2	1132.4	1048.8	1030.3
77.5°	2005.7	1755.8	1478.0	1217.0	1000.5	829.5	645.6	548.1	457.1	447.8	540.6
80°	1015.3	914.1	704.1	561.1	471.9	381.8	302.0	228.5	159.8	192.3	230.4
82.5°	665.2	554.6	434.7	357.6	311.2	258.2	200.6	139.4	102.2	115.2	157.9
85°	359.5	306.5	247.2	195.1	157.9	141.2	94.7	66.8	65.9	70.6	90.2
87.5°	26.0	26.0	20.4	18.5	22.3	18.5	16.7	16.7	15.8	16.7	22.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156883

CATALOG NUMBER: AVS-F04-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2	1110.2
2.5°	1122.2	1125.0	1125.9	1130.6	1133.4	1135.2	1137.1	1137.1	1138.0	1140.8	1141.8
5°	1143.6	1148.2	1153.8	1157.5	1159.4	1165.0	1166.8	1166.8	1168.7	1172.3	1175.1
7.5°	1156.6	1163.1	1168.7	1170.5	1174.2	1176.1	1178.9	1180.7	1180.7	1184.5	1186.3
10°	1161.2	1165.0	1170.5	1170.5	1174.2	1174.2	1177.0	1177.9	1177.9	1181.7	1184.5
12.5°	1161.2	1163.1	1167.8	1167.8	1170.5	1171.4	1175.1	1177.9	1178.9	1183.5	1187.3
15°	1155.6	1157.5	1161.2	1162.2	1168.7	1172.3	1180.7	1186.3	1186.3	1191.0	1192.8
17.5°	1139.9	1144.5	1151.9	1159.4	1171.4	1179.8	1190.1	1194.7	1191.0	1188.2	1185.4
20°	1113.9	1122.2	1139.9	1158.4	1179.8	1191.0	1196.5	1191.9	1178.9	1165.9	1157.5
22.5°	1087.9	1104.6	1134.3	1162.2	1186.3	1193.8	1191.0	1174.2	1152.8	1137.1	1125.9
25°	1099.9	1119.4	1148.2	1173.3	1189.1	1187.3	1176.1	1152.8	1129.6	1109.2	1090.7
27.5°	1150.1	1171.4	1187.3	1195.6	1193.8	1180.7	1163.1	1137.1	1109.2	1082.3	1056.3
30°	1197.4	1208.6	1212.3	1205.8	1191.0	1169.6	1147.3	1117.5	1080.4	1046.9	1017.2
32.5°	1218.9	1207.7	1190.1	1172.3	1148.2	1129.6	1099.0	1066.4	1020.0	980.1	950.4
35°	1218.9	1174.2	1129.6	1092.4	1056.3	1033.1	997.7	954.1	911.3	877.9	854.6
37.5°	1191.9	1106.4	1033.1	972.6	927.2	902.1	849.1	810.1	773.9	762.7	747.9
40°	1142.7	1016.3	910.4	831.4	773.9	736.7	683.7	656.8	642.9	637.3	634.5
42.5°	1076.7	916.0	774.8	677.2	615.0	573.2	537.9	521.1	520.2	519.3	519.3
45°	1006.1	808.2	642.9	526.7	471.9	434.7	418.0	411.5	417.1	416.2	417.1
47.5°	962.4	726.4	522.1	398.5	356.7	332.5	324.2	327.0	331.6	329.7	329.7
50°	956.9	684.7	441.2	310.3	278.7	266.6	264.8	264.8	267.6	265.7	264.8
52.5°	977.3	678.1	399.5	266.6	241.6	231.3	229.4	228.5	227.6	222.1	217.4
55°	1012.5	693.1	387.4	255.4	229.4	218.3	215.5	213.7	209.9	202.5	194.2
57.5°	1083.2	739.5	398.5	261.0	233.2	223.8	221.1	221.1	213.7	201.6	189.5
60°	1253.2	857.4	444.0	282.4	250.8	241.6	243.4	242.5	231.3	213.7	195.1
62.5°	1472.4	1011.7	503.5	312.1	273.2	271.3	280.5	278.7	260.1	233.2	206.2
65°	1573.7	1084.1	520.2	318.7	277.7	286.1	304.7	302.8	279.6	242.5	208.1
66°	1575.5	1084.1	512.7	313.1	271.3	281.5	300.1	299.2	276.0	238.8	204.4
67.5°	1537.5	1054.4	491.4	302.0	258.2	265.7	282.4	281.5	260.1	229.4	197.0
70°	1394.4	943.8	436.6	282.4	240.6	236.9	242.5	238.8	224.8	203.4	181.1
72.5°	1194.7	792.4	380.9	267.6	228.5	213.7	209.9	207.2	196.1	183.9	170.1
75°	941.0	627.0	334.4	256.4	217.4	197.8	191.4	187.7	180.2	171.8	160.7
77.5°	580.6	448.7	291.7	241.6	209.0	189.5	184.9	179.3	168.2	157.9	149.5
80°	259.2	277.7	239.7	210.9	186.7	169.1	161.7	153.3	142.2	135.6	131.0
82.5°	172.7	179.3	173.7	157.9	141.2	127.3	116.2	116.2	114.3	108.7	106.8
85°	110.6	111.5	107.8	97.5	91.1	82.7	78.0	79.0	82.7	81.8	80.8
87.5°	25.1	25.1	29.7	27.9	32.5	34.4	37.2	39.9	45.5	45.5	48.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156883

CATALOG NUMBER: AVS-F04-LED-E-U-T4-8030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1110.2	1110.2	1110.2	1110.2	1110.2
2.5°	1142.7	1144.5	1146.3	1143.6	1144.5
5°	1175.1	1174.2	1178.9	1176.1	1177.9
7.5°	1185.4	1186.3	1190.1	1190.1	1191.0
10°	1186.3	1188.2	1192.8	1195.6	1197.4
12.5°	1191.0	1194.7	1202.1	1203.9	1203.9
15°	1194.7	1196.5	1201.1	1203.0	1204.9
17.5°	1181.7	1177.9	1179.8	1180.7	1179.8
20°	1149.1	1145.4	1144.5	1140.8	1142.7
22.5°	1113.9	1103.6	1097.1	1089.7	1089.7
25°	1071.1	1055.3	1042.3	1029.3	1032.1
27.5°	1031.2	1010.8	997.7	989.3	987.5
30°	992.1	970.8	958.8	948.5	948.5
32.5°	927.2	912.2	896.5	889.9	889.0
35°	837.0	827.8	814.7	811.9	807.3
37.5°	735.8	733.0	721.9	720.9	716.3
40°	629.8	631.7	628.0	626.1	623.3
42.5°	523.9	533.3	531.4	530.5	528.6
45°	422.7	429.2	430.2	433.0	437.5
47.5°	332.5	334.4	336.3	335.3	336.3
50°	260.1	255.4	254.5	251.7	254.5
52.5°	209.9	202.5	198.8	195.1	193.3
55°	184.9	177.4	173.7	171.8	170.1
57.5°	178.3	170.9	165.4	161.7	160.7
60°	180.2	169.1	161.7	157.0	156.1
62.5°	184.9	170.1	159.8	155.1	154.2
65°	183.9	168.2	158.9	153.3	152.3
66°	181.1	166.3	157.0	152.3	151.4
67.5°	176.5	163.5	155.1	151.4	149.5
70°	168.2	159.8	153.3	148.6	146.7
72.5°	160.7	154.2	148.6	144.0	143.1
75°	152.3	146.7	141.2	137.5	136.6
77.5°	142.2	136.6	132.8	130.1	129.1
80°	125.4	121.7	118.0	114.3	114.3
82.5°	104.0	101.2	97.5	94.7	93.8
85°	79.9	79.9	77.1	74.3	73.4
87.5°	47.4	46.4	46.4	43.6	43.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)